

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P135470

Luminaire Tested: **LD6A20D010TE ERM6A20935 6LM1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P135470
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23371)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A20D010TE ERM6A20935 6LM1H
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3500K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2030.1 lumens
Efficiency: N/A
Efficacy: 61.9 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.9
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 32.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P135470

CATALOG NUMBER: LD6A20D010TE ERM6A20935 6LM1H

Luminous Intensity Polar Plot





TEST NUMBER: P135470

CATALOG NUMBER: LD6A20D010TE ERM6A20935 6LM1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	102	101		101	99	98		97
2	108	103	98	95	105	101	97	94	98	94	92		95	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	83	79	95	88	82	78	85	81	77		83	80	76		82
5	91	83	77	73	90	82	76	72	80	75	72		78	74	71		77
6	87	78	71	67	85	77	71	67	75	70	66		74	69	66		73
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65
9	74	64	58	54	73	64	58	54	63	58	54		62	57	54		61
10	71	61	55	51	70	60	55	51	60	54	51		59	54	51		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144391
5°	141700
10°	134680
15°	126061
20°	116139
25°	105185
30°	86332
35°	56125
40°	30106
45°	16202
50°	8911
55°	4356
60°	2649
65°	1729
70°	1278
75°	555
80°	827
85°	0



TEST NUMBER: P135470

CATALOG NUMBER: LD6A20D010TE ERM6A20935 6LM1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.4	10.0
10°-20°	522.1	25.7
20°-30°	660.5	32.5
30°-40°	444.0	21.9
40°-50°	145.9	7.2
50°-60°	39.3	1.9
60°-70°	12.2	0.6
70°-80°	3.5	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1385.0	68.2
0°-40°	1828.9	90.1
0°-60°	2014.1	99.2
0°-90°	2030.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2030.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2213	
5°	2164	202
15°	1866	522
25°	1461	660
35°	705	444
45°	176	146
55°	38	39
65°	11	12
75°	2	4
85°	0	0
90°	0	



TEST NUMBER: P135470

CATALOG NUMBER: LD6A20D010TE ERM6A20935 6LM1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2213.2
2.5°	2192.9
5°	2163.7
7.5°	2109.6
10°	2033.0
12.5°	1952.0
15°	1866.4
17.5°	1769.6
20°	1672.8
22.5°	1573.8
25°	1461.2
27.5°	1323.8
30°	1146.0
32.5°	932.0
35°	704.7
37.5°	504.3
40°	353.5
42.5°	247.6
45°	175.6
47.5°	123.8
50°	87.8
52.5°	58.5
55°	38.3
57.5°	27.0
60°	20.3
62.5°	15.8
65°	11.2
67.5°	9.0
70°	6.7
72.5°	4.5
75°	2.2
77.5°	2.2
80°	2.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)