

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P135227

Luminaire Tested: **LD6A20D010TE ERN6A20840 6LN1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P135227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23370)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A20D010TE ERN6A20840 6LN1H
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 4000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2131.0 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.84
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 32.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P135227

CATALOG NUMBER: LD6A20D010TE ERN6A20840 6LN1H

Luminous Intensity Polar Plot





TEST NUMBER: P135227

CATALOG NUMBER: LD6A20D010TE ERN6A20840 6LN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	56	64	59	55		63	59	55		62
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	183372
5°	177379
10°	158138
15°	137833
20°	119367
25°	102420
30°	85970
35°	60330
40°	31409
45°	14947
50°	7836
55°	4254
60°	2923
65°	1930
70°	1431
75°	1260
80°	939
85°	0



TEST NUMBER: P135227

CATALOG NUMBER: LD6A20D010TE ERN6A20840 6LN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.0	11.6
10°-20°	570.2	26.8
20°-30°	652.5	30.6
30°-40°	464.9	21.8
40°-50°	140.5	6.6
50°-60°	36.4	1.7
60°-70°	13.5	0.6
70°-80°	4.6	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1470.7	69.0
0°-40°	1935.6	90.8
0°-60°	2112.6	99.1
0°-90°	2131.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2131.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2811	
5°	2708	248
15°	2041	570
25°	1423	653
35°	758	465
45°	162	141
55°	37	36
65°	12	14
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P135227

CATALOG NUMBER: LD6A20D010TE ERN6A20840 6LN1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2810.7
2.5°	2778.3
5°	2708.5
7.5°	2569.0
10°	2387.1
12.5°	2205.2
15°	2040.7
17.5°	1881.3
20°	1719.3
22.5°	1567.3
25°	1422.8
27.5°	1285.7
30°	1141.2
32.5°	966.8
35°	757.5
37.5°	543.2
40°	368.8
42.5°	244.2
45°	162.0
47.5°	112.1
50°	77.2
52.5°	49.8
55°	37.4
57.5°	27.4
60°	22.4
62.5°	17.4
65°	12.5
67.5°	10.0
70°	7.5
72.5°	5.0
75°	5.0
77.5°	2.5
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)