

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P135253

Luminaire Tested: **LD6A30D010TE ERN6A30930 6LN1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P135253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23370)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A30D010TE ERN6A30930 6LN1H
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2223.1 lumens
Efficiency: N/A
Efficacy: 49.0 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.84
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 45.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P135253

CATALOG NUMBER: LD6A30D010TE ERN6A30930 6LN1H

Luminous Intensity Polar Plot





TEST NUMBER: P135253

CATALOG NUMBER: LD6A30D010TE ERN6A30930 6LN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	56	64	59	55		63	59	55		62
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	191299
5°	185048
10°	164975
15°	143790
20°	124532
25°	106847
30°	89692
35°	62935
40°	32763
45°	15593
50°	8181
55°	4436
60°	3053
65°	2007
70°	1488
75°	1311
80°	977
85°	0



TEST NUMBER: P135253

CATALOG NUMBER: LD6A30D010TE ERN6A30930 6LN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.7	11.6
10°-20°	594.8	26.8
20°-30°	680.8	30.6
30°-40°	485.0	21.8
40°-50°	146.6	6.6
50°-60°	38.0	1.7
60°-70°	14.1	0.6
70°-80°	4.8	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1534.3	69.0
0°-40°	2019.3	90.8
0°-60°	2203.9	99.1
0°-90°	2223.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2223.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2932	
5°	2826	259
15°	2129	595
25°	1484	681
35°	790	485
45°	169	147
55°	39	38
65°	13	14
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P135253

CATALOG NUMBER: LD6A30D010TE ERN6A30930 6LN1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2932.2
2.5°	2898.4
5°	2825.6
7.5°	2680.0
10°	2490.3
12.5°	2300.6
15°	2128.9
17.5°	1962.6
20°	1793.7
22.5°	1635.1
25°	1484.3
27.5°	1341.3
30°	1190.6
32.5°	1008.6
35°	790.2
37.5°	566.7
40°	384.7
42.5°	254.7
45°	169.0
47.5°	117.0
50°	80.6
52.5°	51.9
55°	39.0
57.5°	28.6
60°	23.4
62.5°	18.2
65°	13.0
67.5°	10.4
70°	7.8
72.5°	5.2
75°	5.2
77.5°	2.6
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)