

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204315

Luminaire Tested: **LD6B50D010TE EU6B30509727 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30509727 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3997.9 lumens
Efficiency: N/A
Efficacy: 68.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204315

CATALOG NUMBER: LD6B50D010TE EU6B30509727 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204315

CATALOG NUMBER: LD6B50D010TE EU6B30509727 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85		100	94	89	84		91	86	83		87	84	81		85	82	79
3	95	86	79	73		93	84	78	73		82	76	72		79	74	70		76	73	69
4	88	77	70	64		86	76	69	63		74	68	63		72	66	62		69	65	61
5	81	70	62	56		79	69	62	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50		74	63	55	50		61	54	49		60	54	49		58	53	49
7	71	58	51	45		69	58	50	45		56	49	45		55	49	44		54	48	44
8	66	54	46	41		65	53	46	41		52	45	40		51	45	40		50	44	40
9	62	50	42	37		61	49	42	37		48	41	37		47	41	37		46	41	37
10	58	46	39	34		57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204315

CATALOG NUMBER: LD6B50D010TE EU6B30509727 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.9	5.5
10°-20°	569.2	14.2
20°-30°	744.5	18.6
30°-40°	788.3	19.7
40°-50°	735.3	18.4
50°-60°	556.9	13.9
60°-70°	301.6	7.5
70°-80°	80.9	2.0
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1533.6	38.4
0°-40°	2322.0	58.1
0°-60°	3614.1	90.4
0°-90°	3997.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3997.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2384	
5°	2349	220
15°	2034	569
25°	1619	745
35°	1260	788
45°	958	735
55°	626	557
65°	302	302
75°	70	81
85°	0	1
90°	0	



TEST NUMBER: P204315

CATALOG NUMBER: LD6B50D010TE EU6B30509727 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2384.3
2.5°	2375.6
5°	2349.3
7.5°	2292.4
10°	2218.1
12.5°	2130.6
15°	2034.3
17.5°	1925.0
20°	1828.7
22.5°	1719.3
25°	1618.7
27.5°	1518.1
30°	1421.8
32.5°	1338.7
35°	1260.0
37.5°	1181.2
40°	1106.8
42.5°	1032.5
45°	958.1
47.5°	875.0
50°	791.9
52.5°	708.7
55°	625.6
57.5°	538.1
60°	455.0
62.5°	376.2
65°	301.9
67.5°	231.9
70°	170.6
72.5°	118.1
75°	70.0
77.5°	30.6
80°	8.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)