

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204822

Luminaire Tested: **LD6B50D010TE EU6B30508030 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508030 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5870.8 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204822

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBSCMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204822

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	108	104	100	97	100	97	94		96	93	91		92
2	101	94	87	82	99	92	86	81	88	84	79		85	81	78		82
3	93	83	75	70	90	81	74	69	79	73	68		76	71	67		73
4	85	74	66	60	83	73	65	59	70	64	58		68	62	58		66
5	79	66	58	52	77	65	57	51	63	56	51		61	55	50		60
6	73	60	52	45	71	59	51	45	57	50	45		56	49	44		54
7	68	55	46	40	66	54	46	40	52	45	40		51	44	40		50
8	63	50	42	36	61	49	41	36	48	41	36		47	40	36		46
9	59	46	38	33	57	45	38	32	44	37	32		43	37	32		42
10	55	42	35	30	54	42	34	30	41	34	29		40	34	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204822

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.2	3.9
10°-20°	646.8	11.0
20°-30°	972.9	16.6
30°-40°	1153.1	19.6
40°-50°	1147.5	19.5
50°-60°	925.0	15.8
60°-70°	559.6	9.5
70°-80°	207.8	3.5
80°-90°	31.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1846.9	31.5
0°-40°	2999.9	51.1
0°-60°	5072.4	86.4
0°-90°	5870.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5870.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2398	
5°	2387	227
15°	2291	647
25°	2113	973
35°	1846	1153
45°	1494	1147
55°	1032	925
65°	562	560
75°	188	208
85°	25	31
90°	0	



TEST NUMBER: P204822

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2397.8
2.5°	2397.8
5°	2387.1
7.5°	2380.0
10°	2358.7
12.5°	2323.1
15°	2291.1
17.5°	2255.5
20°	2212.8
22.5°	2170.1
25°	2113.2
27.5°	2052.7
30°	1985.1
32.5°	1921.1
35°	1846.4
37.5°	1768.1
40°	1675.6
42.5°	1586.7
45°	1494.2
47.5°	1391.0
50°	1277.2
52.5°	1159.8
55°	1031.7
57.5°	917.8
60°	789.8
62.5°	675.9
65°	562.1
67.5°	455.4
70°	355.8
72.5°	266.8
75°	188.5
77.5°	121.0
80°	71.2
82.5°	42.7
85°	24.9
87.5°	10.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)