

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203275

Luminaire Tested: **LD6B50D010TE EU6B30508030 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203275
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508030 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3907.0 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203275

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBMH1

Luminous Intensity Polar Plot






TEST NUMBER: P203275

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	93		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	84		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	78	74		80	76	73
5	90	81	75	70		88	80	74	70		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	75	69	64		73	68	64		72	67	63		70	66	63
7	80	70	64	59		79	70	64	59		68	63	59		67	62	59		66	62	58
8	76	66	60	55		75	65	59	55		64	59	55		63	58	55		62	58	54
9	72	62	56	51		71	61	55	51		60	55	51		60	55	51		59	54	51
10	69	58	52	48		68	58	52	48		57	52	48		56	51	48		55	51	48

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203275

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	353.5	9.0
10°-20°	914.6	23.4
20°-30°	1185.0	30.3
30°-40°	879.8	22.5
40°-50°	371.4	9.5
50°-60°	131.9	3.4
60°-70°	50.9	1.3
70°-80°	17.6	0.5
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2453.1	62.8
0°-40°	3332.9	85.3
0°-60°	3836.2	98.2
0°-90°	3907.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3907.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3866	
5°	3783	354
15°	3264	915
25°	2628	1185
35°	1395	880
45°	458	371
55°	140	132
65°	50	51
75°	17	18
85°	0	2
90°	0	



TEST NUMBER: P203275

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3866.4
2.5°	3855.3
5°	3782.7
7.5°	3676.7
10°	3548.4
12.5°	3408.9
15°	3263.9
17.5°	3102.1
20°	2957.0
22.5°	2806.4
25°	2627.8
27.5°	2382.3
30°	2092.2
32.5°	1751.9
35°	1394.8
37.5°	1093.5
40°	831.3
42.5°	619.3
45°	457.5
47.5°	334.8
50°	245.5
52.5°	184.1
55°	139.5
57.5°	106.0
60°	83.7
62.5°	61.4
65°	50.2
67.5°	39.1
70°	27.9
72.5°	22.3
75°	16.7
77.5°	11.2
80°	5.6
82.5°	5.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)