

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202554

Luminaire Tested: **LD6B50D010TE EU6B30508030 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508030 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5617.2 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202554

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBSWMH1

Luminous Intensity Polar Plot






TEST NUMBER: P202554

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42			
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38			
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35			
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202554

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.5	5.4
10°-20°	785.6	14.0
20°-30°	1041.7	18.5
30°-40°	1111.1	19.8
40°-50°	1038.6	18.5
50°-60°	792.0	14.1
60°-70°	430.8	7.7
70°-80°	115.5	2.1
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2127.8	37.9
0°-40°	3238.9	57.7
0°-60°	5069.5	90.2
0°-90°	5617.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5617.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3248	
5°	3204	301
15°	2801	786
25°	2268	1042
35°	1776	1111
45°	1352	1039
55°	891	792
65°	430	431
75°	100	116
85°	0	1
90°	0	



TEST NUMBER: P202554

CATALOG NUMBER: LD6B50D010TE EU6B30508030 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3248.2
2.5°	3237.9
5°	3203.5
7.5°	3131.2
10°	3048.6
12.5°	2931.7
15°	2800.9
17.5°	2670.1
20°	2529.1
22.5°	2394.9
25°	2267.6
27.5°	2133.4
30°	2006.0
32.5°	1882.2
35°	1775.5
37.5°	1668.8
40°	1558.7
42.5°	1458.9
45°	1352.3
47.5°	1235.3
50°	1125.2
52.5°	1008.2
55°	891.2
57.5°	763.9
60°	646.9
62.5°	536.8
65°	430.1
67.5°	333.8
70°	244.3
72.5°	168.6
75°	99.8
77.5°	44.7
80°	10.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)