

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204517

Luminaire Tested: **LD6B50D010TE EU6B30509030 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204517
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30509030 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4178.6 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204517

CATALOG NUMBER: LD6B50D010TE EU6B30509030 6LBSB1

Luminous Intensity Polar Plot






TEST NUMBER: P204517

CATALOG NUMBER: LD6B50D010TE EU6B30509030 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	105	101	98		100	98	95		97	94	93		93	91	90
2	102	95	89	84	100	93	88	83		90	85	81		86	83	79		84	80	78
3	94	84	77	72	91	83	76	71		80	74	70		77	73	68		75	71	67
4	86	76	68	62	84	74	67	61		72	65	60		70	64	60		68	63	59
5	80	68	60	54	78	67	59	53		65	58	53		63	57	52		61	56	52
6	74	62	53	47	72	61	53	47		59	52	47		57	51	46		56	50	46
7	69	56	48	42	67	55	48	42		54	47	42		52	46	41		51	45	41
8	64	51	43	38	63	51	43	38		49	42	37		48	42	37		47	41	37
9	60	47	39	34	59	47	39	34		46	39	34		45	38	34		44	38	34
10	56	44	36	31	55	43	36	31		42	36	31		41	35	31		40	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204517

CATALOG NUMBER: LD6B50D010TE EU6B30509030 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.0	4.2
10°-20°	493.6	11.8
20°-30°	734.3	17.6
30°-40°	854.5	20.4
40°-50°	832.9	19.9
50°-60°	640.6	15.3
60°-70°	354.1	8.5
70°-80°	93.8	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1402.0	33.6
0°-40°	2256.5	54.0
0°-60°	3730.0	89.3
0°-90°	4178.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4178.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1843	
5°	1833	174
15°	1748	494
25°	1594	734
35°	1372	855
45°	1081	833
55°	715	641
65°	355	354
75°	80	94
85°	0	1
90°	0	



TEST NUMBER: P204517

CATALOG NUMBER: LD6B50D010TE EU6B30509030 6LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1843.3
2.5°	1843.3
5°	1832.7
7.5°	1816.9
10°	1806.3
12.5°	1774.5
15°	1748.0
17.5°	1721.5
20°	1684.4
22.5°	1647.4
25°	1594.4
27.5°	1541.4
30°	1488.4
32.5°	1430.2
35°	1371.9
37.5°	1297.8
40°	1234.2
42.5°	1165.3
45°	1080.6
47.5°	1001.1
50°	911.1
52.5°	815.7
55°	715.1
57.5°	619.7
60°	529.7
62.5°	439.6
65°	354.9
67.5°	275.4
70°	201.3
72.5°	137.7
75°	79.5
77.5°	37.1
80°	5.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)