

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203694

Luminaire Tested: **LD6B50D010TE EU6B30509035 6LBNH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203694  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B50D010TE EU6B30509035 6LBNH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2912.3 lumens  
Efficiency: N/A  
Efficacy: 49.6 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203694

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBNH1

### Luminous Intensity Polar Plot






TEST NUMBER: P203694

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBNH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 94  | 98  | 95  | 92  |  | 95  | 93  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 95  | 90  | 86  | 92  | 88  | 85  |  | 90  | 86  | 84  |  | 87  |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 83  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 73  | 81  | 76  | 73  |  | 80  | 75  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 72  | 68  | 77  | 72  | 68  |  | 75  | 71  | 67  |  | 74  |
| 7   | 83  | 74  | 68  | 64  | 82  | 73  | 68  | 64  | 72  | 67  | 63  |  | 71  | 66  | 63  |  | 70  |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 64  | 60  | 68  | 63  | 59  |  | 67  | 63  | 59  |  | 66  |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 59  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 62  | 57  | 53  | 71  | 62  | 57  | 53  | 61  | 56  | 53  |  | 60  | 56  | 52  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203694

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBNH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 335.7  | 11.5      |
| 10°-20°   | 800.6  | 27.5      |
| 20°-30°   | 917.2  | 31.5      |
| 30°-40°   | 616.2  | 21.2      |
| 40°-50°   | 176.0  | 6.0       |
| 50°-60°   | 43.1   | 1.5       |
| 60°-70°   | 16.3   | 0.6       |
| 70°-80°   | 6.3    | 0.2       |
| 80°-90°   | 0.7    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2053.5 | 70.5      |
| 0°-40°    | 2669.8 | 91.7      |
| 0°-60°    | 2888.9 | 99.2      |
| 0°-90°    | 2912.3 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2912.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3733 |      |
| 5°  | 3627 | 336  |
| 15° | 2873 | 801  |
| 25° | 2002 | 917  |
| 35° | 982  | 616  |
| 45° | 202  | 176  |
| 55° | 48   | 43   |
| 65° | 16   | 16   |
| 75° | 5    | 6    |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P203694

CATALOG NUMBER: LD6B50D010TE EU6B30509035 6LBNH1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3733.3 |
| 2.5°  | 3706.8 |
| 5°    | 3627.1 |
| 7.5°  | 3483.7 |
| 10°   | 3308.5 |
| 12.5° | 3085.4 |
| 15°   | 2873.0 |
| 17.5° | 2650.0 |
| 20°   | 2426.9 |
| 22.5° | 2214.5 |
| 25°   | 2002.1 |
| 27.5° | 1805.6 |
| 30°   | 1577.2 |
| 32.5° | 1274.5 |
| 35°   | 982.4  |
| 37.5° | 716.9  |
| 40°   | 493.9  |
| 42.5° | 323.9  |
| 45°   | 201.8  |
| 47.5° | 122.1  |
| 50°   | 74.3   |
| 52.5° | 58.4   |
| 55°   | 47.8   |
| 57.5° | 37.2   |
| 60°   | 26.6   |
| 62.5° | 21.2   |
| 65°   | 15.9   |
| 67.5° | 10.6   |
| 70°   | 10.6   |
| 72.5° | 5.3    |
| 75°   | 5.3    |
| 77.5° | 5.3    |
| 80°   | 5.3    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)