

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204410

Luminaire Tested: **LD6B50D010TE EU6B30508040 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204410
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508040 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5290.3 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204410

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSPGH1

Luminous Intensity Polar Plot





TEST NUMBER: P204410

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	102	99		101	98	96		97	95	93		93	91	90
2	102	95	89	84		100	93	88	83		90	85	82		87	83	80		84	81	78
3	94	85	78	72		92	83	77	71		80	75	70		78	73	69		75	71	68
4	87	76	68	62		85	75	67	62		72	66	61		70	65	60		68	63	59
5	80	68	60	54		78	67	60	54		65	59	53		63	58	53		62	56	52
6	74	62	54	48		73	61	53	48		59	52	47		58	52	47		56	51	47
7	69	57	48	43		68	56	48	43		54	47	42		53	47	42		52	46	42
8	65	52	44	38		63	51	44	38		50	43	38		49	42	38		48	42	38
9	60	48	40	35		59	47	40	35		46	39	35		45	39	34		44	38	34
10	57	44	37	32		56	44	36	32		43	36	31		42	36	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204410

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.3	4.4
10°-20°	649.4	12.3
20°-30°	947.1	17.9
30°-40°	1080.0	20.4
40°-50°	1036.0	19.6
50°-60°	793.5	15.0
60°-70°	435.4	8.2
70°-80°	115.8	2.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1827.8	34.6
0°-40°	2907.8	55.0
0°-60°	4737.4	89.5
0°-90°	5290.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5290.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2457	
5°	2438	231
15°	2305	649
25°	2057	947
35°	1727	1080
45°	1346	1036
55°	889	793
65°	438	435
75°	102	116
85°	0	2
90°	0	



TEST NUMBER: P204410

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2457.1
2.5°	2450.7
5°	2438.0
7.5°	2419.0
10°	2393.6
12.5°	2349.1
15°	2304.7
17.5°	2253.9
20°	2196.8
22.5°	2126.9
25°	2057.1
27.5°	1987.2
30°	1898.3
32.5°	1815.8
35°	1726.9
37.5°	1638.0
40°	1549.2
42.5°	1453.9
45°	1346.0
47.5°	1238.1
50°	1123.8
52.5°	1003.1
55°	888.9
57.5°	774.6
60°	653.9
62.5°	539.7
65°	438.1
67.5°	336.5
70°	247.6
72.5°	165.1
75°	101.6
77.5°	44.4
80°	12.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)