

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202556

Luminaire Tested: **LD6B50D010TE EU6B30508040 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508040 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5818.5 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202556

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202556

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85		100	94	89	84		91	86	82		87	84	81		84	81	79
3	95	86	79	73		92	84	78	73		81	76	71		79	74	70		76	72	69
4	88	77	70	64		86	76	69	63		74	67	62		71	66	62		69	65	61
5	81	70	62	56		79	69	61	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50		74	63	55	50		61	54	49		59	53	49		58	53	48
7	70	58	50	45		69	57	50	45		56	49	44		55	48	44		53	48	44
8	66	54	46	40		64	53	45	40		52	45	40		50	44	40		49	44	40
9	62	49	42	37		61	49	42	37		48	41	37		47	41	36		46	40	36
10	58	46	39	34		57	45	38	34		45	38	34		44	38	33		43	37	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202556

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.3	5.4
10°-20°	813.7	14.0
20°-30°	1079.0	18.5
30°-40°	1150.9	19.8
40°-50°	1075.8	18.5
50°-60°	820.3	14.1
60°-70°	446.2	7.7
70°-80°	119.7	2.1
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2204.1	37.9
0°-40°	3354.9	57.7
0°-60°	5251.1	90.2
0°-90°	5818.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5818.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3365	
5°	3318	311
15°	2901	814
25°	2349	1079
35°	1839	1151
45°	1401	1076
55°	923	820
65°	446	446
75°	103	120
85°	0	1
90°	0	



TEST NUMBER: P202556

CATALOG NUMBER: LD6B50D010TE EU6B30508040 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3364.6
2.5°	3353.9
5°	3318.3
7.5°	3243.4
10°	3157.9
12.5°	3036.7
15°	2901.3
17.5°	2765.8
20°	2619.7
22.5°	2480.7
25°	2348.8
27.5°	2209.8
30°	2077.9
32.5°	1949.6
35°	1839.1
37.5°	1728.6
40°	1614.6
42.5°	1511.2
45°	1400.7
47.5°	1279.6
50°	1165.5
52.5°	1044.3
55°	923.1
57.5°	791.3
60°	670.1
62.5°	556.0
65°	445.5
67.5°	345.7
70°	253.1
72.5°	174.6
75°	103.4
77.5°	46.3
80°	10.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)