

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175416

Luminaire Tested: **LDA6A10830D010TE LARL20NF 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175416
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26263)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A10830D010TE LARL20NF 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 20° Narrow Flood
Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 890.4 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.84
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175416

CATALOG NUMBER: LDA6A10830D010TE LARL20NF 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175416

CATALOG NUMBER: LDA6A10830D010TE LARL20NF 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97		
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	95		
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93		
4	106	102	98	95	105	101	97	95	99	96	94	97	95	93	95	93	92	91		
5	104	99	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	89		
6	101	96	92	90	100	95	92	89	94	91	89	93	90	88	92	89	88	87		
7	99	93	90	87	98	93	89	87	92	89	87	91	88	86	90	87	86	85		
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	83		
9	95	89	85	83	94	89	85	83	88	85	83	87	84	82	86	84	82	81		
10	93	87	84	81	92	87	83	81	86	83	81	85	83	81	85	82	81	80		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	323214
5°	267235
10°	171852
15°	70057
20°	33440
25°	12533
30°	899
35°	174
40°	72
45°	23
50°	26
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175416

CATALOG NUMBER: LDA6A10830D010TE LARL20NF 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	409.5	46.0
10°-20°	375.1	42.1
20°-30°	102.8	11.6
30°-40°	2.5	0.3
40°-50°	0.4	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	887.5	99.7
0°-40°	890.0	100.0
0°-60°	890.4	100.0
0°-90°	890.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	890.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5896	
5°	4856	410
15°	1234	375
25°	207	103
35°	3	3
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175416

CATALOG NUMBER: LDA6A10830D010TE LARL20NF 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5895.9
1°	5810.0
2°	5619.4
3°	5386.4
4°	5125.1
5°	4856.2
6°	4572.7
7°	4266.1
8°	3915.8
9°	3522.3
10°	3087.2
11°	2627.3
12°	2198.8
13°	1811.9
14°	1498.0
15°	1234.4
17.5°	791.0
20°	573.2
22.5°	387.6
25°	207.2
27.5°	69.4
30°	14.2
32.5°	5.0
35°	2.6
37.5°	1.7
40°	1.0
42.5°	0.7
45°	0.3
47.5°	0.3
50°	0.3
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175416

CATALOG NUMBER: LDA6A10830D010TE LARL20NF 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)