

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205539

Luminaire Tested: **LD6B50D010TE EU6B30508050 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B50D010TE EU6B30508050 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3087.4 lumens
Efficiency: N/A
Efficacy: 52.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205539

CATALOG NUMBER: LD6B50D010TE EU6B30508050 6LBMGPH1

Luminous Intensity Polar Plot




TEST NUMBER: P205539
CATALOG NUMBER: LD6B50D010TE EU6B30508050 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	77	85	80	77		83	79	76		81
5	91	82	76	72	89	81	76	71	79	74	71		78	73	70		76
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	49		57

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205539

CATALOG NUMBER: LD6B50D010TE EU6B30508050 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.5	9.6
10°-20°	766.9	24.8
20°-30°	977.2	31.6
30°-40°	690.6	22.4
40°-50°	252.1	8.2
50°-60°	69.9	2.3
60°-70°	25.3	0.8
70°-80°	9.0	0.3
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2039.6	66.1
0°-40°	2730.2	88.4
0°-60°	3052.2	98.9
0°-90°	3087.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3087.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3217	
5°	3161	296
15°	2731	767
25°	2170	977
35°	1097	691
45°	306	252
55°	75	70
65°	25	25
75°	6	9
85°	0	1
90°	0	



TEST NUMBER: P205539

CATALOG NUMBER: LD6B50D010TE EU6B30508050 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3217.3
2.5°	3204.8
5°	3161.1
7.5°	3073.9
10°	2980.3
12.5°	2855.6
15°	2730.9
17.5°	2606.2
20°	2481.5
22.5°	2331.9
25°	2169.8
27.5°	1945.3
30°	1695.9
32.5°	1396.6
35°	1097.4
37.5°	835.5
40°	611.0
42.5°	442.7
45°	305.5
47.5°	205.8
50°	137.2
52.5°	93.5
55°	74.8
57.5°	56.1
60°	43.6
62.5°	31.2
65°	24.9
67.5°	18.7
70°	12.5
72.5°	12.5
75°	6.2
77.5°	6.2
80°	6.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)