

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683978

Luminaire Tested: **LX6C120D010 EX6C1209050 6LBNH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P683978  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C120D010 EX6C1209050 6LBNH  
Description: 6 INCH 12000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LBN TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8076.9 lumens  
Efficiency: N/A  
Efficacy: 56.8 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 142.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P683978

CATALOG NUMBER: LX6C120D010 EX6C1209050 6LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P683978

CATALOG NUMBER: LX6C120D010 EX6C1209050 6LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	567603
5°	553553
10°	510773
15°	452210
20°	392647
25°	335844
30°	276884
35°	182339
40°	98019
45°	43392
50°	17594
55°	12692
60°	8059
65°	5759
70°	4744
75°	3135
80°	4672
85°	0



TEST NUMBER: P683978

CATALOG NUMBER: LX6C120D010 EX6C1209050 6LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	931.1	11.5
10°-20°	2220.4	27.5
20°-30°	2543.7	31.5
30°-40°	1709.0	21.2
40°-50°	488.3	6.0
50°-60°	119.5	1.5
60°-70°	45.4	0.6
70°-80°	17.6	0.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5695.1	70.5
0°-40°	7404.2	91.7
0°-60°	8012.0	99.2
0°-90°	8076.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8076.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10354	
5°	10059	931
15°	7968	2220
25°	5552	2544
35°	2725	1709
45°	560	488
55°	133	120
65°	44	45
75°	15	18
85°	0	2
90°	0	



TEST NUMBER: P683978

CATALOG NUMBER: LX6C120D010 EX6C1209050 6LBNH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10353.9
2.5°	10280.4
5°	10059.2
7.5°	9661.4
10°	9175.7
12.5°	8556.7
15°	7967.9
17.5°	7349.5
20°	6730.5
22.5°	6141.7
25°	5552.3
27.5°	5007.4
30°	4374.1
32.5°	3534.5
35°	2724.6
37.5°	1988.1
40°	1369.7
42.5°	898.3
45°	559.7
47.5°	338.6
50°	206.3
52.5°	161.9
55°	132.8
57.5°	103.2
60°	73.5
62.5°	58.7
65°	44.4
67.5°	29.6
70°	29.6
72.5°	14.8
75°	14.8
77.5°	14.8
80°	14.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)