

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175505

Luminaire Tested: **LDA6A20835D010TE LAR35FL 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26295)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A20835D010TE LAR35FL 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1717.8 lumens
Efficiency: N/A
Efficacy: 59.0 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175505

CATALOG NUMBER: LDA6A20835D010TE LAR35FL 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175505

CATALOG NUMBER: LDA6A20835D010TE LAR35FL 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	99	96	105	101	98	95	98	96	93		96	94	92		94
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91
5	100	94	90	87	99	93	89	86	92	88	85		90	87	85		89
6	97	90	86	83	96	90	86	83	88	85	82		87	84	82		86
7	94	87	83	80	93	87	82	79	85	82	79		84	81	79		83
8	91	84	80	77	90	84	79	77	83	79	76		82	78	76		81
9	88	81	77	74	87	81	77	74	80	76	74		79	76	73		79
10	86	79	74	72	85	78	74	71	78	74	71		77	74	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	276765
5°	264114
10°	225636
15°	184734
20°	118234
25°	45553
30°	9337
35°	2476
40°	780
45°	248
50°	111
55°	57
60°	66
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175505

CATALOG NUMBER: LDA6A20835D010TE LAR35FL 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	432.3	25.2
10°-20°	868.9	50.6
20°-30°	380.8	22.2
30°-40°	31.8	1.9
40°-50°	3.2	0.2
50°-60°	0.6	0.0
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1682.0	97.9
0°-40°	1713.8	99.8
0°-60°	1717.6	100.0
0°-90°	1717.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1717.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5049	
5°	4800	432
15°	3255	869
25°	753	381
35°	37	32
45°	3	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175505

CATALOG NUMBER: LDA6A20835D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5048.6
1°	5024.3
2°	4984.7
3°	4939.3
4°	4881.9
5°	4799.5
6°	4681.9
7°	4529.9
8°	4363.2
9°	4204.8
10°	4053.4
11°	3901.4
12°	3753.2
13°	3599.3
14°	3435.8
15°	3255.0
17.5°	2699.3
20°	2026.7
22.5°	1323.5
25°	753.1
27.5°	350.7
30°	147.5
32.5°	76.6
35°	37.0
37.5°	19.8
40°	10.9
42.5°	5.7
45°	3.2
47.5°	1.9
50°	1.3
52.5°	0.6
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175505

CATALOG NUMBER: LDA6A20835D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)