

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175509

Luminaire Tested: **LDA6A20935D010TE LAR35FL 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26295)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A20935D010TE LAR35FL 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1408.2 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 29.12
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175509

CATALOG NUMBER: LDA6A20935D010TE LAR35FL 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175509

CATALOG NUMBER: LDA6A20935D010TE LAR35FL 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	99	96	105	101	98	95	98	96	93		96	94	92		94
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91
5	100	94	90	87	99	93	89	86	92	88	85		90	87	85		89
6	97	90	86	83	96	90	86	83	88	85	82		87	84	82		86
7	94	87	83	80	93	87	82	79	85	82	79		84	81	79		83
8	91	84	80	77	90	84	79	77	83	79	76		82	78	76		81
9	88	81	77	74	87	81	77	74	80	76	74		79	76	73		79
10	86	79	74	72	85	78	74	71	78	74	71		77	74	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226873
5°	216503
10°	184967
15°	151437
20°	96923
25°	37339
30°	7659
35°	2034
40°	637
45°	202
50°	85
55°	48
60°	55
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175509

CATALOG NUMBER: LDA6A20935D010TE LAR35FL 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	354.4	25.2
10°-20°	712.3	50.6
20°-30°	312.2	22.2
30°-40°	26.1	1.9
40°-50°	2.6	0.2
50°-60°	0.5	0.0
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1378.8	97.9
0°-40°	1404.9	99.8
0°-60°	1408.0	100.0
0°-90°	1408.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1408.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4138	
5°	3934	354
15°	2668	712
25°	617	312
35°	30	26
45°	3	3
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175509

CATALOG NUMBER: LDA6A20935D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4138.5
1°	4118.6
2°	4086.2
3°	4049.0
4°	4001.9
5°	3934.3
6°	3838.0
7°	3713.4
8°	3576.7
9°	3446.9
10°	3322.8
11°	3198.1
12°	3076.7
13°	2950.5
14°	2816.4
15°	2668.3
17.5°	2212.7
20°	1661.4
22.5°	1084.9
25°	617.3
27.5°	287.5
30°	121.0
32.5°	62.8
35°	30.4
37.5°	16.2
40°	8.9
42.5°	4.7
45°	2.6
47.5°	1.6
50°	1.0
52.5°	0.5
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175509

CATALOG NUMBER: LDA6A20935D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)