

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P135226

Luminaire Tested: **LD6A20D010TE ERN6A20835 6LN1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P135226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23370)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A20D010TE ERN6A20835 6LN1H
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3500K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2088.0 lumens
Efficiency: N/A
Efficacy: 63.7 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.84
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 32.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P135226

CATALOG NUMBER: LD6A20D010TE ERN6A20835 6LN1H

Luminous Intensity Polar Plot





TEST NUMBER: P135226

CATALOG NUMBER: LD6A20D010TE ERN6A20835 6LN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	56	64	59	55		63	59	55		62
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	179666
5°	173803
10°	154945
15°	135050
20°	116958
25°	100354
30°	84238
35°	59112
40°	30770
45°	14642
50°	7683
55°	4163
60°	2871
65°	1883
70°	1392
75°	1235
80°	902
85°	0



TEST NUMBER: P135226

CATALOG NUMBER: LD6A20D010TE ERN6A20835 6LN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.0	11.6
10°-20°	558.7	26.8
20°-30°	639.4	30.6
30°-40°	455.5	21.8
40°-50°	137.7	6.6
50°-60°	35.7	1.7
60°-70°	13.2	0.6
70°-80°	4.5	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1441.0	69.0
0°-40°	1896.5	90.8
0°-60°	2070.0	99.1
0°-90°	2088.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2088.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2754	
5°	2654	243
15°	2000	559
25°	1394	639
35°	742	455
45°	159	138
55°	37	36
65°	12	13
75°	5	4
85°	0	0
90°	0	



TEST NUMBER: P135226

CATALOG NUMBER: LD6A20D010TE ERN6A20835 6LN1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2753.9
2.5°	2722.2
5°	2653.9
7.5°	2517.1
10°	2338.9
12.5°	2160.7
15°	1999.5
17.5°	1843.3
20°	1684.6
22.5°	1535.7
25°	1394.1
27.5°	1259.8
30°	1118.2
32.5°	947.3
35°	742.2
37.5°	532.2
40°	361.3
42.5°	239.3
45°	158.7
47.5°	109.9
50°	75.7
52.5°	48.8
55°	36.6
57.5°	26.9
60°	22.0
62.5°	17.1
65°	12.2
67.5°	9.8
70°	7.3
72.5°	4.9
75°	4.9
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)