

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P136186

Luminaire Tested: **LD6A20D010TE ERW6A20835 6LW1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P136186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23374)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A20D010TE ERW6A20835 6LW1H
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3500K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2377.0 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.09
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 32.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P136186

CATALOG NUMBER: LD6A20D010TE ERW6A20835 6LW1H

Luminous Intensity Polar Plot





TEST NUMBER: P136186

CATALOG NUMBER: LD6A20D010TE ERW6A20835 6LW1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68		
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	61		
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51		
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47		
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	49	45	43		
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106890
5°	106617
10°	105611
15°	104873
20°	102753
25°	98871
30°	91538
35°	77964
40°	59701
45°	42165
50°	28460
55°	18017
60°	10504
65°	4816
70°	2976
75°	1966
80°	977
85°	0



TEST NUMBER: P136186

CATALOG NUMBER: LD6A20D010TE ERW6A20835 6LW1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.3	6.5
10°-20°	436.7	18.4
20°-30°	627.7	26.4
30°-40°	603.7	25.4
40°-50°	359.5	15.1
50°-60°	148.2	6.2
60°-70°	37.3	1.6
70°-80°	8.5	0.4
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1218.7	51.3
0°-40°	1822.4	76.7
0°-60°	2330.1	98.0
0°-90°	2377.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2377.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1638	
5°	1628	154
15°	1553	437
25°	1374	628
35°	979	604
45°	457	360
55°	158	148
65°	31	37
75°	8	9
85°	0	1
90°	0	



TEST NUMBER: P136186

CATALOG NUMBER: LD6A20D010TE ERW6A20835 6LW1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1638.4
2.5°	1630.6
5°	1628.0
7.5°	1615.0
10°	1594.2
12.5°	1573.5
15°	1552.7
17.5°	1521.5
20°	1480.0
22.5°	1430.6
25°	1373.5
27.5°	1303.4
30°	1215.1
32.5°	1106.1
35°	978.9
37.5°	841.3
40°	701.0
42.5°	571.2
45°	457.0
47.5°	360.9
50°	280.4
52.5°	215.5
55°	158.4
57.5°	114.2
60°	80.5
62.5°	51.9
65°	31.2
67.5°	20.8
70°	15.6
72.5°	10.4
75°	7.8
77.5°	5.2
80°	2.6
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)