

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175399

Luminaire Tested: **LDA6A30827D010TE LARL15SP 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26262)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A30827D010TE LARL15SP 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 15° Spot Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2075.5 lumens
Efficiency: N/A
Efficacy: 46.7 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.26
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 44.49
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175399

CATALOG NUMBER: LDA6A30827D010TE LARL15SP 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175399

CATALOG NUMBER: LDA6A30827D010TE LARL15SP 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	115	113	112	110	113	111	110	108		107	106	105			104	103	102			100
2	112	108	106	103	110	107	104	102		104	102	100			101	99	98			98
3	109	104	101	98	107	103	100	98		101	98	96			98	96	95			96
4	106	101	97	94	104	100	96	94		98	95	93			96	94	92			94
5	103	97	94	91	102	97	93	90		95	92	90			94	91	89			92
6	100	95	91	88	99	94	90	88		93	89	87			91	89	87			90
7	98	92	88	85	97	91	88	85		90	87	85			89	86	84			88
8	95	89	86	83	95	89	85	83		88	85	83			87	84	82			86
9	93	87	83	81	92	87	83	81		86	83	81			85	82	80			85
10	91	85	81	79	90	85	81	79		84	81	79			83	81	79			83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1056659
5°	611791
10°	305862
15°	159558
20°	94870
25°	57874
30°	1171
35°	294
40°	186
45°	140
50°	77
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175399

CATALOG NUMBER: LDA6A30827D010TE LARL15SP 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	892.0	43.0
10°-20°	809.4	39.0
20°-30°	368.9	17.8
30°-40°	3.8	0.2
40°-50°	1.2	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2070.3	99.8
0°-40°	2074.2	99.9
0°-60°	2075.5	100.0
0°-90°	2075.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2075.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19275	
5°	11118	892
15°	2811	809
25°	957	369
35°	4	4
45°	2	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175399

CATALOG NUMBER: LDA6A30827D010TE LARL15SP 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	19275.0
1°	18354.3
2°	16540.0
3°	14544.8
4°	12712.9
5°	11117.5
6°	9725.8
7°	8492.3
8°	7388.8
9°	6410.9
10°	5494.6
11°	4681.9
12°	3998.4
13°	3493.2
14°	3118.1
15°	2811.4
17.5°	2164.8
20°	1626.2
22.5°	1295.0
25°	956.8
27.5°	318.0
30°	18.5
32.5°	7.0
35°	4.4
37.5°	3.5
40°	2.6
42.5°	1.8
45°	1.8
47.5°	0.9
50°	0.9
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175399

CATALOG NUMBER: LDA6A30827D010TE LARL15SP 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)