

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175405

Luminaire Tested: **LDA6A30935D010TE LARL15SP 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175405
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26262)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A30935D010TE LARL15SP 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 15° Spot Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1936.2 lumens
Efficiency: N/A
Efficacy: 43.5 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.26
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 44.49
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175405

CATALOG NUMBER: LDA6A30935D010TE LARL15SP 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175405

CATALOG NUMBER: LDA6A30935D010TE LARL15SP 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97		
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95		
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92		
4	106	101	97	94	104	100	96	94	98	95	93	96	94	92	94	92	91	90		
5	103	97	94	91	102	97	93	90	95	92	90	94	91	89	92	90	88	87		
6	100	95	91	88	99	94	90	88	93	89	87	91	89	87	90	88	86	85		
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83		
8	95	89	86	83	95	89	85	83	88	85	83	87	84	82	86	84	82	81		
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79		
10	91	85	81	79	90	85	81	79	84	81	79	83	81	79	83	80	78	78		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	985749
5°	570734
10°	285338
15°	148854
20°	88505
25°	53991
30°	1089
35°	274
40°	179
45°	124
50°	68
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175405

CATALOG NUMBER: LDA6A30935D010TE LARL15SP 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	832.2	43.0
10°-20°	755.1	39.0
20°-30°	344.1	17.8
30°-40°	3.6	0.2
40°-50°	1.1	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1931.4	99.8
0°-40°	1935.0	99.9
0°-60°	1936.2	100.0
0°-90°	1936.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1936.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17982	
5°	10371	832
15°	2623	755
25°	893	344
35°	4	4
45°	2	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175405

CATALOG NUMBER: LDA6A30935D010TE LARL15SP 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	17981.5
1°	17122.6
2°	15430.1
3°	13568.7
4°	11859.8
5°	10371.4
6°	9073.1
7°	7922.4
8°	6893.0
9°	5980.7
10°	5125.9
11°	4367.7
12°	3730.1
13°	3258.8
14°	2908.8
15°	2622.8
17.5°	2019.5
20°	1517.1
22.5°	1208.1
25°	892.6
27.5°	296.7
30°	17.2
32.5°	6.6
35°	4.1
37.5°	3.3
40°	2.5
42.5°	1.6
45°	1.6
47.5°	0.8
50°	0.8
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175405

CATALOG NUMBER: LDA6A30935D010TE LARL15SP 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)