

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P136070

Luminaire Tested: **LD6A20D010TE ERW6A20935 6LW1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P136070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23358)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A20D010TE ERW6A20935 6LW1LI
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3500K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2362.3 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.12
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 32.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P136070

CATALOG NUMBER: LD6A20D010TE ERW6A20935 6LW1LI

Luminous Intensity Polar Plot





TEST NUMBER: P136070

CATALOG NUMBER: LD6A20D010TE ERW6A20935 6LW1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92		
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77		
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65		
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59		
7	79	68	62	57	77	68	61	57	66	61	57	65	60	56	64	59	56	54		
8	74	64	57	53	73	63	57	52	62	56	52	61	56	52	60	55	52	50		
9	70	60	53	49	69	59	53	48	58	52	48	57	52	48	56	51	48	46		
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99264
5°	101791
10°	108731
15°	117408
20°	119318
25°	112009
30°	98649
35°	80353
40°	58347
45°	37450
50°	19680
55°	6734
60°	1931
65°	509
70°	324
75°	429
80°	0
85°	0



TEST NUMBER: P136070

CATALOG NUMBER: LD6A20D010TE ERW6A20935 6LW1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.2	6.4
10°-20°	487.6	20.6
20°-30°	707.5	30.0
30°-40°	623.2	26.4
40°-50°	319.1	13.5
50°-60°	67.3	2.8
60°-70°	5.2	0.2
70°-80°	1.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1346.3	57.0
0°-40°	1969.6	83.4
0°-60°	2355.9	99.7
0°-90°	2362.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2362.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1522	
5°	1554	151
15°	1738	488
25°	1556	708
35°	1009	623
45°	406	319
55°	59	67
65°	3	5
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P136070

CATALOG NUMBER: LD6A20D010TE ERW6A20935 6LW1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1521.5
2.5°	1524.7
5°	1554.3
7.5°	1595.3
10°	1641.3
12.5°	1694.0
15°	1738.3
17.5°	1749.9
20°	1718.6
22.5°	1649.6
25°	1556.0
27.5°	1442.6
30°	1309.5
32.5°	1163.3
35°	1008.9
37.5°	847.8
40°	685.1
42.5°	538.9
45°	405.9
47.5°	290.8
50°	193.9
52.5°	113.4
55°	59.2
57.5°	29.6
60°	14.8
62.5°	6.5
65°	3.3
67.5°	3.3
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)