

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192137

Luminaire Tested: **LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26267)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt
Description: PORTFOLIO 6" Lensed Adjustable, Self-flange Trim Ring, 15° Spot
Optic, at 30° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2469.5 lumens
Efficiency: N/A
Efficacy: 51.8 lumens/watt
Spacing Criteria (0/90/45): 2.44 / 0.33 / 1.32
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192137

CATALOG NUMBER: LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192137

CATALOG NUMBER: LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46
9	66	55	47	43	65	54	47	43	53	47	42	52	46	42	51	46	42
10	62	50	43	39	61	50	43	39	49	43	39	48	42	38	47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	19927	19927	19927
5°	68132	16949	2267
10°	114043	9402	1113
15°	198083	3473	953
20°	404699	2275	1628
25°	759685	4446	28713
30°	1129516	7742	4653
35°	815150	596	381
40°	442737	250	0
45°	245777	271	0
50°	143808	298	0
55°	4569	210	0
60°	1590	384	0
65°	739	454	0
70°	561	561	0
75°	254	932	0
80°	0	1389	0
85°	0	2768	0



TEST NUMBER: P1192137

CATALOG NUMBER: LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	2.1
10°-20°	264.4	10.7
20°-30°	850.9	34.5
30°-40°	885.8	35.9
40°-50°	377.4	15.3
50°-60°	31.4	1.3
60°-70°	3.3	0.1
70°-80°	2.9	0.1
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1166.2	47.2
0°-40°	2052.0	83.1
0°-60°	2460.8	99.6
0°-90°	2469.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2469.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	364	364	364	364	364	
5°	1238	902	308	56	41	141
15°	3490	1662	61	21	17	1141
25°	12559	1770	74	221	475	6032
35°	12180	1264	9	8	6	7540
45°	3170	217	4	2	0	2607
55°	48	7	2	2	0	298
65°	6	4	4	2	0	6
75°	1	4	4	4	0	1
85°	0	4	4	4	0	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192137

CATALOG NUMBER: LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	363.5	363.5	363.5	363.5	363.5	363.5	363.5	363.5	363.5	363.5	363.5
2.5°	807.1	764.7	797.0	778.0	765.9	762.5	781.4	760.2	738.0	737.1	730.4
5°	1238.1	1198.2	1231.5	1202.6	1189.3	1178.2	1187.1	1152.6	1116.1	1117.1	1100.5
7.5°	1613.9	1591.7	1613.9	1582.9	1572.8	1561.7	1558.5	1524.9	1481.8	1485.0	1459.6
10°	2048.7	1984.1	2019.6	1951.8	1935.2	1905.2	1895.1	1840.8	1771.8	1768.6	1731.8
12.5°	2647.6	2622.0	2657.8	2562.1	2542.1	2491.1	2463.2	2376.4	2263.2	2234.1	2149.8
15°	3490.2	3407.9	3443.6	3309.0	3271.3	3182.3	3121.1	2986.7	2878.9	2756.6	2627.7
17.5°	4560.7	4513.8	4559.5	4294.9	4197.2	4023.9	3880.4	3656.0	3426.9	3316.9	3135.6
20°	6937.1	6714.9	6739.3	6247.9	5934.5	5467.7	5094.1	4598.4	4143.7	3882.6	3583.7
22.5°	9574.9	9321.4	9259.0	8627.7	8096.6	7395.0	6739.3	5910.0	5104.2	4520.5	4013.8
25°	12559.4	12394.6	12069.1	11035.4	10121.6	9121.4	8156.5	7071.5	6026.7	5133.0	4372.8
26°	13976.5	13844.1	13355.1	12062.5	10879.8	9682.6	8579.9	7415.0	6288.1	5307.6	4457.4
27°	15322.7	15215.9	14579.9	13075.0	11596.7	10156.1	8887.9	7659.6	6475.7	5419.8	4517.3
28°	16508.5	16399.5	15578.1	13933.1	12164.6	10498.4	9081.2	7812.0	6583.7	5446.5	4513.8
29°	17431.3	17293.4	16232.8	14483.3	12498.2	10663.1	9120.2	7830.7	6568.2	5384.3	4451.7
30°	17843.6	17672.4	16419.7	14601.1	12503.6	10600.7	9010.2	7729.6	6441.4	5237.6	4336.1
31°	17520.0	17374.5	16080.7	14261.1	12164.6	10316.1	8736.7	7496.1	6201.3	5025.3	4182.7
32°	16577.6	16444.2	15251.4	13514.2	11523.4	9834.8	8340.0	7162.7	5882.2	4768.6	4004.9
33°	15284.7	15181.4	14112.2	12488.1	10699.6	9242.5	7865.3	6744.8	5498.7	4480.6	3788.1
34°	13809.8	13728.7	12752.7	11328.9	9800.5	8584.3	7324.0	6143.6	5079.8	4190.6	3625.9
35°	12180.4	12124.6	11328.9	10138.3	8905.6	7900.8	6722.6	5612.2	4657.4	3911.4	3451.3
36°	10631.8	10586.4	9979.3	9046.9	8054.2	7191.6	6071.3	5058.6	4252.7	3660.4	3288.0
37°	9309.1	9275.8	8826.7	8075.4	7236.2	6454.8	5407.7	4540.7	3900.3	3441.4	3120.1
38°	8208.8	8182.1	7817.4	7151.6	6393.6	5692.3	4767.3	4082.6	3600.2	3251.3	2930.0
39°	7182.7	7148.4	6820.5	6218.0	5554.5	4949.6	4342.7	3705.8	3364.7	3053.3	2725.6
40°	6186.7	6142.3	5854.6	5342.1	4788.5	4319.5	3774.8	3474.7	3173.4	2823.2	2516.5
42.5°	4151.6	4127.2	3970.4	3739.3	3504.8	3333.4	3161.3	2893.3	2575.4	2286.4	2059.8
45°	3170.2	3164.5	3087.8	2966.7	2811.1	2666.6	2436.6	2282.0	2067.4	1824.0	1661.8
47.5°	2432.1	2433.1	2362.1	2270.9	2164.1	2070.9	1902.9	1779.6	1626.3	1487.2	1361.7
50°	1686.2	1615.2	1625.0	1552.8	1466.2	1411.7	1256.1	1161.4	943.7	723.5	565.7
51°	1263.8	1170.6	1182.6	1101.5	1011.5	963.7	818.2	722.5	518.1	340.0	222.4
52°	771.3	698.1	696.9	634.7	556.8	514.6	399.0	311.2	176.8	93.5	64.4
53°	345.7	296.9	285.6	243.4	191.1	165.7	113.4	83.3	62.1	47.8	36.7
54°	91.2	81.1	77.9	71.0	64.4	62.1	54.5	45.6	35.5	27.9	23.4
55°	47.8	44.4	43.4	41.2	37.7	36.7	32.3	27.9	22.2	20.0	17.8
57.5°	22.2	22.2	21.2	20.0	19.0	19.0	16.8	15.5	14.5	14.5	12.3
60°	14.5	14.5	14.5	13.3	13.3	12.3	11.1	10.1	8.9	10.1	8.9
61°	12.3	12.3	12.3	11.1	10.1	8.9	8.9	8.9	7.9	7.9	6.7
62°	8.9	8.9	7.9	7.9	6.7	6.7	6.7	6.7	5.7	6.7	6.7
63°	6.7	6.7	5.7	5.7	5.7	5.7	4.4	4.4	4.4	6.7	6.7
64°	5.7	5.7	5.7	4.4	4.4	4.4	4.4	4.4	4.4	5.7	4.4
65°	5.7	4.4	4.4	4.4	4.4	4.4	4.4	4.4	3.5	4.4	4.4
66°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	3.5	3.5	4.4	4.4

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192137

CATALOG NUMBER: LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
72.5°	1.2	1.2	1.2	1.2	0.0	0.0	0.0	0.0	0.0	1.2	1.2
75°	1.2	1.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.2	1.2
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.2	1.2
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.2	1.2
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.2	1.2
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.2	1.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192137

CATALOG NUMBER: LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	67.5°	90°	112.5°
0°	363.5	363.5	363.5	363.5	363.5	363.5	363.5	363.5	363.5	363.5	363.5
2.5°	730.4	716.8	689.2	683.6	656.9	641.4	645.8	636.9	494.7	348.9	217.7
5°	1088.2	1058.1	1016.9	1002.6	957.0	932.6	924.7	902.5	612.5	308.0	102.3
7.5°	1438.4	1399.4	1349.3	1326.2	1263.8	1222.6	1196.0	1162.7	693.7	244.6	56.7
10°	1698.5	1653.9	1601.6	1571.8	1501.7	1460.6	1417.2	1380.4	737.1	168.9	42.2
12.5°	2045.2	1957.4	1848.4	1782.9	1679.5	1622.8	1572.8	1537.2	753.6	101.1	32.3
15°	2507.6	2366.5	2211.9	2093.1	1917.5	1810.7	1726.1	1661.8	740.3	61.2	27.9
17.5°	2955.6	2755.4	2553.2	2391.9	2191.0	2031.9	1869.7	1742.9	683.6	48.8	25.6
20°	3328.0	3093.5	2835.5	2609.9	2377.6	2188.7	1973.0	1793.9	592.6	39.0	27.9
22.5°	3614.8	3315.7	3023.5	2743.3	2466.4	2249.6	2012.9	1805.0	476.9	39.9	39.0
25°	3821.4	3429.1	3117.9	2798.8	2497.7	2259.8	1992.0	1769.5	351.1	73.5	131.2
26°	3863.6	3452.5	3130.0	2793.4	2486.6	2243.0	1967.3	1747.3	316.9	145.5	289.0
27°	3887.0	3449.1	3121.1	2771.2	2463.2	2218.6	1939.7	1727.4	311.2	249.1	431.3
28°	3866.1	3421.2	3083.4	2731.0	2425.5	2186.3	1907.4	1703.9	308.0	305.8	409.1
29°	3808.1	3372.4	3026.7	2668.9	2367.5	2135.2	1858.6	1670.7	275.7	243.4	246.8
30°	3720.3	3303.6	2944.5	2585.5	2294.3	2062.0	1788.5	1617.4	182.2	122.3	104.6
31°	3611.3	3214.6	2843.2	2488.8	2210.9	1973.0	1715.0	1548.3	94.4	52.3	48.8
32°	3491.2	3107.8	2734.4	2390.9	2126.4	1887.4	1653.9	1487.2	62.1	28.9	27.9
33°	3364.7	2983.3	2614.4	2289.8	2031.9	1791.7	1590.5	1421.6	46.6	17.8	16.8
34°	3240.2	2850.1	2493.3	2180.8	1929.6	1706.2	1532.8	1346.1	37.7	13.3	11.1
35°	3098.9	2705.6	2368.8	2065.2	1819.6	1632.9	1475.1	1263.8	30.1	8.9	8.9
36°	2934.4	2552.2	2239.8	1944.1	1715.0	1565.1	1411.7	1173.8	23.4	6.7	7.9
37°	2759.8	2399.8	2109.6	1824.0	1629.5	1502.7	1335.0	1081.5	20.0	5.7	6.7
38°	2579.8	2248.7	1969.8	1708.4	1555.0	1434.9	1248.2	985.9	16.8	4.4	5.7
39°	2403.0	2094.0	1829.7	1615.2	1485.0	1355.0	1149.4	888.2	14.5	4.4	5.7
40°	2230.9	1938.5	1705.2	1534.0	1407.3	1257.1	1047.0	785.9	10.1	3.5	5.7
42.5°	1821.8	1616.2	1468.4	1297.1	1153.8	984.9	770.3	510.2	7.9	3.5	4.4
45°	1524.9	1356.0	1183.9	990.3	849.3	675.9	455.7	216.8	7.9	3.5	4.4
47.5°	1206.1	1007.1	753.6	509.0	332.4	171.1	53.3	30.1	5.7	3.5	4.4
50°	351.1	203.4	75.7	45.6	34.5	21.2	13.3	12.3	4.4	3.5	4.4
51°	101.1	59.9	39.9	26.6	20.0	12.3	10.1	11.1	4.4	3.5	3.5
52°	47.8	34.5	23.4	17.8	13.3	10.1	8.9	10.1	4.4	3.5	3.5
53°	27.9	21.2	16.8	14.5	10.1	8.9	6.7	8.9	4.4	3.5	3.5
54°	19.0	16.8	14.5	12.3	8.9	6.7	6.7	8.9	4.4	3.5	3.5
55°	16.8	14.5	12.3	11.1	7.9	6.7	6.7	6.7	3.5	2.2	3.5
57.5°	11.1	11.1	8.9	8.9	6.7	4.4	2.2	5.7	4.4	3.5	3.5
60°	7.9	7.9	7.9	5.7	2.2	2.2	1.2	4.4	4.4	3.5	4.4
61°	7.9	7.9	5.7	4.4	2.2	2.2	1.2	4.4	4.4	3.5	4.4
62°	6.7	5.7	4.4	4.4	2.2	2.2	1.2	4.4	4.4	3.5	4.4
63°	5.7	4.4	4.4	4.4	2.2	1.2	1.2	4.4	4.4	3.5	4.4
64°	4.4	4.4	4.4	4.4	1.2	1.2	1.2	4.4	4.4	3.5	4.4
65°	4.4	4.4	4.4	3.5	1.2	1.2	1.2	3.5	4.4	3.5	4.4
66°	4.4	4.4	3.5	3.5	1.2	1.2	1.2	3.5	4.4	3.5	4.4



TEST NUMBER: P1192137

CATALOG NUMBER: LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	67.5°	90°	112.5°
72.5°	1.2	2.2	2.2	2.2	0.0	0.0	0.0	3.5	4.4	3.5	4.4
75°	1.2	1.2	2.2	2.2	0.0	0.0	0.0	3.5	4.4	4.4	4.4
77.5°	1.2	1.2	2.2	2.2	0.0	0.0	0.0	3.5	4.4	4.4	5.7
80°	1.2	1.2	2.2	2.2	0.0	0.0	0.0	3.5	4.4	4.4	5.7
82.5°	1.2	1.2	2.2	2.2	0.0	0.0	0.0	3.5	4.4	4.4	5.7
85°	1.2	1.2	2.2	2.2	0.0	0.0	0.0	3.5	4.4	4.4	5.7
87.5°	1.2	1.2	2.2	2.2	0.0	0.0	0.0	3.5	4.4	4.4	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192137

CATALOG NUMBER: LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	363.5	363.5	363.5
2.5°	138.8	100.1	91.2
5°	55.5	45.6	41.2
7.5°	34.5	28.9	26.6
10°	27.9	21.2	20.0
12.5°	22.2	19.0	17.8
15°	21.2	17.8	16.8
17.5°	21.2	20.0	19.0
20°	26.6	26.6	27.9
22.5°	45.6	53.3	59.9
25°	221.2	357.8	474.7
26°	463.6	653.5	699.1
27°	574.6	594.8	571.4
28°	442.4	396.8	373.6
29°	236.7	197.8	181.2
30°	94.4	77.9	73.5
31°	45.6	39.0	37.7
32°	25.6	21.2	21.2
33°	15.5	13.3	12.3
34°	11.1	8.9	7.9
35°	7.9	6.7	5.7
36°	6.7	4.4	3.5
37°	5.7	3.5	3.5
38°	4.4	3.5	2.2
39°	3.5	2.2	1.2
40°	3.5	1.2	0.0
42.5°	2.2	1.2	0.0
45°	2.2	0.0	0.0
47.5°	3.5	2.2	1.2
50°	2.2	1.2	0.0
51°	2.2	0.0	0.0
52°	2.2	0.0	0.0
53°	2.2	0.0	0.0
54°	2.2	0.0	0.0
55°	2.2	0.0	0.0
57.5°	2.2	0.0	0.0
60°	2.2	0.0	0.0
61°	2.2	0.0	0.0
62°	2.2	0.0	0.0
63°	2.2	1.2	0.0
64°	2.2	1.2	0.0
65°	2.2	1.2	0.0
66°	2.2	1.2	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P1192137

CATALOG NUMBER: LDA6A35927D010TE LARL15SP 6LAL1 30° Tilt

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
72.5°	3.5	1.2	0.0
75°	3.5	1.2	0.0
77.5°	3.5	1.2	0.0
80°	3.5	1.2	0.0
82.5°	3.5	1.2	0.0
85°	3.5	1.2	0.0
87.5°	3.5	1.2	0.0
90°	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°	4.4	3.5	3.5	3.5	3.5	3.5	3.5	2.2	2.2	3.5	3.5
70°	3.5	3.5	3.5	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°	3.5	3.5	3.5	3.5	1.2	0.0	0.0	3.5	4.4	3.5	4.4
70°	2.2	2.2	2.2	2.2	0.0	0.0	0.0	3.5	4.4	3.5	4.4

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°	3.5	1.2	0.0
70°	3.5	1.2	0.0

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)