

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192179

Luminaire Tested: **LDA6A40927D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192179
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26668)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40927D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2888.0 lumens
Efficiency: N/A
Efficacy: 58.0 lumens/watt
Spacing Criteria (0/90/45): 2.16 / 1.11 / 1.51
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192179

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192179

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80		
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70		
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62		
5	83	72	65	59	81	71	64	59	69	63	58	67	62	57	66	61	57	55		
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49		
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44		
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39		
9	63	50	43	38	61	50	43	38	49	42	37	48	42	37	47	41	37	35		
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	47677	47677	47677
5°	75798	46990	30371
10°	112812	45156	20513
15°	160290	42991	15437
20°	209837	41053	15775
25°	249855	41512	27262
30°	277087	40038	25675
35°	282683	34131	18892
40°	270192	26306	13976
45°	235637	18940	10544
50°	179644	13756	7010
55°	100288	9902	4081
60°	46115	6842	1645
65°	21753	3697	726
70°	10659	1779	753
75°	5041	1186	826
80°	2494	1231	1010
85°	1510	2013	943

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192179

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	3.1
10°-20°	328.1	11.4
20°-30°	656.3	22.7
30°-40°	805.9	27.9
40°-50°	645.6	22.4
50°-60°	284.0	9.8
60°-70°	64.0	2.2
70°-80°	11.6	0.4
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1074.0	37.2
0°-40°	1879.9	65.1
0°-60°	2809.5	97.3
0°-90°	2888.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2888.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	870	870	870	870	870	
5°	1377	1185	854	632	552	152
15°	2824	1905	758	353	272	824
25°	4131	2353	686	427	451	1901
35°	4224	2121	510	308	282	2615
45°	3039	1400	244	150	136	2311
55°	1049	519	104	59	43	997
65°	168	106	28	10	6	192
75°	24	14	6	5	4	30
85°	2	2	3	3	2	3
90°	0	0	0	0	0	

TEST NUMBER: P1192179

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7
2.5°	1109.3	1080.9	1103.8	1084.0	1077.7	1075.4	1065.8	1059.5	1057.2	1035.1	1017.7
5°	1377.4	1344.2	1367.9	1338.6	1323.6	1315.7	1299.1	1278.5	1262.0	1220.0	1185.2
7.5°	1691.4	1655.8	1677.9	1635.9	1607.5	1593.2	1566.4	1526.9	1489.6	1422.5	1363.9
10°	2026.6	1997.3	2016.3	1957.8	1913.4	1890.6	1851.0	1800.4	1724.5	1626.4	1540.2
12.5°	2417.2	2375.2	2390.2	2312.0	2248.8	2216.3	2160.2	2081.1	1973.6	1840.0	1722.1
15°	2824.3	2784.8	2794.3	2694.7	2607.0	2561.8	2489.1	2376.9	2234.5	2059.7	1904.8
17.5°	3241.9	3188.1	3186.5	3067.9	2950.9	2894.0	2803.0	2655.1	2488.4	2259.0	2067.6
20°	3596.9	3550.3	3537.6	3414.3	3254.5	3188.1	3078.2	2894.7	2690.0	2424.3	2199.7
22.5°	3901.3	3847.6	3824.6	3679.9	3498.8	3421.4	3295.7	3073.5	2845.7	2545.3	2292.2
25°	4130.7	4086.3	4053.1	3890.3	3687.8	3600.9	3463.3	3222.9	2958.8	2629.8	2353.1
27.5°	4312.4	4253.2	4211.3	4033.3	3805.6	3713.9	3566.0	3305.1	3016.5	2663.9	2371.3
30°	4377.3	4318.0	4269.7	4080.0	3838.8	3738.4	3583.4	3306.7	3000.7	2638.6	2331.8
32.5°	4346.5	4284.8	4230.2	4031.8	3781.9	3676.7	3518.6	3237.9	2917.6	2554.0	2244.0
35°	4224.0	4174.9	4113.2	3913.2	3666.5	3551.8	3394.4	3106.6	2788.7	2421.9	2120.6
37.5°	4050.7	3974.8	3917.9	3721.9	3483.0	3366.0	3214.9	2938.2	2616.4	2263.8	1972.0
40°	3775.6	3698.9	3641.9	3453.0	3236.3	3118.5	2979.4	2715.3	2404.5	2076.4	1798.0
42.5°	3432.4	3361.3	3305.9	3130.4	2939.0	2824.3	2701.8	2457.5	2168.9	1868.4	1607.5
45°	3039.4	2970.6	2923.2	2770.6	2600.6	2499.4	2388.7	2172.9	1908.7	1635.9	1400.3
47.5°	2613.3	2542.9	2502.6	2365.8	2221.8	2130.2	2035.2	1848.6	1612.2	1378.2	1173.4
50°	2106.4	2038.4	2002.0	1887.4	1785.4	1700.8	1632.0	1482.5	1288.8	1104.6	937.7
52.5°	1542.6	1489.6	1462.8	1383.7	1322.9	1259.6	1215.3	1111.0	969.4	838.9	713.2
55°	1049.3	1005.7	993.1	944.1	910.9	876.8	845.3	784.4	688.7	602.5	518.7
57.5°	656.3	651.6	660.2	616.8	601.7	587.5	563.0	528.9	468.9	415.1	364.5
60°	420.6	415.9	412.0	396.1	389.0	378.8	366.9	347.1	309.9	278.4	245.1
62.5°	266.4	263.3	267.3	257.8	248.3	248.3	235.7	224.6	201.6	182.7	158.9
65°	167.7	166.9	169.2	162.8	158.1	155.7	149.5	143.1	128.9	117.1	106.0
67.5°	106.0	105.1	106.8	105.1	99.7	98.0	94.1	90.1	80.6	73.6	65.6
70°	66.5	65.6	66.5	64.8	61.7	60.1	57.7	54.5	51.4	43.5	39.5
72.5°	40.3	39.5	40.3	39.5	37.1	37.1	34.0	32.4	30.0	25.3	22.1
75°	23.8	23.8	23.8	22.9	21.4	21.4	19.8	18.9	17.4	15.0	13.5
77.5°	13.5	13.5	13.5	13.5	12.7	12.7	11.8	11.1	10.3	8.7	8.7
80°	7.9	7.9	7.9	7.9	7.1	7.9	7.1	7.1	6.3	5.6	5.6
82.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9
85°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
87.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192179

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7
2.5°	1003.4	978.1	973.3	946.5	941.8	926.7	918.8	904.5	876.1	861.1	842.9
5°	1143.4	1103.8	1080.9	1032.7	1017.7	992.4	966.2	931.5	886.4	853.9	820.0
7.5°	1296.8	1231.9	1183.7	1112.5	1086.4	1049.3	1003.4	948.9	885.6	837.3	789.1
10°	1451.0	1349.7	1275.4	1179.7	1141.7	1092.8	1026.3	952.8	873.8	811.2	751.1
12.5°	1592.5	1466.0	1363.9	1242.2	1191.6	1131.4	1044.5	952.8	858.7	784.4	714.0
15°	1746.7	1579.8	1446.9	1298.3	1235.9	1164.7	1058.0	949.7	842.1	757.5	680.0
17.5°	1872.4	1673.9	1511.0	1337.9	1263.5	1182.1	1059.5	937.0	820.8	728.2	647.6
20°	1964.9	1745.1	1554.5	1360.8	1277.0	1188.4	1053.2	920.4	798.6	703.7	621.5
22.5°	2032.1	1787.7	1576.7	1368.7	1277.7	1185.2	1042.2	906.2	783.5	691.1	612.8
25°	2072.4	1809.1	1583.8	1365.6	1271.4	1175.0	1029.5	893.5	774.1	686.3	614.3
27.5°	2076.4	1800.4	1564.8	1341.8	1245.3	1148.9	1003.4	869.0	753.5	672.9	604.1
30°	2031.3	1751.4	1514.9	1289.7	1192.3	1097.5	954.4	822.3	712.5	632.5	570.1
32.5°	1944.3	1665.2	1431.2	1210.5	1114.9	1022.4	883.2	759.1	651.6	578.0	516.3
35°	1828.9	1556.1	1322.9	1115.7	1022.4	934.6	799.4	677.6	579.6	510.0	453.9
37.5°	1692.1	1428.8	1210.5	1010.5	920.4	838.9	708.5	597.8	503.6	439.7	388.2
40°	1536.3	1284.9	1080.1	890.3	809.7	730.6	612.0	510.8	423.0	367.6	324.1
42.5°	1367.9	1132.3	943.3	767.0	693.4	621.5	513.9	422.3	346.4	301.3	267.3
45°	1182.9	971.0	800.9	646.8	576.4	517.1	415.9	340.0	282.3	244.3	220.7
47.5°	985.2	800.9	653.1	520.3	458.6	408.0	325.0	268.1	226.9	200.8	181.0
50°	786.7	633.4	510.0	395.3	348.7	306.0	251.4	212.7	181.0	161.3	148.6
52.5°	601.0	476.8	379.6	290.2	258.6	229.3	193.7	167.7	143.9	129.7	120.1
55°	435.6	344.0	270.4	212.7	191.3	174.8	148.6	129.7	114.7	103.6	95.7
57.5°	303.7	238.0	189.0	155.0	142.4	130.4	112.2	99.7	89.4	81.5	75.1
60°	205.6	161.3	132.1	112.2	104.4	96.5	84.6	75.9	68.0	62.4	56.2
62.5°	135.2	110.7	94.1	82.2	75.1	69.5	62.4	55.3	49.1	44.2	38.8
65°	87.7	72.7	64.8	55.3	52.2	48.2	41.9	38.0	32.4	28.5	24.5
67.5°	55.3	47.4	41.9	36.4	34.0	30.9	27.7	23.8	20.6	17.4	15.0
70°	33.2	29.2	25.3	22.1	20.6	18.9	16.6	14.2	11.8	11.1	9.5
72.5°	19.8	17.4	15.0	13.5	12.7	11.8	10.3	8.7	7.9	7.1	6.3
75°	11.8	11.1	9.5	7.9	7.9	7.1	7.1	6.3	5.6	5.6	4.7
77.5°	7.9	7.1	6.3	5.6	5.6	5.6	4.7	4.7	4.7	4.7	4.7
80°	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9	3.9	3.9	3.9
82.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.9	3.9
85°	2.4	2.4	2.4	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	2.4	2.4	2.4	2.4	3.2	3.2	3.2	3.2	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192179

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7
2.5°	835.0	811.2	801.8	787.6	773.3	772.5	755.9	747.2	740.9	729.8	718.7
5°	797.0	760.6	738.5	719.6	701.4	688.7	664.2	647.6	632.5	616.8	596.2
7.5°	752.8	706.1	674.5	650.7	629.3	609.6	579.6	557.4	538.5	523.4	498.2
10°	705.3	651.6	612.0	585.9	563.8	535.3	506.0	481.5	461.0	444.4	419.9
12.5°	661.0	601.7	557.4	530.6	507.7	476.8	446.8	421.4	399.3	383.5	361.4
15°	619.9	557.4	510.0	483.1	459.4	428.5	398.5	373.2	352.6	336.1	316.3
17.5°	583.6	517.9	471.2	446.8	422.3	393.8	363.7	340.0	319.4	304.4	288.6
20°	559.0	496.5	451.5	428.5	407.3	380.3	356.6	337.6	317.9	306.0	296.5
22.5°	555.1	499.7	461.0	442.0	425.4	405.6	391.4	381.9	368.5	362.9	362.9
25°	563.0	515.6	484.7	469.7	456.2	445.2	438.0	431.7	427.0	427.7	427.7
27.5°	558.3	515.6	490.3	476.0	464.1	457.0	449.9	445.9	441.2	443.6	443.6
30°	527.4	486.3	465.0	449.9	438.8	432.6	422.3	417.4	412.0	412.7	410.3
32.5°	476.0	437.3	416.7	402.4	390.6	384.3	373.2	367.6	360.6	360.6	355.8
35°	415.9	379.6	360.6	347.9	336.8	330.5	320.2	314.7	307.6	303.7	301.3
37.5°	352.6	321.1	303.7	294.1	285.5	279.1	269.6	265.7	258.6	255.4	252.2
40°	294.1	271.2	254.6	246.7	239.6	234.0	225.4	222.2	215.8	213.5	210.4
42.5°	243.5	226.1	212.7	206.4	198.4	195.3	189.0	185.8	180.3	177.9	174.8
45°	203.2	189.0	177.9	172.4	167.7	163.7	157.4	155.0	149.5	147.1	145.5
47.5°	167.7	156.6	147.8	143.1	140.7	136.0	130.4	128.1	124.2	121.8	119.4
50°	137.5	128.9	121.8	117.8	116.2	111.5	106.8	105.1	101.2	99.7	97.2
52.5°	112.2	105.1	98.9	95.7	92.5	89.4	85.4	83.8	79.8	77.5	74.4
55°	90.1	83.0	77.5	75.1	73.6	68.8	64.8	62.4	59.3	55.3	53.0
57.5°	69.5	63.3	58.5	55.3	54.5	49.8	46.7	42.7	38.8	36.4	34.0
60°	51.4	45.9	41.1	38.0	37.1	32.4	28.5	26.1	22.9	21.4	20.6
62.5°	34.0	30.0	26.1	24.5	22.9	19.8	17.4	15.8	14.2	13.5	12.7
65°	21.4	18.2	15.8	15.0	13.5	11.8	11.1	10.3	9.5	8.7	7.9
67.5°	12.7	11.1	9.5	9.5	8.7	7.9	7.9	7.1	6.3	6.3	6.3
70°	7.9	7.1	6.3	6.3	6.3	6.3	6.3	5.6	5.6	5.6	5.6
72.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	4.7	4.7
75°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
77.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9
80°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
82.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.2	3.2	3.2
85°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	2.4
87.5°	3.2	3.2	3.2	3.2	3.2	2.4	2.4	2.4	2.4	2.4	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192179

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	869.7	869.7	869.7	869.7	869.7	869.7	869.7	869.7
2.5°	710.1	696.6	695.0	691.9	688.7	692.6	690.2	684.0
5°	589.0	572.5	569.3	564.5	559.8	561.4	557.4	551.9
7.5°	487.9	470.4	467.3	461.8	457.0	456.2	452.3	446.8
10°	405.6	392.2	389.0	383.5	377.9	377.1	372.4	368.5
12.5°	347.1	334.4	331.3	325.8	321.1	319.4	315.5	312.3
15°	303.7	291.7	288.6	283.8	278.4	278.4	275.2	272.0
17.5°	276.7	266.4	262.5	258.6	253.8	253.1	251.4	249.0
20°	287.8	278.4	276.7	272.0	272.8	272.8	271.2	270.4
22.5°	359.0	355.8	362.1	357.4	366.1	369.3	370.8	370.8
25°	430.9	431.7	438.0	435.6	443.6	449.9	453.0	450.7
27.5°	443.6	444.4	446.8	445.9	452.3	456.2	458.6	453.0
30°	407.3	406.4	405.6	404.9	408.8	410.3	411.2	405.6
32.5°	351.1	348.7	349.4	345.5	347.1	347.1	350.3	342.3
35°	294.9	291.7	291.7	287.8	287.8	287.8	290.2	282.3
37.5°	247.5	244.3	243.5	239.6	238.8	237.2	239.6	232.5
40°	206.4	203.2	204.0	199.3	200.1	199.3	199.3	195.3
42.5°	170.8	168.4	167.7	166.0	166.9	166.9	169.2	166.0
45°	141.5	139.2	138.4	137.5	138.4	138.4	139.2	136.0
47.5°	117.8	114.7	113.9	112.2	112.2	109.9	109.9	106.8
50°	94.8	90.1	89.4	87.0	86.2	84.6	84.6	82.2
52.5°	71.9	68.0	66.5	64.8	64.1	62.4	62.4	60.9
55°	50.6	46.7	45.9	45.1	44.2	43.5	44.2	42.7
57.5°	31.6	30.0	29.2	28.5	27.7	26.8	26.8	26.1
60°	18.9	17.4	17.4	16.6	15.8	15.0	15.0	15.0
62.5°	11.8	11.1	11.1	10.3	10.3	9.5	9.5	9.5
65°	7.9	7.1	7.1	6.3	6.3	5.6	5.6	5.6
67.5°	5.6	5.6	5.6	5.6	4.7	4.7	4.7	4.7
70°	5.6	4.7	4.7	4.7	4.7	4.7	4.7	4.7
72.5°	4.7	4.7	4.7	4.7	3.9	3.9	3.9	3.9
75°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
77.5°	3.9	3.9	3.9	3.9	3.2	3.2	3.2	3.2
80°	3.9	3.2	3.2	3.2	3.2	3.2	3.2	3.2
82.5°	3.2	3.2	3.2	3.2	3.2	2.4	2.4	2.4
85°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	1.5
87.5°	1.5	1.5	1.5	1.5	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)