

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192188

Luminaire Tested: **LDA6A40930D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192188
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26673)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40930D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3445.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.56 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192188

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192188

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	55	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	53466	53466	53466
5°	107055	50858	13636
10°	179545	43481	3730
15°	274179	32594	5420
20°	392833	23831	63781
25°	584024	39547	32712
30°	682618	17484	5083
35°	686383	3641	2690
40°	568329	2040	1560
45°	425416	1302	1233
50°	298139	930	708
55°	47931	717	564
60°	2927	735	460
65°	869	973	441
70°	545	1074	673
75°	339	1250	890
80°	253	1863	1326
85°	503	3711	1572



TEST NUMBER: P1192188

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.0	2.9
10°-20°	426.7	12.4
20°-30°	1026.6	29.8
30°-40°	1093.8	31.8
40°-50°	682.1	19.8
50°-60°	99.7	2.9
60°-70°	6.3	0.2
70°-80°	4.9	0.1
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1554.3	45.1
0°-40°	2648.2	76.9
0°-60°	3429.9	99.6
0°-90°	3445.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3445.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	975	975	975	975	975	
5°	1945	1560	924	460	248	225
15°	4831	2685	574	89	96	1433
25°	9655	3193	654	677	541	4351
35°	10256	2369	54	50	40	6188
45°	5487	693	17	19	16	4319
55°	502	12	8	8	6	887
65°	7	5	8	7	3	10
75°	2	3	6	6	4	2
85°	1	3	6	5	2	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192188

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3
2.5°	1450.7	1401.4	1418.0	1381.2	1367.8	1371.2	1344.4	1322.7	1310.9	1282.5	1253.1
5°	1945.4	1888.6	1905.3	1850.1	1815.7	1808.2	1766.3	1719.4	1677.6	1614.0	1560.4
7.5°	2545.7	2475.3	2487.0	2404.2	2334.7	2311.2	2247.7	2156.4	2071.9	1963.9	1860.9
10°	3225.4	3159.3	3156.0	3029.6	2910.6	2864.7	2771.7	2621.0	2477.1	2314.6	2145.5
12.5°	4026.6	3926.9	3910.2	3747.8	3570.3	3494.9	3365.2	3135.0	2907.4	2670.5	2426.8
15°	4831.0	4723.9	4697.1	4492.9	4245.0	4143.7	3970.5	3664.1	3350.1	3015.3	2684.6
17.5°	5688.2	5516.6	5371.8	5135.7	4849.4	4745.6	4521.2	4128.7	3733.6	3320.1	2878.0
20°	6733.7	6542.1	6338.6	5935.2	5410.3	5206.0	4959.9	4517.1	4024.0	3546.1	3021.1
22.5°	8166.9	7852.2	7420.2	6771.5	6049.9	5758.5	5378.4	4805.1	4247.5	3711.0	3116.6
25°	9655.3	9220.9	8746.2	7749.2	6635.0	6279.3	5779.4	5025.2	4425.0	3832.3	3192.8
27.5°	10512.5	10163.5	9625.1	8580.4	7109.6	6642.5	6066.6	5190.9	4538.0	3890.9	3214.5
30°	10783.7	10500.9	10011.9	8940.5	7268.7	6712.0	6093.4	5192.7	4483.6	3788.8	3088.9
32.5°	10670.8	10402.0	9861.2	8715.3	6977.4	6465.0	5864.8	4981.7	4215.7	3474.9	2766.6
35°	10256.3	9901.4	9244.3	7967.7	6481.8	5972.8	5412.0	4604.2	3803.8	3048.8	2369.0
37.5°	9326.3	8958.0	8210.5	7009.2	5843.1	5400.3	4949.1	4181.4	3389.5	2661.2	2022.5
40°	7941.7	7552.5	6938.0	6095.0	5154.1	4852.0	4471.0	3713.4	2950.9	2281.2	1701.8
42.5°	6544.6	6295.1	5931.0	5262.9	4607.5	4309.4	3939.4	3203.6	2528.9	1889.4	1292.5
45°	5487.3	5289.8	5047.8	4625.9	4007.3	3726.8	3382.8	2690.5	1971.5	1262.4	693.1
47.5°	4781.6	4540.5	4329.6	3859.1	3195.3	2854.6	2489.6	1773.0	1136.8	547.5	191.7
50°	3495.8	3205.4	3008.6	2481.2	1878.5	1594.8	1327.7	822.8	368.4	122.2	31.8
52.5°	1772.2	1552.9	1437.4	1085.8	717.4	536.6	394.3	169.9	72.8	24.3	18.4
55°	501.5	403.4	361.7	238.6	129.7	91.2	59.5	30.1	21.8	16.8	11.7
57.5°	51.9	44.3	41.9	34.4	27.7	25.9	23.5	18.4	14.2	11.7	7.5
60°	26.7	24.3	23.5	20.9	17.6	15.9	15.0	12.5	9.3	6.7	5.9
62.5°	14.2	13.4	11.7	10.9	9.3	9.3	8.3	6.7	5.9	5.9	5.0
65°	6.7	6.7	6.7	6.7	5.9	5.9	5.0	5.0	5.0	5.0	5.0
67.5°	5.0	5.0	5.0	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
70°	3.4	3.4	3.4	3.4	2.5	2.5	2.5	2.5	2.5	3.4	3.4
72.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	2.5	2.5	3.4	3.4
75°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	2.5	2.5	3.4	3.4
77.5°	0.8	0.8	1.6	1.6	1.6	1.6	1.6	2.5	2.5	3.4	3.4
80°	0.8	0.8	0.8	0.8	1.6	1.6	1.6	2.5	2.5	3.4	3.4
82.5°	0.8	0.8	0.8	0.8	1.6	1.6	1.6	2.5	2.5	3.4	3.4
85°	0.8	0.8	0.8	0.8	1.6	1.6	1.6	1.6	2.5	3.4	3.4
87.5°	0.0	0.0	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192188

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3
2.5°	1218.0	1197.1	1163.6	1130.1	1120.0	1092.5	1059.7	1021.3	985.3	956.9	929.2
5°	1474.2	1418.0	1355.3	1270.7	1240.6	1193.8	1123.4	1048.1	982.8	924.2	869.7
7.5°	1729.5	1624.0	1509.3	1387.1	1335.2	1265.7	1155.2	1048.9	951.8	865.5	784.4
10°	1955.5	1793.1	1631.6	1463.3	1390.5	1300.9	1153.6	1018.0	894.0	781.1	678.9
12.5°	2163.9	1939.6	1725.3	1509.3	1418.0	1310.1	1128.5	964.4	817.0	684.8	565.1
15°	2346.4	2057.7	1792.3	1531.1	1415.6	1291.7	1079.1	890.7	726.7	574.3	444.5
17.5°	2473.7	2124.6	1811.5	1508.5	1381.2	1238.9	1003.7	802.8	622.9	462.9	314.8
20°	2549.9	2142.2	1793.1	1459.1	1318.5	1171.2	933.4	730.0	555.0	408.5	284.6
22.5°	2591.8	2150.6	1779.7	1441.5	1298.4	1157.8	936.7	742.5	592.7	493.9	483.9
25°	2633.6	2177.3	1803.2	1461.6	1327.7	1197.1	986.1	787.8	685.6	653.8	664.6
27.5°	2631.1	2160.6	1781.4	1443.2	1314.2	1178.7	943.4	735.0	664.6	615.3	574.3
30°	2482.1	2001.5	1614.0	1254.9	1107.5	926.7	628.6	431.9	330.6	276.2	248.6
32.5°	2137.2	1632.4	1233.1	872.3	728.3	526.6	270.4	142.3	122.2	108.8	97.1
35°	1776.3	1300.0	928.4	550.0	365.8	200.1	92.9	60.3	56.1	54.4	53.6
37.5°	1464.9	1028.0	610.2	220.1	131.5	74.5	42.7	38.5	37.6	38.5	37.6
40°	1156.0	678.1	241.9	73.7	40.2	32.6	30.1	27.7	27.7	28.5	27.7
42.5°	692.3	252.8	73.7	27.7	25.9	23.5	22.6	21.8	20.9	21.8	21.8
45°	228.6	64.5	24.3	19.2	18.4	17.6	16.8	16.8	16.8	16.8	17.6
47.5°	51.9	22.6	16.8	14.2	14.2	13.4	13.4	12.5	13.4	13.4	14.2
50°	20.1	14.2	11.7	10.9	10.9	10.1	10.1	10.1	10.1	10.9	10.9
52.5°	12.5	10.1	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	9.3
55°	8.3	7.5	6.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5
57.5°	5.9	5.9	5.9	5.9	6.7	5.9	6.7	5.9	5.9	6.7	7.5
60°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.7	6.7	7.5
62.5°	5.0	5.9	5.9	5.9	5.9	5.9	5.9	6.7	6.7	6.7	7.5
65°	5.0	5.0	5.9	5.9	5.9	5.9	6.7	6.7	6.7	7.5	7.5
67.5°	4.2	5.0	5.0	5.9	5.9	5.9	5.9	6.7	6.7	6.7	7.5
70°	4.2	4.2	5.0	5.0	5.0	5.0	5.9	5.9	5.9	6.7	6.7
72.5°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9	6.7
75°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9	6.7
77.5°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9	6.7
80°	4.2	4.2	5.0	5.0	5.0	5.0	5.9	5.9	5.9	5.9	6.7
82.5°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9	5.9
85°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9
87.5°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192188

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3
2.5°	892.4	858.0	841.3	816.2	817.9	776.0	760.1	730.0	713.2	695.7	675.5
5°	803.6	743.3	700.6	667.2	648.8	594.4	557.5	509.8	460.4	412.7	373.3
7.5°	692.3	612.8	547.5	504.8	478.9	369.2	298.8	242.8	221.0	204.3	187.5
10°	568.4	469.6	354.1	295.5	259.5	207.6	186.7	154.8	132.3	111.3	98.8
12.5°	443.7	293.0	211.8	194.2	181.7	134.8	106.4	98.8	80.3	76.2	74.5
15°	278.8	192.6	149.9	128.9	112.1	93.7	86.2	85.4	88.8	89.6	88.8
17.5°	197.6	154.0	113.1	110.5	110.5	120.6	122.2	129.7	136.4	142.3	143.2
20°	253.7	227.6	265.4	282.1	311.4	347.4	400.2	473.8	538.3	603.5	653.8
22.5°	485.5	542.4	626.2	655.5	704.9	781.9	854.7	922.5	991.1	1042.3	1053.1
25°	714.1	753.4	802.8	791.9	807.0	802.8	761.7	706.5	677.2	623.7	605.3
27.5°	546.6	505.6	471.3	431.9	412.7	375.9	323.1	289.7	259.5	229.4	216.8
30°	222.7	195.0	175.0	160.7	152.3	132.3	122.2	111.3	106.4	98.8	94.6
32.5°	87.0	82.1	79.5	77.0	76.2	73.7	71.2	67.8	67.0	67.0	63.6
35°	51.9	51.9	51.9	51.0	51.9	51.0	50.2	49.4	50.2	50.2	47.7
37.5°	36.8	37.6	37.6	37.6	37.6	37.6	37.6	37.6	36.8	36.8	34.4
40°	27.7	28.5	29.3	28.5	29.3	29.3	28.5	27.7	27.7	27.7	25.9
42.5°	22.6	22.6	22.6	22.6	23.5	22.6	22.6	22.6	22.6	22.6	21.8
45°	18.4	18.4	18.4	18.4	19.2	19.2	18.4	18.4	19.2	19.2	18.4
47.5°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	13.4	13.4	13.4	12.5
50°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9	11.7	10.9	10.9
52.5°	9.3	9.3	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	9.3
55°	8.3	8.3	9.3	9.3	9.3	9.3	9.3	8.3	8.3	8.3	7.5
57.5°	7.5	8.3	8.3	8.3	8.3	8.3	8.3	8.3	7.5	7.5	6.7
60°	7.5	7.5	8.3	8.3	8.3	8.3	7.5	7.5	6.7	6.7	5.9
62.5°	7.5	7.5	8.3	8.3	8.3	7.5	7.5	6.7	6.7	5.9	5.9
65°	7.5	8.3	8.3	8.3	8.3	7.5	7.5	6.7	6.7	5.9	5.9
67.5°	7.5	8.3	8.3	8.3	8.3	7.5	7.5	6.7	6.7	5.9	5.9
70°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.9	5.9
72.5°	6.7	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.9	5.9
75°	6.7	6.7	6.7	6.7	7.5	6.7	6.7	6.7	5.9	5.9	5.0
77.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.0
80°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.0	5.0
82.5°	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.0	5.0	5.0
85°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.0	5.0	4.2	4.2
87.5°	5.9	5.9	5.9	5.9	5.9	5.0	5.0	4.2	3.4	3.4	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192188

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	975.3	975.3	975.3	975.3	975.3	975.3	975.3	975.3
2.5°	653.8	639.5	636.2	636.2	628.6	613.6	611.1	606.1
5°	330.6	295.5	288.9	281.2	268.7	253.7	249.5	247.8
7.5°	170.8	155.7	153.2	148.1	140.6	133.1	131.5	130.5
10°	100.5	91.2	87.0	79.5	72.0	67.8	67.8	67.0
12.5°	74.5	74.5	74.5	74.5	74.5	74.5	74.5	74.5
15°	90.4	92.9	92.9	93.7	94.6	95.5	97.1	95.5
17.5°	152.3	164.9	164.1	165.7	171.6	179.1	175.8	180.0
20°	740.0	836.3	863.9	891.6	975.3	1053.9	1038.0	1093.3
22.5°	1063.1	1092.5	1080.7	1073.2	1090.8	1081.6	1121.0	1094.9
25°	570.1	564.2	564.2	539.1	544.2	531.6	548.3	540.8
27.5°	210.2	191.7	190.0	178.3	185.9	168.3	173.3	169.9
30°	90.4	91.2	87.8	85.4	82.9	81.2	81.2	80.3
32.5°	61.9	61.9	60.3	58.6	56.9	55.2	54.4	53.6
35°	46.1	46.1	44.3	43.5	42.7	41.0	40.2	40.2
37.5°	33.5	33.5	32.6	31.8	30.1	29.3	28.5	28.5
40°	25.9	25.1	24.3	24.3	22.6	22.6	21.8	21.8
42.5°	20.9	20.9	20.9	20.1	19.2	18.4	18.4	18.4
45°	18.4	18.4	17.6	16.8	16.8	16.8	15.9	15.9
47.5°	12.5	12.5	11.7	11.7	10.9	10.9	10.1	10.1
50°	10.1	10.1	10.1	10.1	9.3	8.3	8.3	8.3
52.5°	9.3	8.3	8.3	8.3	7.5	7.5	6.7	6.7
55°	7.5	7.5	6.7	6.7	5.9	5.9	5.9	5.9
57.5°	6.7	5.9	5.9	5.9	5.0	5.0	5.0	5.0
60°	5.9	5.0	5.0	5.0	4.2	4.2	4.2	4.2
62.5°	5.0	5.0	5.0	5.0	4.2	4.2	4.2	4.2
65°	5.0	5.0	5.0	4.2	4.2	4.2	4.2	3.4
67.5°	5.0	5.0	5.0	5.0	4.2	4.2	4.2	4.2
70°	5.0	5.0	5.0	5.0	4.2	4.2	4.2	4.2
72.5°	5.0	5.0	5.0	5.0	4.2	4.2	4.2	4.2
75°	5.0	5.0	5.0	5.0	4.2	4.2	4.2	4.2
77.5°	5.0	4.2	4.2	4.2	4.2	4.2	4.2	4.2
80°	5.0	4.2	4.2	4.2	4.2	3.4	3.4	4.2
82.5°	4.2	4.2	4.2	4.2	3.4	3.4	3.4	3.4
85°	3.4	3.4	3.4	3.4	2.5	2.5	2.5	2.5
87.5°	2.5	1.6	1.6	1.6	1.6	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)