

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192191

Luminaire Tested: **LDA6A40930D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26671)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40930D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4075.4 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 2.69 / 0.5 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192191

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192191

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	101		102	100	98		99	97	95		95	94	93
2	105	99	94	89	102	97	92	88		94	90	86		91	87	85		88	85	83
3	98	89	83	78	95	88	82	78		85	80	76		83	79	75		80	77	74
4	91	81	74	69	89	80	73	68		78	72	68		75	71	67		73	69	66
5	84	74	66	61	82	73	66	61		71	65	60		69	64	59		67	63	59
6	78	67	60	54	77	66	59	54		65	58	53		63	57	53		62	57	53
7	73	61	54	48	71	60	53	48		59	53	48		58	52	48		56	51	47
8	68	56	48	43	66	55	48	43		54	48	43		53	47	43		52	46	42
9	63	51	44	39	62	51	44	39		50	43	39		49	43	39		48	42	38
10	59	47	40	35	58	47	40	35		46	39	35		45	39	35		44	39	35

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	34241	34241	34241
5°	90254	31191	10731
10°	182361	24281	6524
15°	335796	18195	9404
20°	520606	14555	15681
25°	611237	12914	19906
30°	662779	12983	15420
35°	698851	7730	8298
40°	716814	3299	3592
45°	671535	1302	1233
50°	469545	571	290
55°	164764	564	0
60°	33221	647	0
65°	2062	765	0
70°	401	1074	0
75°	0	1419	0
80°	0	2115	253
85°	0	4717	503

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P1192191

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.1	2.0
10°-20°	446.8	11.0
20°-30°	1056.2	25.9
30°-40°	1286.7	31.6
40°-50°	957.1	23.5
50°-60°	231.7	5.7
60°-70°	8.6	0.2
70°-80°	4.2	0.1
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1583.1	38.8
0°-40°	2869.8	70.4
0°-60°	4058.6	99.6
0°-90°	4075.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4075.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	625	625	625	625	625	
5°	1640	1226	567	265	195	206
15°	5917	2564	321	147	166	1783
25°	10105	3216	214	310	329	4640
35°	10443	2348	116	126	124	6504
45°	8662	895	17	18	16	6362
55°	1724	19	6	4	0	1950
65°	16	4	6	4	0	53
75°	0	4	7	5	0	0
85°	0	4	8	5	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192191

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6
2.5°	1089.3	1070.9	1069.1	1050.7	1044.0	1041.5	1015.5	1006.4	972.0	965.3	916.8
5°	1640.1	1611.6	1605.8	1563.9	1532.9	1490.2	1467.6	1429.1	1347.9	1305.2	1226.5
7.5°	2333.4	2295.7	2287.3	2221.9	2157.6	2101.4	2054.6	1965.0	1815.9	1713.8	1553.0
10°	3276.0	3170.6	3132.0	2993.9	2860.8	2756.1	2701.7	2504.9	2280.6	2143.3	1918.9
12.5°	4473.3	4297.4	4225.4	4012.0	3777.5	3605.9	3500.4	3191.5	2826.5	2563.6	2242.9
15°	5916.7	5712.4	5583.5	5314.7	4888.5	4644.1	4457.4	3962.6	3430.1	3032.4	2564.4
17.5°	7488.1	7328.2	7135.6	6714.5	6028.0	5734.2	5395.0	4746.2	4016.2	3462.7	2851.6
20°	8923.9	8656.0	8511.2	8042.3	7246.9	6859.3	6441.6	5469.6	4534.4	3813.5	3071.7
22.5°	9701.7	9442.1	9355.1	8948.2	8219.0	7787.8	7256.2	6106.6	4932.1	4053.8	3189.0
25°	10105.2	9868.3	9874.2	9506.6	8848.6	8443.4	7902.5	6588.1	5203.4	4180.2	3215.8
27.5°	10420.9	10129.5	10078.5	9803.8	9218.6	8804.3	8282.6	6850.2	5302.9	4166.9	3142.9
30°	10470.3	10231.7	10268.5	9886.7	9352.5	8921.4	8378.9	6835.9	5200.8	3998.6	2953.7
32.5°	10436.8	10199.9	10284.4	9870.0	9294.8	8821.7	8218.1	6557.9	4901.1	3687.1	2675.8
35°	10442.6	10170.5	10107.8	9757.0	9072.1	8517.0	7788.6	6050.6	4458.2	3281.9	2348.4
37.5°	10318.0	9951.2	9962.1	9500.0	8641.8	7905.9	7081.2	5374.1	3934.1	2849.0	2019.4
40°	10016.6	9741.9	9654.9	8968.3	7823.0	6960.7	6165.3	4639.0	3328.0	2396.9	1633.4
42.5°	9587.0	9256.4	9000.9	8049.9	6662.7	5871.4	5184.0	3873.0	2755.3	1965.0	1268.4
45°	8661.9	8304.4	7809.6	6668.4	5493.9	4807.3	4233.8	3143.7	2228.6	1518.7	895.0
47.5°	7106.3	6770.6	6261.6	5302.9	4386.2	3814.3	3367.3	2462.2	1629.2	957.8	443.8
50°	5505.6	5250.2	4861.7	4029.5	3263.5	2728.5	2330.0	1546.3	831.4	437.0	185.9
52.5°	3588.3	3407.5	3061.8	2428.8	1844.4	1445.9	1175.5	658.0	391.8	184.2	54.4
55°	1723.9	1630.0	1379.8	1000.5	724.2	594.5	502.3	319.0	148.2	44.3	19.2
57.5°	687.4	667.3	594.5	447.9	343.3	291.3	226.0	88.0	29.3	18.4	11.7
60°	303.0	293.9	246.2	163.3	88.0	50.2	36.8	21.8	14.2	10.9	7.5
62.5°	43.5	40.2	34.4	26.7	21.8	18.4	15.9	11.7	7.5	5.9	5.0
65°	15.9	15.9	14.2	11.7	10.1	9.3	8.3	5.9	4.2	4.2	4.2
67.5°	6.7	6.7	6.7	5.0	5.0	4.2	3.4	3.4	3.4	3.4	4.2
70°	2.5	2.5	2.5	1.6	1.6	1.6	2.5	2.5	2.5	3.4	4.2
72.5°	0.0	0.8	0.8	0.8	1.6	1.6	1.6	2.5	2.5	3.4	4.2
75°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	2.5	3.4	4.2
77.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
80°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
82.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	4.2	4.2
85°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	4.2
87.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192191

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6
2.5°	875.7	864.0	824.7	785.3	779.4	762.7	728.4	688.2	636.2	603.6	571.0
5°	1124.3	1065.8	999.7	923.4	900.0	866.6	794.6	717.5	631.3	566.8	506.5
7.5°	1414.9	1284.3	1159.5	1037.3	991.2	939.4	829.7	719.1	601.2	507.3	432.0
10°	1687.0	1486.0	1292.6	1119.4	1050.7	980.4	833.0	690.8	544.2	436.2	359.2
12.5°	1958.3	1670.3	1405.7	1178.8	1085.9	995.5	814.6	639.6	473.9	370.8	308.9
15°	2171.7	1836.9	1487.8	1208.9	1093.4	982.9	769.5	569.3	405.2	320.6	265.4
17.5°	2320.0	1932.3	1518.7	1196.4	1064.1	939.4	698.3	487.3	350.0	281.3	227.7
20°	2422.1	1962.4	1496.9	1144.5	1001.3	864.0	608.7	413.6	310.6	249.5	195.9
22.5°	2450.5	1933.1	1435.0	1066.6	919.2	777.8	515.7	365.1	282.2	224.4	190.1
25°	2423.0	1858.6	1342.0	973.6	818.8	670.6	437.9	335.8	260.4	213.5	221.1
27.5°	2322.4	1727.2	1213.1	854.0	694.9	555.1	385.1	300.6	229.4	225.2	234.4
30°	2156.7	1538.8	1060.0	700.7	549.2	442.8	323.2	236.9	200.9	205.1	211.0
32.5°	1918.1	1307.8	863.2	519.1	402.7	333.2	231.0	164.1	159.0	162.4	166.6
35°	1616.7	1064.1	646.3	358.3	285.5	229.4	135.6	116.3	113.9	115.5	117.2
37.5°	1311.9	822.1	439.6	241.1	173.3	116.3	81.2	76.2	74.5	75.3	76.2
40°	1018.1	571.8	276.3	115.5	67.8	57.8	50.2	47.7	46.1	46.1	46.9
42.5°	743.4	339.1	137.3	45.2	36.8	34.4	30.1	28.5	26.7	27.7	28.5
45°	416.1	150.7	46.9	25.1	22.6	20.9	18.4	17.6	16.8	16.8	16.8
47.5°	177.4	52.8	22.6	15.9	14.2	13.4	11.7	10.9	10.1	10.1	10.1
50°	58.6	20.9	14.2	10.9	9.3	8.3	7.5	6.7	6.7	6.7	7.5
52.5°	20.9	13.4	9.3	7.5	6.7	6.7	5.9	5.9	5.9	5.9	5.9
55°	12.5	9.3	6.7	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
57.5°	8.3	5.9	5.9	5.0	5.0	5.0	5.0	5.0	5.0	5.9	5.9
60°	5.9	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.9	5.9
62.5°	5.0	4.2	4.2	5.0	5.0	5.0	5.0	5.9	5.9	5.9	5.9
65°	4.2	4.2	4.2	5.0	5.0	5.0	5.0	5.9	5.9	5.9	5.9
67.5°	4.2	4.2	5.0	5.0	5.0	5.0	5.9	5.9	5.9	5.9	6.7
70°	4.2	4.2	5.0	5.0	5.0	5.9	5.9	5.9	5.9	6.7	6.7
72.5°	4.2	5.0	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7	6.7
75°	4.2	5.0	5.0	5.9	5.9	5.9	5.9	6.7	6.7	6.7	6.7
77.5°	4.2	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7	6.7	6.7
80°	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7	6.7	6.7	7.5
82.5°	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7	6.7	6.7	7.5
85°	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7	6.7	7.5	7.5
87.5°	5.0	5.0	5.9	5.9	5.9	6.7	6.7	6.7	6.7	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192191

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6
2.5°	537.5	512.4	477.2	465.5	441.2	423.6	404.4	382.6	378.5	356.6	354.2
5°	447.9	407.8	367.5	352.4	331.5	314.0	294.7	273.7	264.6	243.6	231.0
7.5°	369.2	330.7	294.7	279.6	259.5	236.9	214.4	192.6	180.0	160.0	149.9
10°	309.7	271.3	232.8	217.7	199.3	174.2	149.9	127.2	118.9	113.9	114.7
12.5°	258.7	220.2	181.7	164.9	145.7	125.6	124.8	123.0	126.4	125.6	126.4
15°	216.8	175.8	139.0	133.9	133.9	137.3	140.6	141.4	147.3	147.3	149.1
17.5°	178.4	149.9	151.5	151.5	154.9	160.8	167.5	170.8	180.0	180.8	184.2
20°	165.7	172.5	180.0	181.7	187.5	196.8	205.9	212.6	224.4	227.7	234.4
22.5°	196.8	208.5	220.2	223.5	231.0	244.5	261.2	267.0	281.3	281.3	290.5
25°	231.9	249.5	261.2	265.4	273.7	285.5	296.4	299.8	309.7	306.4	309.7
27.5°	246.2	258.7	266.2	270.4	272.1	282.2	287.2	285.5	292.1	287.2	287.2
30°	218.5	227.7	231.9	234.4	234.4	241.9	241.9	239.5	243.6	239.5	236.9
32.5°	171.6	178.4	181.7	181.7	180.8	185.9	184.2	180.8	182.5	180.0	174.2
35°	119.7	124.8	127.2	126.4	125.6	129.8	127.2	124.8	125.6	124.0	119.7
37.5°	78.7	79.5	81.2	82.9	82.1	85.4	83.7	82.1	82.9	81.2	78.7
40°	47.7	49.4	51.0	51.0	51.0	51.9	51.9	51.0	52.8	51.0	49.4
42.5°	28.5	30.1	30.1	30.1	31.0	31.0	31.8	30.1	31.8	30.1	29.3
45°	17.6	17.6	17.6	18.4	17.6	18.4	18.4	17.6	18.4	17.6	16.8
47.5°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.1	10.9	10.1	9.3
50°	6.7	7.5	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.0	5.0
52.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.0	5.0	4.2	3.4	3.4
55°	5.9	5.9	5.9	5.0	5.0	5.0	5.0	4.2	4.2	3.4	2.5
57.5°	5.9	5.9	5.0	5.0	5.0	5.0	4.2	4.2	3.4	2.5	2.5
60°	5.9	5.9	5.9	5.0	5.0	5.0	4.2	4.2	3.4	2.5	2.5
62.5°	5.9	5.9	5.9	5.0	5.0	5.0	5.0	4.2	3.4	2.5	2.5
65°	5.9	5.9	5.9	5.9	5.9	5.0	5.0	4.2	4.2	3.4	2.5
67.5°	6.7	5.9	5.9	5.9	5.9	5.9	5.0	4.2	4.2	3.4	2.5
70°	6.7	6.7	5.9	5.9	5.9	5.9	5.0	5.0	4.2	3.4	2.5
72.5°	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.0	4.2	3.4	3.4
75°	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.0	5.0	4.2	3.4
77.5°	7.5	6.7	6.7	6.7	6.7	6.7	5.9	5.0	5.0	4.2	3.4
80°	7.5	7.5	6.7	6.7	6.7	6.7	5.9	5.0	5.0	4.2	3.4
82.5°	7.5	7.5	6.7	6.7	6.7	6.7	5.9	5.9	5.0	4.2	3.4
85°	7.5	7.5	6.7	6.7	6.7	6.7	5.9	5.0	5.0	4.2	3.4
87.5°	7.5	7.5	6.7	6.7	6.7	6.7	5.9	5.0	5.0	4.2	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192191

CATALOG NUMBER: LDA6A40930D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	624.6	624.6	624.6	624.6	624.6	624.6	624.6	624.6
2.5°	339.1	337.4	331.5	333.2	329.1	319.8	320.6	317.3
5°	222.7	217.7	211.8	211.8	205.9	197.6	197.6	195.0
7.5°	135.6	128.1	122.2	121.4	115.5	111.3	111.3	110.5
10°	114.7	115.5	115.5	116.3	115.5	115.5	116.3	117.2
12.5°	128.9	131.5	131.5	132.3	131.5	133.1	133.1	134.8
15°	154.1	158.2	159.0	160.8	160.0	162.4	164.1	165.7
17.5°	193.4	198.4	200.1	205.1	204.3	206.8	208.5	211.8
20°	243.6	251.2	253.7	260.4	259.5	262.0	266.2	268.8
22.5°	299.8	308.9	309.7	315.6	314.8	317.3	319.0	319.8
25°	314.8	320.6	319.8	323.2	323.2	324.0	324.0	329.1
27.5°	288.0	292.1	292.1	292.1	293.1	293.9	293.9	298.0
30°	236.9	238.7	239.5	236.9	238.7	239.5	239.5	243.6
32.5°	175.8	176.6	177.4	174.2	176.6	176.6	176.6	180.0
35°	121.4	121.4	122.2	119.7	121.4	122.2	121.4	124.0
37.5°	79.5	79.5	79.5	79.5	79.5	79.5	78.7	81.2
40°	49.4	50.2	49.4	49.4	48.6	48.6	48.6	50.2
42.5°	29.3	29.3	28.5	28.5	28.5	28.5	29.3	29.3
45°	16.8	16.8	15.9	15.9	15.0	15.9	15.9	15.9
47.5°	9.3	8.3	8.3	8.3	7.5	7.5	7.5	8.3
50°	4.2	4.2	4.2	3.4	3.4	3.4	2.5	3.4
52.5°	2.5	1.6	1.6	1.6	0.8	0.8	0.0	0.8
55°	1.6	1.6	0.8	0.8	0.0	0.0	0.0	0.0
57.5°	1.6	0.8	0.8	0.8	0.0	0.0	0.0	0.0
60°	1.6	0.8	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.6	0.8	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.6	0.8	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	1.6	1.6	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.5	1.6	1.6	0.8	0.8	0.0	0.0	0.0
72.5°	2.5	1.6	1.6	1.6	0.8	0.8	0.0	0.0
75°	2.5	1.6	1.6	1.6	0.8	0.8	0.0	0.0
77.5°	2.5	2.5	1.6	1.6	0.8	0.8	0.8	0.8
80°	2.5	2.5	1.6	1.6	1.6	0.8	0.8	0.8
82.5°	2.5	2.5	1.6	1.6	1.6	0.8	0.8	0.8
85°	2.5	2.5	1.6	1.6	1.6	0.8	0.8	0.8
87.5°	2.5	2.5	1.6	1.6	1.6	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)