

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192219

Luminaire Tested: **LDA6A40935D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26669)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40935D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3336.8 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 2.14 / 1.07 / 1.49
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192219

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192219

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	100	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62		
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55		
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49		
7	72	59	52	46	70	59	51	46	57	51	46	56	50	45	55	49	45	43		
8	67	54	47	41	65	54	46	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	37	33	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	58586	58586	58586
5°	93781	57853	37514
10°	137033	55560	25283
15°	187351	52690	19098
20°	234386	49885	19275
25°	270754	49721	29899
30°	296590	47064	27808
35°	306267	39900	21462
40°	299740	31130	16903
45°	273230	22979	12978
50°	219609	16946	8691
55°	133720	11995	4913
60°	69380	7927	1908
65°	33817	4190	908
70°	15515	1811	833
75°	6481	1292	911
80°	3315	1357	1105
85°	2201	2705	1635

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192219

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.6	3.3
10°-20°	388.4	11.6
20°-30°	735.3	22.0
30°-40°	890.5	26.7
40°-50°	745.3	22.3
50°-60°	361.2	10.8
60°-70°	88.6	2.7
70°-80°	14.4	0.4
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1233.3	37.0
0°-40°	2123.8	63.6
0°-60°	3230.3	96.8
0°-90°	3336.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3336.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1069	1069	1069	1069	1069	
5°	1704	1468	1051	769	682	186
15°	3301	2295	928	424	336	953
25°	4476	2704	822	484	494	2062
35°	4576	2389	596	344	321	2836
45°	3524	1612	296	180	167	2674
55°	1399	661	126	68	51	1311
65°	261	145	32	10	7	294
75°	31	16	6	5	4	41
85°	4	3	4	4	3	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192219

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7
2.5°	1356.4	1324.9	1331.9	1337.2	1313.6	1328.4	1303.2	1294.5	1273.5	1278.8	1263.1
5°	1704.2	1660.6	1647.5	1647.5	1608.2	1621.4	1598.7	1558.6	1517.6	1505.5	1467.9
7.5°	2078.1	2030.2	2009.3	2000.6	1943.0	1935.2	1916.0	1854.1	1787.0	1751.2	1685.0
10°	2461.7	2418.1	2388.5	2368.4	2289.1	2275.1	2241.2	2154.0	2069.4	1992.8	1883.7
12.5°	2884.4	2826.1	2786.8	2753.7	2651.7	2629.9	2579.3	2462.6	2329.1	2236.8	2093.0
15°	3301.1	3241.9	3190.4	3142.5	3018.7	2987.3	2919.3	2771.2	2615.1	2477.4	2295.2
17.5°	3697.8	3622.8	3560.1	3495.6	3349.9	3310.7	3221.8	3057.0	2839.2	2683.1	2463.4
20°	4017.7	3944.5	3872.1	3790.2	3623.6	3576.6	3468.5	3273.3	3025.7	2838.2	2582.0
22.5°	4279.2	4196.4	4124.9	4017.7	3830.3	3775.4	3650.7	3429.3	3161.6	2942.8	2661.3
25°	4476.2	4388.1	4314.9	4194.6	3987.2	3923.5	3777.9	3538.2	3246.2	3005.6	2704.0
27.5°	4631.3	4530.2	4447.4	4314.1	4085.7	4014.2	3854.7	3595.7	3280.3	3017.8	2702.2
30°	4685.4	4586.9	4493.6	4349.8	4103.9	4024.6	3859.0	3578.4	3249.7	2967.2	2642.2
32.5°	4661.9	4559.8	4458.7	4306.2	4046.4	3961.0	3793.7	3493.8	3156.4	2859.2	2531.4
35°	4576.4	4472.7	4364.6	4206.8	3934.9	3842.4	3675.1	3364.8	3014.3	2717.0	2389.3
37.5°	4421.3	4317.6	4215.5	4045.6	3767.5	3671.6	3506.9	3185.2	2843.5	2543.6	2224.6
40°	4188.5	4085.7	3991.5	3819.8	3540.0	3443.2	3287.1	2968.2	2638.7	2342.3	2035.4
42.5°	3888.6	3790.2	3705.6	3537.3	3263.7	3171.2	3024.8	2716.2	2408.5	2121.8	1833.2
45°	3524.3	3434.5	3356.9	3198.3	2945.5	2856.5	2726.7	2434.7	2147.9	1879.4	1611.7
47.5°	3104.1	3022.2	2954.2	2807.8	2573.2	2492.2	2380.6	2109.5	1853.3	1608.2	1370.3
50°	2575.0	2503.5	2456.5	2330.1	2120.8	2052.8	1966.5	1738.2	1528.1	1317.1	1120.1
52.5°	1964.8	1909.0	1887.2	1792.2	1630.0	1583.0	1527.2	1352.0	1198.6	1032.1	878.7
55°	1399.1	1362.5	1348.5	1286.7	1180.3	1149.8	1101.8	993.7	891.8	774.1	660.7
57.5°	952.8	933.6	923.1	884.8	819.4	798.5	771.4	701.8	636.3	559.6	478.5
60°	632.8	625.0	616.3	592.7	554.4	538.7	525.7	479.5	439.3	391.4	334.7
62.5°	410.5	407.0	401.0	386.2	371.4	360.9	347.0	316.4	292.9	268.5	225.8
65°	260.7	257.2	254.5	244.9	235.4	224.9	219.6	202.2	187.4	171.7	144.7
67.5°	161.3	158.6	157.8	151.6	144.7	138.6	135.1	123.8	115.1	105.4	88.1
70°	96.8	95.9	94.1	90.6	86.3	82.0	80.2	72.3	67.1	61.0	49.7
72.5°	55.8	54.9	54.0	51.4	48.9	47.1	45.4	42.7	36.6	33.1	27.9
75°	30.6	30.6	29.6	27.9	27.1	25.3	24.4	22.6	20.1	18.3	15.7
77.5°	17.4	16.6	16.6	15.7	14.8	14.8	14.0	13.1	11.3	11.3	9.6
80°	10.5	10.5	10.5	9.6	9.6	9.6	8.7	8.7	7.8	7.0	7.0
82.5°	7.0	6.1	6.1	6.1	6.1	6.1	5.2	5.2	5.2	5.2	4.3
85°	3.5	3.5	3.5	3.5	2.6	3.5	2.6	2.6	2.6	2.6	2.6
87.5°	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192219

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7
2.5°	1222.2	1213.4	1195.9	1171.6	1162.8	1157.6	1128.9	1102.7	1084.4	1060.9	1038.2
5°	1399.9	1367.7	1325.9	1275.3	1255.3	1237.8	1184.6	1135.9	1095.7	1051.3	1009.4
7.5°	1583.9	1523.8	1453.1	1373.0	1339.8	1309.3	1229.1	1156.7	1094.8	1031.3	971.1
10°	1756.5	1664.9	1563.0	1455.8	1406.1	1361.6	1255.3	1162.0	1080.0	998.1	924.0
12.5°	1925.6	1800.9	1665.8	1528.1	1463.6	1406.1	1274.4	1160.2	1059.1	963.3	877.8
15°	2088.6	1927.3	1760.8	1591.7	1514.1	1443.5	1287.5	1154.2	1037.3	928.4	833.3
17.5°	2220.2	2030.2	1828.8	1630.0	1542.9	1460.9	1285.7	1136.7	1007.7	889.1	788.0
20°	2312.6	2093.8	1869.8	1647.5	1552.5	1461.9	1272.7	1113.1	977.1	855.1	753.2
22.5°	2364.9	2123.5	1883.7	1647.5	1545.5	1450.5	1254.4	1091.3	954.5	835.1	737.5
25°	2386.7	2128.6	1877.6	1633.5	1528.1	1430.5	1233.5	1070.4	936.2	822.0	731.4
27.5°	2369.3	2098.2	1843.6	1595.2	1487.2	1389.5	1193.4	1033.8	904.0	795.0	708.7
30°	2299.5	2021.5	1767.8	1521.1	1412.2	1317.1	1127.1	972.8	848.1	743.5	661.6
32.5°	2186.3	1909.8	1660.6	1420.0	1311.9	1220.4	1039.1	892.6	773.2	673.8	598.0
35°	2048.5	1777.4	1536.8	1302.3	1198.6	1111.4	940.5	797.6	687.8	596.2	526.5
37.5°	1893.3	1631.0	1392.9	1177.6	1078.3	995.5	836.0	701.8	600.6	516.1	454.2
40°	1719.0	1471.4	1247.4	1043.4	949.3	872.5	721.7	603.2	510.8	435.0	382.7
42.5°	1535.1	1304.1	1095.7	904.8	815.9	746.2	609.3	503.8	422.8	360.9	319.0
45°	1338.1	1124.4	933.6	762.8	688.6	619.0	502.9	407.0	343.5	296.4	265.0
47.5°	1127.9	938.8	770.6	621.5	557.0	496.0	398.4	325.2	279.0	243.2	219.6
50°	917.1	757.5	614.5	487.3	432.4	383.6	308.6	258.9	224.9	198.7	179.6
52.5°	716.6	587.5	470.7	367.0	326.0	291.1	239.7	204.8	179.6	159.5	145.6
55°	537.8	435.9	344.3	266.7	242.4	220.5	186.5	158.6	141.2	125.5	115.1
57.5°	389.7	311.2	244.9	196.2	180.4	165.6	141.2	122.0	108.9	96.8	88.9
60°	273.7	216.2	173.4	143.8	131.7	122.9	103.7	91.6	81.1	72.3	64.5
62.5°	183.9	146.5	121.2	101.9	94.1	88.1	75.8	65.4	57.5	50.5	43.6
65°	117.7	98.5	82.0	68.8	63.7	59.3	51.4	42.7	37.4	32.3	27.1
67.5°	72.3	61.9	51.4	42.7	39.2	36.6	31.4	26.1	22.6	19.1	16.6
70°	41.9	35.7	29.6	25.3	23.6	21.8	18.3	15.7	14.0	11.3	9.6
72.5°	23.6	20.9	17.4	14.8	14.0	13.1	11.3	9.6	8.7	7.8	7.0
75°	14.0	12.2	10.5	9.6	8.7	8.7	7.8	7.0	6.1	6.1	5.2
77.5°	8.7	7.8	7.0	7.0	6.1	6.1	6.1	5.2	5.2	5.2	5.2
80°	6.1	6.1	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3	4.3
82.5°	4.3	4.3	4.3	3.5	3.5	3.5	3.5	3.5	4.3	4.3	4.3
85°	2.6	2.6	3.5	3.5	3.5	3.5	3.5	3.5	4.3	4.3	4.3
87.5°	2.6	2.6	2.6	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192219

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7
2.5°	1013.8	1003.4	984.1	966.8	964.1	939.7	914.4	909.1	900.5	886.5	870.0
5°	967.6	939.7	906.6	882.2	871.7	836.8	802.0	786.3	768.8	741.8	726.1
7.5°	913.6	872.5	826.3	798.5	783.6	740.0	700.0	677.3	653.7	625.0	605.8
10°	854.2	802.9	748.8	717.4	700.0	652.9	610.2	584.1	558.8	530.0	509.9
12.5°	798.5	740.0	680.8	647.7	628.5	579.7	536.0	508.2	483.0	459.4	435.9
15°	748.8	683.5	621.5	588.4	568.3	518.7	476.8	448.9	424.5	401.9	380.9
17.5°	700.8	632.8	571.8	539.5	519.5	473.3	433.3	408.0	384.4	363.5	345.2
20°	667.7	603.2	545.7	515.2	497.8	456.7	422.8	402.7	386.2	367.9	352.1
22.5°	659.0	601.5	551.8	526.5	513.4	481.2	456.7	444.6	439.3	428.0	419.3
25°	659.0	608.5	566.6	545.7	535.2	510.8	491.6	487.3	483.8	476.8	472.5
27.5°	642.4	595.4	557.9	539.5	530.9	509.1	492.5	487.3	483.0	477.7	472.5
30°	598.9	555.3	520.4	503.8	495.1	474.2	456.7	450.7	446.3	438.4	434.1
32.5°	540.5	498.6	469.8	450.7	442.8	422.8	406.2	399.2	395.7	388.7	380.9
35°	475.0	438.4	410.5	394.9	387.0	369.6	354.8	347.8	344.3	336.5	326.9
37.5°	408.8	375.7	353.0	338.2	332.2	318.2	305.1	299.9	296.4	290.3	282.5
40°	343.5	319.9	299.9	288.5	283.3	272.0	260.7	255.4	252.7	247.6	241.4
42.5°	289.4	270.2	254.5	244.9	240.6	231.9	222.3	217.1	214.5	209.2	204.8
45°	242.4	227.5	215.3	206.6	203.1	195.2	187.4	183.1	180.4	176.1	171.7
47.5°	203.1	190.0	179.6	173.4	169.9	163.9	156.9	152.6	150.8	147.3	143.0
50°	166.5	156.9	148.2	143.0	140.3	134.2	128.2	124.7	122.9	119.4	115.1
52.5°	134.2	127.2	119.4	114.2	111.6	107.2	101.1	97.6	95.0	91.6	86.3
55°	105.4	99.4	93.3	88.1	86.3	81.1	75.8	70.6	68.0	64.5	60.2
57.5°	82.0	75.0	68.8	64.5	62.7	57.5	52.3	47.1	44.4	40.1	37.4
60°	58.4	52.3	46.2	43.6	41.9	36.6	32.3	27.9	26.1	23.6	21.8
62.5°	38.4	33.9	28.8	26.1	25.3	21.8	18.3	17.4	15.7	14.8	14.0
65°	23.6	20.9	17.4	15.7	14.8	14.0	12.2	11.3	10.5	9.6	9.6
67.5°	14.0	13.1	11.3	10.5	9.6	8.7	8.7	7.8	7.8	7.0	7.0
70°	9.6	8.7	7.8	7.0	7.0	7.0	7.0	7.0	7.0	6.1	6.1
72.5°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
75°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
77.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	4.3	4.3
80°	4.3	5.2	5.2	5.2	5.2	4.3	4.3	4.3	4.3	4.3	4.3
82.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
85°	4.3	4.3	4.3	4.3	4.3	3.5	3.5	3.5	3.5	3.5	2.6
87.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	2.6	2.6	2.6	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192219

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7	1068.7
2.5°	868.2	860.4	852.6	864.7	863.9	851.6	860.4	846.4
5°	717.4	706.1	697.3	705.2	700.8	688.6	693.8	681.7
7.5°	594.5	581.4	570.9	577.1	570.1	558.8	557.0	551.8
10°	496.9	483.0	473.3	477.7	470.7	460.2	457.7	454.2
12.5°	422.8	409.7	401.0	404.5	397.5	387.9	386.2	388.7
15°	365.3	355.6	348.7	351.3	341.7	336.5	334.7	336.5
17.5°	332.2	321.7	316.4	319.0	312.1	306.9	305.9	305.1
20°	346.0	338.2	336.5	340.8	335.6	331.2	333.9	330.4
22.5°	421.9	421.0	421.9	432.4	429.8	428.0	429.8	429.8
25°	475.0	478.5	479.5	490.8	491.6	489.9	494.3	494.3
27.5°	473.3	474.2	473.3	484.7	486.4	483.0	487.3	488.1
30°	431.5	431.5	428.9	438.4	438.4	436.7	438.4	439.3
32.5°	376.6	375.7	374.9	379.2	379.2	376.6	378.3	378.3
35°	325.2	321.7	321.7	324.2	323.4	320.7	321.7	320.7
37.5°	280.7	276.3	276.3	278.1	275.5	272.8	273.7	273.7
40°	239.7	236.2	236.2	238.9	237.1	234.4	236.2	236.2
42.5°	201.3	200.5	200.5	202.2	202.2	200.5	203.1	204.0
45°	169.9	167.4	167.4	169.1	169.1	167.4	168.2	167.4
47.5°	141.2	138.6	138.6	138.6	136.8	134.2	134.2	133.4
50°	112.4	108.1	107.2	107.2	105.4	102.9	102.9	101.9
52.5°	83.7	79.3	79.3	78.5	76.7	75.8	75.0	75.0
55°	57.5	54.0	54.9	53.2	53.2	51.4	52.3	51.4
57.5°	35.7	33.9	33.9	33.1	31.4	30.6	30.6	29.6
60°	20.9	19.1	19.1	19.1	18.3	17.4	17.4	17.4
62.5°	14.0	13.1	13.1	13.1	11.3	11.3	10.5	10.5
65°	8.7	7.8	7.8	7.8	7.0	7.0	7.0	7.0
67.5°	7.0	7.0	6.1	6.1	6.1	6.1	6.1	6.1
70°	6.1	6.1	6.1	6.1	6.1	5.2	5.2	5.2
72.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
75°	5.2	5.2	4.3	5.2	4.3	4.3	4.3	4.3
77.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
80°	4.3	4.3	4.3	4.3	4.3	3.5	3.5	3.5
82.5°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
85°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
87.5°	2.6	1.7	1.7	1.7	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)