

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192231

Luminaire Tested: **LDA6A40940D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26672)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40940D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4597.3 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 2.54 / 0.51 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192231

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192231

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75
5	85	75	68	62	83	74	67	62	72	66	62		70	65	61		69
6	80	69	61	56	78	68	61	56	66	60	55		64	59	55		63
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50
10	61	49	42	37	60	49	42	37	48	41	37		47	41	37		46

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	56574	56574	56574
5°	144667	52157	19029
10°	310916	42078	7003
15°	453555	30772	8014
20°	513588	22128	12356
25°	556762	17795	19162
30°	621228	14610	18452
35°	630542	9450	12294
40°	635197	4537	6219
45°	631221	1899	2597
50°	505382	853	853
55°	150723	612	86
60°	30765	702	0
65°	2932	830	0
70°	305	1154	0
75°	0	1525	0
80°	0	2557	284
85°	0	5095	566

TEST NUMBER: P1192231

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.3	2.9
10°-20°	644.8	14.0
20°-30°	1185.0	25.8
30°-40°	1359.6	29.6
40°-50°	1028.6	22.4
50°-60°	227.9	5.0
60°-70°	9.7	0.2
70°-80°	4.3	0.1
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1963.1	42.7
0°-40°	3322.6	72.3
0°-60°	4579.2	99.6
0°-90°	4597.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4597.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1032	1032	1032	1032	1032	
5°	2629	1964	948	464	346	348
15°	7992	4334	542	140	141	2227
25°	9205	5097	294	285	317	4294
35°	9422	3146	141	176	184	5902
45°	8142	890	24	32	34	6076
55°	1577	34	6	4	1	1952
65°	23	4	6	4	0	60
75°	0	4	7	4	0	0
85°	0	4	8	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192231

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0
2.5°	1748.0	1730.9	1735.4	1757.1	1667.5	1664.7	1623.2	1617.7	1576.0	1500.0	1462.0
5°	2628.9	2618.0	2599.0	2606.3	2503.9	2435.1	2362.7	2310.2	2203.4	2059.4	1963.5
7.5°	4033.8	3916.1	3859.1	3749.5	3619.2	3486.1	3352.2	3196.4	2972.0	2721.2	2518.4
10°	5585.4	5533.8	5417.0	5347.4	5058.5	4863.0	4654.8	4336.2	3925.1	3470.8	3092.3
12.5°	7106.2	7045.6	6869.1	6720.6	6335.8	6161.2	5890.5	5488.5	4967.1	4319.8	3721.5
15°	7991.6	8005.2	7805.1	7797.9	7466.6	7239.3	7004.9	6529.6	5867.9	5124.7	4334.3
17.5°	8510.3	8543.8	8345.6	8401.6	8071.2	7835.9	7661.2	7313.5	6610.2	5718.5	4807.8
20°	8803.6	8857.0	8646.0	8689.6	8407.1	8247.7	8070.3	7726.3	7105.3	6121.4	5076.6
22.5°	9027.2	9048.1	8813.5	8871.5	8562.8	8403.5	8277.7	7955.4	7342.5	6334.1	5160.9
25°	9204.6	9257.1	8989.2	8993.7	8686.8	8527.4	8388.1	8094.8	7443.9	6390.2	5096.6
27.5°	9459.9	9502.4	9108.6	9074.3	8777.3	8601.7	8450.5	8161.7	7439.4	6265.3	4853.9
30°	9813.9	9576.7	9173.9	9085.1	8751.1	8572.7	8410.7	8035.9	7272.8	5928.5	4413.1
32.5°	9712.5	9520.5	9123.1	8981.9	8650.6	8459.5	8274.0	7817.8	6886.3	5407.0	3812.0
35°	9421.9	9360.4	8943.0	8898.7	8497.6	8297.5	8111.0	7487.3	6293.4	4725.4	3145.8
37.5°	9176.5	9071.5	8802.7	8733.0	8312.0	8091.2	7794.2	6994.0	5509.4	3856.4	2512.0
40°	8876.1	8805.4	8545.5	8471.4	7984.3	7647.6	7284.6	6099.6	4562.5	3001.8	1940.0
42.5°	8556.4	8493.1	8247.7	8092.1	7443.0	6997.6	6433.7	5016.9	3512.4	2262.3	1453.8
45°	8141.9	8052.2	7745.3	7455.7	6525.1	5887.7	5253.2	3828.3	2570.9	1610.4	889.9
47.5°	7429.4	7287.3	6915.2	6333.2	5189.8	4577.8	3917.0	2596.3	1587.8	829.2	448.1
50°	5925.8	5677.8	5182.6	4490.1	3324.1	2737.5	2219.7	1319.9	681.7	427.3	263.4
52.5°	3651.8	3424.6	3002.7	2334.7	1532.6	1180.4	929.7	614.6	375.7	241.7	97.7
55°	1577.0	1434.8	1233.0	940.5	668.1	549.5	441.7	306.9	193.7	74.3	33.5
57.5°	595.7	553.1	501.5	411.9	307.8	257.1	216.3	135.8	47.1	28.1	19.0
60°	280.6	254.4	224.5	178.4	117.7	85.1	53.4	34.4	22.6	15.4	10.9
62.5°	76.9	57.9	47.9	38.9	29.8	26.2	22.6	17.2	12.7	8.1	6.4
65°	22.6	20.0	19.0	16.3	13.6	11.7	10.0	8.1	6.4	4.5	4.5
67.5°	8.1	8.1	7.2	6.4	5.5	4.5	4.5	3.6	3.6	3.6	3.6
70°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.7	2.7	3.6	3.6
72.5°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.7	2.7	3.6	3.6
75°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.7	2.7	3.6	3.6
77.5°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6	4.5
80°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6	4.5
82.5°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6	4.5
85°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6	4.5
87.5°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192231

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0
2.5°	1430.3	1377.8	1303.5	1265.6	1232.0	1223.0	1154.2	1109.8	1057.4	1003.1	946.0
5°	1873.8	1739.9	1597.7	1478.3	1417.6	1382.3	1248.3	1147.9	1051.0	947.8	860.0
7.5°	2313.8	2073.9	1866.6	1673.8	1567.9	1488.2	1296.3	1145.1	998.5	864.5	745.9
10°	2739.3	2393.5	2063.1	1802.3	1656.6	1538.0	1290.0	1093.6	909.8	755.9	631.9
12.5°	3170.2	2665.9	2226.9	1871.2	1697.3	1545.3	1246.6	1007.6	813.0	650.0	521.4
15°	3554.9	2877.8	2329.2	1887.4	1677.5	1498.2	1161.5	898.0	704.3	542.2	430.0
17.5°	3822.0	2991.9	2335.5	1827.8	1594.1	1401.4	1042.9	783.0	594.8	451.7	353.0
20°	3943.2	2988.2	2249.5	1703.7	1459.3	1258.3	902.6	665.3	496.0	379.3	295.1
22.5°	3907.0	2874.1	2097.5	1528.1	1294.5	1093.6	772.2	561.2	426.4	325.9	258.9
25°	3726.0	2675.0	1919.1	1352.4	1117.0	929.7	654.5	479.8	370.2	294.2	235.4
27.5°	3430.0	2403.4	1679.2	1147.0	931.5	785.8	551.3	414.6	325.9	259.8	245.3
30°	2997.3	2073.9	1397.7	925.2	752.3	621.9	447.2	334.0	260.7	230.8	231.8
32.5°	2520.3	1710.9	1098.9	707.0	566.7	479.8	330.4	233.5	191.0	189.2	190.1
35°	2045.0	1332.6	817.5	516.9	415.5	345.8	212.7	146.7	142.2	141.2	143.0
37.5°	1623.2	991.2	589.3	361.2	275.2	210.9	115.0	99.6	96.0	97.7	98.7
40°	1212.1	695.3	398.3	213.7	133.9	96.9	69.7	64.3	62.4	63.4	63.4
42.5°	833.7	434.5	237.2	88.7	64.3	53.4	44.3	41.7	39.8	38.9	39.8
45°	449.0	270.6	92.4	45.3	38.1	34.4	28.1	26.2	25.3	24.5	24.5
47.5°	287.0	100.5	41.7	28.1	24.5	22.6	19.0	17.2	16.3	15.4	15.4
50°	107.7	38.9	25.3	18.1	15.4	14.5	11.7	10.9	10.0	10.0	10.0
52.5°	37.1	23.6	16.3	11.7	10.0	9.1	8.1	7.2	7.2	7.2	7.2
55°	20.8	14.5	10.0	7.2	7.2	6.4	6.4	6.4	6.4	6.4	6.4
57.5°	12.7	8.1	6.4	5.5	5.5	5.5	5.5	6.4	6.4	6.4	6.4
60°	7.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5	6.4	6.4	6.4
62.5°	4.5	4.5	4.5	4.5	4.5	5.5	5.5	6.4	6.4	6.4	6.4
65°	4.5	4.5	4.5	4.5	4.5	5.5	5.5	6.4	6.4	6.4	6.4
67.5°	3.6	4.5	4.5	5.5	5.5	5.5	5.5	6.4	6.4	7.2	6.4
70°	4.5	4.5	4.5	5.5	5.5	5.5	6.4	6.4	7.2	7.2	7.2
72.5°	4.5	4.5	4.5	5.5	5.5	5.5	6.4	6.4	7.2	7.2	7.2
75°	4.5	4.5	5.5	5.5	5.5	6.4	6.4	7.2	7.2	7.2	7.2
77.5°	4.5	4.5	5.5	5.5	5.5	6.4	6.4	7.2	7.2	8.1	7.2
80°	4.5	4.5	5.5	6.4	6.4	6.4	6.4	7.2	7.2	8.1	8.1
82.5°	4.5	5.5	5.5	6.4	6.4	6.4	7.2	7.2	8.1	8.1	8.1
85°	4.5	5.5	5.5	6.4	6.4	6.4	7.2	7.2	8.1	8.1	8.1
87.5°	4.5	5.5	5.5	6.4	6.4	6.4	7.2	7.2	8.1	8.1	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192231

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0
2.5°	915.2	862.8	820.2	821.1	785.8	758.7	724.2	705.2	689.8	664.4	641.0
5°	795.7	715.1	654.5	642.7	602.0	560.3	517.8	486.2	463.5	439.0	416.4
7.5°	666.3	573.9	504.3	487.9	453.5	414.6	375.7	344.0	316.8	290.6	263.4
10°	540.5	456.2	392.9	376.6	342.1	301.4	264.4	236.3	215.4	194.6	173.8
12.5°	437.2	363.0	303.3	282.5	254.4	222.7	192.8	165.6	143.0	133.9	131.3
15°	354.0	283.3	236.3	219.1	195.6	162.9	145.8	141.2	140.3	140.3	140.3
17.5°	286.1	230.8	188.2	170.1	158.4	156.6	156.6	156.6	157.5	159.3	162.9
20°	239.9	191.0	174.7	176.5	176.5	178.4	182.0	184.6	188.2	192.8	198.2
22.5°	212.7	202.8	201.0	206.4	207.3	212.7	219.9	225.4	231.8	239.0	243.5
25°	232.7	236.3	239.0	247.1	249.9	258.9	269.7	277.9	285.1	293.3	298.7
27.5°	253.5	259.8	265.2	273.4	275.2	287.0	296.1	301.4	306.9	310.5	314.2
30°	239.0	245.3	250.8	258.0	258.0	270.6	275.2	279.7	284.2	286.1	289.7
32.5°	196.5	202.8	208.2	213.7	214.6	223.6	229.0	230.8	234.4	235.4	238.0
35°	147.5	150.3	155.7	160.3	161.1	167.5	172.0	173.8	176.5	176.5	178.4
37.5°	101.4	103.2	107.7	110.5	112.2	116.8	119.5	121.3	123.1	124.1	124.9
40°	66.0	67.0	69.7	72.4	74.3	76.9	78.8	80.5	81.5	83.3	83.3
42.5°	40.7	41.7	43.4	45.3	45.3	47.9	48.9	50.7	51.6	52.5	52.5
45°	25.3	26.2	26.2	27.2	28.1	29.0	30.8	30.8	31.7	31.7	31.7
47.5°	15.4	16.3	15.4	16.3	16.3	17.2	18.1	18.1	18.1	18.1	18.1
50°	10.0	10.0	10.0	10.0	10.0	10.0	10.9	10.9	10.9	10.9	10.0
52.5°	7.2	7.2	6.4	7.2	6.4	6.4	6.4	6.4	6.4	6.4	5.5
55°	6.4	6.4	6.4	6.4	5.5	5.5	5.5	4.5	4.5	3.6	3.6
57.5°	6.4	6.4	5.5	5.5	5.5	4.5	4.5	4.5	3.6	3.6	2.7
60°	6.4	6.4	5.5	5.5	5.5	4.5	4.5	3.6	3.6	2.7	2.7
62.5°	6.4	6.4	5.5	5.5	5.5	5.5	4.5	4.5	3.6	3.6	2.7
65°	6.4	6.4	6.4	5.5	5.5	5.5	4.5	4.5	3.6	3.6	2.7
67.5°	6.4	6.4	6.4	6.4	5.5	5.5	5.5	4.5	3.6	3.6	2.7
70°	6.4	6.4	6.4	6.4	6.4	5.5	5.5	4.5	4.5	3.6	2.7
72.5°	7.2	7.2	6.4	6.4	6.4	5.5	5.5	4.5	4.5	3.6	3.6
75°	7.2	7.2	6.4	6.4	6.4	5.5	5.5	4.5	4.5	3.6	3.6
77.5°	7.2	7.2	7.2	7.2	6.4	6.4	5.5	5.5	4.5	4.5	3.6
80°	7.2	7.2	7.2	7.2	6.4	6.4	6.4	5.5	4.5	4.5	3.6
82.5°	7.2	7.2	7.2	7.2	7.2	6.4	6.4	5.5	4.5	4.5	3.6
85°	7.2	7.2	7.2	7.2	7.2	6.4	6.4	5.5	4.5	4.5	3.6
87.5°	7.2	7.2	7.2	7.2	7.2	6.4	6.4	5.5	4.5	4.5	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192231

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0	1032.0
2.5°	619.2	607.4	606.5	596.5	576.7	586.7	573.9	564.8
5°	396.5	383.8	371.1	373.0	358.5	361.2	351.2	345.8
7.5°	251.6	238.0	234.4	234.4	218.2	218.2	211.8	208.2
10°	158.4	147.5	143.9	137.6	130.3	129.4	126.7	125.8
12.5°	128.6	128.6	125.8	126.7	126.7	126.7	125.8	125.8
15°	140.3	141.2	138.5	139.4	141.2	140.3	141.2	141.2
17.5°	162.0	166.5	162.9	164.8	168.4	167.5	168.4	169.3
20°	198.2	205.5	201.0	204.6	209.1	208.2	210.9	211.8
22.5°	247.1	256.1	251.6	255.3	262.5	260.7	264.4	266.1
25°	301.4	310.5	305.1	309.6	314.2	315.9	315.9	316.8
27.5°	314.2	319.5	315.9	320.4	322.3	324.0	322.3	323.2
30°	287.8	292.4	288.8	293.3	293.3	295.1	293.3	291.5
32.5°	237.2	240.8	236.3	241.7	240.8	241.7	242.6	243.5
35°	179.2	181.0	178.4	179.2	180.1	181.0	183.7	183.7
37.5°	124.9	127.7	124.9	125.8	125.8	127.7	129.4	129.4
40°	83.3	86.0	83.3	85.1	84.1	85.1	86.9	86.9
42.5°	52.5	54.3	52.5	53.4	53.4	53.4	54.3	55.2
45°	31.7	32.6	31.7	32.6	32.6	32.6	33.5	33.5
47.5°	18.1	19.0	18.1	18.1	19.0	18.1	19.0	19.0
50°	10.0	10.0	10.0	10.0	10.0	9.1	9.1	10.0
52.5°	5.5	5.5	4.5	4.5	4.5	4.5	4.5	4.5
55°	2.7	2.7	1.9	1.9	1.9	0.9	1.9	0.9
57.5°	1.9	1.9	0.9	0.9	0.9	0.9	0.0	0.0
60°	1.9	1.9	0.9	0.9	0.9	0.0	0.0	0.0
62.5°	1.9	1.9	0.9	0.9	0.9	0.0	0.0	0.0
65°	1.9	1.9	0.9	0.9	0.9	0.0	0.0	0.0
67.5°	2.7	1.9	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.7	1.9	1.9	0.9	0.9	0.0	0.0	0.0
72.5°	2.7	1.9	1.9	1.9	0.9	0.9	0.0	0.0
75°	2.7	1.9	1.9	1.9	0.9	0.9	0.0	0.0
77.5°	2.7	2.7	1.9	1.9	0.9	0.9	0.9	0.0
80°	2.7	2.7	1.9	1.9	1.9	0.9	0.9	0.9
82.5°	2.7	2.7	1.9	1.9	1.9	0.9	0.9	0.9
85°	2.7	2.7	1.9	1.9	1.9	0.9	0.9	0.9
87.5°	2.7	2.7	1.9	1.9	1.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)