

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192236

Luminaire Tested: **LDA6A40940D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26669)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40940D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3465.6 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 2.14 / 1.07 / 1.49
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192236

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192236

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62		
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55		
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49		
7	72	59	52	46	70	59	51	46	57	51	46	56	50	45	55	49	45	43		
8	67	54	47	41	65	54	46	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	37	33	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	60845	60845	60845
5°	97397	60081	38955
10°	142321	57703	26252
15°	194581	54722	19830
20°	243429	51816	20022
25°	281200	51638	31048
30°	308041	48881	28884
35°	318085	41445	22299
40°	311312	32332	17554
45°	283774	23863	13474
50°	228086	17611	9040
55°	138882	12454	5104
60°	72067	8234	1984
65°	35114	4345	934
70°	16108	1875	882
75°	6714	1356	953
80°	3441	1421	1137
85°	2264	2830	1698

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192236

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.9	3.3
10°-20°	403.4	11.6
20°-30°	763.7	22.0
30°-40°	924.9	26.7
40°-50°	774.1	22.3
50°-60°	375.1	10.8
60°-70°	92.0	2.7
70°-80°	15.0	0.4
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1280.9	37.0
0°-40°	2205.8	63.6
0°-60°	3355.0	96.8
0°-90°	3465.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3465.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1110	1110	1110	1110	1110	
5°	1770	1525	1092	799	708	193
15°	3428	2384	964	441	349	990
25°	4649	2808	854	502	513	2141
35°	4753	2482	619	358	333	2946
45°	3660	1674	308	187	174	2777
55°	1453	686	130	71	53	1362
65°	271	150	34	11	7	305
75°	32	16	6	6	4	43
85°	4	3	4	4	3	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192236

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9
2.5°	1408.7	1376.2	1383.4	1388.8	1364.3	1379.8	1353.5	1344.5	1322.7	1328.1	1311.9
5°	1769.9	1724.7	1711.1	1711.1	1670.4	1683.9	1660.4	1618.7	1576.2	1563.5	1524.6
7.5°	2158.4	2108.6	2086.8	2077.7	2018.0	2009.8	1990.0	1925.7	1855.9	1818.8	1750.0
10°	2556.7	2511.4	2480.7	2459.8	2377.4	2363.0	2327.6	2237.1	2149.3	2069.6	1956.4
12.5°	2995.8	2935.1	2894.4	2859.9	2754.1	2731.5	2678.9	2557.6	2419.0	2323.1	2173.7
15°	3428.5	3367.0	3313.6	3263.8	3135.2	3102.6	3032.0	2878.0	2716.0	2573.0	2383.8
17.5°	3840.5	3762.6	3697.4	3630.4	3479.2	3438.5	3346.2	3175.0	2948.7	2786.7	2558.5
20°	4172.7	4096.7	4021.5	3936.4	3763.5	3714.7	3602.3	3399.6	3142.4	2947.8	2681.7
22.5°	4444.3	4358.3	4284.0	4172.7	3978.1	3921.0	3791.6	3561.6	3283.6	3056.4	2764.1
25°	4648.9	4557.5	4481.4	4356.6	4141.0	4074.9	3923.8	3674.7	3371.5	3121.6	2808.4
27.5°	4810.1	4705.1	4619.1	4480.5	4243.3	4169.1	4003.4	3734.5	3406.8	3134.3	2806.5
30°	4866.3	4763.9	4667.0	4517.6	4262.3	4179.9	4007.9	3716.4	3375.1	3081.8	2744.1
32.5°	4841.8	4735.8	4630.8	4472.4	4202.6	4113.9	3940.0	3628.7	3278.3	2969.5	2629.1
35°	4753.0	4645.3	4533.1	4369.2	4086.7	3990.8	3816.9	3494.6	3130.7	2822.0	2481.6
37.5°	4591.9	4484.1	4378.3	4201.7	3912.9	3813.3	3642.2	3308.1	2953.2	2641.8	2310.4
40°	4350.2	4243.3	4145.6	3967.2	3676.6	3576.1	3414.1	3082.6	2740.5	2432.6	2113.9
42.5°	4038.7	3936.4	3848.6	3673.9	3389.6	3293.6	3141.6	2821.0	2501.4	2203.6	1904.0
45°	3660.3	3567.0	3486.5	3321.7	3059.2	2966.8	2832.0	2528.6	2230.8	1951.9	1674.0
47.5°	3223.9	3138.8	3068.2	2916.1	2672.6	2588.4	2472.5	2190.9	1924.8	1670.4	1423.2
50°	2674.4	2600.2	2551.2	2420.0	2202.7	2132.0	2042.4	1805.2	1587.0	1367.9	1163.3
52.5°	2040.7	1982.7	1960.0	1861.4	1693.0	1644.1	1586.1	1404.1	1244.8	1071.9	912.5
55°	1453.1	1415.1	1400.5	1336.3	1225.9	1194.2	1144.3	1032.1	926.1	803.9	686.2
57.5°	989.6	969.6	958.7	918.9	851.0	829.3	801.2	728.8	660.9	581.2	497.1
60°	657.3	649.1	640.0	615.7	575.8	559.5	545.9	498.0	456.3	406.5	347.7
62.5°	426.4	422.8	416.4	401.1	385.7	374.9	360.3	328.7	304.2	278.9	234.4
65°	270.7	267.0	264.4	254.4	244.4	233.6	228.2	210.1	194.6	178.4	150.3
67.5°	167.5	164.8	163.9	157.5	150.3	143.9	140.3	128.6	119.5	109.6	91.4
70°	100.5	99.6	97.8	94.1	89.6	85.1	83.3	75.1	69.7	63.4	51.6
72.5°	57.9	57.0	56.2	53.4	50.7	48.9	47.1	44.3	38.1	34.4	29.0
75°	31.7	31.7	30.8	29.0	28.1	26.2	25.3	23.6	20.8	19.0	16.3
77.5°	18.1	17.2	17.2	16.3	15.4	15.4	14.5	13.6	11.7	11.7	10.0
80°	10.9	10.9	10.9	10.0	10.0	10.0	9.1	9.1	8.1	7.2	7.2
82.5°	7.2	6.4	6.4	6.4	6.4	6.4	5.5	5.5	5.5	5.5	4.5
85°	3.6	3.6	3.6	3.6	2.7	3.6	2.7	2.7	2.7	2.7	2.7
87.5°	0.0	0.0	0.9	0.9	0.9	0.9	0.9	1.9	1.9	1.9	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192236

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9
2.5°	1269.3	1260.2	1242.1	1216.8	1207.8	1202.3	1172.4	1145.2	1126.2	1101.8	1078.3
5°	1453.9	1420.5	1377.0	1324.5	1303.6	1285.5	1230.4	1179.7	1138.0	1091.8	1048.4
7.5°	1645.0	1582.5	1509.2	1426.0	1391.5	1359.8	1276.5	1201.4	1137.1	1071.1	1008.5
10°	1824.3	1729.2	1623.3	1512.0	1460.3	1414.1	1303.6	1206.8	1121.7	1036.6	959.7
12.5°	1999.9	1870.4	1730.1	1587.0	1520.1	1460.3	1323.6	1205.0	1100.0	1000.4	911.7
15°	2169.2	2001.7	1828.8	1653.2	1572.5	1499.2	1337.2	1198.7	1077.3	964.2	865.5
17.5°	2305.9	2108.6	1899.5	1693.0	1602.5	1517.4	1335.4	1180.6	1046.6	923.4	818.4
20°	2401.9	2174.6	1941.9	1711.1	1612.5	1518.2	1321.7	1156.1	1014.9	888.2	782.2
22.5°	2456.2	2205.4	1956.4	1711.1	1605.2	1506.5	1302.8	1133.5	991.3	867.3	766.0
25°	2478.8	2210.8	1950.1	1696.6	1587.0	1485.6	1281.0	1111.8	972.3	853.7	759.6
27.5°	2460.7	2179.2	1914.8	1656.8	1544.6	1443.1	1239.5	1073.7	938.9	825.7	736.0
30°	2388.3	2099.5	1836.0	1579.8	1466.7	1367.9	1170.6	1010.4	880.9	772.2	687.2
32.5°	2270.6	1983.6	1724.7	1474.8	1362.6	1267.4	1079.2	927.0	803.1	699.8	621.1
35°	2127.5	1846.0	1596.1	1352.6	1244.8	1154.3	976.8	828.4	714.3	619.3	546.8
37.5°	1966.4	1693.9	1446.7	1223.1	1119.9	1033.9	868.2	728.8	623.8	535.9	471.6
40°	1785.4	1528.2	1295.5	1083.7	985.9	906.3	749.6	626.5	530.5	451.8	397.5
42.5°	1594.3	1354.4	1138.0	939.7	847.4	775.0	632.8	523.3	439.0	374.9	331.3
45°	1389.7	1167.9	969.6	792.2	715.2	642.8	522.4	422.8	356.7	307.8	275.3
47.5°	1171.6	975.1	800.3	645.5	578.5	515.2	413.7	337.7	289.7	252.5	228.2
50°	952.5	786.7	638.3	506.1	449.0	398.3	320.5	268.9	233.6	206.5	186.5
52.5°	744.1	610.2	488.9	381.1	338.6	302.4	248.9	212.7	186.5	165.7	151.2
55°	558.6	452.7	357.6	277.0	251.7	229.1	193.7	164.8	146.7	130.3	119.5
57.5°	404.7	323.2	254.4	203.7	187.4	172.0	146.7	126.7	113.2	100.5	92.4
60°	284.3	224.6	180.1	149.4	136.7	127.7	107.7	95.0	84.1	75.1	67.0
62.5°	191.0	152.1	125.8	106.0	97.8	91.4	78.8	67.9	59.8	52.5	45.3
65°	122.2	102.4	85.1	71.5	66.0	61.5	53.4	44.3	38.9	33.5	28.1
67.5°	75.1	64.3	53.4	44.3	40.7	38.1	32.6	27.2	23.6	20.0	17.2
70°	43.4	37.1	30.8	26.2	24.5	22.6	19.0	16.3	14.5	11.7	10.0
72.5°	24.5	21.7	18.1	15.4	14.5	13.6	11.7	10.0	9.1	8.1	7.2
75°	14.5	12.7	10.9	10.0	9.1	9.1	8.1	7.2	6.4	6.4	5.5
77.5°	9.1	8.1	7.2	7.2	6.4	6.4	6.4	5.5	5.5	5.5	5.5
80°	6.4	6.4	5.5	5.5	5.5	5.5	4.5	4.5	4.5	4.5	4.5
82.5°	4.5	4.5	4.5	3.6	3.6	3.6	3.6	3.6	4.5	4.5	4.5
85°	2.7	2.7	3.6	3.6	3.6	3.6	3.6	3.6	4.5	4.5	4.5
87.5°	2.7	2.7	2.7	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192236

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9
2.5°	1053.0	1042.1	1022.1	1004.0	1001.3	976.0	949.7	944.2	935.2	920.8	903.5
5°	1004.9	976.0	941.5	916.2	905.3	869.1	832.9	816.7	798.6	770.5	754.1
7.5°	948.8	906.3	858.2	829.3	813.9	768.6	727.0	703.4	679.0	649.1	629.2
10°	887.2	833.8	777.7	745.1	727.0	678.1	633.8	606.6	580.3	550.4	529.7
12.5°	829.3	768.6	707.1	672.7	652.8	602.1	556.8	527.8	501.6	477.1	452.7
15°	777.7	709.8	645.5	611.1	590.3	538.7	495.2	466.3	440.9	417.3	395.6
17.5°	727.9	657.3	593.9	560.4	539.5	491.6	449.9	423.7	399.2	377.5	358.5
20°	693.5	626.5	566.7	535.0	516.9	474.4	439.0	418.3	401.1	382.1	365.8
22.5°	684.5	624.7	573.1	546.8	533.3	499.7	474.4	461.8	456.3	444.5	435.4
25°	684.5	631.9	588.5	566.7	555.9	530.5	510.6	506.1	502.5	495.2	490.7
27.5°	667.2	618.3	579.5	560.4	551.4	528.7	511.6	506.1	501.6	496.1	490.7
30°	621.9	576.7	540.5	523.3	514.2	492.5	474.4	468.0	463.5	455.4	450.9
32.5°	561.4	517.8	488.0	468.0	459.9	439.0	421.9	414.7	411.1	403.8	395.6
35°	493.5	455.4	426.4	410.1	402.0	383.9	368.5	361.3	357.6	349.4	339.5
37.5°	424.6	390.2	366.6	351.3	344.9	330.4	316.8	311.5	307.8	301.5	293.4
40°	356.7	332.3	311.5	299.7	294.2	282.5	270.7	265.3	262.5	257.1	250.8
42.5°	300.6	280.6	264.4	254.4	249.9	240.8	230.8	225.4	222.7	217.3	212.7
45°	251.7	236.3	223.6	214.6	211.0	202.8	194.6	190.1	187.4	182.9	178.4
47.5°	211.0	197.4	186.5	180.1	176.5	170.2	162.9	158.4	156.7	153.0	148.4
50°	172.9	162.9	153.9	148.4	145.8	139.4	133.1	129.5	127.7	124.1	119.5
52.5°	139.4	132.2	124.1	118.6	115.9	111.4	105.0	101.4	98.7	95.0	89.6
55°	109.6	103.2	96.9	91.4	89.6	84.1	78.8	73.3	70.6	67.0	62.4
57.5°	85.1	77.9	71.5	67.0	65.2	59.8	54.3	48.9	46.2	41.7	38.9
60°	60.7	54.3	47.9	45.3	43.4	38.1	33.5	29.0	27.2	24.5	22.6
62.5°	39.8	35.3	29.8	27.2	26.2	22.6	19.0	18.1	16.3	15.4	14.5
65°	24.5	21.7	18.1	16.3	15.4	14.5	12.7	11.7	10.9	10.0	10.0
67.5°	14.5	13.6	11.7	10.9	10.0	9.1	9.1	8.1	8.1	7.2	7.2
70°	10.0	9.1	8.1	7.2	7.2	7.2	7.2	7.2	7.2	6.4	6.4
72.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
75°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
77.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.5	4.5
80°	4.5	5.5	5.5	5.5	5.5	4.5	4.5	4.5	4.5	4.5	4.5
82.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
85°	4.5	4.5	4.5	4.5	4.5	3.6	3.6	3.6	3.6	3.6	2.7
87.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	2.7	2.7	2.7	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192236

CATALOG NUMBER: LDA6A40940D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9	1109.9
2.5°	901.7	893.6	885.4	898.1	897.2	884.6	893.6	879.1
5°	745.1	733.3	724.3	732.4	727.9	715.2	720.7	707.9
7.5°	617.4	603.8	593.0	599.3	592.1	580.3	578.5	573.1
10°	516.1	501.6	491.6	496.1	488.9	478.0	475.4	471.6
12.5°	439.0	425.5	416.4	420.1	412.8	402.8	401.1	403.8
15°	379.4	369.4	362.1	364.9	354.9	349.4	347.7	349.4
17.5°	344.9	334.1	328.7	331.3	324.1	318.7	317.8	316.8
20°	359.4	351.3	349.4	354.0	348.5	344.0	346.8	343.2
22.5°	438.2	437.3	438.2	449.0	446.3	444.5	446.3	446.3
25°	493.5	497.1	498.0	509.7	510.6	508.8	513.3	513.3
27.5°	491.6	492.5	491.6	503.3	505.2	501.6	506.1	507.0
30°	448.2	448.2	445.4	455.4	455.4	453.5	455.4	456.3
32.5°	391.1	390.2	389.3	393.8	393.8	391.1	393.0	393.0
35°	337.7	334.1	334.1	336.8	335.9	333.2	334.1	333.2
37.5°	291.5	287.0	287.0	288.9	286.1	283.4	284.3	284.3
40°	248.9	245.3	245.3	248.0	246.3	243.5	245.3	245.3
42.5°	209.1	208.2	208.2	210.1	210.1	208.2	211.0	211.8
45°	176.5	173.8	173.8	175.6	175.6	173.8	174.8	173.8
47.5°	146.7	143.9	143.9	143.9	142.2	139.4	139.4	138.6
50°	116.8	112.2	111.4	111.4	109.6	106.9	106.9	106.0
52.5°	86.9	82.4	82.4	81.5	79.6	78.8	77.9	77.9
55°	59.8	56.2	57.0	55.2	55.2	53.4	54.3	53.4
57.5°	37.1	35.3	35.3	34.4	32.6	31.7	31.7	30.8
60°	21.7	20.0	20.0	20.0	19.0	18.1	18.1	18.1
62.5°	14.5	13.6	13.6	13.6	11.7	11.7	10.9	10.9
65°	9.1	8.1	8.1	8.1	7.2	7.2	7.2	7.2
67.5°	7.2	7.2	6.4	6.4	6.4	6.4	6.4	6.4
70°	6.4	6.4	6.4	6.4	6.4	5.5	5.5	5.5
72.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
75°	5.5	5.5	4.5	5.5	4.5	4.5	4.5	4.5
77.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
80°	4.5	4.5	4.5	4.5	4.5	3.6	3.6	3.6
82.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
85°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
87.5°	2.7	1.9	1.9	1.9	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)