

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192239

Luminaire Tested: **LDA6A40950D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192239
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26673)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40950D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3874.5 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.56 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192239

CATALOG NUMBER: LDA6A40950D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192239

CATALOG NUMBER: LDA6A40950D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	55	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	60127	60127	60127
5°	120410	57198	15337
10°	201922	48897	4192
15°	308356	36652	6090
20°	441808	26806	71733
25°	656832	44476	36788
30°	767719	19661	5722
35°	771944	4096	3018
40°	639176	2290	1753
45°	478445	1458	1388
50°	335307	1040	810
55°	53895	803	640
60°	3311	822	515
65°	973	1090	480
70°	593	1202	753
75°	424	1419	996
80°	284	2115	1484
85°	566	4214	1761



TEST NUMBER: P1192239

CATALOG NUMBER: LDA6A40950D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.6	2.9
10°-20°	479.9	12.4
20°-30°	1154.6	29.8
30°-40°	1230.2	31.8
40°-50°	767.1	19.8
50°-60°	112.1	2.9
60°-70°	7.1	0.2
70°-80°	5.6	0.1
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1748.1	45.1
0°-40°	2978.3	76.9
0°-60°	3857.5	99.6
0°-90°	3874.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3874.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1097	1097	1097	1097	1097	
5°	2188	1755	1039	518	279	253
15°	5433	3019	646	100	107	1612
25°	10859	3591	735	762	608	4893
35°	11535	2664	61	56	45	6959
45°	6171	780	19	22	18	4858
55°	564	13	8	10	7	997
65°	8	6	8	8	4	11
75°	2	4	7	7	5	2
85°	1	4	7	6	3	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192239

CATALOG NUMBER: LDA6A40950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8
2.5°	1631.6	1576.0	1594.9	1553.3	1538.4	1542.1	1512.0	1487.5	1474.3	1442.4	1409.4
5°	2188.1	2123.9	2142.7	2080.7	2042.0	2033.5	1986.5	1933.8	1886.8	1815.2	1754.9
7.5°	2862.9	2783.9	2797.1	2703.9	2625.8	2599.4	2527.9	2425.2	2330.2	2208.6	2092.9
10°	3627.4	3553.1	3549.3	3407.1	3273.5	3221.7	3117.3	2947.8	2785.8	2603.2	2413.0
12.5°	4528.5	4416.5	4397.6	4215.0	4015.3	3930.7	3784.8	3525.8	3269.8	3003.3	2729.4
15°	5433.2	5312.7	5282.6	5052.9	4774.2	4660.2	4465.3	4120.9	3767.8	3391.1	3019.2
17.5°	6397.4	6204.2	6041.5	5775.8	5454.0	5337.2	5084.9	4643.4	4199.0	3733.9	3236.8
20°	7573.2	7357.6	7128.8	6675.0	6084.7	5855.1	5578.1	5080.2	4525.7	3988.1	3397.8
22.5°	9185.0	8831.0	8345.2	7615.6	6804.0	6476.4	6049.0	5404.0	4777.0	4173.5	3505.1
25°	10859.0	10370.3	9836.5	8715.2	7462.1	7061.9	6499.9	5651.7	4976.6	4310.0	3590.8
27.5°	11822.9	11430.4	10825.0	9650.1	7995.8	7470.6	6822.8	5838.0	5103.7	4375.9	3615.2
30°	12128.1	11809.8	11260.0	10054.8	8174.7	7548.7	6853.0	5840.0	5042.5	4261.1	3474.0
32.5°	12000.9	11698.8	11090.6	9801.7	7847.2	7271.0	6595.9	5602.7	4741.3	3908.1	3111.6
35°	11534.8	11135.7	10396.7	8961.0	7289.8	6717.5	6086.6	5178.1	4278.0	3428.8	2664.4
37.5°	10488.9	10074.7	9234.0	7882.9	6571.6	6073.4	5566.0	4702.7	3812.0	2992.9	2274.6
40°	8931.7	8494.0	7802.9	6854.8	5796.6	5456.8	5028.4	4176.4	3318.7	2565.6	1914.0
42.5°	7360.4	7079.9	6670.4	5919.1	5181.8	4846.7	4430.6	3603.0	2844.1	2124.9	1453.7
45°	6171.3	5949.2	5677.0	5202.6	4506.8	4191.5	3804.5	3025.9	2217.2	1419.8	779.6
47.5°	5377.7	5106.5	4869.3	4340.1	3593.5	3210.5	2800.0	1994.1	1278.6	615.7	215.6
50°	3931.6	3604.8	3383.6	2790.5	2112.7	1793.5	1493.1	925.5	414.2	137.5	35.8
52.5°	1993.1	1746.4	1616.5	1221.1	806.8	603.5	443.5	191.0	82.0	27.2	20.8
55°	563.9	453.9	406.7	268.3	145.9	102.6	66.9	33.9	24.5	18.8	13.2
57.5°	58.4	49.8	47.1	38.6	31.0	29.2	26.3	20.8	16.0	13.2	8.4
60°	30.2	27.2	26.3	23.5	19.8	17.9	17.0	14.1	10.4	7.5	6.7
62.5°	16.0	15.1	13.2	12.2	10.4	10.4	9.5	7.5	6.7	6.7	5.7
65°	7.5	7.5	7.5	7.5	6.7	6.7	5.7	5.7	5.7	5.7	5.7
67.5°	5.7	5.7	5.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
70°	3.7	3.7	3.7	3.7	2.8	2.8	2.8	2.8	2.8	3.7	3.7
72.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.8	2.8	3.7	3.7
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.8	2.8	3.7	3.7
77.5°	0.9	0.9	2.0	2.0	2.0	2.0	2.0	2.8	2.8	3.7	3.7
80°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.8	2.8	3.7	3.7
82.5°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.8	2.8	3.7	3.7
85°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.0	2.8	3.7	3.7
87.5°	0.0	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192239

CATALOG NUMBER: LDA6A40950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8
2.5°	1369.8	1346.3	1308.6	1271.0	1259.8	1228.6	1191.9	1148.6	1108.1	1076.1	1045.0
5°	1657.9	1594.9	1524.3	1429.2	1395.3	1342.5	1263.5	1178.7	1105.2	1039.4	978.1
7.5°	1945.0	1826.4	1697.5	1560.0	1501.7	1423.6	1299.2	1179.7	1070.5	973.4	882.1
10°	2199.3	2016.7	1835.0	1645.7	1563.7	1463.1	1297.4	1144.8	1005.6	878.4	763.6
12.5°	2433.7	2181.4	1940.3	1697.5	1594.9	1473.4	1269.1	1084.6	918.8	770.1	635.4
15°	2638.9	2314.1	2015.6	1722.0	1592.0	1452.7	1213.5	1001.7	817.2	645.8	499.9
17.5°	2782.1	2389.5	2037.4	1696.6	1553.3	1393.4	1128.8	902.8	700.4	520.7	354.0
20°	2867.7	2409.3	2016.7	1641.0	1482.7	1317.2	1049.7	821.0	624.2	459.5	320.1
22.5°	2914.8	2418.6	2001.6	1621.3	1460.2	1302.1	1053.4	835.1	666.6	555.5	544.2
25°	2961.9	2448.7	2028.0	1643.8	1493.1	1346.3	1109.1	885.9	771.1	735.3	747.4
27.5°	2959.0	2429.9	2003.5	1623.1	1478.0	1325.6	1061.0	826.7	747.4	691.9	645.8
30°	2791.5	2251.0	1815.2	1411.3	1245.6	1042.2	707.1	485.8	371.9	310.6	279.7
32.5°	2403.5	1835.8	1386.8	981.0	819.1	592.2	304.1	160.1	137.5	122.4	109.2
35°	1997.8	1462.1	1044.1	618.6	411.4	225.0	104.5	67.8	63.1	61.2	60.2
37.5°	1647.6	1156.2	686.3	247.5	147.9	83.7	48.0	43.4	42.3	43.4	42.3
40°	1300.2	762.5	272.1	82.8	45.1	36.7	33.9	31.0	31.0	32.0	31.0
42.5°	778.6	284.3	82.8	31.0	29.2	26.3	25.5	24.5	23.5	24.5	24.5
45°	257.0	72.5	27.2	21.6	20.8	19.8	18.8	18.8	18.8	18.8	19.8
47.5°	58.4	25.5	18.8	16.0	16.0	15.1	15.1	14.1	15.1	15.1	16.0
50°	22.6	16.0	13.2	12.2	12.2	11.3	11.3	11.3	11.3	12.2	12.2
52.5°	14.1	11.3	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	10.4
55°	9.5	8.4	7.5	7.5	7.5	7.5	7.5	8.4	8.4	8.4	8.4
57.5°	6.7	6.7	6.7	6.7	7.5	6.7	7.5	6.7	6.7	7.5	8.4
60°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.5	7.5	8.4
62.5°	5.7	6.7	6.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5	8.4
65°	5.7	5.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5	8.4	8.4
67.5°	4.7	5.7	5.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5	8.4
70°	4.7	4.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5
72.5°	4.7	4.7	5.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	7.5
75°	4.7	4.7	5.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	7.5
77.5°	4.7	4.7	5.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	7.5
80°	4.7	4.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	6.7	7.5
82.5°	4.7	4.7	5.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	6.7
85°	4.7	4.7	5.7	5.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7
87.5°	4.7	4.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192239

CATALOG NUMBER: LDA6A40950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8
2.5°	1003.6	965.0	946.2	917.9	919.9	872.8	854.9	821.0	802.2	782.4	759.8
5°	903.8	836.1	788.0	750.4	729.7	668.4	627.0	573.4	517.8	464.2	420.0
7.5°	778.6	689.2	615.7	567.7	538.5	415.2	336.1	273.0	248.6	229.7	210.9
10°	639.2	528.2	398.2	332.3	291.8	233.5	209.9	174.2	148.7	125.2	111.1
12.5°	499.0	329.5	238.2	218.5	204.4	151.6	119.6	111.1	90.4	85.7	83.7
15°	313.5	216.5	168.5	145.0	126.2	105.5	96.9	96.1	99.8	100.8	99.8
17.5°	222.2	173.2	127.1	124.3	124.3	135.5	137.5	145.9	153.4	160.1	161.0
20°	285.2	256.2	298.5	317.3	350.3	390.7	450.1	532.9	605.4	678.8	735.3
22.5°	546.0	610.2	704.3	737.3	792.8	879.3	961.3	1037.5	1114.7	1172.1	1184.5
25°	803.1	847.3	902.8	890.7	907.5	902.8	856.8	794.6	761.6	701.4	680.7
27.5°	614.8	568.6	530.1	485.8	464.2	422.7	363.4	325.7	291.8	257.9	243.8
30°	250.4	219.3	196.8	180.8	171.4	148.7	137.5	125.2	119.6	111.1	106.4
32.5°	97.9	92.2	89.4	86.6	85.7	82.8	80.0	76.2	75.3	75.3	71.6
35°	58.4	58.4	58.4	57.4	58.4	57.4	56.5	55.5	56.5	56.5	53.7
37.5°	41.4	42.3	42.3	42.3	42.3	42.3	42.3	42.3	41.4	41.4	38.6
40°	31.0	32.0	33.0	32.0	33.0	33.0	32.0	31.0	31.0	31.0	29.2
42.5°	25.5	25.5	25.5	25.5	26.3	25.5	25.5	25.5	25.5	25.5	24.5
45°	20.8	20.8	20.8	20.8	21.6	21.6	20.8	20.8	21.6	21.6	20.8
47.5°	16.0	16.0	16.0	16.0	16.0	16.0	16.0	15.1	15.1	15.1	14.1
50°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	13.2	12.2	12.2
52.5°	10.4	10.4	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	10.4
55°	9.5	9.5	10.4	10.4	10.4	10.4	10.4	9.5	9.5	9.5	8.4
57.5°	8.4	9.5	9.5	9.5	9.5	9.5	9.5	9.5	8.4	8.4	7.5
60°	8.4	8.4	9.5	9.5	9.5	9.5	8.4	8.4	7.5	7.5	6.7
62.5°	8.4	8.4	9.5	9.5	9.5	8.4	8.4	7.5	7.5	6.7	6.7
65°	8.4	9.5	9.5	9.5	9.5	8.4	8.4	7.5	7.5	6.7	6.7
67.5°	8.4	9.5	9.5	9.5	9.5	8.4	8.4	7.5	7.5	6.7	6.7
70°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	7.5	7.5	6.7	6.7
72.5°	7.5	8.4	8.4	8.4	8.4	8.4	7.5	7.5	7.5	6.7	6.7
75°	7.5	7.5	7.5	7.5	8.4	7.5	7.5	7.5	6.7	6.7	5.7
77.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.7
80°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.7	5.7
82.5°	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.7	5.7	5.7
85°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.7	5.7	4.7	4.7
87.5°	6.7	6.7	6.7	6.7	6.7	5.7	5.7	4.7	3.7	3.7	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192239

CATALOG NUMBER: LDA6A40950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8	1096.8
2.5°	735.3	719.3	715.5	715.5	707.1	690.1	687.2	681.6
5°	371.9	332.3	324.8	316.4	302.2	285.2	280.5	278.7
7.5°	192.0	175.1	172.2	166.7	158.1	149.7	147.9	146.8
10°	112.9	102.6	97.9	89.4	81.0	76.2	76.2	75.3
12.5°	83.7	83.7	83.7	83.7	83.7	83.7	83.7	83.7
15°	101.6	104.5	104.5	105.5	106.4	107.3	109.2	107.3
17.5°	171.4	185.5	184.5	186.4	193.0	201.4	197.7	202.4
20°	832.2	940.5	971.6	1002.7	1096.8	1185.3	1167.4	1229.6
22.5°	1195.7	1228.6	1215.4	1207.0	1226.8	1216.4	1260.7	1231.5
25°	641.2	634.5	634.5	606.3	611.9	597.8	616.6	608.2
27.5°	236.3	215.6	213.7	200.5	209.0	189.3	194.9	191.0
30°	101.6	102.6	98.8	96.1	93.2	91.3	91.3	90.4
32.5°	69.7	69.7	67.8	65.9	64.0	62.2	61.2	60.2
35°	51.8	51.8	49.8	49.0	48.0	46.1	45.1	45.1
37.5°	37.6	37.6	36.7	35.8	33.9	33.0	32.0	32.0
40°	29.2	28.3	27.2	27.2	25.5	25.5	24.5	24.5
42.5°	23.5	23.5	23.5	22.6	21.6	20.8	20.8	20.8
45°	20.8	20.8	19.8	18.8	18.8	18.8	17.9	17.9
47.5°	14.1	14.1	13.2	13.2	12.2	12.2	11.3	11.3
50°	11.3	11.3	11.3	11.3	10.4	9.5	9.5	9.5
52.5°	10.4	9.5	9.5	9.5	8.4	8.4	7.5	7.5
55°	8.4	8.4	7.5	7.5	6.7	6.7	6.7	6.7
57.5°	7.5	6.7	6.7	6.7	5.7	5.7	5.7	5.7
60°	6.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7
62.5°	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7
65°	5.7	5.7	5.7	4.7	4.7	4.7	4.7	3.7
67.5°	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7
70°	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7
72.5°	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7
75°	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7
77.5°	5.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
80°	5.7	4.7	4.7	4.7	4.7	3.7	3.7	4.7
82.5°	4.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7
85°	3.7	3.7	3.7	3.7	2.8	2.8	2.8	2.8
87.5°	2.8	2.0	2.0	2.0	2.0	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)