

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192248

Luminaire Tested: **LDA6A40950D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26672)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40950D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4781.2 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 2.54 / 0.51 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192248

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192248

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	62	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	40	39		
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	58838	58838	58838
5°	150456	54243	19789
10°	323352	43759	7281
15°	471700	32004	8331
20°	534129	23015	12852
25°	579033	18509	19931
30°	646080	15192	19193
35°	655766	9824	12782
40°	660602	4716	6469
45°	656471	1977	2698
50°	525595	887	887
55°	156754	640	86
60°	31993	735	0
65°	3048	869	0
70°	321	1202	0
75°	0	1589	0
80°	0	2652	284
85°	0	5284	566



TEST NUMBER: P1192248

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.6	2.9
10°-20°	670.6	14.0
20°-30°	1232.4	25.8
30°-40°	1413.9	29.6
40°-50°	1069.8	22.4
50°-60°	237.1	5.0
60°-70°	10.1	0.2
70°-80°	4.4	0.1
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2041.6	42.7
0°-40°	3455.5	72.3
0°-60°	4762.3	99.6
0°-90°	4781.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4781.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1073	1073	1073	1073	1073	
5°	2734	2042	986	482	360	361
15°	8311	4508	564	146	147	2316
25°	9573	5300	306	296	330	4466
35°	9799	3272	147	184	191	6138
45°	8468	926	26	33	35	6319
55°	1640	35	7	5	1	2030
65°	24	5	7	4	0	63
75°	0	4	8	5	0	0
85°	0	5	8	5	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192248

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3
2.5°	1817.9	1800.1	1804.8	1827.4	1734.2	1731.3	1688.1	1682.4	1639.0	1560.0	1520.5
5°	2734.1	2722.7	2703.0	2710.6	2604.1	2532.5	2457.2	2402.6	2291.5	2141.8	2042.0
7.5°	4195.2	4072.7	4013.5	3899.5	3764.0	3625.5	3486.3	3324.3	3090.9	2830.0	2619.1
10°	5808.8	5755.2	5633.7	5561.3	5260.8	5057.5	4841.0	4509.6	4082.1	3609.6	3216.0
12.5°	7390.4	7327.4	7143.9	6989.4	6589.2	6407.6	6126.1	5708.0	5165.8	4492.6	3870.4
15°	8311.3	8325.4	8117.3	8109.8	7765.3	7528.9	7285.1	6790.8	6102.6	5329.7	4507.7
17.5°	8850.7	8885.6	8679.4	8737.7	8394.0	8149.3	7967.6	7606.0	6874.6	5947.2	5000.1
20°	9155.7	9211.3	8991.8	9037.2	8743.4	8577.6	8393.1	8035.4	7389.5	6366.3	5279.7
22.5°	9388.3	9410.0	9166.0	9226.4	8905.3	8739.6	8608.8	8273.6	7636.2	6587.5	5367.3
25°	9572.8	9627.4	9348.8	9353.4	9034.3	8868.5	8723.6	8418.6	7741.7	6645.8	5300.5
27.5°	9838.3	9882.5	9472.9	9437.3	9128.4	8945.8	8788.5	8488.2	7737.0	6515.9	5048.1
30°	10206.5	9959.8	9540.9	9448.5	9101.1	8915.6	8747.1	8357.3	7563.7	6165.6	4589.6
32.5°	10101.0	9901.3	9488.0	9341.2	8996.6	8797.9	8605.0	8130.5	7161.8	5623.3	3964.5
35°	9798.8	9734.8	9300.7	9254.6	8837.5	8629.4	8435.4	7786.8	6545.1	4914.4	3271.6
37.5°	9543.6	9434.4	9154.8	9082.3	8644.5	8414.8	8106.0	7273.8	5729.8	4010.7	2612.5
40°	9231.1	9157.6	8887.3	8810.3	8303.7	7953.5	7576.0	6343.6	4745.0	3121.9	2017.6
42.5°	8898.7	8832.8	8577.6	8415.8	7740.7	7277.5	6691.0	5217.6	3652.9	2352.8	1512.0
45°	8467.6	8374.3	8055.1	7753.9	6786.1	6123.2	5463.3	3981.4	2673.7	1674.8	925.5
47.5°	7726.6	7578.8	7191.8	6586.5	5397.4	4760.9	4073.7	2700.2	1651.3	862.4	466.0
50°	6162.8	5904.9	5389.9	4669.7	3457.1	2847.0	2308.5	1372.7	709.0	444.4	273.9
52.5°	3797.9	3561.6	3122.8	2428.1	1593.9	1227.6	966.9	639.2	390.7	251.4	101.6
55°	1640.1	1492.2	1282.3	978.1	694.8	571.5	459.4	319.2	201.4	77.3	34.8
57.5°	619.5	575.2	521.6	428.4	320.1	267.4	225.0	141.2	49.0	29.2	19.8
60°	291.8	264.6	233.5	185.5	122.4	88.5	55.5	35.8	23.5	16.0	11.3
62.5°	80.0	60.2	49.8	40.5	31.0	27.2	23.5	17.9	13.2	8.4	6.7
65°	23.5	20.8	19.8	17.0	14.1	12.2	10.4	8.4	6.7	4.7	4.7
67.5°	8.4	8.4	7.5	6.7	5.7	4.7	4.7	3.7	3.7	3.7	3.7
70°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.8	2.8	3.7	3.7
72.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	2.8	3.7	3.7
75°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	2.8	3.7	3.7
77.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
80°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
87.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192248

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3
2.5°	1487.5	1432.9	1355.6	1316.2	1281.3	1271.9	1200.4	1154.2	1099.7	1043.2	983.8
5°	1948.8	1809.5	1661.6	1537.4	1474.3	1437.6	1298.2	1193.8	1093.0	985.7	894.4
7.5°	2406.4	2156.9	1941.3	1740.8	1630.6	1547.7	1348.2	1190.9	1038.4	899.1	775.7
10°	2848.9	2489.2	2145.6	1874.4	1722.9	1599.5	1341.6	1137.3	946.2	786.1	657.2
12.5°	3297.0	2772.5	2316.0	1946.0	1765.2	1607.1	1296.5	1047.9	845.5	676.0	542.3
15°	3697.1	2992.9	2422.4	1962.9	1744.6	1558.1	1208.0	933.9	732.5	563.9	447.2
17.5°	3974.9	3111.6	2428.9	1900.9	1657.9	1457.5	1084.6	814.3	618.6	469.8	367.1
20°	4100.9	3107.7	2339.5	1771.8	1517.7	1308.6	938.7	691.9	515.8	394.5	306.9
22.5°	4063.3	2989.1	2181.4	1589.2	1346.3	1137.3	803.1	583.6	443.5	338.9	269.3
25°	3875.0	2782.0	1995.9	1406.5	1161.7	966.9	680.7	499.0	385.0	306.0	244.8
27.5°	3567.2	2499.5	1746.4	1192.9	968.8	817.2	573.4	431.2	338.9	270.2	255.1
30°	3117.2	2156.9	1453.6	962.2	782.4	646.8	465.1	347.4	271.1	240.0	241.1
32.5°	2621.1	1779.3	1142.9	735.3	589.4	499.0	343.6	242.8	198.6	196.8	197.7
35°	2126.8	1385.9	850.2	537.6	432.1	359.6	221.2	152.6	147.9	146.8	148.7
37.5°	1688.1	1030.8	612.9	375.6	286.2	219.3	119.6	103.6	99.8	101.6	102.6
40°	1260.6	723.1	414.2	222.2	139.3	100.8	72.5	66.9	64.9	65.9	65.9
42.5°	867.0	451.9	246.7	92.2	66.9	55.5	46.1	43.4	41.4	40.5	41.4
45°	467.0	281.4	96.1	47.1	39.6	35.8	29.2	27.2	26.3	25.5	25.5
47.5°	298.5	104.5	43.4	29.2	25.5	23.5	19.8	17.9	17.0	16.0	16.0
50°	112.0	40.5	26.3	18.8	16.0	15.1	12.2	11.3	10.4	10.4	10.4
52.5°	38.6	24.5	17.0	12.2	10.4	9.5	8.4	7.5	7.5	7.5	7.5
55°	21.6	15.1	10.4	7.5	7.5	6.7	6.7	6.7	6.7	6.7	6.7
57.5°	13.2	8.4	6.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	6.7
60°	7.5	5.7	5.7	5.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7
62.5°	4.7	4.7	4.7	4.7	4.7	5.7	5.7	6.7	6.7	6.7	6.7
65°	4.7	4.7	4.7	4.7	4.7	5.7	5.7	6.7	6.7	6.7	6.7
67.5°	3.7	4.7	4.7	5.7	5.7	5.7	5.7	6.7	6.7	7.5	6.7
70°	4.7	4.7	4.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	7.5
72.5°	4.7	4.7	4.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	7.5
75°	4.7	4.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	7.5	7.5
77.5°	4.7	4.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	8.4	7.5
80°	4.7	4.7	5.7	6.7	6.7	6.7	6.7	7.5	7.5	8.4	8.4
82.5°	4.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	8.4	8.4	8.4
85°	4.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	8.4	8.4	8.4
87.5°	4.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	8.4	8.4	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192248

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3
2.5°	951.8	897.3	853.0	853.9	817.2	789.0	753.2	733.4	717.4	691.0	666.6
5°	827.5	743.7	680.7	668.4	626.1	582.7	538.5	505.6	482.0	456.6	433.1
7.5°	693.0	596.9	524.5	507.4	471.6	431.2	390.7	357.8	329.5	302.2	273.9
10°	562.1	474.4	408.6	391.7	355.8	313.5	275.0	245.8	224.0	202.4	180.8
12.5°	454.7	377.5	315.4	293.8	264.6	231.6	200.5	172.2	148.7	139.3	136.6
15°	368.2	294.6	245.8	227.9	203.4	169.4	151.6	146.8	145.9	145.9	145.9
17.5°	297.5	240.0	195.7	176.9	164.7	162.9	162.9	162.9	163.8	165.7	169.4
20°	249.5	198.6	181.7	183.6	183.6	185.5	189.3	192.0	195.7	200.5	206.1
22.5°	221.2	210.9	209.0	214.7	215.6	221.2	228.7	234.4	241.1	248.6	253.2
25°	242.0	245.8	248.6	257.0	259.9	269.3	280.5	289.0	296.5	305.0	310.6
27.5°	263.6	270.2	275.8	284.3	286.2	298.5	307.9	313.5	319.2	322.9	326.8
30°	248.6	255.1	260.8	268.3	268.3	281.4	286.2	290.9	295.6	297.5	301.3
32.5°	204.4	210.9	216.5	222.2	223.2	232.5	238.2	240.0	243.8	244.8	247.5
35°	153.4	156.3	161.9	166.7	167.5	174.2	178.9	180.8	183.6	183.6	185.5
37.5°	105.5	107.3	112.0	114.9	116.7	121.5	124.3	126.2	128.0	129.1	129.9
40°	68.6	69.7	72.5	75.3	77.3	80.0	82.0	83.7	84.8	86.6	86.6
42.5°	42.3	43.4	45.1	47.1	47.1	49.8	50.9	52.7	53.7	54.6	54.6
45°	26.3	27.2	27.2	28.3	29.2	30.2	32.0	32.0	33.0	33.0	33.0
47.5°	16.0	17.0	16.0	17.0	17.0	17.9	18.8	18.8	18.8	18.8	18.8
50°	10.4	10.4	10.4	10.4	10.4	10.4	11.3	11.3	11.3	11.3	10.4
52.5°	7.5	7.5	6.7	7.5	6.7	6.7	6.7	6.7	6.7	6.7	5.7
55°	6.7	6.7	6.7	6.7	5.7	5.7	5.7	4.7	4.7	3.7	3.7
57.5°	6.7	6.7	5.7	5.7	5.7	4.7	4.7	4.7	3.7	3.7	2.8
60°	6.7	6.7	5.7	5.7	5.7	4.7	4.7	3.7	3.7	2.8	2.8
62.5°	6.7	6.7	5.7	5.7	5.7	5.7	4.7	4.7	3.7	3.7	2.8
65°	6.7	6.7	6.7	5.7	5.7	5.7	4.7	4.7	3.7	3.7	2.8
67.5°	6.7	6.7	6.7	6.7	5.7	5.7	5.7	4.7	3.7	3.7	2.8
70°	6.7	6.7	6.7	6.7	6.7	5.7	5.7	4.7	4.7	3.7	2.8
72.5°	7.5	7.5	6.7	6.7	6.7	5.7	5.7	4.7	4.7	3.7	3.7
75°	7.5	7.5	6.7	6.7	6.7	5.7	5.7	4.7	4.7	3.7	3.7
77.5°	7.5	7.5	7.5	7.5	6.7	6.7	5.7	5.7	4.7	4.7	3.7
80°	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.7	4.7	4.7	3.7
82.5°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.7	4.7	4.7	3.7
85°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.7	4.7	4.7	3.7
87.5°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.7	4.7	4.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192248

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3	1073.3
2.5°	644.0	631.7	630.8	620.4	599.8	610.2	596.9	587.4
5°	412.4	399.2	385.9	387.9	372.8	375.6	365.2	359.6
7.5°	261.7	247.5	243.8	243.8	226.9	226.9	220.3	216.5
10°	164.7	153.4	149.7	143.1	135.5	134.6	131.8	130.8
12.5°	133.7	133.7	130.8	131.8	131.8	131.8	130.8	130.8
15°	145.9	146.8	144.0	145.0	146.8	145.9	146.8	146.8
17.5°	168.5	173.2	169.4	171.4	175.1	174.2	175.1	176.1
20°	206.1	213.7	209.0	212.8	217.5	216.5	219.3	220.3
22.5°	257.0	266.3	261.7	265.5	273.0	271.1	275.0	276.7
25°	313.5	322.9	317.3	322.0	326.8	328.5	328.5	329.5
27.5°	326.8	332.3	328.5	333.2	335.2	337.0	335.2	336.1
30°	299.3	304.1	300.4	305.0	305.0	306.9	305.0	303.2
32.5°	246.7	250.4	245.8	251.4	250.4	251.4	252.3	253.2
35°	186.4	188.2	185.5	186.4	187.3	188.2	191.0	191.0
37.5°	129.9	132.8	129.9	130.8	130.8	132.8	134.6	134.6
40°	86.6	89.4	86.6	88.5	87.5	88.5	90.4	90.4
42.5°	54.6	56.5	54.6	55.5	55.5	55.5	56.5	57.4
45°	33.0	33.9	33.0	33.9	33.9	33.9	34.8	34.8
47.5°	18.8	19.8	18.8	18.8	19.8	18.8	19.8	19.8
50°	10.4	10.4	10.4	10.4	10.4	9.5	9.5	10.4
52.5°	5.7	5.7	4.7	4.7	4.7	4.7	4.7	4.7
55°	2.8	2.8	2.0	2.0	2.0	0.9	2.0	0.9
57.5°	2.0	2.0	0.9	0.9	0.9	0.9	0.0	0.0
60°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
62.5°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
65°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
67.5°	2.8	2.0	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.8	2.0	2.0	0.9	0.9	0.0	0.0	0.0
72.5°	2.8	2.0	2.0	2.0	0.9	0.9	0.0	0.0
75°	2.8	2.0	2.0	2.0	0.9	0.9	0.0	0.0
77.5°	2.8	2.8	2.0	2.0	0.9	0.9	0.9	0.0
80°	2.8	2.8	2.0	2.0	2.0	0.9	0.9	0.9
82.5°	2.8	2.8	2.0	2.0	2.0	0.9	0.9	0.9
85°	2.8	2.8	2.0	2.0	2.0	0.9	0.9	0.9
87.5°	2.8	2.8	2.0	2.0	2.0	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)