

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192253

Luminaire Tested: **LDA6A40950D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26669)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40950D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3604.2 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 2.14 / 1.07 / 1.49
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192253

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192253

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62		
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55		
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49		
7	72	59	52	46	70	59	51	46	57	51	46	56	50	45	55	49	45	43		
8	67	54	47	41	65	54	46	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	37	33	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63279	63279	63279
5°	101293	62486	40513
10°	148016	60013	27304
15°	202362	56913	20624
20°	253165	53887	20821
25°	292450	53701	32288
30°	320366	50837	30043
35°	330807	43105	23189
40°	323764	33627	18256
45°	295124	24817	14017
50°	237212	18319	9398
55°	144435	12951	5304
60°	74950	8563	2061
65°	36515	4514	973
70°	16750	1955	914
75°	6990	1419	996
80°	3567	1484	1168
85°	2327	2956	1761

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192253

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.4	3.3
10°-20°	419.5	11.6
20°-30°	794.2	22.0
30°-40°	961.9	26.7
40°-50°	805.1	22.3
50°-60°	390.1	10.8
60°-70°	95.7	2.7
70°-80°	15.6	0.4
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1332.1	37.0
0°-40°	2294.0	63.6
0°-60°	3489.2	96.8
0°-90°	3604.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3604.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1154	1154	1154	1154	1154	
5°	1841	1586	1136	830	736	201
15°	3566	2479	1003	458	363	1029
25°	4835	2921	888	523	534	2227
35°	4943	2581	644	372	346	3063
45°	3807	1741	320	195	181	2888
55°	1511	714	136	73	56	1416
65°	282	156	35	11	8	317
75°	33	17	7	6	5	45
85°	4	3	5	4	3	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192253

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3
2.5°	1465.0	1431.2	1438.7	1444.4	1418.9	1435.0	1407.6	1398.3	1375.6	1381.2	1364.4
5°	1840.7	1793.7	1779.5	1779.5	1737.2	1751.3	1726.8	1683.4	1639.2	1626.0	1585.6
7.5°	2244.7	2192.9	2170.3	2160.8	2098.7	2090.2	2069.6	2002.7	1930.1	1891.6	1820.0
10°	2659.0	2611.9	2579.9	2558.2	2472.5	2457.5	2420.7	2326.6	2235.3	2152.4	2034.7
12.5°	3115.6	3052.5	3010.2	2974.3	2864.3	2840.8	2786.1	2659.9	2515.8	2416.0	2260.6
15°	3565.6	3501.7	3446.1	3394.4	3260.6	3226.7	3153.3	2993.1	2824.6	2675.9	2479.2
17.5°	3994.1	3913.1	3845.3	3775.6	3618.4	3576.0	3480.0	3302.0	3066.6	2898.2	2660.8
20°	4339.6	4260.6	4182.4	4093.9	3914.0	3863.3	3746.4	3535.6	3268.1	3065.7	2789.0
22.5°	4622.1	4532.6	4455.4	4339.6	4137.2	4077.8	3943.3	3704.1	3414.9	3178.7	2874.7
25°	4834.9	4739.8	4660.7	4530.9	4306.6	4237.9	4080.8	3821.7	3506.4	3246.5	2920.7
27.5°	5002.5	4893.3	4803.9	4659.7	4413.0	4335.9	4163.5	3883.9	3543.1	3259.7	2918.8
30°	5061.0	4954.5	4853.7	4698.3	4432.8	4347.1	4168.2	3865.1	3510.1	3205.1	2853.9
32.5°	5035.5	4925.2	4816.0	4651.3	4370.7	4278.5	4097.6	3773.8	3409.4	3088.3	2734.3
35°	4943.1	4831.1	4714.4	4544.0	4250.2	4150.4	3969.6	3634.4	3255.9	2934.9	2580.9
37.5°	4775.6	4663.5	4553.4	4369.8	4069.4	3965.8	3787.9	3440.4	3071.3	2747.5	2402.8
40°	4524.2	4413.0	4311.4	4125.9	3823.7	3719.1	3550.7	3205.9	2850.1	2529.9	2198.5
42.5°	4200.2	4093.9	4002.5	3820.9	3525.2	3425.3	3267.3	2933.8	2601.5	2291.7	1980.2
45°	3806.7	3709.7	3626.0	3454.6	3181.6	3085.5	2945.3	2629.7	2320.0	2030.0	1741.0
47.5°	3352.9	3264.4	3190.9	3032.7	2779.5	2691.9	2571.4	2278.5	2001.8	1737.2	1480.1
50°	2781.4	2704.2	2653.2	2516.8	2290.8	2217.3	2124.1	1877.4	1650.5	1422.6	1209.8
52.5°	2122.3	2062.0	2038.4	1935.9	1760.7	1709.9	1649.5	1460.3	1294.6	1114.8	949.0
55°	1511.2	1471.7	1456.5	1389.8	1274.9	1242.0	1190.1	1073.4	963.1	836.1	713.6
57.5°	1029.2	1008.4	997.0	955.7	885.0	862.5	833.2	758.0	687.3	604.4	517.0
60°	683.6	675.1	665.6	640.3	598.8	581.9	567.7	517.9	474.6	422.8	361.6
62.5°	443.5	439.7	433.1	417.1	401.1	389.9	374.7	341.8	316.4	290.1	243.8
65°	281.5	277.7	275.0	264.6	254.2	242.9	237.3	218.5	202.4	185.5	156.3
67.5°	174.2	171.4	170.5	163.8	156.3	149.7	145.9	133.7	124.3	114.0	95.1
70°	104.5	103.6	101.7	97.9	93.2	88.5	86.6	78.1	72.5	65.9	53.7
72.5°	60.2	59.3	58.4	55.5	52.7	50.9	49.0	46.1	39.6	35.8	30.2
75°	33.0	33.0	32.0	30.2	29.2	27.2	26.3	24.5	21.6	19.8	17.0
77.5°	18.8	17.9	17.9	17.0	16.0	16.0	15.1	14.1	12.2	12.2	10.4
80°	11.3	11.3	11.3	10.4	10.4	10.4	9.5	9.5	8.4	7.5	7.5
82.5°	7.5	6.7	6.7	6.7	6.7	6.7	5.7	5.7	5.7	5.7	4.7
85°	3.7	3.7	3.7	3.7	2.8	3.7	2.8	2.8	2.8	2.8	2.8
87.5°	0.0	0.0	0.9	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192253

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3
2.5°	1320.1	1310.6	1291.8	1265.5	1256.1	1250.4	1219.3	1191.0	1171.2	1145.9	1121.4
5°	1512.1	1477.3	1432.1	1377.5	1355.7	1336.9	1279.6	1226.9	1183.5	1135.5	1090.3
7.5°	1710.8	1645.8	1569.6	1483.0	1447.2	1414.2	1327.6	1249.5	1182.6	1113.9	1048.8
10°	1897.3	1798.4	1688.2	1572.5	1518.7	1470.7	1355.7	1255.1	1166.6	1078.1	998.1
12.5°	2079.9	1945.2	1799.3	1650.5	1580.9	1518.7	1376.5	1253.2	1144.0	1040.4	948.2
15°	2256.0	2081.8	1902.0	1719.3	1635.4	1559.2	1390.7	1246.6	1120.4	1002.8	900.1
17.5°	2398.1	2192.9	1975.5	1760.7	1666.6	1578.1	1388.8	1227.8	1088.5	960.3	851.1
20°	2498.0	2261.6	2019.6	1779.5	1677.0	1578.9	1374.6	1202.3	1055.5	923.7	813.5
22.5°	2554.4	2293.6	2034.7	1779.5	1669.4	1566.8	1354.9	1178.8	1031.0	902.0	796.6
25°	2578.0	2299.2	2028.1	1764.5	1650.5	1545.0	1332.2	1156.3	1011.2	887.8	790.0
27.5°	2559.1	2266.4	1991.4	1723.1	1606.4	1500.8	1289.1	1116.6	976.5	858.7	765.4
30°	2483.8	2183.5	1909.4	1643.0	1525.4	1422.6	1217.4	1050.8	916.1	803.1	714.7
32.5°	2361.4	2062.9	1793.7	1533.8	1417.1	1318.1	1122.4	964.1	835.2	727.8	645.9
35°	2212.6	1919.8	1659.9	1406.7	1294.6	1200.5	1015.9	861.5	742.9	644.1	568.7
37.5°	2045.1	1761.7	1504.6	1272.0	1164.7	1075.3	902.9	758.0	648.8	557.3	490.5
40°	1856.8	1589.3	1347.3	1127.0	1025.3	942.6	779.6	651.6	551.7	469.9	413.4
42.5°	1658.1	1408.6	1183.5	977.3	881.3	806.0	658.1	544.2	456.6	389.9	344.6
45°	1445.3	1214.6	1008.4	823.9	743.8	668.5	543.3	439.7	371.0	320.1	286.3
47.5°	1218.5	1014.1	832.3	671.3	601.6	535.8	430.2	351.2	301.3	262.6	237.3
50°	990.6	818.2	663.8	526.3	467.0	414.2	333.3	279.7	242.9	214.8	194.0
52.5°	773.9	634.6	508.5	396.3	352.1	314.5	258.9	221.2	194.0	172.3	157.2
55°	580.9	470.8	371.9	288.1	261.8	238.3	201.4	171.4	152.6	135.5	124.3
57.5°	420.9	336.1	264.6	211.8	194.9	178.9	152.6	131.8	117.7	104.5	96.1
60°	295.7	233.6	187.3	155.4	142.2	132.8	112.0	98.8	87.5	78.1	69.7
62.5°	198.6	158.2	130.8	110.2	101.7	95.1	82.0	70.6	62.2	54.6	47.1
65°	127.1	106.5	88.5	74.4	68.6	64.0	55.5	46.1	40.5	34.8	29.2
67.5°	78.1	66.9	55.5	46.1	42.3	39.6	33.9	28.3	24.5	20.8	17.9
70°	45.1	38.6	32.0	27.2	25.5	23.5	19.8	17.0	15.1	12.2	10.4
72.5°	25.5	22.6	18.8	16.0	15.1	14.1	12.2	10.4	9.5	8.4	7.5
75°	15.1	13.2	11.3	10.4	9.5	9.5	8.4	7.5	6.7	6.7	5.7
77.5°	9.5	8.4	7.5	7.5	6.7	6.7	6.7	5.7	5.7	5.7	5.7
80°	6.7	6.7	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7	4.7
82.5°	4.7	4.7	4.7	3.7	3.7	3.7	3.7	3.7	4.7	4.7	4.7
85°	2.8	2.8	3.7	3.7	3.7	3.7	3.7	3.7	4.7	4.7	4.7
87.5°	2.8	2.8	2.8	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192253

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3
2.5°	1095.1	1083.8	1063.0	1044.2	1041.4	1015.0	987.7	982.0	972.6	957.6	939.6
5°	1045.1	1015.0	979.2	952.8	941.5	903.9	866.2	849.4	830.5	801.3	784.3
7.5°	986.8	942.6	892.5	862.5	846.5	799.3	756.1	731.5	706.2	675.1	654.4
10°	922.7	867.2	808.8	774.9	756.1	705.2	659.2	630.9	603.5	572.4	550.9
12.5°	862.5	799.3	735.4	699.6	678.9	626.2	579.1	548.9	521.7	496.2	470.8
15°	808.8	738.2	671.3	635.5	613.9	560.2	515.0	485.0	458.5	434.0	411.4
17.5°	757.0	683.6	617.7	582.8	561.1	511.3	467.9	440.6	415.2	392.6	372.8
20°	721.2	651.6	589.4	556.4	537.6	493.4	456.6	435.0	417.1	397.4	380.4
22.5°	711.9	649.7	596.0	568.7	554.6	519.7	493.4	480.3	474.6	462.3	452.8
25°	711.9	657.2	612.0	589.4	578.1	551.7	531.0	526.3	522.6	515.0	510.3
27.5°	693.9	643.0	602.7	582.8	573.5	549.8	532.1	526.3	521.7	515.9	510.3
30°	646.8	599.8	562.1	544.2	534.8	512.2	493.4	486.7	482.0	473.6	468.9
32.5°	583.9	538.5	507.5	486.7	478.3	456.6	438.8	431.3	427.5	420.0	411.4
35°	513.2	473.6	443.5	426.5	418.1	399.3	383.2	375.8	371.9	363.4	353.1
37.5°	441.6	405.8	381.3	365.4	358.7	343.6	329.5	324.0	320.1	313.6	305.1
40°	371.0	345.6	324.0	311.7	306.0	293.8	281.5	275.9	273.0	267.4	260.8
42.5°	312.6	291.8	275.0	264.6	259.9	250.4	240.0	234.4	231.6	226.0	221.2
45°	261.8	245.8	232.5	223.2	219.4	210.9	202.4	197.7	194.9	190.2	185.5
47.5°	219.4	205.3	194.0	187.3	183.6	177.0	169.4	164.7	163.0	159.1	154.3
50°	179.8	169.4	160.1	154.3	151.6	145.0	138.4	134.7	132.8	129.1	124.3
52.5°	145.0	137.5	129.1	123.3	120.5	115.9	109.2	105.5	102.6	98.8	93.2
55°	114.0	107.3	100.8	95.1	93.2	87.5	82.0	76.2	73.4	69.7	64.9
57.5°	88.5	81.0	74.4	69.7	67.8	62.2	56.5	50.9	48.0	43.4	40.5
60°	63.1	56.5	49.8	47.1	45.1	39.6	34.8	30.2	28.3	25.5	23.5
62.5°	41.4	36.7	31.0	28.3	27.2	23.5	19.8	18.8	17.0	16.0	15.1
65°	25.5	22.6	18.8	17.0	16.0	15.1	13.2	12.2	11.3	10.4	10.4
67.5°	15.1	14.1	12.2	11.3	10.4	9.5	9.5	8.4	8.4	7.5	7.5
70°	10.4	9.5	8.4	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7
72.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
75°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
77.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	4.7	4.7
80°	4.7	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7	4.7	4.7
82.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
85°	4.7	4.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7	3.7	2.8
87.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	2.8	2.8	2.8	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192253

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3	1154.3
2.5°	937.8	929.3	920.8	934.0	933.1	920.0	929.3	914.3
5°	774.9	762.6	753.3	761.7	757.0	743.8	749.5	736.2
7.5°	642.1	628.0	616.7	623.3	615.8	603.5	601.6	596.0
10°	536.7	521.7	511.3	515.9	508.5	497.1	494.4	490.5
12.5°	456.6	442.5	433.1	436.9	429.3	418.9	417.1	420.0
15°	394.6	384.2	376.6	379.5	369.1	363.4	361.6	363.4
17.5°	358.7	347.5	341.8	344.6	337.1	331.4	330.5	329.5
20°	373.8	365.4	363.4	368.2	362.4	357.8	360.7	356.9
22.5°	455.7	454.8	455.7	467.0	464.2	462.3	464.2	464.2
25°	513.2	517.0	517.9	530.1	531.0	529.2	533.8	533.8
27.5°	511.3	512.2	511.3	523.4	525.4	521.7	526.3	527.3
30°	466.1	466.1	463.2	473.6	473.6	471.6	473.6	474.6
32.5°	406.7	405.8	404.9	409.6	409.6	406.7	408.7	408.7
35°	351.2	347.5	347.5	350.3	349.3	346.5	347.5	346.5
37.5°	303.2	298.5	298.5	300.5	297.5	294.7	295.7	295.7
40°	258.9	255.1	255.1	257.9	256.2	253.2	255.1	255.1
42.5°	217.5	216.5	216.5	218.5	218.5	216.5	219.4	220.3
45°	183.6	180.8	180.8	182.6	182.6	180.8	181.8	180.8
47.5°	152.6	149.7	149.7	149.7	147.9	145.0	145.0	144.1
50°	121.5	116.7	115.9	115.9	114.0	111.2	111.2	110.2
52.5°	90.4	85.7	85.7	84.8	82.8	82.0	81.0	81.0
55°	62.2	58.4	59.3	57.4	57.4	55.5	56.5	55.5
57.5°	38.6	36.7	36.7	35.8	33.9	33.0	33.0	32.0
60°	22.6	20.8	20.8	20.8	19.8	18.8	18.8	18.8
62.5°	15.1	14.1	14.1	14.1	12.2	12.2	11.3	11.3
65°	9.5	8.4	8.4	8.4	7.5	7.5	7.5	7.5
67.5°	7.5	7.5	6.7	6.7	6.7	6.7	6.7	6.7
70°	6.7	6.7	6.7	6.7	6.7	5.7	5.7	5.7
72.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
75°	5.7	5.7	4.7	5.7	4.7	4.7	4.7	4.7
77.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
80°	4.7	4.7	4.7	4.7	4.7	3.7	3.7	3.7
82.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
85°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
87.5°	2.8	2.0	2.0	2.0	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)