

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179614

Luminaire Tested: **LDA6A45835D010TE LARH40FL 6LFC1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26667)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A45835D010TE LARH40FL 6LFC1H
Description: PORTFOLIO 6" Flat Cone, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5004.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.61
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179614

CATALOG NUMBER: LDA6A45835D010TE LARH40FL 6LFC1H

Luminous Intensity Polar Plot





TEST NUMBER: P179614

CATALOG NUMBER: LDA6A45835D010TE LARH40FL 6LFC1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96			96
2	110	107	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92			92
3	106	101	97	94	105	100	96	94	98	95	92	95	93	91	93	91	89	88			88
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84			84
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81			81
6	96	89	84	81	94	88	84	81	87	83	80	85	82	79	84	81	79	78			78
7	92	85	81	77	91	85	80	77	83	80	77	82	79	76	81	78	76	75			75
8	89	82	77	74	88	81	77	74	80	76	74	80	76	73	79	75	73	72			72
9	86	79	74	71	85	78	74	71	78	74	71	77	73	71	76	73	70	69			69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	683750
5°	614658
10°	559147
15°	511110
20°	375046
25°	185388
30°	40259
35°	7629
40°	2075
45°	930
50°	512
55°	478
60°	329
65°	389
70°	321
75°	212
80°	316
85°	0



TEST NUMBER: P179614

CATALOG NUMBER: LDA6A45835D010TE LARH40FL 6LFC1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1033.3	20.6
10°-20°	2422.5	48.4
20°-30°	1407.3	28.1
30°-40°	122.1	2.4
40°-50°	10.5	0.2
50°-60°	4.1	0.1
60°-70°	2.6	0.1
70°-80°	1.2	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4863.1	97.2
0°-40°	4985.2	99.6
0°-60°	4999.8	99.9
0°-90°	5004.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5004.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12473	
5°	11170	###
15°	9006	2423
25°	3065	1407
35°	114	122
45°	12	11
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P179614

CATALOG NUMBER: LDA6A45835D010TE LARH40FL 6LFC1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	12472.6
2.5°	11820.6
5°	11169.6
7.5°	10578.7
10°	10044.7
12.5°	9575.7
15°	9005.7
17.5°	8054.7
20°	6428.8
22.5°	4656.8
25°	3064.9
27.5°	1600.9
30°	636.0
32.5°	330.0
35°	114.0
37.5°	47.0
40°	29.0
42.5°	18.0
45°	12.0
47.5°	8.0
50°	6.0
52.5°	5.0
55°	5.0
57.5°	4.0
60°	3.0
62.5°	3.0
65°	3.0
67.5°	2.0
70°	2.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)