

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192322

Luminaire Tested: **LDA6A45950D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192322
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26670)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A45950D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4484.7 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.6 / 1.28
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 53.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192322

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192322

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	109	106	104	110	107	105	102		103	101	99			99	98	96			96
2	106	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	91	85	81	97	90	84	80		87	83	79			85	81	77			82
4	92	83	77	72	91	82	76	71		80	75	71			78	73	70			76
5	86	76	69	64	85	75	69	64		74	68	63			72	67	63			70
6	81	70	63	58	79	69	62	58		68	62	57			66	61	57			65
7	76	64	57	52	74	64	57	52		62	56	52			61	55	51			60
8	71	59	52	47	69	59	52	47		57	51	47			56	51	47			55
9	66	55	48	43	65	54	47	43		53	47	43			52	47	43			51
10	62	51	44	39	61	50	44	39		49	43	39			48	43	39			48

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	78689	78689	78689
5°	151425	75385	28230
10°	250469	66153	10153
15°	369775	53377	16186
20°	536923	33988	27402
25°	771311	29693	33226
30°	873609	25713	24181
35°	873681	13351	12408
40°	705672	4974	5195
45°	528404	1729	1868
50°	345916	682	606
55°	40658	573	96
60°	1217	658	0
65°	272	778	0
70°	160	962	0
75°	0	1504	0
80°	0	2241	316
85°	0	4466	629



TEST NUMBER: P1192322

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.1	3.3
10°-20°	600.0	13.4
20°-30°	1316.5	29.4
30°-40°	1461.5	32.6
40°-50°	846.0	18.9
50°-60°	100.5	2.2
60°-70°	3.9	0.1
70°-80°	4.2	0.1
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2064.6	46.0
0°-40°	3526.1	78.6
0°-60°	4472.7	99.7
0°-90°	4484.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4484.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1435	1435	1435	1435	1435	
5°	2752	2225	1370	784	513	316
15°	6515	3769	940	255	285	1956
25°	12752	4376	491	546	549	5759
35°	13055	3192	200	197	185	7871
45°	6816	752	22	26	24	5327
55°	425	6	6	4	1	936
65°	2	4	6	4	0	3
75°	0	4	7	4	0	0
85°	0	4	7	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192322

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4
2.5°	2087.4	2046.2	2004.8	2001.8	1967.5	1922.1	1953.4	1886.9	1907.0	1856.6	1825.4
5°	2751.7	2706.4	2646.0	2628.7	2570.4	2502.8	2527.9	2411.0	2399.0	2302.1	2224.6
7.5°	3566.1	3513.7	3419.0	3373.6	3276.9	3176.2	3188.1	3000.6	2944.2	2785.0	2642.8
10°	4499.5	4462.2	4326.2	4232.4	4080.1	3933.1	3907.9	3630.7	3507.7	3257.7	3034.0
12.5°	5546.8	5491.4	5302.9	5160.7	4953.1	4766.5	4711.1	4314.0	4093.3	3731.5	3414.0
15°	6515.4	6478.1	6315.8	6102.2	5839.1	5598.2	5503.4	5039.7	4691.0	4210.2	3768.8
17.5°	7757.3	7654.4	7362.1	6942.7	6566.9	6326.9	6212.0	5631.4	5204.1	4617.4	4054.0
20°	9203.6	9064.5	8616.9	8036.5	7412.5	6991.2	6738.2	6113.3	5584.0	4902.7	4239.5
22.5°	11297.1	11014.0	10164.2	9124.0	8256.1	7693.7	7331.9	6423.7	5861.3	5081.1	4342.3
25°	12751.6	12502.6	11726.5	10358.7	8967.8	8320.6	7811.6	6680.8	6042.7	5186.9	4376.5
27.5°	13673.0	13540.9	12647.9	11281.1	9518.1	8676.5	8101.0	6843.0	6111.2	5184.0	4307.1
30°	13800.9	13809.0	12980.4	11528.0	9561.4	8685.6	8038.5	6773.5	5969.1	4988.5	4078.2
32.5°	13745.5	13635.6	12613.6	11060.3	9081.6	8312.6	7697.8	6480.1	5626.4	4595.2	3681.1
35°	13055.0	12810.2	11729.6	10016.0	8383.2	7651.4	7077.8	6010.5	5081.1	4074.2	3192.2
37.5°	11789.0	11401.0	10194.5	8735.0	7526.5	6881.3	6447.9	5409.7	4516.6	3531.8	2706.4
40°	9860.9	9443.6	8592.8	7573.8	6621.3	6178.8	5762.4	4750.5	3880.7	2977.5	2236.7
42.5°	8158.4	7929.6	7294.7	6514.4	5880.5	5424.8	5027.7	4064.1	3271.8	2438.3	1584.5
45°	6815.7	6660.6	6260.4	5687.9	5059.0	4643.7	4281.9	3299.0	2390.9	1548.1	751.9
47.5°	5869.3	5696.9	5243.4	4640.6	3901.8	3450.2	3043.0	2057.2	1305.3	598.7	175.3
50°	4056.0	3852.5	3369.6	2789.0	2157.1	1817.4	1533.1	831.6	342.7	103.8	20.2
52.5°	1835.5	1694.4	1391.9	1067.4	705.5	524.2	341.6	144.0	36.3	15.1	11.1
55°	425.4	372.9	283.3	174.3	86.7	57.5	38.3	15.1	11.1	8.0	6.0
57.5°	27.2	24.1	21.2	17.2	14.0	12.2	11.1	8.0	6.0	5.0	4.1
60°	11.1	11.1	10.1	8.0	7.1	6.0	6.0	4.1	4.1	4.1	4.1
62.5°	5.0	5.0	5.0	4.1	3.0	3.0	3.0	3.0	3.0	3.0	4.1
65°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.0	3.0	4.1
67.5°	1.0	1.0	1.0	1.0	2.1	2.1	2.1	2.1	3.0	3.0	4.1
70°	1.0	1.0	1.0	1.0	2.1	2.1	2.1	2.1	3.0	4.1	4.1
72.5°	0.0	1.0	1.0	1.0	2.1	2.1	2.1	2.1	3.0	4.1	4.1
75°	0.0	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1
77.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	2.1	3.0	4.1	4.1
80°	0.0	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1
82.5°	0.0	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1
85°	0.0	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1
87.5°	0.0	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192322

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4
2.5°	1779.0	1735.7	1690.3	1643.9	1622.7	1588.5	1534.1	1495.8	1461.5	1416.2	1358.8
5°	2130.9	2034.0	1932.2	1837.5	1791.1	1730.7	1624.8	1539.1	1459.5	1369.9	1281.1
7.5°	2481.5	2314.2	2152.9	1998.8	1924.2	1837.5	1674.2	1542.1	1417.2	1293.2	1172.3
10°	2793.1	2551.1	2320.2	2105.7	2004.8	1889.0	1675.2	1498.8	1341.6	1188.4	1042.2
12.5°	3083.3	2755.8	2454.4	2176.2	2044.1	1905.1	1646.0	1436.3	1247.9	1069.4	899.1
15°	3339.3	2926.0	2549.1	2209.4	2055.2	1889.0	1592.6	1352.7	1142.0	940.5	721.7
17.5°	3521.8	3023.9	2583.4	2190.2	2016.9	1832.5	1505.9	1248.9	1021.1	773.1	512.1
20°	3618.6	3054.2	2561.2	2129.8	1943.3	1743.7	1404.1	1138.9	878.0	582.6	418.3
22.5°	3652.8	3035.9	2499.7	2044.1	1847.6	1645.0	1300.2	1024.1	713.6	493.9	428.4
25°	3636.7	2981.5	2420.1	1943.3	1746.8	1543.2	1199.4	876.9	577.6	490.9	456.7
27.5°	3528.9	2859.5	2270.9	1792.1	1594.6	1393.0	1024.1	647.1	511.1	460.6	469.7
30°	3291.0	2611.5	2015.9	1545.2	1358.8	1146.1	696.5	475.8	401.2	406.2	406.2
32.5°	2907.9	2240.7	1660.0	1227.7	986.8	714.6	397.1	298.4	303.4	302.3	298.4
35°	2438.3	1830.4	1274.1	754.0	483.8	328.6	200.5	194.5	200.5	199.5	196.6
37.5°	2006.8	1403.1	789.3	302.3	194.5	142.2	118.9	118.9	121.0	121.0	119.9
40°	1513.9	824.5	276.1	99.7	69.5	66.6	67.6	67.6	68.5	69.5	70.5
42.5°	847.7	272.2	72.6	39.3	39.3	37.3	37.3	37.3	39.3	39.3	40.4
45°	228.8	58.4	24.1	23.1	22.3	21.2	21.2	21.2	22.3	22.3	23.1
47.5°	34.2	17.2	14.0	13.1	13.1	12.2	12.2	12.2	13.1	13.1	13.1
50°	13.1	10.1	9.0	8.0	8.0	8.0	7.1	7.1	8.0	8.0	8.0
52.5°	8.0	7.1	6.0	5.0	6.0	5.0	5.0	5.0	6.0	6.0	6.0
55°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	6.0	6.0
57.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	6.0	6.0
60°	4.1	5.0	5.0	5.0	5.0	5.0	5.0	5.0	6.0	6.0	6.0
62.5°	4.1	5.0	5.0	5.0	5.0	5.0	5.0	5.0	6.0	6.0	6.0
65°	4.1	5.0	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
67.5°	4.1	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
70°	5.0	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
72.5°	5.0	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	7.1
75°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1
77.5°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1
80°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1
82.5°	5.0	5.0	6.0	6.0	6.0	7.1	6.0	7.1	7.1	7.1	7.1
85°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1
87.5°	5.0	5.0	6.0	6.0	6.0	7.1	6.0	6.0	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192322

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4
2.5°	1318.4	1295.2	1252.9	1223.7	1211.6	1187.4	1142.0	1137.0	1082.5	1054.4	1025.1
5°	1205.5	1148.2	1076.5	1031.2	1005.0	953.5	883.0	850.6	784.3	740.8	677.4
7.5°	1067.4	978.7	880.9	823.5	781.1	694.4	569.5	494.9	396.1	338.7	297.3
10°	909.2	791.2	643.1	548.3	478.8	376.9	299.4	275.1	249.0	227.9	207.7
12.5°	723.7	525.2	382.0	326.6	300.4	270.1	237.8	209.6	204.6	206.6	213.7
15°	492.9	350.7	302.3	280.2	262.1	232.9	239.8	247.9	255.0	260.0	269.2
17.5°	370.9	324.6	277.2	278.2	285.2	292.3	303.4	315.4	325.5	332.6	344.8
20°	365.9	336.6	342.7	354.8	362.9	372.9	392.1	403.2	416.3	425.4	438.5
22.5°	398.1	424.3	432.3	441.6	453.5	464.7	484.8	499.9	510.0	519.1	528.1
25°	472.7	492.9	499.9	507.1	515.1	523.1	536.2	549.3	546.3	549.3	550.4
27.5°	477.8	492.9	496.0	499.9	499.9	507.1	507.1	515.1	502.0	499.9	496.0
30°	411.3	416.3	419.3	419.3	415.3	420.4	415.3	421.4	406.2	401.2	396.1
32.5°	303.4	310.4	307.4	306.4	303.4	308.5	302.3	308.5	295.3	292.3	287.2
35°	194.5	205.6	200.5	203.6	201.6	206.6	202.6	206.6	196.6	195.5	192.5
37.5°	122.0	125.9	124.0	125.0	125.0	128.0	125.9	128.0	124.0	124.0	121.0
40°	71.6	73.5	73.5	74.6	75.6	76.6	75.6	77.7	75.6	76.6	73.5
42.5°	41.4	42.3	42.3	43.3	44.3	44.3	44.3	46.4	44.3	45.3	43.3
45°	23.1	25.2	24.1	25.2	25.2	26.2	26.2	26.2	26.2	26.2	25.2
47.5°	14.0	15.1	15.1	15.1	15.1	15.1	16.1	16.1	15.1	15.1	15.1
50°	9.0	9.0	9.0	9.0	10.1	10.1	10.1	9.0	9.0	9.0	8.0
52.5°	6.0	6.0	6.0	6.0	7.1	6.0	6.0	6.0	5.0	5.0	5.0
55°	6.0	6.0	6.0	6.0	6.0	5.0	5.0	5.0	4.1	3.0	3.0
57.5°	6.0	6.0	6.0	6.0	6.0	5.0	5.0	4.1	4.1	3.0	3.0
60°	6.0	6.0	6.0	6.0	6.0	5.0	5.0	4.1	4.1	3.0	3.0
62.5°	6.0	6.0	6.0	6.0	6.0	5.0	5.0	4.1	4.1	3.0	3.0
65°	6.0	6.0	6.0	6.0	6.0	5.0	5.0	5.0	4.1	3.0	3.0
67.5°	6.0	7.1	6.0	6.0	6.0	6.0	5.0	5.0	4.1	3.0	3.0
70°	6.0	7.1	6.0	6.0	6.0	6.0	5.0	5.0	4.1	3.0	3.0
72.5°	7.1	7.1	7.1	6.0	6.0	6.0	6.0	5.0	4.1	3.0	3.0
75°	7.1	7.1	7.1	6.0	6.0	6.0	6.0	5.0	4.1	3.0	3.0
77.5°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.0	4.1	4.1	3.0
80°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.0	4.1	4.1	3.0
82.5°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.0	4.1	4.1	3.0
85°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.0	4.1	4.1	3.0
87.5°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.0	4.1	4.1	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192322

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4	1435.4
2.5°	1032.1	1022.0	1015.0	998.9	989.9	979.8	964.6	957.5
5°	655.2	624.9	605.8	577.6	534.2	544.2	521.1	513.0
7.5°	282.3	269.2	265.0	259.1	249.0	244.0	242.9	240.9
10°	193.5	182.4	181.4	182.4	183.5	182.4	182.4	182.4
12.5°	217.8	218.8	220.7	223.8	224.7	224.7	223.8	223.8
15°	274.2	276.1	279.2	283.3	285.2	285.2	285.2	285.2
17.5°	351.7	354.8	359.8	363.9	367.8	367.8	367.8	368.9
20°	452.5	452.5	458.6	463.6	466.8	467.7	468.7	469.7
22.5°	542.4	543.3	547.4	551.4	554.3	553.3	551.4	551.4
25°	559.4	556.4	557.4	557.4	556.4	551.4	551.4	549.3
27.5°	498.9	494.9	494.9	491.9	490.9	488.8	484.8	482.8
30°	396.1	394.2	393.1	390.1	395.2	388.0	384.1	382.0
32.5°	285.2	286.2	285.2	282.3	287.2	280.2	278.2	275.1
35°	191.5	192.5	191.5	189.5	189.5	189.5	187.5	185.4
37.5°	121.0	119.9	121.0	121.0	123.0	119.9	119.9	117.9
40°	73.5	73.5	74.6	74.6	75.6	73.5	72.6	72.6
42.5°	43.3	43.3	44.3	44.3	45.3	43.3	43.3	43.3
45°	25.2	25.2	25.2	25.2	26.2	25.2	24.1	24.1
47.5°	14.0	14.0	14.0	14.0	14.0	14.0	14.0	13.1
50°	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1
52.5°	5.0	4.1	4.1	4.1	4.1	3.0	3.0	3.0
55°	2.1	2.1	2.1	2.1	2.1	1.0	1.0	1.0
57.5°	2.1	2.1	2.1	1.0	1.0	1.0	0.0	0.0
60°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
62.5°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
65°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
67.5°	2.1	2.1	2.1	1.0	1.0	0.0	0.0	0.0
70°	2.1	2.1	2.1	1.0	1.0	1.0	0.0	0.0
72.5°	2.1	2.1	2.1	1.0	1.0	1.0	0.0	0.0
75°	3.0	2.1	2.1	2.1	1.0	1.0	0.0	0.0
77.5°	3.0	2.1	2.1	2.1	1.0	1.0	1.0	0.0
80°	3.0	2.1	2.1	2.1	1.0	1.0	1.0	1.0
82.5°	3.0	2.1	2.1	2.1	1.0	1.0	1.0	1.0
85°	3.0	2.1	2.1	2.1	1.0	1.0	1.0	1.0
87.5°	3.0	2.1	2.1	2.1	1.0	1.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)