

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192324

Luminaire Tested: **LDA6A45950D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192324
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26673)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A45950D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4148.0 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.56 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 53.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192324

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1192324

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91	103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80	96	89	84	79		87	82	78		84	80	77		82	79	76
4	92	83	76	71	90	82	76	71		79	74	70		77	73	69		75	71	68
5	86	76	69	64	84	75	68	63		73	67	63		71	66	62		69	65	61
6	80	69	62	57	79	69	62	57		67	61	56		65	60	56		64	59	55
7	75	64	56	51	73	63	56	51		62	55	51		60	55	51		59	54	50
8	70	59	51	46	69	58	51	46		57	50	46		56	50	46		55	49	46
9	66	54	47	42	64	53	47	42		52	46	42		51	46	42		50	45	41
10	62	50	43	38	60	49	43	38		48	42	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	64375	64375	64375
5°	128907	61231	16421
10°	216184	52354	4487
15°	330127	39245	6521
20°	473002	28697	76791
25°	703208	47616	39383
30°	821930	21054	6128
35°	826460	4383	3239
40°	684318	2447	1875
45°	512224	1566	1481
50°	358982	1117	861
55°	57699	860	679
60°	3541	877	548
65°	1038	1167	532
70°	657	1282	801
75°	445	1504	1059
80°	316	2241	1578
85°	629	4466	1887



TEST NUMBER: P1192324

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.7	2.9
10°-20°	513.7	12.4
20°-30°	1236.1	29.8
30°-40°	1317.0	31.8
40°-50°	821.3	19.8
50°-60°	120.0	2.9
60°-70°	7.6	0.2
70°-80°	6.0	0.1
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1871.5	45.1
0°-40°	3188.6	76.9
0°-60°	4129.9	99.6
0°-90°	4148.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4148.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1174	1174	1174	1174	1174	
5°	2342	1879	1113	554	298	271
15°	5817	3232	692	107	115	1726
25°	11626	3844	787	815	651	5239
35°	12349	2852	66	60	48	7451
45°	6607	835	20	23	19	5201
55°	604	14	9	10	7	1068
65°	8	6	9	8	4	12
75°	2	4	7	7	5	2
85°	1	4	7	6	3	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192324

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3
2.5°	1746.8	1687.4	1707.5	1663.1	1647.0	1651.0	1618.8	1592.6	1578.4	1544.2	1508.9
5°	2342.5	2273.9	2294.0	2227.7	2186.3	2177.1	2126.7	2070.3	2020.0	1943.3	1878.9
7.5°	3065.1	2980.4	2994.6	2894.8	2811.2	2782.9	2706.4	2596.5	2494.8	2364.6	2240.7
10°	3883.6	3804.0	3800.0	3647.8	3504.6	3449.2	3337.4	3156.0	2982.5	2787.0	2583.4
12.5°	4848.3	4728.4	4708.2	4512.7	4298.9	4208.2	4051.9	3774.8	3500.6	3215.4	2922.1
15°	5816.8	5687.9	5655.6	5409.7	5111.3	4989.3	4780.7	4411.9	4033.8	3630.6	3232.4
17.5°	6849.1	6642.4	6468.0	6183.7	5839.1	5714.0	5444.0	4971.2	4495.5	3997.6	3465.3
20°	8107.9	7877.2	7632.1	7146.5	6514.4	6268.5	5972.1	5438.9	4845.3	4269.7	3637.7
22.5°	9833.6	9454.5	8934.4	8153.3	7284.5	6933.7	6476.1	5785.6	5114.3	4468.2	3752.5
25°	11625.7	11102.5	10531.1	9330.7	7989.1	7560.6	6959.0	6050.7	5328.0	4614.4	3844.4
27.5°	12657.8	12237.6	11589.4	10331.5	8560.4	7998.1	7304.5	6250.3	5464.1	4684.9	3870.6
30°	12984.5	12643.7	12055.2	10764.8	8752.0	8081.7	7336.9	6252.4	5398.5	4562.0	3719.4
32.5°	12848.3	12524.8	11873.7	10493.8	8401.3	7784.4	7061.7	5998.3	5076.0	4184.0	3331.3
35°	12349.4	11922.0	11130.8	9593.7	7804.6	7191.8	6516.3	5543.7	4580.1	3670.9	2852.5
37.5°	11229.5	10786.0	9886.0	8439.5	7035.5	6502.3	5959.0	5034.7	4081.2	3204.2	2435.2
40°	9562.5	9093.8	8353.9	7338.9	6206.0	5842.1	5383.5	4471.3	3553.1	2746.7	2049.2
42.5°	7880.2	7579.8	7141.4	6337.0	5547.7	5189.0	4743.4	3857.4	3044.9	2274.9	1556.4
45°	6607.0	6369.3	6077.9	5569.9	4825.1	4487.4	4073.2	3239.6	2373.8	1520.1	834.6
47.5°	5757.4	5467.1	5213.1	4646.6	3847.3	3437.1	2997.7	2134.8	1368.8	659.2	230.8
50°	4209.2	3859.4	3622.5	2987.6	2261.9	1920.0	1598.6	990.8	443.5	147.2	38.3
52.5°	2133.9	1869.7	1730.7	1307.3	863.8	646.2	474.8	204.6	87.8	29.2	22.3
55°	603.7	485.9	435.4	287.2	156.2	109.8	71.6	36.3	26.2	20.2	14.0
57.5°	62.5	53.4	50.4	41.4	33.2	31.3	28.2	22.3	17.2	14.0	9.0
60°	32.3	29.2	28.2	25.2	21.2	19.1	18.1	15.1	11.1	8.0	7.1
62.5°	17.2	16.1	14.0	13.1	11.1	11.1	10.1	8.0	7.1	7.1	6.0
65°	8.0	8.0	8.0	8.0	7.1	7.1	6.0	6.0	6.0	6.0	6.0
67.5°	6.0	6.0	6.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
70°	4.1	4.1	4.1	4.1	3.0	3.0	3.0	3.0	3.0	4.1	4.1
72.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.0	3.0	4.1	4.1
75°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.0	3.0	4.1	4.1
77.5°	1.0	1.0	2.1	2.1	2.1	2.1	2.1	3.0	3.0	4.1	4.1
80°	1.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	3.0	4.1	4.1
82.5°	1.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	3.0	4.1	4.1
85°	1.0	1.0	1.0	1.0	2.1	2.1	2.1	2.1	3.0	4.1	4.1
87.5°	0.0	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192324

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3
2.5°	1466.5	1441.3	1401.0	1360.7	1348.7	1315.4	1276.1	1229.7	1186.3	1152.1	1118.8
5°	1775.0	1707.5	1632.0	1530.0	1493.8	1437.3	1352.7	1261.9	1183.3	1112.7	1047.2
7.5°	2082.4	1955.4	1817.4	1670.1	1607.6	1524.0	1390.9	1263.0	1146.1	1042.2	944.4
10°	2354.6	2159.0	1964.6	1762.0	1674.2	1566.4	1389.0	1225.6	1076.5	940.5	817.4
12.5°	2605.6	2335.4	2077.4	1817.4	1707.5	1577.4	1358.8	1161.2	983.7	824.5	680.4
15°	2825.3	2477.6	2158.0	1843.6	1704.5	1555.3	1299.2	1072.4	875.0	691.5	535.2
17.5°	2978.6	2558.2	2181.2	1816.4	1663.1	1491.8	1208.5	966.6	749.8	557.4	379.0
20°	3070.2	2579.4	2159.0	1756.9	1587.5	1410.1	1123.8	879.0	668.3	491.9	342.7
22.5°	3120.6	2589.5	2142.9	1735.7	1563.3	1394.0	1127.9	894.1	713.6	594.7	582.6
25°	3171.1	2621.6	2171.2	1759.9	1598.6	1441.3	1187.4	948.5	825.4	787.2	800.3
27.5°	3167.9	2601.5	2144.9	1737.7	1582.5	1419.2	1136.0	885.0	800.3	740.8	691.5
30°	2988.6	2410.0	1943.3	1511.0	1333.6	1115.8	757.0	520.1	398.1	332.6	299.4
32.5°	2573.3	1965.5	1484.7	1050.3	876.9	634.0	325.5	171.4	147.2	131.0	116.9
35°	2138.9	1565.4	1117.8	662.3	440.5	240.9	111.9	72.6	67.6	65.5	64.5
37.5°	1763.8	1237.8	734.8	265.0	158.3	89.6	51.4	46.4	45.3	46.4	45.3
40°	1391.9	816.4	291.3	88.6	48.4	39.3	36.3	33.2	33.2	34.2	33.2
42.5°	833.6	304.4	88.6	33.2	31.3	28.2	27.2	26.2	25.2	26.2	26.2
45°	275.1	77.7	29.2	23.1	22.3	21.2	20.2	20.2	20.2	20.2	21.2
47.5°	62.5	27.2	20.2	17.2	17.2	16.1	16.1	15.1	16.1	16.1	17.2
50°	24.1	17.2	14.0	13.1	13.1	12.2	12.2	12.2	12.2	13.1	13.1
52.5°	15.1	12.2	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	11.1
55°	10.1	9.0	8.0	8.0	8.0	8.0	8.0	9.0	9.0	9.0	9.0
57.5°	7.1	7.1	7.1	7.1	8.0	7.1	8.0	7.1	7.1	8.0	9.0
60°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	8.0	8.0	9.0
62.5°	6.0	7.1	7.1	7.1	7.1	7.1	7.1	8.0	8.0	8.0	9.0
65°	6.0	6.0	7.1	7.1	7.1	7.1	8.0	8.0	8.0	9.0	9.0
67.5°	5.0	6.0	6.0	7.1	7.1	7.1	7.1	8.0	8.0	8.0	9.0
70°	5.0	5.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0
72.5°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	8.0
75°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	8.0
77.5°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	8.0
80°	5.0	5.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1	8.0
82.5°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1
85°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1
87.5°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192324

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3
2.5°	1074.4	1033.1	1013.0	982.7	984.8	934.4	915.3	879.0	858.8	837.6	813.5
5°	967.6	895.1	843.6	803.4	781.1	715.6	671.3	613.8	554.3	497.0	449.6
7.5°	833.6	737.9	659.2	607.9	576.6	444.5	359.8	292.3	266.0	246.0	225.8
10°	684.3	565.4	426.3	355.8	312.4	249.9	224.7	186.5	159.2	134.1	118.9
12.5°	534.2	352.8	255.0	233.9	218.8	162.3	128.0	118.9	96.8	91.7	89.6
15°	335.6	231.8	180.4	155.2	135.0	112.9	103.8	102.9	106.9	107.8	106.9
17.5°	237.8	185.4	136.0	133.1	133.1	145.1	147.2	156.2	164.2	171.4	172.3
20°	305.3	274.2	319.6	339.8	375.0	418.3	481.8	570.5	648.1	726.8	787.2
22.5°	584.6	653.2	754.0	789.3	848.7	941.4	1029.1	1110.8	1193.4	1254.9	1268.1
25°	859.9	907.1	966.6	953.5	971.6	966.6	917.2	850.6	815.4	750.9	728.8
27.5°	658.2	608.7	567.5	520.1	497.0	452.5	389.1	348.8	312.4	276.1	261.0
30°	268.1	234.8	210.6	193.5	183.5	159.2	147.2	134.1	128.0	118.9	113.9
32.5°	104.8	98.7	95.8	92.8	91.7	88.6	85.7	81.6	80.6	80.6	76.6
35°	62.5	62.5	62.5	61.5	62.5	61.5	60.4	59.5	60.4	60.4	57.5
37.5°	44.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	44.3	44.3	41.4
40°	33.2	34.2	35.3	34.2	35.3	35.3	34.2	33.2	33.2	33.2	31.3
42.5°	27.2	27.2	27.2	27.2	28.2	27.2	27.2	27.2	27.2	27.2	26.2
45°	22.3	22.3	22.3	22.3	23.1	23.1	22.3	22.3	23.1	23.1	22.3
47.5°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	16.1	16.1	16.1	15.1
50°	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	14.0	13.1	13.1
52.5°	11.1	11.1	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	11.1
55°	10.1	10.1	11.1	11.1	11.1	11.1	11.1	10.1	10.1	10.1	9.0
57.5°	9.0	10.1	10.1	10.1	10.1	10.1	10.1	10.1	9.0	9.0	8.0
60°	9.0	9.0	10.1	10.1	10.1	10.1	9.0	9.0	8.0	8.0	7.1
62.5°	9.0	9.0	10.1	10.1	10.1	9.0	9.0	8.0	8.0	7.1	7.1
65°	9.0	10.1	10.1	10.1	10.1	9.0	9.0	8.0	8.0	7.1	7.1
67.5°	9.0	10.1	10.1	10.1	10.1	9.0	9.0	8.0	8.0	7.1	7.1
70°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	8.0	8.0	7.1	7.1
72.5°	8.0	9.0	9.0	9.0	9.0	9.0	8.0	8.0	8.0	7.1	7.1
75°	8.0	8.0	8.0	8.0	9.0	8.0	8.0	8.0	7.1	7.1	6.0
77.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	6.0
80°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0	6.0
82.5°	8.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0	6.0	6.0
85°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.0	5.0
87.5°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.0	4.1	4.1	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192324

CATALOG NUMBER: LDA6A45950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3
2.5°	787.2	770.0	766.1	766.1	757.0	738.9	735.8	729.7
5°	398.1	355.8	347.8	338.7	323.5	305.3	300.4	298.4
7.5°	205.6	187.5	184.4	178.5	169.3	160.3	158.3	157.2
10°	121.0	109.8	104.8	95.8	86.7	81.6	81.6	80.6
12.5°	89.6	89.6	89.6	89.6	89.6	89.6	89.6	89.6
15°	108.8	111.9	111.9	112.9	113.9	114.9	116.9	114.9
17.5°	183.5	198.6	197.6	199.5	206.6	215.7	211.6	216.7
20°	891.0	1006.9	1040.2	1073.5	1174.3	1268.9	1249.9	1316.3
22.5°	1280.0	1315.4	1301.2	1292.2	1313.4	1302.3	1349.7	1318.4
25°	686.4	679.3	679.3	649.1	655.2	640.0	660.2	651.1
27.5°	253.0	230.8	228.8	214.7	223.8	202.6	208.7	204.6
30°	108.8	109.8	105.9	102.9	99.7	97.9	97.9	96.8
32.5°	74.6	74.6	72.6	70.5	68.5	66.6	65.5	64.5
35°	55.4	55.4	53.4	52.4	51.4	49.4	48.4	48.4
37.5°	40.4	40.4	39.3	38.3	36.3	35.3	34.2	34.2
40°	31.3	30.3	29.2	29.2	27.2	27.2	26.2	26.2
42.5°	25.2	25.2	25.2	24.1	23.1	22.3	22.3	22.3
45°	22.3	22.3	21.2	20.2	20.2	20.2	19.1	19.1
47.5°	15.1	15.1	14.0	14.0	13.1	13.1	12.2	12.2
50°	12.2	12.2	12.2	12.2	11.1	10.1	10.1	10.1
52.5°	11.1	10.1	10.1	10.1	9.0	9.0	8.0	8.0
55°	9.0	9.0	8.0	8.0	7.1	7.1	7.1	7.1
57.5°	8.0	7.1	7.1	7.1	6.0	6.0	6.0	6.0
60°	7.1	6.0	6.0	6.0	5.0	5.0	5.0	5.0
62.5°	6.0	6.0	6.0	6.0	5.0	5.0	5.0	5.0
65°	6.0	6.0	6.0	5.0	5.0	5.0	5.0	4.1
67.5°	6.0	6.0	6.0	6.0	5.0	5.0	5.0	5.0
70°	6.0	6.0	6.0	6.0	5.0	5.0	5.0	5.0
72.5°	6.0	6.0	6.0	6.0	5.0	5.0	5.0	5.0
75°	6.0	6.0	6.0	6.0	5.0	5.0	5.0	5.0
77.5°	6.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
80°	6.0	5.0	5.0	5.0	5.0	4.1	4.1	5.0
82.5°	5.0	5.0	5.0	5.0	4.1	4.1	4.1	4.1
85°	4.1	4.1	4.1	4.1	3.0	3.0	3.0	3.0
87.5°	3.0	2.1	2.1	2.1	2.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)