

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192329

Luminaire Tested: **LDA6A45950D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192329
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26674)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A45950D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4561.2 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 2.68 / 0.47 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 53.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192329

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192329

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91		
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	59	54	77	66	59	54	65	58	53	63	57	53	61	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39399	39399	39399
5°	103835	35945	11589
10°	207333	27549	4604
15°	377454	19336	5028
20°	580391	13873	31748
25°	680664	20729	26276
30°	741108	13015	7659
35°	780008	5394	3172
40°	799820	2376	1803
45°	742457	1566	1333
50°	520776	1194	606
55°	190464	860	392
60°	40227	877	230
65°	3399	1038	272
70°	1138	1282	481
75°	212	1694	868
80°	316	2526	1294
85°	0	5032	1321



TEST NUMBER: P1192329

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	2.0
10°-20°	497.2	10.9
20°-30°	1201.7	26.3
30°-40°	1412.8	31.0
40°-50°	1067.2	23.4
50°-60°	267.7	5.9
60°-70°	12.9	0.3
70°-80°	6.2	0.1
80°-90°	5.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1789.4	39.2
0°-40°	3202.2	70.2
0°-60°	4537.1	99.5
0°-90°	4561.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4561.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	719	719	719	719	719	
5°	1887	1370	653	277	211	235
15°	6651	2885	341	92	89	2013
25°	11253	3589	343	476	434	5177
35°	11655	2645	81	58	47	7258
45°	9577	1039	20	21	17	7056
55°	1993	29	9	8	4	2205
65°	26	7	8	7	2	71
75°	1	5	8	7	4	3
85°	0	5	8	6	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1192329

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7
2.5°	1253.9	1233.8	1219.7	1195.4	1183.4	1188.4	1163.2	1129.0	1118.9	1088.7	1036.3
5°	1886.9	1865.8	1832.5	1781.0	1742.8	1736.7	1687.4	1604.6	1552.3	1474.6	1369.9
7.5°	2664.2	2646.0	2590.4	2513.9	2449.4	2425.2	2352.6	2207.5	2091.5	1936.4	1755.8
10°	3724.6	3653.9	3550.0	3394.9	3246.7	3178.1	3050.1	2810.3	2621.7	2409.1	2164.1
12.5°	5054.1	4929.0	4760.7	4527.8	4272.8	4144.8	3941.2	3574.3	3244.7	2879.8	2523.0
15°	6650.7	6524.5	6280.8	5919.9	5509.6	5304.0	5003.6	4425.0	3934.1	3398.9	2884.9
17.5°	8534.6	8328.9	8004.4	7481.2	6846.2	6523.7	6098.2	5296.8	4565.1	3866.6	3201.3
20°	9948.7	9798.6	9491.1	8943.8	8186.8	7771.6	7200.0	6096.3	5151.7	4240.6	3441.3
22.5°	10816.6	10681.6	10399.3	9941.7	9246.2	8785.5	8141.4	6797.8	5607.4	4499.6	3561.2
25°	11253.0	11156.4	10959.8	10560.7	9952.8	9490.1	8839.0	7316.9	5915.8	4639.8	3589.4
27.5°	11637.1	11474.8	11155.4	10883.2	10344.9	9874.1	9257.4	7575.0	6023.7	4623.6	3517.9
30°	11707.7	11614.9	11362.9	10973.9	10472.9	9997.1	9347.0	7537.7	5901.8	4436.1	3323.3
32.5°	11647.2	11566.5	11376.0	10951.7	10391.3	9866.1	9152.4	7231.3	5543.9	4088.3	2994.7
35°	11655.3	11527.3	11193.6	10830.8	10131.3	9514.3	8676.6	6670.9	5043.0	3636.8	2644.9
37.5°	11500.9	11290.3	11015.3	10547.5	9603.0	8838.0	7880.4	5948.2	4440.2	3176.2	2236.7
40°	11176.5	11016.2	10650.3	9931.6	8702.8	7741.3	6856.3	5118.6	3781.9	2673.2	1823.4
42.5°	10646.3	10454.8	9943.8	8860.1	7399.5	6560.9	5764.6	4269.8	3134.8	2186.3	1431.4
45°	9576.7	9284.5	8616.2	7324.0	6078.2	5366.5	4717.3	3481.6	2541.1	1710.5	1039.2
47.5°	7868.3	7619.4	6912.8	5834.2	4853.4	4303.0	3749.7	2745.7	1891.0	1099.7	534.2
50°	6106.3	5909.8	5370.6	4424.0	3605.5	3071.3	2635.9	1752.9	1008.0	506.1	239.9
52.5°	4017.8	3893.8	3431.2	2761.8	2070.3	1689.4	1371.8	761.0	469.7	224.8	82.7
55°	1992.8	1833.5	1612.8	1195.4	864.9	699.6	593.6	375.0	194.5	64.5	29.2
57.5°	812.4	777.1	699.6	540.3	415.3	350.8	280.3	116.9	43.3	26.2	18.1
60°	366.9	350.8	304.4	213.7	116.0	71.6	50.4	32.3	22.3	16.1	12.2
62.5°	64.5	59.5	52.4	40.4	32.3	28.2	24.1	18.1	14.0	11.1	9.0
65°	26.2	26.2	24.1	21.2	17.2	16.1	14.0	11.1	9.0	8.0	7.1
67.5°	14.0	13.1	13.1	11.1	10.1	9.0	8.0	7.1	7.1	6.0	6.0
70°	7.1	7.1	7.1	6.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
72.5°	4.1	4.1	4.1	4.1	4.1	4.1	3.0	3.0	3.0	4.1	4.1
75°	1.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
77.5°	1.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
80°	1.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
82.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	3.0	4.1	5.0
85°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	3.0	4.1	5.0
87.5°	0.0	0.0	1.0	1.0	1.0	2.1	2.1	3.0	3.0	4.1	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192329

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7
2.5°	1034.2	981.8	941.5	903.1	894.1	862.8	833.6	783.2	737.9	695.4	647.1
5°	1329.5	1226.7	1141.0	1057.4	1030.1	977.7	907.1	816.4	731.7	653.2	570.5
7.5°	1651.0	1476.7	1324.5	1183.4	1134.0	1059.3	945.5	816.4	694.5	581.6	480.8
10°	1966.6	1706.5	1476.7	1273.1	1198.5	1101.8	945.5	781.1	626.0	494.9	395.2
12.5°	2270.9	1914.1	1603.8	1334.6	1236.8	1115.8	920.3	719.8	539.2	410.3	326.6
15°	2508.8	2089.5	1693.4	1358.8	1236.8	1096.7	861.7	634.0	451.6	340.7	266.0
17.5°	2687.3	2193.4	1723.7	1335.6	1194.5	1037.3	773.1	533.2	371.9	282.3	210.6
20°	2791.2	2219.6	1692.4	1268.1	1113.8	947.4	663.3	439.5	315.5	237.8	170.4
22.5°	2815.3	2183.3	1619.8	1181.3	1022.1	853.7	566.5	393.1	304.4	242.9	212.7
25°	2788.0	2109.6	1524.0	1093.7	935.4	769.1	531.2	423.3	364.9	342.7	366.9
27.5°	2680.2	1972.7	1406.2	995.9	836.6	681.4	504.0	426.4	366.9	356.8	345.8
30°	2487.8	1765.9	1224.7	814.4	646.2	517.1	357.9	254.1	202.6	205.6	203.6
32.5°	2186.3	1465.6	958.6	569.5	444.5	349.8	236.9	150.2	141.1	141.1	139.0
35°	1854.7	1190.4	720.6	400.2	309.5	246.0	141.1	109.8	92.8	80.6	72.6
37.5°	1517.0	926.3	497.0	270.2	196.6	125.9	67.6	55.4	49.4	46.4	45.3
40°	1174.4	652.2	317.5	148.2	86.7	55.4	43.3	37.3	34.2	33.2	33.2
42.5°	868.9	420.4	171.4	58.4	46.4	38.3	31.3	27.2	26.2	26.2	25.2
45°	523.1	210.6	64.5	36.3	30.3	27.2	23.1	21.2	20.2	20.2	21.2
47.5°	241.9	78.6	35.3	24.1	22.3	20.2	18.1	17.2	17.2	17.2	18.1
50°	87.8	34.2	22.3	17.2	16.1	15.1	14.0	13.1	13.1	14.0	14.0
52.5°	33.2	21.2	16.1	13.1	12.2	12.2	11.1	11.1	11.1	11.1	11.1
55°	20.2	15.1	12.2	10.1	10.1	9.0	9.0	9.0	9.0	9.0	9.0
57.5°	13.1	11.1	9.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
60°	10.1	8.0	7.1	7.1	7.1	7.1	7.1	8.0	8.0	8.0	8.0
62.5°	8.0	7.1	7.1	7.1	7.1	7.1	7.1	7.1	8.0	8.0	8.0
65°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	8.0	8.0	8.0	9.0
67.5°	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0
70°	5.0	5.0	6.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0
72.5°	5.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0
75°	5.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1	8.0	8.0	8.0
77.5°	5.0	6.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0	9.0
80°	5.0	6.0	6.0	7.1	7.1	7.1	7.1	8.0	8.0	8.0	9.0
82.5°	5.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0	9.0	9.0
85°	5.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0	8.0	9.0
87.5°	5.0	6.0	6.0	7.1	7.1	7.1	7.1	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192329

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7
2.5°	620.9	579.6	550.4	524.2	514.1	490.9	465.7	436.5	412.3	410.3	390.1
5°	515.1	457.6	416.3	390.1	376.9	352.8	323.5	304.4	277.2	269.2	249.0
7.5°	416.3	362.9	324.6	300.5	285.3	255.9	222.8	201.6	179.4	162.3	140.1
10°	338.7	287.2	246.0	221.7	206.6	175.3	141.1	116.9	96.8	92.8	90.7
12.5°	272.2	219.8	178.5	152.3	136.0	106.9	97.9	93.7	90.7	87.8	87.8
15°	211.6	158.3	113.9	103.8	100.8	97.9	95.8	93.7	91.7	90.7	91.7
17.5°	154.1	111.9	106.9	105.9	103.8	103.8	105.9	106.9	108.8	110.9	113.9
20°	136.0	137.1	148.2	156.2	153.3	168.4	189.5	206.6	247.9	273.2	307.4
22.5°	244.0	280.3	331.6	362.9	380.0	430.5	485.9	569.5	611.8	672.4	726.8
25°	417.2	459.7	504.0	516.2	525.2	530.2	523.1	484.8	475.8	458.6	453.5
27.5°	312.4	292.3	299.4	302.3	299.4	295.4	283.3	262.1	257.0	249.0	251.0
30°	184.4	178.5	186.5	185.4	185.4	185.4	181.4	164.2	156.2	147.2	141.1
32.5°	136.0	125.0	116.0	107.8	104.8	99.7	96.8	89.6	86.7	82.7	82.7
35°	67.6	64.5	64.5	62.5	61.5	62.5	62.5	59.5	57.5	56.5	56.5
37.5°	44.3	44.3	45.3	44.3	44.3	44.3	44.3	43.3	42.3	41.4	41.4
40°	33.2	33.2	34.2	34.2	33.2	33.2	33.2	32.3	32.3	32.3	32.3
42.5°	26.2	26.2	26.2	26.2	25.2	26.2	26.2	26.2	25.2	25.2	24.1
45°	22.3	21.2	21.2	21.2	21.2	21.2	22.3	21.2	21.2	20.2	20.2
47.5°	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	17.2	17.2
50°	14.0	14.0	14.0	14.0	14.0	13.1	13.1	12.2	12.2	11.1	11.1
52.5°	11.1	11.1	10.1	10.1	10.1	10.1	10.1	10.1	9.0	9.0	9.0
55°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	8.0	7.1	7.1
57.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0
60°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	7.1	6.0	6.0	6.0
62.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	7.1	6.0	6.0	5.0
65°	9.0	9.0	9.0	9.0	8.0	8.0	8.0	7.1	7.1	6.0	6.0
67.5°	9.0	9.0	9.0	9.0	9.0	8.0	8.0	8.0	7.1	7.1	6.0
70°	9.0	9.0	9.0	9.0	9.0	8.0	8.0	8.0	7.1	7.1	6.0
72.5°	9.0	9.0	9.0	9.0	9.0	8.0	8.0	8.0	7.1	7.1	6.0
75°	9.0	9.0	9.0	9.0	9.0	8.0	8.0	8.0	7.1	7.1	6.0
77.5°	9.0	9.0	9.0	9.0	9.0	8.0	8.0	8.0	7.1	7.1	6.0
80°	9.0	9.0	9.0	9.0	9.0	8.0	8.0	8.0	7.1	7.1	6.0
82.5°	9.0	9.0	9.0	9.0	9.0	8.0	8.0	8.0	7.1	7.1	6.0
85°	9.0	9.0	8.0	8.0	8.0	8.0	8.0	7.1	6.0	6.0	5.0
87.5°	8.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0	5.0	5.0	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192329

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	718.7	718.7	718.7	718.7	718.7	718.7	718.7	718.7
2.5°	386.2	371.9	368.9	372.9	356.8	356.8	356.8	363.9
5°	240.9	226.8	222.8	223.8	210.6	201.6	206.6	210.6
7.5°	131.0	116.0	110.9	110.9	97.9	92.8	93.7	95.8
10°	87.8	85.7	85.7	84.7	82.7	81.6	82.7	82.7
12.5°	84.7	83.6	83.6	82.7	82.7	81.6	81.6	82.7
15°	88.6	88.6	88.6	87.8	87.8	86.7	88.6	88.6
17.5°	112.9	114.9	118.9	121.0	125.0	121.0	128.0	127.0
20°	331.6	364.9	426.4	449.6	516.2	483.8	553.3	544.2
22.5°	750.9	775.2	785.3	790.3	791.2	823.5	828.6	839.7
25°	443.5	437.4	432.3	432.3	414.2	435.4	431.5	434.4
27.5°	236.9	234.9	229.8	231.8	222.8	229.8	231.8	231.8
30°	134.1	130.0	125.9	125.9	117.9	122.0	121.0	121.0
32.5°	77.7	75.6	73.5	72.6	70.5	70.5	69.5	69.5
35°	53.4	52.4	51.4	50.4	48.4	47.4	47.4	47.4
37.5°	39.3	38.3	37.3	37.3	36.3	34.2	34.2	34.2
40°	30.3	29.2	28.2	28.2	27.2	25.2	25.2	25.2
42.5°	23.1	22.3	21.2	20.2	20.2	19.1	18.1	18.1
45°	19.1	19.1	18.1	18.1	17.2	17.2	17.2	17.2
47.5°	16.1	16.1	15.1	15.1	15.1	14.0	14.0	13.1
50°	10.1	9.0	9.0	8.0	8.0	7.1	7.1	7.1
52.5°	8.0	7.1	7.1	6.0	6.0	5.0	5.0	5.0
55°	6.0	6.0	5.0	5.0	5.0	4.1	4.1	4.1
57.5°	5.0	5.0	4.1	4.1	4.1	3.0	3.0	3.0
60°	5.0	4.1	4.1	3.0	3.0	3.0	2.1	2.1
62.5°	5.0	4.1	4.1	3.0	3.0	2.1	2.1	2.1
65°	5.0	4.1	4.1	3.0	3.0	3.0	3.0	2.1
67.5°	5.0	5.0	4.1	4.1	4.1	3.0	3.0	3.0
70°	6.0	5.0	5.0	4.1	4.1	4.1	4.1	3.0
72.5°	6.0	5.0	5.0	5.0	4.1	4.1	4.1	4.1
75°	6.0	5.0	5.0	5.0	4.1	4.1	4.1	4.1
77.5°	6.0	5.0	5.0	5.0	4.1	4.1	4.1	4.1
80°	6.0	5.0	5.0	5.0	4.1	4.1	4.1	4.1
82.5°	5.0	5.0	5.0	4.1	4.1	4.1	4.1	4.1
85°	4.1	4.1	4.1	3.0	3.0	3.0	3.0	2.1
87.5°	3.0	3.0	2.1	2.1	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)