

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192341

Luminaire Tested: **LDA6A50927D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192341
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26673)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50927D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3712.0 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.56 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192341

CATALOG NUMBER: LDA6A50927D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1192341

CATALOG NUMBER: LDA6A50927D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		69
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64
7	75	64	56	51	73	63	56	51	62	55	51		60	55	51		59
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		55
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		50
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	57605	57605	57605
5°	115358	54798	14693
10°	193461	46848	4019
15°	295427	35119	5834
20°	423286	25675	68728
25°	629292	42613	35252
30°	735531	18845	5482
35°	739594	3928	2898
40°	612383	2190	1682
45°	458389	1403	1326
50°	321252	998	768
55°	51640	774	602
60°	3169	789	493
65°	934	1051	467
70°	577	1154	721
75°	381	1334	953
80°	284	1989	1421
85°	566	3963	1698



TEST NUMBER: P1192341

CATALOG NUMBER: LDA6A50927D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.9	2.9
10°-20°	459.7	12.4
20°-30°	1106.2	29.8
30°-40°	1178.6	31.8
40°-50°	735.0	19.8
50°-60°	107.4	2.9
60°-70°	6.8	0.2
70°-80°	5.3	0.1
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1674.8	45.1
0°-40°	2853.4	76.9
0°-60°	3695.8	99.6
0°-90°	3712.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3712.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1051	1051	1051	1051	1051	
5°	2096	1681	996	496	267	242
15°	5205	2893	619	96	103	1544
25°	10404	3440	704	730	583	4688
35°	11051	2553	59	54	43	6667
45°	5913	747	18	21	17	4654
55°	540	13	8	9	6	955
65°	7	5	8	7	4	11
75°	2	4	6	6	4	2
85°	1	4	6	5	3	1
90°	0	0	0	0	0	

TEST NUMBER: P1192341

CATALOG NUMBER: LDA6A50927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8
2.5°	1563.2	1510.0	1527.9	1488.3	1473.8	1477.5	1448.6	1425.1	1412.6	1381.8	1350.2
5°	2096.3	2034.9	2053.0	1993.4	1956.5	1948.4	1903.2	1852.7	1807.6	1739.1	1681.4
7.5°	2743.0	2667.3	2679.8	2590.5	2515.6	2490.4	2421.9	2323.6	2232.4	2116.1	2005.2
10°	3475.4	3404.1	3400.5	3264.3	3136.3	3086.6	2986.5	2824.2	2669.0	2494.0	2311.9
12.5°	4338.7	4231.3	4213.3	4038.3	3847.1	3765.9	3626.1	3378.0	3132.7	2877.4	2614.9
15°	5205.4	5089.9	5061.2	4841.0	4574.1	4464.9	4278.2	3948.0	3609.8	3249.0	2892.7
17.5°	6129.2	5944.2	5788.2	5533.7	5225.3	5113.4	4871.8	4448.6	4022.9	3577.4	3101.1
20°	7255.7	7049.1	6830.0	6395.2	5829.6	5609.6	5344.4	4867.2	4336.0	3820.9	3255.3
22.5°	8800.0	8460.8	7995.4	7296.3	6518.7	6204.9	5795.4	5177.5	4576.8	3998.6	3358.1
25°	10403.7	9935.5	9424.1	8349.8	7149.2	6765.9	6227.4	5414.7	4768.0	4129.4	3440.3
27.5°	11327.3	10951.3	10371.2	9245.5	7660.7	7157.3	6536.8	5593.4	4889.7	4192.5	3463.6
30°	11619.6	11314.8	10788.0	9633.4	7832.1	7232.2	6565.7	5595.1	4831.1	4082.4	3328.4
32.5°	11497.9	11208.3	10625.6	9390.8	7518.1	6966.1	6319.4	5367.8	4542.5	3744.2	2981.1
35°	11051.4	10668.9	9960.8	8585.3	6984.2	6435.7	5831.5	4961.1	4098.7	3285.1	2552.7
37.5°	10049.3	9652.3	8846.8	7552.5	6295.9	5818.8	5332.7	4505.6	3652.3	2867.5	2179.2
40°	8557.3	8137.9	7475.8	6567.4	5553.7	5228.0	4817.6	4001.3	3179.6	2458.0	1833.8
42.5°	7051.8	6783.0	6390.7	5670.9	4964.6	4643.5	4244.9	3451.9	2724.9	2035.8	1392.7
45°	5912.6	5699.8	5439.1	4984.4	4317.9	4015.8	3645.0	2899.1	2124.2	1360.2	746.8
47.5°	5152.3	4892.4	4665.2	4158.3	3443.0	3075.8	2682.5	1910.5	1224.9	589.9	206.6
50°	3766.8	3453.8	3241.8	2673.5	2024.1	1718.3	1430.5	886.6	396.8	131.7	34.3
52.5°	1909.5	1673.3	1548.7	1169.8	773.0	578.2	424.9	183.1	78.5	26.2	19.8
55°	540.3	434.7	389.7	257.0	139.8	98.4	64.1	32.5	23.5	18.1	12.7
57.5°	55.9	47.8	45.1	37.0	29.8	27.9	25.2	19.8	15.4	12.7	8.1
60°	28.9	26.2	25.2	22.5	18.9	17.1	16.2	13.5	10.0	7.2	6.3
62.5°	15.4	14.4	12.7	11.7	10.0	10.0	9.0	7.2	6.3	6.3	5.4
65°	7.2	7.2	7.2	7.2	6.3	6.3	5.4	5.4	5.4	5.4	5.4
67.5°	5.4	5.4	5.4	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
70°	3.6	3.6	3.6	3.6	2.7	2.7	2.7	2.7	2.7	3.6	3.6
72.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.7	2.7	3.6	3.6
75°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.7	2.7	3.6	3.6
77.5°	0.9	0.9	1.8	1.8	1.8	1.8	1.8	2.7	2.7	3.6	3.6
80°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.6	3.6
82.5°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.6	3.6
85°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	1.8	2.7	3.6	3.6
87.5°	0.0	0.0	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.6	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192341

CATALOG NUMBER: LDA6A50927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8
2.5°	1312.5	1289.9	1253.8	1217.7	1206.9	1177.1	1141.9	1100.5	1061.6	1031.0	1001.2
5°	1588.4	1527.9	1460.3	1369.3	1336.7	1286.3	1210.5	1129.4	1058.9	995.8	937.2
7.5°	1863.5	1749.9	1626.3	1494.6	1438.7	1363.9	1244.7	1130.2	1025.6	932.6	845.2
10°	2107.1	1932.1	1758.0	1576.7	1498.3	1401.7	1243.0	1096.8	963.4	841.6	731.6
12.5°	2331.7	2089.9	1859.1	1626.3	1527.9	1411.6	1215.9	1039.1	880.4	737.8	608.8
15°	2528.3	2217.2	1931.2	1649.8	1525.2	1391.8	1162.7	959.7	783.0	618.8	479.0
17.5°	2665.4	2289.3	1951.9	1625.4	1488.3	1335.0	1081.5	865.0	671.1	498.8	339.2
20°	2747.6	2308.2	1932.1	1572.2	1420.7	1261.9	1005.8	786.5	598.0	440.1	306.7
22.5°	2792.6	2317.3	1917.6	1553.3	1399.0	1247.4	1009.4	800.1	638.6	532.2	521.4
25°	2837.7	2346.1	1942.9	1574.9	1430.5	1289.9	1062.6	848.8	738.7	704.5	716.2
27.5°	2835.0	2328.1	1919.5	1555.1	1416.1	1270.0	1016.6	791.9	716.2	662.9	618.8
30°	2674.4	2156.7	1739.1	1352.1	1193.3	998.5	677.4	465.4	356.3	297.7	267.8
32.5°	2302.8	1758.9	1328.6	939.9	784.7	567.4	291.3	153.3	131.7	117.3	104.6
35°	1914.1	1400.8	1000.4	592.6	394.1	215.6	100.1	64.9	60.4	58.7	57.7
37.5°	1578.5	1107.6	657.5	237.2	141.7	80.3	46.0	41.5	40.6	41.5	40.6
40°	1245.7	730.6	260.7	79.3	43.3	35.2	32.5	29.8	29.8	30.6	29.8
42.5°	745.9	272.4	79.3	29.8	27.9	25.2	24.3	23.5	22.5	23.5	23.5
45°	246.2	69.5	26.2	20.8	19.8	18.9	18.1	18.1	18.1	18.1	18.9
47.5°	55.9	24.3	18.1	15.4	15.4	14.4	14.4	13.5	14.4	14.4	15.4
50°	21.6	15.4	12.7	11.7	11.7	10.8	10.8	10.8	10.8	11.7	11.7
52.5°	13.5	10.8	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	10.0
55°	9.0	8.1	7.2	7.2	7.2	7.2	7.2	8.1	8.1	8.1	8.1
57.5°	6.3	6.3	6.3	6.3	7.2	6.3	7.2	6.3	6.3	7.2	8.1
60°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.2	7.2	8.1
62.5°	5.4	6.3	6.3	6.3	6.3	6.3	6.3	7.2	7.2	7.2	8.1
65°	5.4	5.4	6.3	6.3	6.3	6.3	7.2	7.2	7.2	8.1	8.1
67.5°	4.5	5.4	5.4	6.3	6.3	6.3	6.3	7.2	7.2	7.2	8.1
70°	4.5	4.5	5.4	5.4	5.4	5.4	6.3	6.3	6.3	7.2	7.2
72.5°	4.5	4.5	5.4	5.4	5.4	5.4	5.4	6.3	6.3	6.3	7.2
75°	4.5	4.5	5.4	5.4	5.4	5.4	5.4	6.3	6.3	6.3	7.2
77.5°	4.5	4.5	5.4	5.4	5.4	5.4	5.4	6.3	6.3	6.3	7.2
80°	4.5	4.5	5.4	5.4	5.4	5.4	6.3	6.3	6.3	6.3	7.2
82.5°	4.5	4.5	5.4	5.4	5.4	5.4	5.4	6.3	6.3	6.3	6.3
85°	4.5	4.5	5.4	5.4	5.4	5.4	5.4	5.4	6.3	6.3	6.3
87.5°	4.5	4.5	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192341

CATALOG NUMBER: LDA6A50927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8
2.5°	961.5	924.5	906.5	879.5	881.2	836.2	819.0	786.5	768.6	749.5	727.9
5°	866.0	800.9	754.9	718.9	699.1	640.4	600.7	549.3	496.1	444.7	402.4
7.5°	745.9	660.2	589.9	543.9	516.0	397.8	322.1	261.6	238.1	220.1	202.0
10°	612.4	506.0	381.6	318.4	279.6	223.7	201.2	166.9	142.5	120.0	106.5
12.5°	478.1	315.7	228.2	209.3	195.8	145.2	114.6	106.5	86.6	82.0	80.3
15°	300.4	207.5	161.5	138.9	120.9	101.1	93.0	92.0	95.7	96.5	95.7
17.5°	212.9	166.0	121.7	119.0	119.0	129.9	131.7	139.8	147.1	153.3	154.2
20°	273.4	245.3	285.9	304.0	335.6	374.3	431.1	510.6	579.9	650.4	704.5
22.5°	523.1	584.5	674.7	706.2	759.5	842.5	920.9	994.0	1068.0	1123.0	1134.8
25°	769.4	811.9	865.0	853.3	869.5	865.0	820.8	761.3	729.7	672.0	652.1
27.5°	589.0	544.8	507.9	465.4	444.7	405.1	348.1	312.1	279.6	247.2	233.6
30°	239.9	210.2	188.5	173.2	164.2	142.5	131.7	120.0	114.6	106.5	101.9
32.5°	93.8	88.4	85.7	83.0	82.0	79.3	76.6	73.0	72.2	72.2	68.5
35°	55.9	55.9	55.9	55.0	55.9	55.0	54.1	53.2	54.1	54.1	51.4
37.5°	39.7	40.6	40.6	40.6	40.6	40.6	40.6	40.6	39.7	39.7	37.0
40°	29.8	30.6	31.6	30.6	31.6	31.6	30.6	29.8	29.8	29.8	27.9
42.5°	24.3	24.3	24.3	24.3	25.2	24.3	24.3	24.3	24.3	24.3	23.5
45°	19.8	19.8	19.8	19.8	20.8	20.8	19.8	19.8	20.8	20.8	19.8
47.5°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	14.4	14.4	14.4	13.5
50°	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	12.7	11.7	11.7
52.5°	10.0	10.0	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.0
55°	9.0	9.0	10.0	10.0	10.0	10.0	10.0	9.0	9.0	9.0	8.1
57.5°	8.1	9.0	9.0	9.0	9.0	9.0	9.0	9.0	8.1	8.1	7.2
60°	8.1	8.1	9.0	9.0	9.0	9.0	8.1	8.1	7.2	7.2	6.3
62.5°	8.1	8.1	9.0	9.0	9.0	8.1	8.1	7.2	7.2	6.3	6.3
65°	8.1	9.0	9.0	9.0	9.0	8.1	8.1	7.2	7.2	6.3	6.3
67.5°	8.1	9.0	9.0	9.0	9.0	8.1	8.1	7.2	7.2	6.3	6.3
70°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	7.2	7.2	6.3	6.3
72.5°	7.2	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.3	6.3
75°	7.2	7.2	7.2	7.2	8.1	7.2	7.2	7.2	6.3	6.3	5.4
77.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.3	6.3	6.3	5.4
80°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.3	6.3	5.4	5.4
82.5°	7.2	7.2	7.2	7.2	7.2	7.2	6.3	6.3	5.4	5.4	5.4
85°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	5.4	5.4	4.5	4.5
87.5°	6.3	6.3	6.3	6.3	6.3	5.4	5.4	4.5	3.6	3.6	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192341

CATALOG NUMBER: LDA6A50927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8
2.5°	704.5	689.1	685.6	685.6	677.4	661.2	658.5	653.1
5°	356.3	318.4	311.2	303.1	289.6	273.4	268.8	267.0
7.5°	184.0	167.7	165.0	159.6	151.5	143.4	141.7	140.7
10°	108.2	98.4	93.8	85.7	77.6	73.0	73.0	72.2
12.5°	80.3	80.3	80.3	80.3	80.3	80.3	80.3	80.3
15°	97.4	100.1	100.1	101.1	101.9	102.8	104.6	102.8
17.5°	164.2	177.7	176.8	178.6	184.9	193.1	189.4	193.9
20°	797.4	901.1	930.9	960.7	1050.8	1135.6	1118.4	1178.1
22.5°	1145.5	1177.1	1164.4	1156.3	1175.4	1165.4	1207.8	1179.8
25°	614.2	608.0	608.0	580.9	586.3	572.8	590.9	582.8
27.5°	226.4	206.6	204.7	192.1	200.2	181.3	186.7	183.1
30°	97.4	98.4	94.7	92.0	89.3	87.4	87.4	86.6
32.5°	66.8	66.8	64.9	63.1	61.4	59.5	58.7	57.7
35°	49.6	49.6	47.8	46.9	46.0	44.2	43.3	43.3
37.5°	36.0	36.0	35.2	34.3	32.5	31.6	30.6	30.6
40°	27.9	27.1	26.2	26.2	24.3	24.3	23.5	23.5
42.5°	22.5	22.5	22.5	21.6	20.8	19.8	19.8	19.8
45°	19.8	19.8	18.9	18.1	18.1	18.1	17.1	17.1
47.5°	13.5	13.5	12.7	12.7	11.7	11.7	10.8	10.8
50°	10.8	10.8	10.8	10.8	10.0	9.0	9.0	9.0
52.5°	10.0	9.0	9.0	9.0	8.1	8.1	7.2	7.2
55°	8.1	8.1	7.2	7.2	6.3	6.3	6.3	6.3
57.5°	7.2	6.3	6.3	6.3	5.4	5.4	5.4	5.4
60°	6.3	5.4	5.4	5.4	4.5	4.5	4.5	4.5
62.5°	5.4	5.4	5.4	5.4	4.5	4.5	4.5	4.5
65°	5.4	5.4	5.4	4.5	4.5	4.5	4.5	3.6
67.5°	5.4	5.4	5.4	5.4	4.5	4.5	4.5	4.5
70°	5.4	5.4	5.4	5.4	4.5	4.5	4.5	4.5
72.5°	5.4	5.4	5.4	5.4	4.5	4.5	4.5	4.5
75°	5.4	5.4	5.4	5.4	4.5	4.5	4.5	4.5
77.5°	5.4	4.5	4.5	4.5	4.5	4.5	4.5	4.5
80°	5.4	4.5	4.5	4.5	4.5	3.6	3.6	4.5
82.5°	4.5	4.5	4.5	4.5	3.6	3.6	3.6	3.6
85°	3.6	3.6	3.6	3.6	2.7	2.7	2.7	2.7
87.5°	2.7	1.8	1.8	1.8	1.8	1.8	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)