

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192346

Luminaire Tested: **LDA6A50927D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192346
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26674)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50927D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4081.8 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 2.68 / 0.47 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192346

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192346

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91		
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	59	54	77	66	59	54	65	58	53	63	57	53	61	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35260	35260	35260
5°	92923	32165	10373
10°	185534	24649	4114
15°	337777	17304	4501
20°	519387	12420	28417
25°	609126	18551	23511
30°	663210	11647	6849
35°	698014	4832	2838
40°	715748	2133	1610
45°	664418	1403	1194
50°	466040	1083	537
55°	170441	774	344
60°	35995	789	197
65°	3048	934	233
70°	1010	1154	433
75°	191	1525	763
80°	284	2273	1137
85°	0	4529	1132

TEST NUMBER: P1192346

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.9	2.0
10°-20°	445.0	10.9
20°-30°	1075.4	26.3
30°-40°	1264.3	31.0
40°-50°	955.1	23.4
50°-60°	239.6	5.9
60°-70°	11.6	0.3
70°-80°	5.5	0.1
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1601.3	39.2
0°-40°	2865.6	70.2
0°-60°	4060.2	99.5
0°-90°	4081.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4081.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	643	643	643	643	643	
5°	1689	1226	584	248	188	210
15°	5952	2582	305	82	79	1801
25°	10070	3212	307	426	389	4633
35°	10430	2367	72	51	42	6495
45°	8570	930	18	19	15	6315
55°	1783	26	8	7	4	1973
65°	24	6	7	6	2	63
75°	1	4	7	6	4	2
85°	0	4	7	5	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192346

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2
2.5°	1122.1	1104.1	1091.4	1069.8	1058.9	1063.5	1041.0	1010.2	1001.3	974.2	927.2
5°	1688.6	1669.6	1639.9	1593.9	1559.6	1554.2	1510.0	1436.0	1389.1	1319.6	1225.8
7.5°	2384.1	2367.9	2318.2	2249.7	2191.9	2170.3	2105.3	1975.5	1871.7	1732.8	1571.4
10°	3333.0	3269.9	3176.9	3038.1	2905.4	2844.0	2729.5	2514.8	2346.1	2155.9	1936.6
12.5°	4522.8	4411.0	4260.2	4051.9	3823.7	3709.2	3526.9	3198.6	2903.7	2577.1	2257.8
15°	5951.6	5838.8	5620.6	5297.6	4930.4	4746.5	4477.6	3959.9	3520.6	3041.7	2581.6
17.5°	7637.5	7453.5	7163.0	6694.9	6126.6	5838.0	5457.3	4740.2	4085.2	3460.1	2864.8
20°	8903.0	8768.6	8493.5	8003.7	7326.2	6954.6	6443.2	5455.4	4610.3	3794.9	3079.5
22.5°	9679.7	9558.8	9306.2	8896.7	8274.2	7862.0	7285.6	6083.3	5018.0	4026.7	3186.9
25°	10070.3	9983.7	9807.7	9450.5	8906.6	8492.6	7909.9	6547.8	5294.1	4152.0	3212.1
27.5°	10413.9	10268.7	9982.7	9739.2	9257.5	8836.2	8284.2	6778.7	5390.5	4137.6	3148.0
30°	10477.1	10394.1	10168.5	9820.4	9372.0	8946.3	8364.5	6745.4	5281.4	3969.9	2974.0
32.5°	10423.0	10350.8	10180.3	9800.6	9299.0	8829.1	8190.4	6471.2	4961.2	3658.6	2680.0
35°	10430.1	10315.6	10017.0	9692.3	9066.3	8514.3	7764.6	5969.7	4512.8	3254.5	2366.9
37.5°	10292.1	10103.6	9857.4	9438.8	8593.6	7909.0	7052.1	5322.8	3973.4	2842.3	2001.5
40°	10001.7	9858.3	9530.8	8887.6	7788.1	6927.5	6135.6	4580.6	3384.4	2392.2	1631.8
42.5°	9527.2	9355.8	8898.5	7928.8	6621.8	5871.3	5158.7	3821.0	2805.3	1956.5	1280.9
45°	8570.1	8308.6	7710.5	6554.2	5439.2	4802.4	4221.5	3115.6	2274.0	1530.8	929.9
47.5°	7041.3	6818.5	6186.1	5220.9	4343.2	3850.7	3355.5	2457.2	1692.2	984.2	478.1
50°	5464.5	5288.5	4806.0	3959.0	3226.6	2748.5	2358.8	1568.7	902.0	452.8	214.7
52.5°	3595.5	3484.5	3070.4	2471.5	1852.7	1511.7	1227.7	681.0	420.3	201.2	73.9
55°	1783.3	1640.7	1443.2	1069.8	774.0	626.1	531.3	335.6	174.1	57.7	26.2
57.5°	727.0	695.4	626.1	483.5	371.6	313.9	250.7	104.6	38.7	23.5	16.2
60°	328.3	313.9	272.4	191.2	103.8	64.1	45.1	28.9	19.8	14.4	10.8
62.5°	57.7	53.2	46.9	36.0	28.9	25.2	21.6	16.2	12.7	10.0	8.1
65°	23.5	23.5	21.6	18.9	15.4	14.4	12.7	10.0	8.1	7.2	6.3
67.5°	12.7	11.7	11.7	10.0	9.0	8.1	7.2	6.3	6.3	5.4	5.4
70°	6.3	6.3	6.3	5.4	4.5	4.5	4.5	4.5	4.5	4.5	4.5
72.5°	3.6	3.6	3.6	3.6	3.6	3.6	2.7	2.7	2.7	3.6	3.6
75°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.6	3.6	4.5
77.5°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.6	3.6	4.5
80°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.6	3.6	4.5
82.5°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.6	4.5
85°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.6	4.5
87.5°	0.0	0.0	0.9	0.9	0.9	1.8	1.8	2.7	2.7	3.6	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192346

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2
2.5°	925.5	878.5	842.5	808.2	800.1	772.2	746.0	700.8	660.3	622.4	579.1
5°	1189.8	1097.8	1021.1	946.3	921.8	875.0	811.9	730.6	654.8	584.5	510.6
7.5°	1477.5	1321.5	1185.2	1058.9	1014.8	948.0	846.1	730.6	621.5	520.4	430.3
10°	1759.9	1527.1	1321.5	1139.2	1072.5	985.9	846.1	699.1	560.2	442.8	353.6
12.5°	2032.3	1712.9	1435.1	1194.3	1106.8	998.6	823.6	644.0	482.6	367.1	292.3
15°	2245.2	1869.9	1515.4	1216.0	1106.8	981.5	771.3	567.4	404.1	304.9	238.1
17.5°	2404.8	1962.8	1542.5	1195.2	1068.9	928.2	691.9	477.1	332.9	252.6	188.5
20°	2497.7	1986.3	1514.4	1134.8	996.7	847.9	593.5	393.3	282.3	212.9	152.5
22.5°	2519.4	1953.8	1449.5	1057.2	914.7	764.0	506.9	351.8	272.4	217.4	190.4
25°	2495.0	1887.9	1363.9	978.6	837.1	688.3	475.4	378.9	326.5	306.7	328.3
27.5°	2398.5	1765.3	1258.3	891.2	748.7	609.7	451.1	381.6	328.3	319.4	309.4
30°	2226.2	1580.3	1096.0	728.9	578.2	462.8	320.2	227.3	181.3	184.0	182.2
32.5°	1956.5	1311.5	857.9	509.6	397.8	313.0	212.0	134.4	126.3	126.3	124.5
35°	1659.8	1065.3	645.0	358.1	276.9	220.1	126.3	98.4	83.0	72.2	64.9
37.5°	1357.5	829.0	444.7	241.8	175.9	112.8	60.4	49.6	44.2	41.5	40.6
40°	1050.8	583.6	284.2	132.6	77.6	49.6	38.7	33.3	30.6	29.8	29.8
42.5°	777.6	376.2	153.3	52.3	41.5	34.3	27.9	24.4	23.5	23.5	22.5
45°	468.2	188.5	57.7	32.5	27.1	24.4	20.8	18.9	18.1	18.1	18.9
47.5°	216.4	70.3	31.6	21.6	19.8	18.1	16.2	15.4	15.4	15.4	16.2
50°	78.5	30.6	19.8	15.4	14.4	13.5	12.7	11.7	11.7	12.7	12.7
52.5°	29.8	18.9	14.4	11.7	10.8	10.8	10.0	10.0	10.0	10.0	10.0
55°	18.1	13.5	10.8	9.0	9.0	8.1	8.1	8.1	8.1	8.1	8.1
57.5°	11.7	10.0	8.1	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
60°	9.0	7.2	6.3	6.3	6.3	6.3	6.3	7.2	7.2	7.2	7.2
62.5°	7.2	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.2	7.2	7.2
65°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.2	7.2	7.2	8.1
67.5°	5.4	5.4	5.4	5.4	5.4	6.3	6.3	6.3	7.2	7.2	7.2
70°	4.5	4.5	5.4	5.4	5.4	6.3	6.3	6.3	7.2	7.2	7.2
72.5°	4.5	5.4	5.4	5.4	5.4	6.3	6.3	6.3	7.2	7.2	7.2
75°	4.5	5.4	5.4	5.4	6.3	6.3	6.3	6.3	7.2	7.2	7.2
77.5°	4.5	5.4	5.4	5.4	6.3	6.3	6.3	7.2	7.2	7.2	8.1
80°	4.5	5.4	5.4	6.3	6.3	6.3	6.3	7.2	7.2	7.2	8.1
82.5°	4.5	5.4	5.4	6.3	6.3	6.3	7.2	7.2	7.2	8.1	8.1
85°	4.5	5.4	5.4	6.3	6.3	6.3	7.2	7.2	7.2	7.2	8.1
87.5°	4.5	5.4	5.4	6.3	6.3	6.3	6.3	7.2	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192346

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2
2.5°	555.6	518.7	492.5	469.0	460.0	439.3	416.8	390.6	368.9	367.1	349.1
5°	460.9	409.5	372.5	349.1	337.3	315.7	289.6	272.4	248.0	240.8	222.8
7.5°	372.5	324.8	290.5	268.8	255.3	229.1	199.3	180.4	160.6	145.2	125.4
10°	303.1	257.0	220.1	198.5	184.9	156.9	126.3	104.6	86.6	83.0	81.2
12.5°	243.5	196.6	159.6	136.2	121.8	95.7	87.4	83.9	81.2	78.5	78.5
15°	189.4	141.7	101.9	93.0	90.3	87.4	85.7	83.9	82.0	81.2	82.0
17.5°	138.0	100.1	95.7	94.7	93.0	93.0	94.7	95.7	97.4	99.2	101.9
20°	121.8	122.7	132.6	139.8	137.1	150.6	169.6	184.9	222.0	244.5	275.1
22.5°	218.3	250.7	296.7	324.8	340.0	385.2	434.7	509.6	547.5	601.6	650.4
25°	373.5	411.3	451.1	461.9	470.0	474.4	468.2	433.9	425.7	410.4	405.9
27.5°	279.6	261.6	268.0	270.7	268.0	264.3	253.5	234.5	230.0	222.8	224.6
30°	165.0	159.6	166.9	166.0	166.0	166.0	162.3	147.1	139.8	131.7	126.3
32.5°	121.8	111.9	103.8	96.5	93.8	89.3	86.6	80.3	77.6	73.9	73.9
35°	60.4	57.7	57.7	55.9	55.0	55.9	55.9	53.2	51.4	50.5	50.5
37.5°	39.7	39.7	40.6	39.7	39.7	39.7	39.7	38.7	37.9	37.0	37.0
40°	29.8	29.8	30.6	30.6	29.8	29.8	29.8	28.9	28.9	28.9	28.9
42.5°	23.5	23.5	23.5	23.5	22.5	23.5	23.5	23.5	22.5	22.5	21.6
45°	19.8	18.9	18.9	18.9	18.9	18.9	19.8	18.9	18.9	18.1	18.1
47.5°	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	15.4	15.4
50°	12.7	12.7	12.7	12.7	12.7	11.7	11.7	10.8	10.8	10.0	10.0
52.5°	10.0	10.0	9.0	9.0	9.0	9.0	9.0	9.0	8.1	8.1	8.1
55°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	7.2	6.3	6.3
57.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.3	6.3	5.4
60°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.3	5.4	5.4	5.4
62.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.3	5.4	5.4	4.5
65°	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.3	6.3	5.4	5.4
67.5°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.3	6.3	5.4
70°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.3	6.3	5.4
72.5°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.3	6.3	5.4
75°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.3	6.3	5.4
77.5°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.3	6.3	5.4
80°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.3	6.3	5.4
82.5°	8.1	8.1	8.1	8.1	8.1	7.2	7.2	7.2	6.3	6.3	5.4
85°	8.1	8.1	7.2	7.2	7.2	7.2	7.2	6.3	5.4	5.4	4.5
87.5°	7.2	7.2	7.2	7.2	7.2	6.3	6.3	5.4	4.5	4.5	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192346

CATALOG NUMBER: LDA6A50927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	643.2	643.2	643.2	643.2	643.2	643.2	643.2	643.2
2.5°	345.4	332.9	330.2	333.8	319.4	319.4	319.4	325.6
5°	215.6	202.9	199.3	200.2	188.5	180.4	184.9	188.5
7.5°	117.3	103.8	99.2	99.2	87.4	83.0	83.9	85.7
10°	78.5	76.6	76.6	75.8	73.9	73.1	73.9	73.9
12.5°	75.8	74.9	74.9	73.9	73.9	73.1	73.1	73.9
15°	79.3	79.3	79.3	78.5	78.5	77.6	79.3	79.3
17.5°	101.1	102.8	106.5	108.2	111.9	108.2	114.6	113.6
20°	296.7	326.5	381.6	402.4	461.9	433.0	495.2	487.1
22.5°	672.0	693.7	702.7	707.2	708.1	737.0	741.4	751.4
25°	396.8	391.4	387.0	387.0	370.8	389.7	386.0	388.7
27.5°	212.0	210.2	205.6	207.5	199.3	205.6	207.5	207.5
30°	120.0	116.3	112.8	112.8	105.5	109.2	108.2	108.2
32.5°	69.5	67.6	65.8	64.9	63.1	63.1	62.2	62.2
35°	47.8	46.9	46.0	45.1	43.3	42.4	42.4	42.4
37.5°	35.2	34.3	33.3	33.3	32.5	30.6	30.6	30.6
40°	27.1	26.2	25.2	25.2	24.4	22.5	22.5	22.5
42.5°	20.8	19.8	18.9	18.1	18.1	17.1	16.2	16.2
45°	17.1	17.1	16.2	16.2	15.4	15.4	15.4	15.4
47.5°	14.4	14.4	13.5	13.5	13.5	12.7	12.7	11.7
50°	9.0	8.1	8.1	7.2	7.2	6.3	6.3	6.3
52.5°	7.2	6.3	6.3	5.4	5.4	4.5	4.5	4.5
55°	5.4	5.4	4.5	4.5	4.5	3.6	3.6	3.6
57.5°	4.5	4.5	3.6	3.6	3.6	2.7	2.7	2.7
60°	4.5	3.6	3.6	2.7	2.7	2.7	1.8	1.8
62.5°	4.5	3.6	3.6	2.7	2.7	1.8	1.8	1.8
65°	4.5	3.6	3.6	2.7	2.7	2.7	2.7	1.8
67.5°	4.5	4.5	3.6	3.6	3.6	2.7	2.7	2.7
70°	5.4	4.5	4.5	3.6	3.6	3.6	3.6	2.7
72.5°	5.4	4.5	4.5	4.5	3.6	3.6	3.6	3.6
75°	5.4	4.5	4.5	4.5	3.6	3.6	3.6	3.6
77.5°	5.4	4.5	4.5	4.5	3.6	3.6	3.6	3.6
80°	5.4	4.5	4.5	4.5	3.6	3.6	3.6	3.6
82.5°	4.5	4.5	4.5	3.6	3.6	3.6	3.6	3.6
85°	3.6	3.6	3.6	2.7	2.7	2.7	2.7	1.8
87.5°	2.7	2.7	1.8	1.8	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)