

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192358

Luminaire Tested: **LDA6A50930D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26673)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50930D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3930.8 lumens
Efficiency: N/A
Efficacy: 68.5 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.56 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192358

CATALOG NUMBER: LDA6A50930D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1192358

CATALOG NUMBER: LDA6A50930D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		69
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64
7	75	64	56	51	73	63	56	51	62	55	51		60	55	51		59
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		55
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		50
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61004	61004	61004
5°	122149	58029	15557
10°	204861	49609	4253
15°	312834	37191	6181
20°	448226	27192	72771
25°	666365	45124	37321
30°	778867	19946	5805
35°	783161	4156	3072
40°	648465	2326	1782
45°	485399	1481	1411
50°	340168	1058	810
55°	54689	822	640
60°	3344	833	526
65°	986	1116	506
70°	625	1218	769
75°	402	1419	1017
80°	284	2115	1515
85°	566	4214	1761



TEST NUMBER: P1192358

CATALOG NUMBER: LDA6A50930D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	2.9
10°-20°	486.8	12.4
20°-30°	1171.4	29.8
30°-40°	1248.0	31.8
40°-50°	778.3	19.8
50°-60°	113.7	2.9
60°-70°	7.2	0.2
70°-80°	5.7	0.1
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1773.5	45.1
0°-40°	3021.5	76.9
0°-60°	3913.6	99.6
0°-90°	3930.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3930.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1113	1113	1113	1113	1113	
5°	2220	1780	1054	525	283	257
15°	5512	3063	655	101	109	1635
25°	11017	3643	746	773	617	4964
35°	11702	2703	62	57	46	7060
45°	6261	791	19	22	18	4928
55°	572	13	9	10	7	1012
65°	8	6	9	8	4	11
75°	2	4	7	7	5	2
85°	1	4	7	6	3	1
90°	0	0	0	0	0	

TEST NUMBER: P1192358

CATALOG NUMBER: LDA6A50930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8
2.5°	1655.3	1599.0	1618.0	1576.0	1560.7	1564.6	1533.9	1509.2	1495.8	1463.3	1429.8
5°	2219.7	2154.8	2174.0	2110.9	2071.7	2063.2	2015.4	1961.9	1914.1	1841.6	1780.4
7.5°	2904.6	2824.3	2837.7	2743.2	2663.9	2637.1	2564.6	2460.5	2364.0	2240.7	2123.3
10°	3680.2	3604.7	3601.0	3456.7	3321.0	3268.6	3162.5	2990.5	2826.3	2641.0	2448.0
12.5°	4594.3	4480.6	4461.5	4276.2	4073.7	3987.7	3839.7	3577.0	3317.3	3047.0	2768.9
15°	5512.1	5390.0	5359.3	5126.3	4843.6	4728.0	4530.3	4180.7	3822.5	3440.4	3063.2
17.5°	6490.2	6294.4	6129.2	5859.8	5533.1	5414.7	5158.7	4710.8	4260.0	3788.2	3283.8
20°	7683.2	7464.5	7232.3	6772.0	6173.2	5940.1	5659.2	5154.0	4591.4	4046.0	3447.1
22.5°	9318.4	8959.3	8466.4	7726.2	6902.9	6570.5	6136.8	5482.6	4846.4	4234.2	3556.0
25°	11016.6	10521.0	9979.4	8841.9	7570.5	7164.6	6594.3	5733.7	5048.9	4372.7	3643.0
27.5°	11994.7	11596.5	10982.3	9790.2	8112.0	7579.1	6922.0	5922.8	5177.9	4439.5	3667.8
30°	12304.2	11981.4	11423.6	10201.0	8293.6	7658.4	6952.5	5924.8	5115.8	4323.0	3524.4
32.5°	12175.3	11868.6	11251.6	9944.1	7961.2	7376.6	6691.7	5684.1	4810.1	3964.8	3156.7
35°	11702.4	11297.5	10547.7	9091.2	7395.7	6815.0	6175.1	5253.3	4340.2	3478.7	2703.1
37.5°	10641.3	10221.1	9368.2	7997.5	6667.0	6161.7	5646.9	4770.9	3867.4	3036.4	2307.6
40°	9061.5	8617.3	7916.3	6954.4	5880.8	5536.1	5101.5	4237.0	3366.9	2602.8	1941.8
42.5°	7467.3	7182.7	6767.2	6005.0	5257.1	4917.1	4494.9	3655.3	2885.5	2155.8	1474.8
45°	6261.0	6035.6	5759.6	5278.1	4572.3	4252.3	3859.8	3069.9	2249.4	1440.4	790.9
47.5°	5455.8	5180.7	4940.1	4403.2	3645.8	3257.1	2840.6	2023.0	1297.1	624.7	218.8
50°	3988.6	3657.3	3432.8	2831.0	2143.3	1819.6	1514.9	938.9	420.3	139.4	36.3
52.5°	2022.1	1771.8	1640.0	1238.9	818.6	612.2	449.9	193.9	83.1	27.7	21.0
55°	572.2	460.3	412.7	272.2	148.0	104.1	67.8	34.4	24.9	19.1	13.4
57.5°	59.3	50.6	47.8	39.2	31.6	29.6	26.8	21.0	16.2	13.4	8.6
60°	30.5	27.7	26.8	23.8	20.1	18.2	17.1	14.3	10.6	7.6	6.7
62.5°	16.2	15.3	13.4	12.4	10.6	10.6	9.5	7.6	6.7	6.7	5.8
65°	7.6	7.6	7.6	7.6	6.7	6.7	5.8	5.8	5.8	5.8	5.8
67.5°	5.8	5.8	5.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
70°	3.9	3.9	3.9	3.9	2.8	2.8	2.8	2.8	2.8	3.9	3.9
72.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8	2.8	3.9	3.9
75°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8	2.8	3.9	3.9
77.5°	0.9	0.9	1.9	1.9	1.9	1.9	1.9	2.8	2.8	3.9	3.9
80°	0.9	0.9	0.9	0.9	1.9	1.9	1.9	2.8	2.8	3.9	3.9
82.5°	0.9	0.9	0.9	0.9	1.9	1.9	1.9	2.8	2.8	3.9	3.9
85°	0.9	0.9	0.9	0.9	1.9	1.9	1.9	1.9	2.8	3.9	3.9
87.5°	0.0	0.0	0.9	0.9	0.9	1.9	1.9	1.9	2.8	3.9	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192358

CATALOG NUMBER: LDA6A50930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8
2.5°	1389.7	1365.9	1327.7	1289.4	1277.9	1246.5	1209.2	1165.3	1124.2	1091.8	1060.2
5°	1682.1	1618.0	1546.4	1449.9	1415.5	1362.1	1281.8	1195.9	1121.4	1054.5	992.4
7.5°	1973.4	1852.9	1722.1	1582.6	1523.5	1444.1	1318.1	1196.8	1086.0	987.6	895.0
10°	2231.2	2045.9	1861.6	1669.6	1586.5	1484.3	1316.2	1161.5	1020.1	891.2	774.7
12.5°	2469.0	2213.0	1968.6	1722.1	1618.0	1494.8	1287.6	1100.4	932.2	781.3	644.7
15°	2677.3	2347.8	2045.0	1747.0	1615.2	1473.8	1231.2	1016.3	829.1	655.3	507.2
17.5°	2822.4	2424.2	2066.9	1721.1	1576.0	1413.6	1145.2	916.0	710.7	528.2	359.2
20°	2909.4	2444.3	2045.9	1664.8	1504.4	1336.3	1065.0	832.9	633.2	466.1	324.8
22.5°	2957.2	2453.8	2030.7	1644.7	1481.5	1321.0	1068.8	847.2	676.3	563.5	552.1
25°	3005.0	2484.3	2057.4	1667.7	1514.9	1365.9	1125.1	898.8	782.3	746.0	758.3
27.5°	3002.0	2465.3	2032.5	1646.7	1499.5	1344.8	1076.4	838.6	758.3	702.0	655.3
30°	2832.1	2283.7	1841.6	1431.8	1263.6	1057.4	717.3	492.8	377.2	315.1	283.7
32.5°	2438.5	1862.6	1406.9	995.3	831.0	600.8	308.6	162.3	139.4	124.2	110.8
35°	2026.8	1483.3	1059.3	627.6	417.4	228.3	106.0	68.8	64.0	62.1	61.2
37.5°	1671.5	1172.9	696.3	251.2	150.0	85.0	48.7	43.9	43.0	43.9	43.0
40°	1319.0	773.7	276.1	84.0	45.9	37.2	34.4	31.6	31.6	32.5	31.6
42.5°	789.9	288.5	84.0	31.6	29.6	26.8	25.8	24.9	23.8	24.9	24.9
45°	260.8	73.6	27.7	21.9	21.0	20.1	19.1	19.1	19.1	19.1	20.1
47.5°	59.3	25.8	19.1	16.2	16.2	15.3	15.3	14.3	15.3	15.3	16.2
50°	22.9	16.2	13.4	12.4	12.4	11.5	11.5	11.5	11.5	12.4	12.4
52.5°	14.3	11.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	10.6
55°	9.5	8.6	7.6	7.6	7.6	7.6	7.6	8.6	8.6	8.6	8.6
57.5°	6.7	6.7	6.7	6.7	7.6	6.7	7.6	6.7	6.7	7.6	8.6
60°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.6	7.6	8.6
62.5°	5.8	6.7	6.7	6.7	6.7	6.7	6.7	7.6	7.6	7.6	8.6
65°	5.8	5.8	6.7	6.7	6.7	6.7	7.6	7.6	7.6	8.6	8.6
67.5°	4.8	5.8	5.8	6.7	6.7	6.7	6.7	7.6	7.6	7.6	8.6
70°	4.8	4.8	5.8	5.8	5.8	5.8	6.7	6.7	6.7	7.6	7.6
72.5°	4.8	4.8	5.8	5.8	5.8	5.8	5.8	6.7	6.7	6.7	7.6
75°	4.8	4.8	5.8	5.8	5.8	5.8	5.8	6.7	6.7	6.7	7.6
77.5°	4.8	4.8	5.8	5.8	5.8	5.8	5.8	6.7	6.7	6.7	7.6
80°	4.8	4.8	5.8	5.8	5.8	5.8	6.7	6.7	6.7	6.7	7.6
82.5°	4.8	4.8	5.8	5.8	5.8	5.8	5.8	6.7	6.7	6.7	6.7
85°	4.8	4.8	5.8	5.8	5.8	5.8	5.8	5.8	6.7	6.7	6.7
87.5°	4.8	4.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192358

CATALOG NUMBER: LDA6A50930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8
2.5°	1018.2	979.0	959.9	931.2	933.2	885.5	867.3	832.9	813.7	793.8	770.8
5°	916.9	848.1	799.4	761.3	740.3	678.2	636.2	581.7	525.4	470.9	425.9
7.5°	789.9	699.2	624.7	575.9	546.4	421.2	341.0	277.0	252.1	233.1	214.0
10°	648.6	535.8	404.0	337.2	296.1	236.9	213.0	176.6	150.9	127.0	112.7
12.5°	506.2	334.3	241.7	221.6	207.3	153.8	121.4	112.7	91.7	87.0	85.0
15°	318.1	219.7	171.0	147.1	127.9	106.9	98.4	97.4	101.3	102.2	101.3
17.5°	225.5	175.7	129.0	126.1	126.1	137.6	139.4	148.0	155.6	162.3	163.4
20°	289.4	259.7	302.8	321.8	355.3	396.4	456.6	540.6	614.2	688.6	746.0
22.5°	554.0	618.9	714.4	747.9	804.2	892.1	975.2	1052.6	1130.9	1189.2	1201.5
25°	814.8	859.6	916.0	903.5	920.8	916.0	869.1	806.1	772.7	711.6	690.6
27.5°	623.7	576.9	537.8	492.8	470.9	428.9	368.7	330.5	296.1	261.7	247.4
30°	254.1	222.5	199.6	183.3	173.8	150.9	139.4	127.0	121.4	112.7	108.0
32.5°	99.3	93.7	90.7	87.9	87.0	84.0	81.2	77.3	76.4	76.4	72.5
35°	59.3	59.3	59.3	58.2	59.3	58.2	57.3	56.3	57.3	57.3	54.5
37.5°	42.0	43.0	43.0	43.0	43.0	43.0	43.0	43.0	42.0	42.0	39.2
40°	31.6	32.5	33.5	32.5	33.5	33.5	32.5	31.6	31.6	31.6	29.6
42.5°	25.8	25.8	25.8	25.8	26.8	25.8	25.8	25.8	25.8	25.8	24.9
45°	21.0	21.0	21.0	21.0	21.9	21.9	21.0	21.0	21.9	21.9	21.0
47.5°	16.2	16.2	16.2	16.2	16.2	16.2	16.2	15.3	15.3	15.3	14.3
50°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	13.4	12.4	12.4
52.5°	10.6	10.6	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	10.6
55°	9.5	9.5	10.6	10.6	10.6	10.6	10.6	9.5	9.5	9.5	8.6
57.5°	8.6	9.5	9.5	9.5	9.5	9.5	9.5	9.5	8.6	8.6	7.6
60°	8.6	8.6	9.5	9.5	9.5	9.5	8.6	8.6	7.6	7.6	6.7
62.5°	8.6	8.6	9.5	9.5	9.5	8.6	8.6	7.6	7.6	6.7	6.7
65°	8.6	9.5	9.5	9.5	9.5	8.6	8.6	7.6	7.6	6.7	6.7
67.5°	8.6	9.5	9.5	9.5	9.5	8.6	8.6	7.6	7.6	6.7	6.7
70°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	7.6	7.6	6.7	6.7
72.5°	7.6	8.6	8.6	8.6	8.6	8.6	7.6	7.6	7.6	6.7	6.7
75°	7.6	7.6	7.6	7.6	8.6	7.6	7.6	7.6	6.7	6.7	5.8
77.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	6.7	6.7	6.7	5.8
80°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	6.7	6.7	5.8	5.8
82.5°	7.6	7.6	7.6	7.6	7.6	7.6	6.7	6.7	5.8	5.8	5.8
85°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.8	5.8	4.8	4.8
87.5°	6.7	6.7	6.7	6.7	6.7	5.8	5.8	4.8	3.9	3.9	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192358

CATALOG NUMBER: LDA6A50930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8	1112.8
2.5°	746.0	729.7	725.9	725.9	717.3	700.1	697.3	691.6
5°	377.2	337.2	329.6	320.9	306.6	289.4	284.6	282.7
7.5°	194.8	177.7	174.8	169.0	160.4	151.9	150.0	148.9
10°	114.7	104.1	99.3	90.7	82.2	77.3	77.3	76.4
12.5°	85.0	85.0	85.0	85.0	85.0	85.0	85.0	85.0
15°	103.2	106.0	106.0	106.9	108.0	108.9	110.8	108.9
17.5°	173.8	188.1	187.2	189.1	195.8	204.3	200.6	205.4
20°	844.4	954.2	985.7	1017.3	1112.8	1202.5	1184.4	1247.4
22.5°	1213.0	1246.5	1233.1	1224.5	1244.6	1234.0	1279.0	1249.3
25°	650.5	643.8	643.8	615.1	620.9	606.6	625.6	617.0
27.5°	239.8	218.8	216.8	203.4	212.1	192.0	197.8	193.9
30°	103.2	104.1	100.2	97.4	94.6	92.6	92.6	91.7
32.5°	70.7	70.7	68.8	66.9	64.9	63.0	62.1	61.2
35°	52.6	52.6	50.6	49.6	48.7	46.8	45.9	45.9
37.5°	38.3	38.3	37.2	36.3	34.4	33.5	32.5	32.5
40°	29.6	28.6	27.7	27.7	25.8	25.8	24.9	24.9
42.5°	23.8	23.8	23.8	22.9	21.9	21.0	21.0	21.0
45°	21.0	21.0	20.1	19.1	19.1	19.1	18.2	18.2
47.5°	14.3	14.3	13.4	13.4	12.4	12.4	11.5	11.5
50°	11.5	11.5	11.5	11.5	10.6	9.5	9.5	9.5
52.5°	10.6	9.5	9.5	9.5	8.6	8.6	7.6	7.6
55°	8.6	8.6	7.6	7.6	6.7	6.7	6.7	6.7
57.5°	7.6	6.7	6.7	6.7	5.8	5.8	5.8	5.8
60°	6.7	5.8	5.8	5.8	4.8	4.8	4.8	4.8
62.5°	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8
65°	5.8	5.8	5.8	4.8	4.8	4.8	4.8	3.9
67.5°	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8
70°	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8
72.5°	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8
75°	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8
77.5°	5.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
80°	5.8	4.8	4.8	4.8	4.8	3.9	3.9	4.8
82.5°	4.8	4.8	4.8	4.8	3.9	3.9	3.9	3.9
85°	3.9	3.9	3.9	3.9	2.8	2.8	2.8	2.8
87.5°	2.8	1.9	1.9	1.9	1.9	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)