

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192366

Luminaire Tested: **LDA6A50930D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192366
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26668)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50930D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3489.4 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 2.16 / 1.11 / 1.51
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192366

CATALOG NUMBER: LDA6A50930D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192366

CATALOG NUMBER: LDA6A50930D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80		
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70		
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62		
5	83	72	65	59	81	71	64	59	69	63	58	67	62	57	66	61	57	55		
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49		
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44		
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39		
9	63	50	43	38	61	50	43	38	49	42	37	48	42	37	47	41	37	35		
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	57605	57605	57605
5°	91580	56780	36694
10°	136298	54564	24782
15°	193673	51947	18649
20°	253527	49599	19065
25°	301874	50156	32935
30°	334786	48381	31024
35°	341535	41238	22827
40°	326454	31795	16882
45°	284704	22886	12738
50°	217050	16614	8477
55°	121162	11957	4932
60°	55719	8278	1995
65°	26280	4462	869
70°	12871	2148	930
75°	6058	1419	1017
80°	2999	1515	1231
85°	1761	2453	1195

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192366

CATALOG NUMBER: LDA6A50930D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.3	3.1
10°-20°	396.4	11.4
20°-30°	792.9	22.7
30°-40°	973.7	27.9
40°-50°	780.0	22.4
50°-60°	343.1	9.8
60°-70°	77.4	2.2
70°-80°	14.1	0.4
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1297.7	37.2
0°-40°	2271.4	65.1
0°-60°	3394.5	97.3
0°-90°	3489.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3489.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1051	1051	1051	1051	1051	
5°	1664	1432	1032	764	667	183
15°	3412	2301	915	426	329	995
25°	4991	2843	829	516	544	2296
35°	5103	2562	616	372	341	3160
45°	3672	1692	295	180	164	2792
55°	1268	627	125	72	52	1205
65°	203	128	34	12	7	232
75°	29	16	7	6	5	36
85°	3	3	4	4	2	4
90°	0	0	0	0	0	

TEST NUMBER: P1192366

CATALOG NUMBER: LDA6A50930D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8
2.5°	1340.4	1306.0	1333.7	1309.8	1302.1	1299.3	1287.8	1280.2	1277.2	1250.6	1229.5
5°	1664.2	1624.1	1652.7	1617.4	1599.2	1589.7	1569.6	1544.7	1524.8	1474.1	1432.1
7.5°	2043.4	2000.5	2027.2	1976.5	1942.2	1925.0	1892.5	1844.7	1799.9	1718.7	1648.0
10°	2448.5	2413.2	2436.2	2365.4	2311.9	2284.2	2236.4	2175.3	2083.6	1965.2	1861.0
12.5°	2920.4	2869.9	2888.1	2793.5	2717.0	2677.8	2610.0	2514.5	2384.5	2223.0	2080.8
15°	3412.5	3364.7	3376.2	3255.8	3149.8	3095.3	3007.4	2871.7	2699.8	2488.6	2301.4
17.5°	3916.9	3851.9	3850.0	3706.7	3565.3	3496.5	3386.6	3208.0	3006.5	2729.4	2498.3
20°	4345.8	4289.5	4274.2	4125.2	3932.2	3851.9	3719.2	3497.4	3250.0	2929.1	2657.8
22.5°	4713.7	4648.6	4620.9	4446.2	4227.4	4133.7	3981.8	3713.4	3438.3	3075.3	2769.5
25°	4990.7	4937.2	4897.1	4700.3	4455.7	4350.6	4184.4	3893.9	3574.9	3177.5	2843.1
27.5°	5210.4	5138.8	5088.2	4873.2	4598.0	4487.2	4308.6	3993.3	3644.6	3218.6	2865.0
30°	5288.8	5217.1	5158.8	4929.5	4638.2	4516.8	4329.6	3995.2	3625.5	3187.9	2817.3
32.5°	5251.5	5177.0	5111.1	4871.3	4569.4	4442.3	4251.2	3912.1	3525.3	3085.7	2711.3
35°	5103.4	5044.2	4969.6	4728.0	4430.0	4291.4	4101.3	3753.6	3369.5	2926.2	2562.2
37.5°	4894.2	4802.5	4733.7	4496.8	4208.3	4066.9	3884.4	3550.0	3161.2	2735.1	2382.6
40°	4561.8	4469.1	4400.3	4172.0	3910.2	3767.9	3599.7	3280.7	2905.2	2508.7	2172.4
42.5°	4147.1	4061.2	3994.3	3782.2	3551.0	3412.5	3264.3	2969.2	2620.4	2257.4	1942.2
45°	3672.3	3589.2	3531.8	3347.6	3142.2	3019.9	2886.1	2625.3	2306.2	1976.5	1691.9
47.5°	3157.4	3072.3	3023.6	2858.4	2684.5	2573.7	2459.1	2233.6	1947.9	1665.2	1417.7
50°	2545.0	2462.8	2418.9	2280.4	2157.2	2054.9	1971.8	1791.2	1557.2	1334.6	1133.0
52.5°	1863.9	1799.9	1767.4	1671.8	1598.3	1521.8	1468.3	1342.3	1171.3	1013.6	861.7
55°	1267.7	1215.2	1199.9	1140.6	1100.6	1059.5	1021.3	947.7	832.0	727.9	626.6
57.5°	793.0	787.2	797.7	745.2	727.0	709.9	680.2	639.1	566.6	501.5	440.4
60°	508.2	502.5	497.8	478.6	470.1	457.6	443.3	419.4	374.5	336.3	296.1
62.5°	322.0	318.1	322.9	311.4	300.0	300.0	284.7	271.4	243.7	220.7	192.0
65°	202.6	201.5	204.5	196.8	191.1	188.1	180.5	172.9	155.8	141.4	128.1
67.5°	128.1	127.1	129.0	127.1	120.4	118.4	113.7	108.9	97.4	88.9	79.3
70°	80.3	79.3	80.3	78.3	74.5	72.7	69.7	66.0	62.1	52.6	47.8
72.5°	48.7	47.8	48.7	47.8	45.0	45.0	41.1	39.2	36.3	30.5	26.8
75°	28.6	28.6	28.6	27.7	25.8	25.8	23.8	22.9	21.0	18.2	16.2
77.5°	16.2	16.2	16.2	16.2	15.3	15.3	14.3	13.4	12.4	10.6	10.6
80°	9.5	9.5	9.5	9.5	8.6	9.5	8.6	8.6	7.6	6.7	6.7
82.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8
85°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
87.5°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	1.9	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192366

CATALOG NUMBER: LDA6A50930D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8
2.5°	1212.3	1181.7	1176.1	1143.6	1137.8	1119.6	1110.1	1093.0	1058.5	1040.4	1018.4
5°	1381.5	1333.7	1306.0	1247.7	1229.5	1199.0	1167.4	1125.4	1070.9	1031.8	990.7
7.5°	1566.8	1488.4	1430.2	1344.1	1312.7	1267.7	1212.3	1146.4	1070.0	1011.7	953.4
10°	1753.1	1630.8	1541.0	1425.4	1379.5	1320.3	1240.0	1151.2	1055.6	980.2	907.5
12.5°	1924.1	1771.3	1648.0	1500.8	1439.7	1367.1	1262.0	1151.2	1037.5	947.7	862.7
15°	2110.3	1908.8	1748.3	1568.7	1493.2	1407.2	1278.3	1147.3	1017.4	915.3	821.6
17.5°	2262.2	2022.4	1825.6	1616.4	1526.7	1428.2	1280.2	1132.1	991.7	879.8	782.4
20°	2374.0	2108.5	1878.2	1644.1	1542.9	1435.9	1272.5	1112.0	964.9	850.2	750.9
22.5°	2455.2	2160.0	1904.9	1653.7	1543.8	1432.1	1259.2	1094.8	946.7	835.0	740.4
25°	2503.9	2185.8	1913.5	1649.9	1536.2	1419.6	1243.9	1079.6	935.3	829.2	742.3
27.5°	2508.7	2175.3	1890.6	1621.3	1504.7	1388.2	1212.3	1049.9	910.5	813.0	729.9
30°	2454.2	2116.1	1830.4	1558.1	1440.6	1326.1	1153.1	993.6	860.8	764.3	688.9
32.5°	2349.2	2012.0	1729.1	1462.6	1347.1	1235.2	1067.1	917.1	787.2	698.4	623.8
35°	2209.8	1880.1	1598.3	1348.0	1235.2	1129.2	965.9	818.7	700.2	616.2	548.4
37.5°	2044.4	1726.3	1462.6	1220.9	1112.0	1013.6	856.0	722.2	608.6	531.2	469.0
40°	1856.2	1552.5	1304.9	1075.7	978.3	882.8	739.4	617.1	511.2	444.3	391.7
42.5°	1652.7	1368.1	1139.7	926.7	837.8	750.9	621.0	510.1	418.4	364.0	322.9
45°	1429.2	1173.1	967.7	781.5	696.5	624.8	502.5	410.8	341.1	295.2	266.6
47.5°	1190.4	967.7	789.1	628.6	554.1	493.0	392.6	323.8	274.2	242.6	218.8
50°	950.6	765.3	616.2	477.7	421.2	369.7	303.8	257.0	218.8	194.8	179.6
52.5°	726.1	576.1	458.6	350.6	312.4	277.0	234.0	202.6	173.8	156.7	145.2
55°	526.4	415.6	326.8	257.0	231.2	211.2	179.6	156.7	138.5	125.1	115.6
57.5°	366.9	287.6	228.3	187.2	171.9	157.6	135.7	120.4	108.0	98.4	90.7
60°	248.4	194.8	159.5	135.7	126.1	116.6	102.2	91.7	82.2	75.5	67.8
62.5°	163.4	133.8	113.7	99.4	90.7	84.0	75.5	66.9	59.3	53.5	46.8
65°	106.0	87.9	78.3	66.9	63.0	58.3	50.6	45.9	39.2	34.4	29.6
67.5°	66.9	57.3	50.6	43.9	41.1	37.2	33.5	28.6	24.9	21.0	18.2
70°	40.1	35.3	30.5	26.8	24.9	22.9	20.1	17.3	14.3	13.4	11.5
72.5°	23.8	21.0	18.2	16.2	15.3	14.3	12.4	10.6	9.5	8.6	7.6
75°	14.3	13.4	11.5	9.5	9.5	8.6	8.6	7.6	6.7	6.7	5.8
77.5°	9.5	8.6	7.6	6.7	6.7	6.7	5.8	5.8	5.8	5.8	5.8
80°	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
82.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	4.8	4.8
85°	2.8	2.8	2.8	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
87.5°	2.8	2.8	2.8	2.8	3.9	3.9	3.9	3.9	3.9	3.9	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192366

CATALOG NUMBER: LDA6A50930D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8
2.5°	1008.8	980.2	968.7	951.5	934.3	933.3	913.3	902.8	895.2	881.8	868.4
5°	963.0	919.0	892.3	869.4	847.4	832.0	802.5	782.4	764.3	745.2	720.3
7.5°	909.5	853.2	814.9	786.3	760.5	736.6	700.2	673.5	650.6	632.4	601.9
10°	852.1	787.2	739.4	707.9	681.1	646.7	611.4	581.8	556.9	536.9	507.3
12.5°	798.7	727.0	673.5	641.1	613.4	576.1	539.8	509.2	482.4	463.4	436.6
15°	749.0	673.5	616.2	583.7	555.1	517.8	481.5	450.9	426.1	406.0	382.2
17.5°	705.1	625.7	569.4	539.8	510.1	475.7	439.4	410.8	385.9	367.8	348.7
20°	675.5	600.0	545.5	517.8	492.0	459.5	430.9	408.0	384.0	369.7	358.2
22.5°	670.7	603.8	556.9	534.0	514.0	490.1	472.9	461.4	445.2	438.5	438.5
25°	680.2	622.9	585.6	567.5	551.2	537.9	529.2	521.6	515.8	516.8	516.8
27.5°	674.4	622.9	592.3	575.1	560.8	552.2	543.5	538.9	533.1	535.9	535.9
30°	637.2	587.6	561.7	543.5	530.2	522.5	510.1	504.5	497.8	498.7	495.8
32.5°	575.1	528.3	503.4	486.3	472.0	464.3	450.9	444.3	435.7	435.7	429.9
35°	502.5	458.6	435.7	420.3	406.9	399.3	386.9	380.2	371.6	366.9	364.0
37.5°	426.1	387.9	366.9	355.4	344.8	337.2	325.8	321.0	312.4	308.6	304.7
40°	355.4	327.7	307.6	298.1	289.4	282.7	272.3	268.4	260.8	258.0	254.1
42.5°	294.3	273.2	257.0	249.3	239.8	235.9	228.3	224.5	217.8	214.9	211.2
45°	245.5	228.3	214.9	208.2	202.6	197.8	190.1	187.2	180.5	177.7	175.8
47.5°	202.6	189.2	178.6	172.9	170.1	164.3	157.6	154.8	150.0	147.1	144.3
50°	166.2	155.8	147.1	142.4	140.4	134.7	129.0	127.1	122.3	120.4	117.5
52.5°	135.7	127.1	119.4	115.6	111.7	108.0	103.2	101.3	96.5	93.7	89.8
55°	108.9	100.4	93.7	90.7	88.9	83.1	78.3	75.5	71.6	66.9	64.0
57.5°	84.0	76.4	70.7	66.9	66.0	60.2	56.3	51.6	46.8	43.9	41.1
60°	62.1	55.4	49.6	45.9	45.0	39.2	34.4	31.6	27.7	25.8	24.9
62.5°	41.1	36.3	31.6	29.6	27.7	23.8	21.0	19.1	17.3	16.2	15.3
65°	25.8	21.9	19.1	18.2	16.2	14.3	13.4	12.4	11.5	10.6	9.5
67.5°	15.3	13.4	11.5	11.5	10.6	9.5	9.5	8.6	7.6	7.6	7.6
70°	9.5	8.6	7.6	7.6	7.6	7.6	7.6	6.7	6.7	6.7	6.7
72.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.8	5.8
75°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
77.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8
80°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
82.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	3.9	3.9	3.9
85°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	2.8
87.5°	3.9	3.9	3.9	3.9	3.9	2.8	2.8	2.8	2.8	2.8	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192366

CATALOG NUMBER: LDA6A50930D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8	1050.8
2.5°	857.9	841.7	839.8	835.9	832.0	836.9	834.0	826.4
5°	711.7	691.7	687.8	682.2	676.4	678.3	673.5	666.8
7.5°	589.4	568.4	564.6	557.9	552.2	551.2	546.5	539.8
10°	490.1	473.8	470.1	463.4	456.7	455.8	450.0	445.2
12.5°	419.4	404.1	400.2	393.5	387.9	385.9	381.2	377.4
15°	366.9	352.5	348.7	343.0	336.3	336.3	332.5	328.6
17.5°	334.4	322.0	317.1	312.4	306.7	305.8	303.8	300.9
20°	347.8	336.3	334.4	328.6	329.6	329.6	327.7	326.8
22.5°	433.7	429.9	437.6	431.8	442.4	446.1	448.0	448.0
25°	520.7	521.6	529.2	526.4	535.9	543.5	547.4	544.5
27.5°	535.9	536.9	539.8	538.9	546.5	551.2	554.1	547.4
30°	492.0	491.1	490.1	489.1	493.9	495.8	496.8	490.1
32.5°	424.2	421.2	422.3	417.5	419.4	419.4	423.2	413.6
35°	356.3	352.5	352.5	347.8	347.8	347.8	350.6	341.1
37.5°	299.1	295.2	294.3	289.4	288.5	286.6	289.4	280.9
40°	249.3	245.5	246.5	240.7	241.7	240.7	240.7	235.9
42.5°	206.3	203.5	202.6	200.6	201.5	201.5	204.5	200.6
45°	171.0	168.2	167.1	166.2	167.1	167.1	168.2	164.3
47.5°	142.4	138.5	137.6	135.7	135.7	132.7	132.7	129.0
50°	114.7	108.9	108.0	105.0	104.1	102.2	102.2	99.4
52.5°	87.0	82.2	80.3	78.3	77.3	75.5	75.5	73.6
55°	61.2	56.3	55.4	54.5	53.5	52.6	53.5	51.6
57.5°	38.3	36.3	35.3	34.4	33.5	32.5	32.5	31.6
60°	22.9	21.0	21.0	20.1	19.1	18.2	18.2	18.2
62.5°	14.3	13.4	13.4	12.4	12.4	11.5	11.5	11.5
65°	9.5	8.6	8.6	7.6	7.6	6.7	6.7	6.7
67.5°	6.7	6.7	6.7	6.7	5.8	5.8	5.8	5.8
70°	6.7	5.8	5.8	5.8	5.8	5.8	5.8	5.8
72.5°	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8
75°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
77.5°	4.8	4.8	4.8	4.8	3.9	3.9	3.9	3.9
80°	4.8	3.9	3.9	3.9	3.9	3.9	3.9	3.9
82.5°	3.9	3.9	3.9	3.9	3.9	2.8	2.8	2.8
85°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	1.9
87.5°	1.9	1.9	1.9	1.9	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)