

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192367

Luminaire Tested: **LDA6A50930D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192367
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26672)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50930D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4850.6 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 2.54 / 0.51 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192367

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192367

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	62	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	40	39		
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	59694	59694	59694
5°	152636	55030	20080
10°	328050	44394	7387
15°	478550	32475	8451
20°	541888	23347	13039
25°	587441	18775	20221
30°	655462	15414	19465
35°	665296	9965	12976
40°	670191	4788	6562
45°	666007	2000	2737
50°	533236	904	904
55°	159029	640	86
60°	32465	735	0
65°	3087	869	0
70°	305	1218	0
75°	0	1610	0
80°	0	2715	284
85°	0	5409	566

TEST NUMBER: P1192367

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.6	2.9
10°-20°	680.3	14.0
20°-30°	1250.3	25.8
30°-40°	1434.5	29.6
40°-50°	1085.3	22.4
50°-60°	240.5	5.0
60°-70°	10.2	0.2
70°-80°	4.5	0.1
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2071.2	42.7
0°-40°	3505.7	72.3
0°-60°	4831.5	99.6
0°-90°	4850.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4850.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1089	1089	1089	1089	1089	
5°	2774	2072	1000	489	365	367
15°	8432	4573	572	148	149	2350
25°	9712	5377	310	301	334	4531
35°	9941	3319	149	186	194	6227
45°	8591	939	26	34	35	6411
55°	1664	35	7	5	1	2060
65°	24	5	7	4	0	64
75°	0	4	8	5	0	0
85°	0	5	9	5	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192367

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9
2.5°	1844.4	1826.2	1831.0	1853.9	1759.4	1756.5	1712.6	1706.8	1662.9	1582.6	1542.5
5°	2773.7	2762.2	2742.2	2749.9	2641.9	2569.4	2492.9	2437.5	2324.8	2172.9	2071.7
7.5°	4256.1	4132.0	4071.7	3956.1	3818.7	3678.2	3536.9	3372.6	3135.7	2871.2	2657.2
10°	5893.2	5838.8	5715.5	5642.1	5337.4	5131.0	4911.3	4575.2	4141.5	3662.0	3262.8
12.5°	7497.8	7433.9	7247.6	7091.0	6685.0	6500.6	6215.1	5791.0	5240.9	4557.9	3926.6
15°	8432.0	8446.3	8235.3	8227.5	7878.0	7638.2	7390.9	6889.4	6191.2	5407.1	4573.2
17.5°	8979.3	9014.6	8805.5	8864.6	8516.0	8267.7	8083.4	7716.6	6974.5	6033.6	5072.8
20°	9288.7	9345.1	9122.6	9168.4	8870.4	8702.3	8515.1	8152.2	7496.9	6458.6	5356.4
22.5°	9524.6	9546.7	9299.3	9360.4	9034.7	8866.6	8733.8	8393.7	7747.1	6683.2	5445.2
25°	9711.8	9767.2	9484.6	9489.3	9165.6	8997.4	8850.3	8540.9	7854.2	6742.3	5377.4
27.5°	9981.2	10026.1	9610.6	9574.4	9261.0	9075.8	8916.3	8611.6	7849.4	6610.5	5121.5
30°	10354.7	10104.4	9679.4	9585.8	9233.3	9045.1	8874.3	8478.8	7673.7	6255.2	4656.3
32.5°	10247.7	10045.3	9625.9	9477.0	9127.3	8925.8	8730.0	8248.5	7265.8	5705.1	4022.1
35°	9941.2	9876.1	9435.9	9389.0	8965.9	8754.8	8558.1	7899.9	6640.2	4985.8	3319.2
37.5°	9682.2	9571.4	9287.8	9214.3	8770.1	8537.0	8223.8	7379.4	5813.0	4068.9	2650.5
40°	9365.1	9290.7	9016.5	8938.2	8424.4	8069.1	7686.0	6435.7	4813.9	3167.3	2046.8
42.5°	9028.0	8961.1	8702.3	8538.0	7853.1	7383.3	6788.2	5293.4	3705.9	2386.9	1533.9
45°	8590.6	8496.0	8172.1	7866.5	6884.7	6212.3	5542.7	4039.2	2712.6	1699.2	938.9
47.5°	7838.8	7688.9	7296.3	6682.2	5475.9	4830.2	4132.9	2739.3	1675.4	874.9	472.8
50°	6252.4	5990.7	5468.2	4737.5	3507.3	2888.4	2342.0	1392.6	719.3	450.8	277.9
52.5°	3853.1	3613.3	3168.2	2463.3	1617.0	1245.6	980.9	648.6	396.4	255.0	103.2
55°	1663.9	1513.9	1300.9	992.4	704.9	579.8	466.1	323.8	204.3	78.3	35.3
57.5°	628.5	583.6	529.1	434.6	324.8	271.2	228.3	143.3	49.6	29.6	20.1
60°	296.1	268.4	236.9	188.1	124.2	89.8	56.3	36.3	23.8	16.2	11.5
62.5°	81.2	61.2	50.6	41.1	31.6	27.7	23.8	18.2	13.4	8.6	6.7
65°	23.8	21.0	20.1	17.1	14.3	12.4	10.6	8.6	6.7	4.8	4.8
67.5°	8.6	8.6	7.6	6.7	5.8	4.8	4.8	3.9	3.9	3.9	3.9
70°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8	2.8	3.9	3.9
72.5°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.8	2.8	3.9	3.9
75°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.8	2.8	3.9	3.9
77.5°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.8	3.9	3.9	4.8
80°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.8	3.9	3.9	4.8
82.5°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.8	3.9	3.9	4.8
85°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.8	3.9	3.9	4.8
87.5°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	2.8	3.9	3.9	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192367

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9
2.5°	1509.2	1453.8	1375.4	1335.3	1299.9	1290.4	1217.9	1171.0	1115.6	1058.3	998.1
5°	1977.1	1835.8	1685.8	1559.8	1495.8	1458.5	1317.1	1211.2	1108.9	1000.0	907.4
7.5°	2441.3	2188.3	1969.5	1766.1	1654.4	1570.2	1367.7	1208.2	1053.5	912.2	787.0
10°	2890.3	2525.4	2176.8	1901.7	1747.9	1622.8	1361.0	1153.8	959.9	797.5	666.7
12.5°	3344.9	2812.9	2349.7	1974.3	1790.9	1630.4	1315.3	1063.0	857.8	685.8	550.1
15°	3750.9	3036.4	2457.5	1991.4	1769.9	1580.8	1225.5	947.5	743.1	572.2	453.6
17.5°	4032.7	3156.7	2464.2	1928.4	1682.1	1478.5	1100.4	826.2	627.5	476.6	372.5
20°	4160.6	3153.0	2373.5	1797.6	1539.7	1327.6	952.2	702.0	523.4	400.2	311.4
22.5°	4122.3	3032.5	2213.0	1612.2	1365.9	1153.8	814.7	592.1	449.9	343.9	273.1
25°	3931.4	2822.4	2024.9	1427.0	1178.6	980.9	690.6	506.2	390.6	310.4	248.4
27.5°	3619.0	2535.9	1771.7	1210.2	982.9	829.1	581.7	437.4	343.9	274.2	258.8
30°	3162.5	2188.3	1474.8	976.2	793.7	656.2	471.8	352.5	275.1	243.5	244.5
32.5°	2659.1	1805.2	1159.5	746.0	597.9	506.2	348.6	246.5	201.5	199.6	200.6
35°	2157.6	1406.0	862.4	545.4	438.4	364.9	224.4	154.7	150.0	148.9	150.9
37.5°	1712.6	1045.9	621.8	381.1	290.4	222.5	121.2	105.0	101.3	103.2	104.1
40°	1278.9	733.6	420.3	225.5	141.3	102.2	73.6	67.8	66.0	66.9	66.9
42.5°	879.7	458.5	250.2	93.5	67.8	56.3	46.8	43.9	42.0	41.1	42.0
45°	473.7	285.6	97.4	47.8	40.1	36.3	29.6	27.7	26.8	25.8	25.8
47.5°	302.8	106.0	43.9	29.6	25.8	23.8	20.1	18.2	17.1	16.2	16.2
50°	113.6	41.1	26.8	19.1	16.2	15.3	12.4	11.5	10.6	10.6	10.6
52.5°	39.2	24.9	17.1	12.4	10.6	9.5	8.6	7.6	7.6	7.6	7.6
55°	21.9	15.3	10.6	7.6	7.6	6.7	6.7	6.7	6.7	6.7	6.7
57.5°	13.4	8.6	6.7	5.8	5.8	5.8	5.8	6.7	6.7	6.7	6.7
60°	7.6	5.8	5.8	5.8	5.8	5.8	5.8	5.8	6.7	6.7	6.7
62.5°	4.8	4.8	4.8	4.8	4.8	5.8	5.8	6.7	6.7	6.7	6.7
65°	4.8	4.8	4.8	4.8	4.8	5.8	5.8	6.7	6.7	6.7	6.7
67.5°	3.9	4.8	4.8	5.8	5.8	5.8	5.8	6.7	6.7	7.6	6.7
70°	4.8	4.8	4.8	5.8	5.8	5.8	6.7	6.7	7.6	7.6	7.6
72.5°	4.8	4.8	4.8	5.8	5.8	5.8	6.7	6.7	7.6	7.6	7.6
75°	4.8	4.8	5.8	5.8	5.8	6.7	6.7	7.6	7.6	7.6	7.6
77.5°	4.8	4.8	5.8	5.8	5.8	6.7	6.7	7.6	7.6	8.6	7.6
80°	4.8	4.8	5.8	6.7	6.7	6.7	6.7	7.6	7.6	8.6	8.6
82.5°	4.8	5.8	5.8	6.7	6.7	6.7	7.6	7.6	8.6	8.6	8.6
85°	4.8	5.8	5.8	6.7	6.7	6.7	7.6	7.6	8.6	8.6	8.6
87.5°	4.8	5.8	5.8	6.7	6.7	6.7	7.6	7.6	8.6	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192367

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9
2.5°	965.6	910.2	865.4	866.3	829.1	800.4	764.1	744.0	727.8	701.1	676.3
5°	839.6	754.6	690.6	678.2	635.2	591.2	546.4	512.9	489.1	463.3	439.3
7.5°	702.9	605.5	532.0	514.8	478.5	437.4	396.4	362.9	334.3	306.6	277.9
10°	570.2	481.3	414.6	397.3	361.0	318.1	278.9	249.3	227.3	205.4	183.3
12.5°	461.4	383.0	320.0	298.0	268.4	235.0	203.4	174.8	150.9	141.3	138.5
15°	373.5	298.9	249.3	231.1	206.3	171.9	153.8	148.9	148.0	148.0	148.0
17.5°	301.9	243.5	198.7	179.6	167.1	165.3	165.3	165.3	166.2	168.1	171.9
20°	253.1	201.5	184.4	186.3	186.3	188.1	192.0	194.8	198.7	203.4	209.2
22.5°	224.4	214.0	212.1	217.7	218.8	224.4	232.0	237.8	244.5	252.1	256.9
25°	245.4	249.3	252.1	260.8	263.6	273.1	284.6	293.2	300.8	309.5	315.1
27.5°	267.5	274.2	279.8	288.5	290.4	302.8	312.3	318.1	323.8	327.6	331.5
30°	252.1	258.8	264.6	272.2	272.2	285.6	290.4	295.2	299.9	301.9	305.6
32.5°	207.3	214.0	219.7	225.5	226.4	235.9	241.7	243.5	247.4	248.4	251.2
35°	155.6	158.6	164.3	169.0	170.1	176.6	181.5	183.3	186.3	186.3	188.1
37.5°	106.9	108.9	113.6	116.6	118.4	123.2	126.1	127.9	129.9	130.9	131.8
40°	69.7	70.7	73.6	76.4	78.3	81.2	83.1	85.0	85.9	87.9	87.9
42.5°	43.0	43.9	45.9	47.8	47.8	50.6	51.5	53.5	54.5	55.4	55.4
45°	26.8	27.7	27.7	28.6	29.6	30.5	32.5	32.5	33.5	33.5	33.5
47.5°	16.2	17.1	16.2	17.1	17.1	18.2	19.1	19.1	19.1	19.1	19.1
50°	10.6	10.6	10.6	10.6	10.6	10.6	11.5	11.5	11.5	11.5	10.6
52.5°	7.6	7.6	6.7	7.6	6.7	6.7	6.7	6.7	6.7	6.7	5.8
55°	6.7	6.7	6.7	6.7	5.8	5.8	5.8	4.8	4.8	3.9	3.9
57.5°	6.7	6.7	5.8	5.8	5.8	4.8	4.8	4.8	3.9	3.9	2.8
60°	6.7	6.7	5.8	5.8	5.8	4.8	4.8	3.9	3.9	2.8	2.8
62.5°	6.7	6.7	5.8	5.8	5.8	5.8	4.8	4.8	3.9	3.9	2.8
65°	6.7	6.7	6.7	5.8	5.8	5.8	4.8	4.8	3.9	3.9	2.8
67.5°	6.7	6.7	6.7	6.7	5.8	5.8	5.8	4.8	3.9	3.9	2.8
70°	6.7	6.7	6.7	6.7	6.7	5.8	5.8	4.8	4.8	3.9	2.8
72.5°	7.6	7.6	6.7	6.7	6.7	5.8	5.8	4.8	4.8	3.9	3.9
75°	7.6	7.6	6.7	6.7	6.7	5.8	5.8	4.8	4.8	3.9	3.9
77.5°	7.6	7.6	7.6	7.6	6.7	6.7	5.8	5.8	4.8	4.8	3.9
80°	7.6	7.6	7.6	7.6	6.7	6.7	6.7	5.8	4.8	4.8	3.9
82.5°	7.6	7.6	7.6	7.6	7.6	6.7	6.7	5.8	4.8	4.8	3.9
85°	7.6	7.6	7.6	7.6	7.6	6.7	6.7	5.8	4.8	4.8	3.9
87.5°	7.6	7.6	7.6	7.6	7.6	6.7	6.7	5.8	4.8	4.8	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192367

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9
2.5°	653.3	640.9	639.9	629.5	608.5	618.9	605.5	596.0
5°	418.3	404.9	391.6	393.5	378.3	381.1	370.5	364.9
7.5°	265.5	251.2	247.4	247.4	230.2	230.2	223.5	219.7
10°	167.1	155.6	151.9	145.2	137.6	136.6	133.7	132.7
12.5°	135.7	135.7	132.7	133.7	133.7	133.7	132.7	132.7
15°	148.0	148.9	146.1	147.1	148.9	148.0	148.9	148.9
17.5°	171.0	175.7	171.9	173.8	177.7	176.6	177.7	178.6
20°	209.2	216.8	212.1	215.8	220.7	219.7	222.5	223.5
22.5°	260.8	270.3	265.5	269.4	277.0	275.1	278.9	280.8
25°	318.1	327.6	321.8	326.6	331.5	333.3	333.3	334.3
27.5°	331.5	337.2	333.3	338.1	340.0	341.9	340.0	341.0
30°	303.8	308.5	304.7	309.5	309.5	311.4	309.5	307.5
32.5°	250.2	254.1	249.3	255.0	254.1	255.0	256.0	256.9
35°	189.1	191.1	188.1	189.1	190.0	191.1	193.9	193.9
37.5°	131.8	134.6	131.8	132.7	132.7	134.6	136.6	136.6
40°	87.9	90.7	87.9	89.8	88.9	89.8	91.7	91.7
42.5°	55.4	57.3	55.4	56.3	56.3	56.3	57.3	58.2
45°	33.5	34.4	33.5	34.4	34.4	34.4	35.3	35.3
47.5°	19.1	20.1	19.1	19.1	20.1	19.1	20.1	20.1
50°	10.6	10.6	10.6	10.6	10.6	9.5	9.5	10.6
52.5°	5.8	5.8	4.8	4.8	4.8	4.8	4.8	4.8
55°	2.8	2.8	1.9	1.9	1.9	0.9	1.9	0.9
57.5°	1.9	1.9	0.9	0.9	0.9	0.9	0.0	0.0
60°	1.9	1.9	0.9	0.9	0.9	0.0	0.0	0.0
62.5°	1.9	1.9	0.9	0.9	0.9	0.0	0.0	0.0
65°	1.9	1.9	0.9	0.9	0.9	0.0	0.0	0.0
67.5°	2.8	1.9	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.8	1.9	1.9	0.9	0.9	0.0	0.0	0.0
72.5°	2.8	1.9	1.9	1.9	0.9	0.9	0.0	0.0
75°	2.8	1.9	1.9	1.9	0.9	0.9	0.0	0.0
77.5°	2.8	2.8	1.9	1.9	0.9	0.9	0.9	0.0
80°	2.8	2.8	1.9	1.9	1.9	0.9	0.9	0.9
82.5°	2.8	2.8	1.9	1.9	1.9	0.9	0.9	0.9
85°	2.8	2.8	1.9	1.9	1.9	0.9	0.9	0.9
87.5°	2.8	2.8	1.9	1.9	1.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)