

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192372

Luminaire Tested: **LDA6A50930D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26669)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50930D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3656.6 lumens
Efficiency: N/A
Efficacy: 63.7 lumens/watt
Spacing Criteria (0/90/45): 2.14 / 1.07 / 1.49
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192372

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192372

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	104	97	92	88	101	96	91	87	92	88	85		89	86	83		86
3	96	88	81	76	94	86	80	75	84	78	74		81	77	73		79
4	89	79	72	66	87	78	71	66	76	70	65		74	68	64		71
5	83	72	64	58	81	71	64	58	69	62	58		67	61	57		65
6	77	65	57	52	75	64	57	52	63	56	51		61	55	51		60
7	72	59	52	46	70	59	51	46	57	51	46		56	50	45		55
8	67	54	47	41	65	54	46	41	53	46	41		51	45	41		50
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	64200	64200	64200
5°	102768	63394	41107
10°	150164	60887	27705
15°	205308	57742	20925
20°	256846	54669	21124
25°	296697	54487	32766
30°	325012	51578	30479
35°	335613	43728	23523
40°	328465	34107	18528
45°	299411	25181	14226
50°	240649	18575	9526
55°	146528	13151	5381
60°	76047	8684	2094
65°	37047	4579	986
70°	16990	1988	930
75°	7096	1419	1017
80°	3631	1515	1231
85°	2453	3019	1761

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192372

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.1	3.3
10°-20°	425.6	11.6
20°-30°	805.7	22.0
30°-40°	975.9	26.7
40°-50°	816.8	22.3
50°-60°	395.8	10.8
60°-70°	97.0	2.7
70°-80°	15.8	0.4
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1351.5	37.0
0°-40°	2327.4	63.6
0°-60°	3539.9	96.8
0°-90°	3656.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3656.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1171	1171	1171	1171	1171	
5°	1868	1609	1152	842	747	204
15°	3618	2515	1017	465	369	1044
25°	4905	2963	901	530	542	2259
35°	5015	2618	653	377	352	3108
45°	3862	1766	325	198	184	2930
55°	1533	724	138	74	56	1437
65°	286	159	35	12	8	322
75°	34	17	7	6	5	45
85°	4	3	5	4	3	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192372

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1
2.5°	1486.4	1452.0	1459.6	1465.4	1439.6	1455.8	1428.1	1418.6	1395.6	1401.3	1384.2
5°	1867.5	1819.7	1805.4	1805.4	1762.5	1776.8	1751.9	1708.0	1663.0	1649.7	1608.6
7.5°	2277.2	2224.8	2201.8	2192.3	2129.2	2120.7	2099.7	2031.8	1958.2	1919.0	1846.5
10°	2697.6	2649.8	2617.4	2595.3	2508.5	2493.2	2455.9	2360.3	2267.7	2183.7	2064.2
12.5°	3160.8	3096.9	3053.9	3017.6	2905.8	2881.9	2826.5	2698.5	2552.4	2451.1	2293.6
15°	3617.5	3552.5	3496.2	3443.6	3308.0	3273.6	3199.1	3036.6	2865.8	2714.8	2515.2
17.5°	4052.1	3970.0	3901.2	3830.5	3670.9	3628.0	3530.5	3350.0	3111.2	2940.2	2699.6
20°	4402.7	4322.5	4243.1	4153.3	3970.9	3919.3	3800.9	3586.9	3315.6	3110.2	2829.4
22.5°	4689.2	4598.5	4520.2	4402.7	4197.3	4137.1	4000.5	3757.9	3464.6	3224.9	2916.3
25°	4905.1	4808.6	4728.4	4596.6	4369.3	4299.6	4139.9	3877.3	3557.3	3293.7	2963.2
27.5°	5075.2	4964.4	4873.6	4727.5	4477.2	4398.9	4224.1	3940.3	3594.5	3307.1	2961.2
30°	5134.4	5026.5	4924.2	4766.6	4497.2	4410.4	4228.8	3921.3	3561.1	3251.7	2895.3
32.5°	5108.6	4996.9	4886.1	4718.8	4434.2	4340.6	4157.2	3828.6	3458.9	3133.1	2774.0
35°	5014.9	4901.3	4782.9	4610.0	4311.9	4210.7	4027.3	3687.2	3303.2	2977.5	2618.3
37.5°	4845.0	4731.3	4619.5	4433.3	4128.6	4023.5	3842.9	3490.4	3116.0	2787.3	2437.8
40°	4589.9	4477.2	4374.0	4185.8	3879.3	3773.2	3602.1	3252.6	2891.5	2566.7	2230.4
42.5°	4261.3	4153.3	4060.7	3876.3	3576.4	3475.1	3314.7	2976.6	2639.3	2325.0	2008.8
45°	3862.0	3763.6	3678.7	3504.7	3227.7	3130.3	2987.9	2668.0	2353.7	2059.5	1766.2
47.5°	3401.6	3311.8	3237.4	3076.8	2819.9	2731.0	2608.7	2311.6	2030.9	1762.5	1501.7
50°	2821.7	2743.5	2691.8	2553.3	2324.1	2249.5	2155.1	1904.7	1674.5	1443.3	1227.5
52.5°	2153.1	2091.9	2068.1	1964.0	1786.3	1734.8	1673.6	1481.6	1313.4	1131.0	962.9
55°	1533.1	1493.1	1477.7	1409.9	1293.4	1260.0	1207.4	1089.0	977.2	848.2	724.1
57.5°	1044.0	1023.0	1011.6	969.6	897.9	875.0	845.4	769.0	697.3	613.3	524.4
60°	693.6	684.9	675.4	649.5	607.5	590.4	576.1	525.4	481.5	428.9	366.8
62.5°	449.9	446.1	439.4	423.1	406.9	395.4	380.2	346.7	321.0	294.3	247.4
65°	285.6	281.8	278.9	268.4	257.9	246.5	240.7	221.6	205.4	188.1	158.6
67.5°	176.8	173.8	172.9	166.2	158.6	151.9	148.0	135.7	126.1	115.6	96.5
70°	106.0	105.0	103.2	99.3	94.6	89.8	87.9	79.2	73.6	66.9	54.5
72.5°	61.2	60.2	59.3	56.3	53.5	51.5	49.6	46.8	40.1	36.3	30.5
75°	33.5	33.5	32.5	30.5	29.6	27.7	26.8	24.9	21.9	20.1	17.1
77.5°	19.1	18.2	18.2	17.1	16.2	16.2	15.3	14.3	12.4	12.4	10.6
80°	11.5	11.5	11.5	10.6	10.6	10.6	9.5	9.5	8.6	7.6	7.6
82.5°	7.6	6.7	6.7	6.7	6.7	6.7	5.8	5.8	5.8	5.8	4.8
85°	3.9	3.9	3.9	3.9	2.8	3.9	2.8	2.8	2.8	2.8	2.8
87.5°	0.0	0.0	0.9	0.9	0.9	0.9	0.9	1.9	1.9	1.9	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192372

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1
2.5°	1339.2	1329.7	1310.6	1283.8	1274.3	1268.6	1237.0	1208.3	1188.3	1162.6	1137.7
5°	1534.1	1498.7	1452.9	1397.5	1375.5	1356.5	1298.1	1244.7	1200.7	1152.0	1106.1
7.5°	1735.7	1669.7	1592.4	1504.5	1468.2	1434.8	1346.8	1267.6	1199.8	1130.1	1064.1
10°	1924.8	1824.5	1712.7	1595.2	1540.7	1492.0	1375.5	1273.4	1183.6	1093.8	1012.6
12.5°	2110.1	1973.5	1825.5	1674.5	1603.9	1540.7	1396.6	1271.4	1160.6	1055.5	962.0
15°	2288.8	2112.0	1929.6	1744.3	1659.3	1581.8	1410.9	1264.7	1136.7	1017.4	913.2
17.5°	2433.0	2224.8	2004.1	1786.3	1690.7	1601.0	1408.9	1245.7	1104.2	974.3	863.5
20°	2534.3	2294.5	2049.0	1805.4	1701.3	1601.9	1394.6	1219.8	1070.8	937.1	825.4
22.5°	2591.6	2326.9	2064.2	1805.4	1693.7	1589.6	1374.5	1195.9	1046.0	915.1	808.1
25°	2615.4	2332.6	2057.5	1790.2	1674.5	1567.5	1351.7	1173.0	1025.9	900.8	801.4
27.5°	2596.4	2299.2	2020.3	1748.1	1629.6	1522.7	1307.8	1132.9	990.6	871.1	776.6
30°	2519.9	2215.2	1937.2	1666.9	1547.4	1443.3	1235.1	1066.1	929.5	814.8	725.0
32.5°	2395.7	2093.0	1819.7	1556.1	1437.7	1337.3	1138.6	978.2	847.3	738.4	655.3
35°	2244.9	1947.7	1684.1	1427.1	1313.4	1218.0	1030.6	874.1	753.6	653.4	577.0
37.5°	2074.8	1787.2	1526.4	1290.5	1181.6	1090.9	916.1	769.0	658.1	565.5	497.7
40°	1883.7	1612.5	1366.9	1143.4	1040.3	956.2	791.0	661.0	559.7	476.6	419.4
42.5°	1682.2	1429.0	1200.7	991.6	894.1	817.7	667.7	552.1	463.3	395.4	349.7
45°	1466.3	1232.3	1023.0	835.8	754.6	678.2	551.2	446.1	376.4	324.8	290.4
47.5°	1236.0	1028.8	844.4	681.1	610.5	543.5	436.5	356.3	305.6	266.6	240.7
50°	1004.9	830.1	673.5	533.9	473.8	420.3	338.1	283.7	246.5	217.8	196.8
52.5°	785.2	643.8	515.8	402.1	357.3	319.0	262.7	224.5	196.8	174.8	159.5
55°	589.3	477.6	377.4	292.3	265.6	241.7	204.5	173.8	154.7	137.6	126.1
57.5°	427.0	341.0	268.4	214.9	197.8	181.5	154.7	133.7	119.4	106.0	97.4
60°	300.0	236.9	190.1	157.6	144.3	134.7	113.6	100.4	88.9	79.2	70.7
62.5°	201.5	160.4	132.7	111.7	103.2	96.5	83.1	71.6	63.0	55.4	47.8
65°	129.0	108.0	89.8	75.5	69.7	64.9	56.3	46.8	41.1	35.3	29.6
67.5°	79.2	67.8	56.3	46.8	43.0	40.1	34.4	28.6	24.9	21.0	18.2
70°	45.9	39.2	32.5	27.7	25.8	23.8	20.1	17.1	15.3	12.4	10.6
72.5°	25.8	22.9	19.1	16.2	15.3	14.3	12.4	10.6	9.5	8.6	7.6
75°	15.3	13.4	11.5	10.6	9.5	9.5	8.6	7.6	6.7	6.7	5.8
77.5°	9.5	8.6	7.6	7.6	6.7	6.7	6.7	5.8	5.8	5.8	5.8
80°	6.7	6.7	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8	4.8
82.5°	4.8	4.8	4.8	3.9	3.9	3.9	3.9	3.9	4.8	4.8	4.8
85°	2.8	2.8	3.9	3.9	3.9	3.9	3.9	3.9	4.8	4.8	4.8
87.5°	2.8	2.8	2.8	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192372

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1
2.5°	1110.9	1099.4	1078.4	1059.4	1056.5	1029.7	1002.0	996.3	986.7	971.5	953.3
5°	1060.3	1029.7	993.4	966.7	955.3	917.0	878.8	861.6	842.5	812.9	795.7
7.5°	1001.1	956.2	905.5	875.0	858.8	811.0	767.0	742.3	716.4	684.9	663.9
10°	936.2	879.8	820.5	786.2	767.0	715.5	668.7	640.0	612.3	580.8	558.8
12.5°	875.0	811.0	746.0	709.7	688.7	635.2	587.4	556.9	529.2	503.4	477.6
15°	820.5	749.0	681.1	644.8	622.8	568.3	522.5	491.9	465.1	440.4	417.5
17.5°	768.0	693.6	626.6	591.3	569.4	518.7	474.8	447.1	421.2	398.4	378.3
20°	731.7	661.0	598.0	564.6	545.4	500.6	463.3	441.3	423.1	403.1	385.9
22.5°	722.2	659.2	604.7	577.0	562.7	527.2	500.6	487.2	481.5	469.0	459.5
25°	722.2	666.8	620.9	598.0	586.5	559.7	538.7	533.9	530.2	522.5	517.7
27.5°	704.0	652.5	611.4	591.3	581.7	557.9	539.7	533.9	529.2	523.5	517.7
30°	656.2	608.5	570.3	552.1	542.6	519.6	500.6	493.9	489.1	480.5	475.7
32.5°	592.3	546.4	514.9	493.9	485.2	463.3	445.2	437.4	433.7	426.1	417.5
35°	520.7	480.5	449.9	432.8	424.2	405.1	388.7	381.1	377.4	368.7	358.2
37.5°	448.0	411.7	386.9	370.7	364.0	348.7	334.3	328.6	324.8	318.1	309.5
40°	376.4	350.6	328.6	316.2	310.4	298.0	285.6	279.9	277.0	271.2	264.6
42.5°	317.1	296.1	278.9	268.4	263.6	254.1	243.5	237.8	235.0	229.2	224.5
45°	265.6	249.3	235.9	226.4	222.5	214.0	205.4	200.6	197.8	193.0	188.1
47.5°	222.5	208.2	196.8	190.1	186.3	179.6	171.9	167.1	165.3	161.4	156.7
50°	182.4	171.9	162.4	156.7	153.8	147.1	140.4	136.6	134.7	130.9	126.1
52.5°	147.1	139.4	130.9	125.1	122.3	117.5	110.8	107.0	104.1	100.4	94.6
55°	115.6	108.9	102.2	96.5	94.6	88.9	83.1	77.3	74.5	70.7	66.0
57.5°	89.8	82.2	75.5	70.7	68.8	63.0	57.3	51.5	48.7	43.9	41.1
60°	64.0	57.3	50.6	47.8	45.9	40.1	35.3	30.5	28.6	25.8	23.8
62.5°	42.0	37.2	31.6	28.6	27.7	23.8	20.1	19.1	17.1	16.2	15.3
65°	25.8	22.9	19.1	17.1	16.2	15.3	13.4	12.4	11.5	10.6	10.6
67.5°	15.3	14.3	12.4	11.5	10.6	9.5	9.5	8.6	8.6	7.6	7.6
70°	10.6	9.5	8.6	7.6	7.6	7.6	7.6	7.6	7.6	6.7	6.7
72.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
75°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
77.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	4.8	4.8
80°	4.8	5.8	5.8	5.8	5.8	4.8	4.8	4.8	4.8	4.8	4.8
82.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
85°	4.8	4.8	4.8	4.8	4.8	3.9	3.9	3.9	3.9	3.9	2.8
87.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	2.8	2.8	2.8	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192372

CATALOG NUMBER: LDA6A50930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1	1171.1
2.5°	951.4	942.8	934.2	947.5	946.6	933.2	942.8	927.6
5°	786.2	773.7	764.2	772.8	768.0	754.6	760.3	747.0
7.5°	651.4	637.1	625.7	632.4	624.8	612.3	610.5	604.7
10°	544.5	529.2	518.7	523.5	515.8	504.3	501.5	497.7
12.5°	463.3	448.9	439.4	443.2	435.6	425.1	423.1	426.1
15°	400.2	389.8	382.0	385.0	374.4	368.7	366.8	368.7
17.5°	364.0	352.5	346.7	349.7	342.0	336.3	335.3	334.3
20°	379.2	370.7	368.7	373.5	367.7	363.0	365.8	362.1
22.5°	462.3	461.4	462.3	473.8	470.9	469.0	470.9	470.9
25°	520.7	524.4	525.4	537.8	538.7	536.9	541.7	541.7
27.5°	518.7	519.6	518.7	531.1	533.0	529.2	533.9	535.0
30°	472.9	472.9	470.0	480.5	480.5	478.5	480.5	481.5
32.5°	412.7	411.7	410.8	415.5	415.5	412.7	414.6	414.6
35°	356.3	352.5	352.5	355.4	354.3	351.5	352.5	351.5
37.5°	307.6	302.8	302.8	304.7	301.9	298.9	300.0	300.0
40°	262.7	258.9	258.9	261.7	259.9	256.9	258.9	258.9
42.5°	220.7	219.7	219.7	221.6	221.6	219.7	222.5	223.5
45°	186.3	183.5	183.5	185.3	185.3	183.5	184.4	183.5
47.5°	154.7	151.9	151.9	151.9	150.0	147.1	147.1	146.1
50°	123.2	118.4	117.5	117.5	115.6	112.7	112.7	111.7
52.5°	91.7	87.0	87.0	85.9	84.0	83.1	82.2	82.2
55°	63.0	59.3	60.2	58.2	58.2	56.3	57.3	56.3
57.5°	39.2	37.2	37.2	36.3	34.4	33.5	33.5	32.5
60°	22.9	21.0	21.0	21.0	20.1	19.1	19.1	19.1
62.5°	15.3	14.3	14.3	14.3	12.4	12.4	11.5	11.5
65°	9.5	8.6	8.6	8.6	7.6	7.6	7.6	7.6
67.5°	7.6	7.6	6.7	6.7	6.7	6.7	6.7	6.7
70°	6.7	6.7	6.7	6.7	6.7	5.8	5.8	5.8
72.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
75°	5.8	5.8	4.8	5.8	4.8	4.8	4.8	4.8
77.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
80°	4.8	4.8	4.8	4.8	4.8	3.9	3.9	3.9
82.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
85°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
87.5°	2.8	1.9	1.9	1.9	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)