

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192373

Luminaire Tested: **LDA6A50935D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26670)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50935D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4424.8 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.6 / 1.28
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192373

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192373

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	75		
4	92	84	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	77636	77636	77636
5°	149405	74372	27856
10°	247134	65268	10020
15°	364849	52662	15976
20°	529765	33539	27040
25°	761034	29294	32784
30°	861968	25371	23858
35°	862036	13184	12247
40°	696262	4916	5124
45°	521364	1690	1845
50°	341302	682	588
55°	40113	573	86
60°	1195	658	0
65°	259	778	0
70°	144	962	0
75°	0	1461	0
80°	0	2178	284
85°	0	4340	566



TEST NUMBER: P1192373

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.1	3.3
10°-20°	592.0	13.4
20°-30°	1299.0	29.4
30°-40°	1442.0	32.6
40°-50°	834.8	18.9
50°-60°	99.2	2.2
60°-70°	3.8	0.1
70°-80°	4.1	0.1
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2037.1	46.0
0°-40°	3479.1	78.6
0°-60°	4413.1	99.7
0°-90°	4424.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4424.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1416	1416	1416	1416	1416	
5°	2715	2195	1352	774	506	312
15°	6429	3718	928	252	282	1930
25°	12582	4318	484	539	542	5682
35°	12881	3150	197	194	183	7766
45°	6725	742	22	26	24	5256
55°	420	6	6	4	1	923
65°	2	4	6	4	0	3
75°	0	4	7	4	0	0
85°	0	4	7	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192373

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2
2.5°	2059.6	2018.9	1978.1	1975.1	1941.3	1896.5	1927.4	1861.8	1881.6	1831.9	1801.1
5°	2715.0	2670.3	2610.6	2593.7	2536.1	2469.4	2494.3	2378.9	2366.9	2271.5	2194.9
7.5°	3518.6	3466.9	3373.4	3328.7	3233.2	3133.7	3145.7	2960.7	2905.0	2747.9	2607.7
10°	4439.6	4402.7	4268.5	4176.0	4025.9	3880.7	3855.8	3582.3	3460.9	3214.3	2993.5
12.5°	5472.8	5418.1	5232.2	5091.9	4887.1	4703.1	4648.4	4256.5	4038.8	3681.7	3368.5
15°	6428.6	6391.8	6231.6	6020.8	5761.2	5523.5	5430.1	4972.6	4628.4	4154.1	3718.5
17.5°	7653.8	7552.4	7264.0	6850.3	6479.3	6242.7	6129.3	5556.4	5134.7	4555.9	3999.9
20°	9080.9	8943.7	8502.2	7929.3	7313.7	6897.9	6648.4	6031.7	5509.7	4837.4	4182.9
22.5°	11146.6	10867.1	10028.7	9002.4	8146.1	7591.1	7234.1	6338.1	5783.1	5013.4	4284.4
25°	12581.7	12336.0	11570.3	10220.7	8848.2	8209.8	7707.6	6591.7	5962.1	5117.8	4318.2
27.5°	13490.7	13360.4	12479.2	11130.7	9391.3	8560.9	7992.9	6751.8	6029.7	5114.8	4249.6
30°	13617.0	13624.9	12807.4	11374.3	9434.0	8569.8	7931.3	6683.2	5889.6	4921.9	4023.9
32.5°	13562.3	13453.9	12445.4	10912.9	8960.6	8201.8	7595.1	6393.7	5551.5	4534.1	3632.0
35°	12881.0	12639.3	11573.2	9882.6	8271.4	7549.4	6983.5	5930.3	5013.4	4019.9	3149.7
37.5°	11631.9	11249.0	10058.5	8618.5	7426.1	6789.6	6361.9	5337.6	4456.5	3484.8	2670.3
40°	9729.4	9317.7	8478.2	7472.8	6533.0	6096.4	5685.7	4687.1	3828.9	2937.8	2206.8
42.5°	8049.6	7823.9	7197.4	6427.6	5802.0	5352.5	4960.7	4009.9	3228.2	2405.8	1563.4
45°	6724.9	6571.8	6176.9	5612.1	4991.5	4581.7	4224.7	3255.1	2359.1	1527.6	741.9
47.5°	5791.1	5621.1	5173.5	4578.8	3849.8	3404.3	3002.5	2029.8	1287.9	590.7	173.0
50°	4001.9	3801.1	3324.7	2751.8	2128.3	1793.1	1512.7	820.4	338.1	102.5	19.8
52.5°	1811.0	1671.8	1373.5	1053.2	696.1	517.1	337.1	142.3	35.8	14.9	10.9
55°	419.7	368.0	279.5	172.1	85.6	56.7	37.8	14.9	10.9	8.0	6.0
57.5°	26.9	23.8	20.9	16.9	14.0	12.0	10.9	8.0	6.0	4.9	4.0
60°	10.9	10.9	10.0	8.0	6.9	6.0	6.0	4.0	4.0	4.0	4.0
62.5°	4.9	4.9	4.9	4.0	2.9	2.9	2.9	2.9	2.9	2.9	4.0
65°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.9	2.9	4.0
67.5°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.0	2.9	2.9	4.0
70°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.0	2.9	4.0	4.0
72.5°	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.0	2.9	4.0	4.0
75°	0.0	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0
77.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.0	2.9	4.0	4.0
80°	0.0	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0
82.5°	0.0	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0
85°	0.0	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0
87.5°	0.0	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192373

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2
2.5°	1755.3	1712.6	1667.9	1622.1	1601.2	1567.4	1513.6	1475.8	1442.0	1397.3	1340.6
5°	2102.4	2006.9	1906.5	1813.0	1767.3	1707.6	1603.2	1518.7	1440.0	1351.5	1264.0
7.5°	2448.5	2283.5	2124.3	1972.1	1898.5	1813.0	1651.9	1521.6	1398.3	1275.9	1156.6
10°	2755.8	2517.2	2289.3	2077.6	1978.1	1863.7	1652.9	1478.9	1323.7	1172.5	1028.3
12.5°	3042.3	2719.0	2421.6	2147.2	2016.9	1879.6	1624.1	1417.1	1231.2	1055.2	887.1
15°	3294.9	2887.1	2515.2	2179.9	2027.8	1863.7	1571.4	1334.6	1126.8	927.9	712.1
17.5°	3474.9	2983.6	2549.0	2161.1	1990.0	1808.0	1485.8	1232.2	1007.4	762.8	505.2
20°	3570.3	3013.4	2527.1	2101.4	1917.4	1720.6	1385.3	1123.8	866.2	574.9	412.7
22.5°	3604.1	2995.4	2466.5	2016.9	1822.9	1623.0	1282.9	1010.5	704.1	487.3	422.7
25°	3588.2	2941.8	2387.8	1917.4	1723.5	1522.7	1183.5	865.3	569.8	484.3	450.5
27.5°	3481.8	2821.5	2240.6	1768.2	1573.4	1374.4	1010.5	638.5	504.2	454.5	463.5
30°	3247.1	2576.8	1989.0	1524.5	1340.6	1130.8	687.2	469.4	395.8	400.8	400.8
32.5°	2869.2	2210.8	1637.9	1211.3	973.6	705.2	391.8	294.4	299.3	298.4	294.4
35°	2405.8	1806.0	1257.1	743.9	477.4	324.2	197.9	191.9	197.9	197.0	193.9
37.5°	1980.1	1384.4	778.8	298.4	191.9	140.3	117.4	117.4	119.4	119.4	118.3
40°	1493.8	813.5	272.5	98.5	68.7	65.6	66.7	66.7	67.6	68.7	69.6
42.5°	836.4	268.5	71.6	38.7	38.7	36.9	36.9	36.9	38.7	38.7	39.8
45°	225.7	57.6	23.8	22.9	21.8	20.9	20.9	20.9	21.8	21.8	22.9
47.5°	33.8	16.9	14.0	12.9	12.9	12.0	12.0	12.0	12.9	12.9	12.9
50°	12.9	10.0	8.9	8.0	8.0	8.0	6.9	6.9	8.0	8.0	8.0
52.5°	8.0	6.9	6.0	4.9	6.0	4.9	4.9	4.9	6.0	6.0	6.0
55°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.0	6.0
57.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.0	6.0
60°	4.0	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.0	6.0	6.0
62.5°	4.0	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.0	6.0	6.0
65°	4.0	4.9	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.0	6.0
67.5°	4.0	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
70°	4.9	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
72.5°	4.9	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.9
75°	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.9	6.9
77.5°	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.0	6.9	6.9	6.9
80°	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.0	6.9	6.9	6.9
82.5°	4.9	4.9	6.0	6.0	6.0	6.9	6.0	6.9	6.9	6.9	6.9
85°	4.9	4.9	6.0	6.0	6.0	6.0	6.0	6.9	6.9	6.9	6.9
87.5°	4.9	4.9	6.0	6.0	6.0	6.9	6.0	6.0	6.9	6.9	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192373

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2
2.5°	1300.8	1277.9	1236.2	1207.4	1195.4	1171.5	1126.8	1121.8	1068.1	1040.3	1011.4
5°	1189.4	1132.8	1062.1	1017.4	991.6	940.9	871.3	839.3	773.7	731.0	668.3
7.5°	1053.2	965.7	869.3	812.6	770.8	685.2	561.9	488.3	390.8	334.2	293.4
10°	897.1	780.6	634.5	541.0	472.4	372.0	295.4	271.5	245.7	224.8	204.8
12.5°	714.1	518.2	376.9	322.2	296.4	266.6	234.7	206.8	201.9	203.9	210.8
15°	486.3	346.1	298.4	276.5	258.6	229.7	236.7	244.6	251.6	256.6	265.5
17.5°	366.0	320.2	273.5	274.5	281.5	288.4	299.3	311.3	321.2	328.2	340.1
20°	361.0	332.2	338.1	350.1	358.0	368.0	386.9	397.8	410.7	419.7	432.6
22.5°	392.8	418.7	426.6	435.6	447.5	458.5	478.4	493.3	503.2	512.2	521.1
25°	466.4	486.3	493.3	500.2	508.2	516.2	529.1	542.0	539.0	542.0	543.0
27.5°	471.4	486.3	489.3	493.3	493.3	500.2	500.2	508.2	495.3	493.3	489.3
30°	405.8	410.7	413.7	413.7	409.7	414.7	409.7	415.7	400.8	395.8	390.8
32.5°	299.3	306.3	303.3	302.3	299.3	304.3	298.4	304.3	291.4	288.4	283.5
35°	191.9	202.9	197.9	200.9	198.9	203.9	199.9	203.9	193.9	193.0	189.9
37.5°	120.3	124.3	122.3	123.4	123.4	126.3	124.3	126.3	122.3	122.3	119.4
40°	70.7	72.7	72.7	73.6	74.5	75.6	74.5	76.5	74.5	75.6	72.7
42.5°	40.7	41.8	41.8	42.7	43.8	43.8	43.8	45.8	43.8	44.7	42.7
45°	22.9	24.9	23.8	24.9	24.9	25.8	25.8	25.8	25.8	25.8	24.9
47.5°	14.0	14.9	14.9	14.9	14.9	14.9	16.0	16.0	14.9	14.9	14.9
50°	8.9	8.9	8.9	8.9	10.0	10.0	10.0	8.9	8.9	8.9	8.0
52.5°	6.0	6.0	6.0	6.0	6.9	6.0	6.0	6.0	4.9	4.9	4.9
55°	6.0	6.0	6.0	6.0	6.0	4.9	4.9	4.9	4.0	2.9	2.9
57.5°	6.0	6.0	6.0	6.0	6.0	4.9	4.9	4.0	4.0	2.9	2.9
60°	6.0	6.0	6.0	6.0	6.0	4.9	4.9	4.0	4.0	2.9	2.9
62.5°	6.0	6.0	6.0	6.0	6.0	4.9	4.9	4.0	4.0	2.9	2.9
65°	6.0	6.0	6.0	6.0	6.0	4.9	4.9	4.9	4.0	2.9	2.9
67.5°	6.0	6.9	6.0	6.0	6.0	6.0	4.9	4.9	4.0	2.9	2.9
70°	6.0	6.9	6.0	6.0	6.0	6.0	4.9	4.9	4.0	2.9	2.9
72.5°	6.9	6.9	6.9	6.0	6.0	6.0	6.0	4.9	4.0	2.9	2.9
75°	6.9	6.9	6.9	6.0	6.0	6.0	6.0	4.9	4.0	2.9	2.9
77.5°	6.9	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.0	4.0	2.9
80°	6.9	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.0	4.0	2.9
82.5°	6.9	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.0	4.0	2.9
85°	6.9	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.0	4.0	2.9
87.5°	6.9	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.0	4.0	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192373

CATALOG NUMBER: LDA6A50935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2
2.5°	1018.4	1008.5	1001.5	985.6	976.7	966.7	951.8	944.8
5°	646.5	616.6	597.7	569.8	527.1	537.1	514.2	506.2
7.5°	278.5	265.5	261.5	255.6	245.7	240.7	239.7	237.7
10°	191.0	180.0	179.0	180.0	181.0	180.0	180.0	180.0
12.5°	214.8	215.8	217.8	220.8	221.8	221.8	220.8	220.8
15°	270.5	272.5	275.5	279.5	281.5	281.5	281.5	281.5
17.5°	347.1	350.1	355.0	359.0	363.0	363.0	363.0	364.0
20°	446.5	446.5	452.5	457.5	460.4	461.5	462.4	463.5
22.5°	535.1	536.0	540.0	544.0	547.0	546.0	544.0	544.0
25°	552.0	548.9	550.0	550.0	548.9	544.0	544.0	542.0
27.5°	492.3	488.3	488.3	485.3	484.3	482.4	478.4	476.4
30°	390.8	388.9	387.9	384.9	389.9	382.9	378.9	376.9
32.5°	281.5	282.4	281.5	278.5	283.5	276.5	274.5	271.5
35°	189.0	189.9	189.0	187.0	187.0	187.0	185.0	183.0
37.5°	119.4	118.3	119.4	119.4	121.4	118.3	118.3	116.3
40°	72.7	72.7	73.6	73.6	74.5	72.7	71.6	71.6
42.5°	42.7	42.7	43.8	43.8	44.7	42.7	42.7	42.7
45°	24.9	24.9	24.9	24.9	25.8	24.9	23.8	23.8
47.5°	14.0	14.0	14.0	14.0	14.0	14.0	14.0	12.9
50°	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9
52.5°	4.9	4.0	4.0	4.0	4.0	2.9	2.9	2.9
55°	2.0	2.0	2.0	2.0	2.0	0.9	0.9	0.9
57.5°	2.0	2.0	2.0	0.9	0.9	0.9	0.0	0.0
60°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
62.5°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
65°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
67.5°	2.0	2.0	2.0	0.9	0.9	0.0	0.0	0.0
70°	2.0	2.0	2.0	0.9	0.9	0.9	0.0	0.0
72.5°	2.0	2.0	2.0	0.9	0.9	0.9	0.0	0.0
75°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
77.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.9	0.0
80°	2.9	2.0	2.0	2.0	0.9	0.9	0.9	0.9
82.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.9	0.9
85°	2.9	2.0	2.0	2.0	0.9	0.9	0.9	0.9
87.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)