

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192380

Luminaire Tested: **LDA6A50935D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192380
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26674)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50935D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4500.5 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 2.68 / 0.47 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192380

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192380

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91		
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	59	54	77	66	59	54	65	58	53	63	57	53	61	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	38878	38878	38878
5°	102454	35467	11441
10°	204561	27182	4542
15°	372420	19081	4972
20°	572661	13692	31334
25°	671597	20451	25925
30°	731226	12844	7558
35°	769609	5327	3125
40°	789164	2354	1782
45°	732564	1535	1310
50°	513834	1194	588
55°	187922	851	382
60°	39690	877	219
65°	3347	1038	259
70°	1106	1282	465
75°	191	1694	847
80°	284	2526	1263
85°	0	5032	1258



TEST NUMBER: P1192380

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.2	2.0
10°-20°	490.6	10.9
20°-30°	1185.7	26.3
30°-40°	1393.9	31.0
40°-50°	1053.0	23.4
50°-60°	264.2	5.9
60°-70°	12.8	0.3
70°-80°	6.1	0.1
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1765.6	39.2
0°-40°	3159.5	70.2
0°-60°	4476.7	99.5
0°-90°	4500.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4500.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	709	709	709	709	709	
5°	1862	1352	644	274	208	232
15°	6562	2846	336	90	88	1986
25°	11103	3542	338	469	429	5108
35°	11500	2610	80	57	47	7161
45°	9449	1025	20	21	17	6962
55°	1966	29	9	8	4	2175
65°	26	7	8	7	2	70
75°	1	5	8	7	4	3
85°	0	5	8	6	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192380

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2
2.5°	1237.2	1217.3	1203.4	1179.6	1167.6	1172.5	1147.7	1113.9	1104.0	1074.1	1022.4
5°	1861.8	1840.9	1808.1	1757.4	1719.6	1713.6	1664.9	1583.3	1531.6	1455.1	1351.5
7.5°	2628.5	2610.7	2556.0	2480.4	2416.7	2392.9	2321.3	2178.1	2063.6	1910.5	1732.5
10°	3674.8	3605.2	3502.7	3349.7	3203.4	3135.8	3009.5	2772.8	2586.8	2377.0	2135.2
12.5°	4986.7	4863.3	4697.2	4467.5	4215.9	4089.6	3888.6	3526.7	3201.4	2841.5	2489.3
15°	6562.0	6437.7	6197.0	5841.0	5436.2	5233.3	4936.9	4366.0	3881.7	3353.5	2846.4
17.5°	8420.8	8217.9	7897.7	7381.5	6755.0	6436.7	6017.0	5226.3	4504.3	3815.1	3158.7
20°	9816.2	9667.9	9364.6	8824.6	8077.7	7667.9	7104.1	6015.0	5083.1	4184.1	3395.3
22.5°	10672.5	10539.2	10260.8	9809.2	9123.0	8668.5	8032.9	6707.2	5532.7	4439.6	3513.8
25°	11103.1	11007.6	10813.7	10419.8	9820.2	9363.6	8721.2	7219.4	5837.0	4577.9	3541.6
27.5°	11482.0	11321.9	11006.7	10738.1	10207.0	9742.6	9133.9	7474.0	5943.4	4562.0	3470.9
30°	11551.6	11460.1	11211.5	10827.6	10333.3	9863.9	9222.4	7437.2	5823.1	4377.0	3279.0
32.5°	11492.0	11412.4	11224.4	10805.7	10252.8	9734.6	9030.5	7134.8	5470.0	4033.8	2954.8
35°	11499.9	11373.6	11044.5	10686.4	9996.2	9387.5	8561.0	6581.9	4975.7	3588.3	2609.6
37.5°	11347.7	11139.9	10868.4	10406.9	9475.0	8720.1	7775.3	5868.8	4381.0	3133.8	2206.9
40°	11027.6	10869.3	10508.3	9799.3	8586.9	7638.1	6764.8	5050.3	3731.5	2637.6	1799.1
42.5°	10504.4	10315.5	9811.2	8742.1	7301.0	6473.5	5687.8	4212.9	3093.0	2157.2	1412.2
45°	9449.1	9160.8	8501.4	7226.4	5997.1	5295.0	4654.5	3435.1	2507.3	1687.7	1025.4
47.5°	7763.4	7517.8	6820.6	5756.4	4788.8	4245.7	3699.7	2709.2	1865.7	1085.1	527.1
50°	6024.9	5831.0	5299.0	4365.1	3557.5	3030.4	2600.7	1729.5	994.5	499.3	236.7
52.5°	3964.2	3841.9	3385.5	2725.0	2042.7	1666.8	1353.5	750.8	463.5	221.8	81.6
55°	1966.2	1809.1	1591.3	1179.6	853.3	690.3	585.8	370.0	191.9	63.6	28.9
57.5°	801.6	766.8	690.3	533.1	409.7	346.1	276.5	115.4	42.7	25.8	18.0
60°	362.0	346.1	300.4	210.8	114.3	70.7	49.8	31.8	21.8	16.0	12.0
62.5°	63.6	58.7	51.8	39.8	31.8	27.8	23.8	18.0	14.0	10.9	8.9
65°	25.8	25.8	23.8	20.9	16.9	16.0	14.0	10.9	8.9	8.0	6.9
67.5°	14.0	12.9	12.9	10.9	10.0	8.9	8.0	6.9	6.9	6.0	6.0
70°	6.9	6.9	6.9	6.0	4.9	4.9	4.9	4.9	4.9	4.9	4.9
72.5°	4.0	4.0	4.0	4.0	4.0	4.0	2.9	2.9	2.9	4.0	4.0
75°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
77.5°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
80°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	2.9	4.0	4.9
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	2.9	4.0	4.9
87.5°	0.0	0.0	0.9	0.9	0.9	2.0	2.0	2.9	2.9	4.0	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192380

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2
2.5°	1020.4	968.7	928.9	891.1	882.2	851.3	822.5	772.8	728.1	686.3	638.5
5°	1311.7	1210.3	1125.8	1043.3	1016.4	964.7	895.1	805.5	722.1	644.5	562.9
7.5°	1629.1	1457.1	1306.8	1167.6	1118.9	1045.3	932.9	805.5	685.2	573.8	474.4
10°	1940.4	1683.8	1457.1	1256.1	1182.5	1087.0	932.9	770.8	617.6	488.3	389.9
12.5°	2240.7	1888.6	1582.3	1316.8	1220.3	1100.9	908.0	710.1	532.0	404.8	322.2
15°	2475.4	2061.6	1670.8	1340.6	1220.3	1082.1	850.4	625.6	445.5	336.2	262.6
17.5°	2651.4	2164.1	1700.7	1317.7	1178.5	1023.4	762.8	526.1	367.0	278.5	207.9
20°	2753.9	2190.0	1669.8	1251.2	1099.0	934.9	654.5	433.6	311.3	234.7	168.1
22.5°	2777.7	2154.1	1598.3	1165.6	1008.5	842.4	558.9	387.9	300.4	239.7	209.9
25°	2751.0	2081.6	1503.8	1079.1	922.9	758.8	524.2	417.7	360.0	338.1	362.0
27.5°	2644.5	1946.4	1387.3	982.6	825.5	672.3	497.3	420.7	362.0	352.1	341.1
30°	2454.5	1742.4	1208.3	803.6	637.4	510.2	353.1	250.6	199.9	202.9	200.9
32.5°	2157.2	1446.0	945.8	561.9	438.6	345.1	233.7	148.2	139.2	139.2	137.2
35°	1829.9	1174.5	711.2	394.8	305.3	242.7	139.2	108.5	91.6	79.6	71.6
37.5°	1496.8	914.0	490.3	266.6	193.9	124.3	66.7	54.7	48.7	45.8	44.7
40°	1158.7	643.4	313.3	146.2	85.6	54.7	42.7	36.9	33.8	32.9	32.9
42.5°	857.3	414.7	169.0	57.6	45.8	37.8	30.9	26.9	25.8	25.8	24.9
45°	516.2	207.9	63.6	35.8	29.8	26.9	22.9	20.9	19.8	19.8	20.9
47.5°	238.7	77.6	34.9	23.8	21.8	19.8	18.0	16.9	16.9	16.9	18.0
50°	86.5	33.8	21.8	16.9	16.0	14.9	14.0	12.9	12.9	14.0	14.0
52.5°	32.9	20.9	16.0	12.9	12.0	12.0	10.9	10.9	10.9	10.9	10.9
55°	19.8	14.9	12.0	10.0	10.0	8.9	8.9	8.9	8.9	8.9	8.9
57.5°	12.9	10.9	8.9	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
60°	10.0	8.0	6.9	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.0
62.5°	8.0	6.9	6.9	6.9	6.9	6.9	6.9	6.9	8.0	8.0	8.0
65°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.9
67.5°	6.0	6.0	6.0	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0
70°	4.9	4.9	6.0	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0
72.5°	4.9	6.0	6.0	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0
75°	4.9	6.0	6.0	6.0	6.9	6.9	6.9	6.9	8.0	8.0	8.0
77.5°	4.9	6.0	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0	8.9
80°	4.9	6.0	6.0	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.9
82.5°	4.9	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0	8.9	8.9
85°	4.9	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.0	8.0	8.9
87.5°	4.9	6.0	6.0	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192380

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2
2.5°	612.7	571.8	543.1	517.1	507.2	484.4	459.5	430.6	406.8	404.8	384.9
5°	508.2	451.5	410.8	384.9	372.0	348.1	319.3	300.4	273.5	265.5	245.7
7.5°	410.8	358.0	320.2	296.4	281.5	252.6	219.8	198.9	177.0	160.1	138.3
10°	334.2	283.5	242.7	218.8	203.9	173.0	139.2	115.4	95.4	91.6	89.6
12.5°	268.5	216.8	176.1	150.1	134.3	105.4	96.5	92.5	89.6	86.5	86.5
15°	208.8	156.1	112.3	102.5	99.4	96.5	94.5	92.5	90.5	89.6	90.5
17.5°	152.1	110.4	105.4	104.5	102.5	102.5	104.5	105.4	107.4	109.4	112.3
20°	134.3	135.2	146.2	154.1	151.2	166.1	187.0	203.9	244.6	269.5	303.3
22.5°	240.7	276.5	327.2	358.0	374.9	424.7	479.3	561.9	603.6	663.4	717.0
25°	411.7	453.5	497.3	509.2	518.2	523.1	516.2	478.4	469.4	452.5	447.5
27.5°	308.3	288.4	295.4	298.4	295.4	291.4	279.5	258.6	253.6	245.7	247.7
30°	182.0	176.1	184.0	183.0	183.0	183.0	179.0	162.1	154.1	145.2	139.2
32.5°	134.3	123.4	114.3	106.5	103.4	98.5	95.4	88.5	85.6	81.6	81.6
35°	66.7	63.6	63.6	61.6	60.7	61.6	61.6	58.7	56.7	55.8	55.8
37.5°	43.8	43.8	44.7	43.8	43.8	43.8	43.8	42.7	41.8	40.7	40.7
40°	32.9	32.9	33.8	33.8	32.9	32.9	32.9	31.8	31.8	31.8	31.8
42.5°	25.8	25.8	25.8	25.8	24.9	25.8	25.8	25.8	24.9	24.9	23.8
45°	21.8	20.9	20.9	20.9	20.9	20.9	21.8	20.9	20.9	19.8	19.8
47.5°	18.0	18.0	18.0	18.0	18.0	18.0	18.0	18.0	18.0	16.9	16.9
50°	14.0	14.0	14.0	14.0	14.0	12.9	12.9	12.0	12.0	10.9	10.9
52.5°	10.9	10.9	10.0	10.0	10.0	10.0	10.0	10.0	8.9	8.9	8.9
55°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.0	6.9	6.9
57.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.0
60°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.0	6.0	6.0
62.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.0	6.0	4.9
65°	8.9	8.9	8.9	8.9	8.0	8.0	8.0	6.9	6.9	6.0	6.0
67.5°	8.9	8.9	8.9	8.9	8.9	8.0	8.0	8.0	6.9	6.9	6.0
70°	8.9	8.9	8.9	8.9	8.9	8.0	8.0	8.0	6.9	6.9	6.0
72.5°	8.9	8.9	8.9	8.9	8.9	8.0	8.0	8.0	6.9	6.9	6.0
75°	8.9	8.9	8.9	8.9	8.9	8.0	8.0	8.0	6.9	6.9	6.0
77.5°	8.9	8.9	8.9	8.9	8.9	8.0	8.0	8.0	6.9	6.9	6.0
80°	8.9	8.9	8.9	8.9	8.9	8.0	8.0	8.0	6.9	6.9	6.0
82.5°	8.9	8.9	8.9	8.9	8.9	8.0	8.0	8.0	6.9	6.9	6.0
85°	8.9	8.9	8.0	8.0	8.0	8.0	8.0	6.9	6.0	6.0	4.9
87.5°	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.0	4.9	4.9	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192380

CATALOG NUMBER: LDA6A50935D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	709.2	709.2	709.2	709.2	709.2	709.2	709.2	709.2
2.5°	380.9	367.0	364.0	368.0	352.1	352.1	352.1	359.0
5°	237.7	223.8	219.8	220.8	207.9	198.9	203.9	207.9
7.5°	129.3	114.3	109.4	109.4	96.5	91.6	92.5	94.5
10°	86.5	84.5	84.5	83.6	81.6	80.5	81.6	81.6
12.5°	83.6	82.5	82.5	81.6	81.6	80.5	80.5	81.6
15°	87.6	87.6	87.6	86.5	86.5	85.6	87.6	87.6
17.5°	111.4	113.4	117.4	119.4	123.4	119.4	126.3	125.4
20°	327.2	360.0	420.7	443.5	509.2	477.4	546.0	537.1
22.5°	741.0	764.8	774.8	779.7	780.8	812.6	817.5	828.4
25°	437.6	431.6	426.6	426.6	408.8	429.7	425.7	428.6
27.5°	233.7	231.7	226.8	228.8	219.8	226.8	228.8	228.8
30°	132.3	128.3	124.3	124.3	116.3	120.3	119.4	119.4
32.5°	76.5	74.6	72.7	71.6	69.6	69.6	68.7	68.7
35°	52.7	51.8	50.7	49.8	47.8	46.7	46.7	46.7
37.5°	38.7	37.8	36.9	36.9	35.8	33.8	33.8	33.8
40°	29.8	28.9	27.8	27.8	26.9	24.9	24.9	24.9
42.5°	22.9	21.8	20.9	19.8	19.8	18.9	18.0	18.0
45°	18.9	18.9	18.0	18.0	16.9	16.9	16.9	16.9
47.5°	16.0	16.0	14.9	14.9	14.9	14.0	14.0	12.9
50°	10.0	8.9	8.9	8.0	8.0	6.9	6.9	6.9
52.5°	8.0	6.9	6.9	6.0	6.0	4.9	4.9	4.9
55°	6.0	6.0	4.9	4.9	4.9	4.0	4.0	4.0
57.5°	4.9	4.9	4.0	4.0	4.0	2.9	2.9	2.9
60°	4.9	4.0	4.0	2.9	2.9	2.9	2.0	2.0
62.5°	4.9	4.0	4.0	2.9	2.9	2.0	2.0	2.0
65°	4.9	4.0	4.0	2.9	2.9	2.9	2.9	2.0
67.5°	4.9	4.9	4.0	4.0	4.0	2.9	2.9	2.9
70°	6.0	4.9	4.9	4.0	4.0	4.0	4.0	2.9
72.5°	6.0	4.9	4.9	4.9	4.0	4.0	4.0	4.0
75°	6.0	4.9	4.9	4.9	4.0	4.0	4.0	4.0
77.5°	6.0	4.9	4.9	4.9	4.0	4.0	4.0	4.0
80°	6.0	4.9	4.9	4.9	4.0	4.0	4.0	4.0
82.5°	4.9	4.9	4.9	4.0	4.0	4.0	4.0	4.0
85°	4.0	4.0	4.0	2.9	2.9	2.9	2.9	2.0
87.5°	2.9	2.9	2.0	2.0	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)