

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192384

Luminaire Tested: **LDA6A50935D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26672)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50935D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5050.4 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 2.54 / 0.51 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192384

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192384

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	62	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47		
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	40	39		
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	62150	62150	62150
5°	158931	57297	20906
10°	341571	46225	7699
15°	498272	33808	8808
20°	564226	24310	13575
25°	611660	19550	21056
30°	682472	16053	20269
35°	692707	10386	13512
40°	697815	4981	6827
45°	693452	2085	2861
50°	555206	930	930
55°	165576	659	86
60°	33802	757	0
65°	3230	895	0
70°	321	1282	0
75°	0	1694	0
80°	0	2810	284
85°	0	5598	566

TEST NUMBER: P1192384

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.4	2.9
10°-20°	708.3	14.0
20°-30°	1301.9	25.8
30°-40°	1493.6	29.6
40°-50°	1130.0	22.4
50°-60°	250.4	5.0
60°-70°	10.6	0.2
70°-80°	4.6	0.1
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2156.6	42.7
0°-40°	3650.2	72.3
0°-60°	5030.6	99.6
0°-90°	5050.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5050.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1134	1134	1134	1134	1134	
5°	2888	2157	1041	509	380	382
15°	8780	4762	596	154	155	2447
25°	10112	5599	323	313	348	4718
35°	10351	3456	155	194	202	6484
45°	8945	978	27	35	37	6675
55°	1732	37	7	5	1	2145
65°	25	5	7	4	0	66
75°	0	4	8	5	0	0
85°	0	5	9	5	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192384

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7
2.5°	1920.4	1901.5	1906.5	1930.3	1831.9	1828.9	1783.1	1777.1	1731.5	1647.9	1606.1
5°	2888.1	2876.1	2855.2	2863.2	2750.8	2675.3	2595.7	2537.9	2420.7	2262.5	2157.1
7.5°	4431.5	4302.3	4239.6	4119.3	3976.1	3829.8	3682.7	3511.6	3264.9	2989.5	2766.7
10°	6136.1	6079.4	5951.1	5874.6	5557.3	5342.5	5113.8	4763.7	4312.2	3812.9	3397.2
12.5°	7806.9	7740.2	7546.3	7383.3	6960.5	6768.6	6471.3	6029.7	5456.9	4745.8	4088.4
15°	8779.5	8794.4	8574.6	8566.7	8202.7	7953.1	7695.5	7173.4	6446.4	5629.9	4761.7
17.5°	9349.4	9386.1	9168.4	9230.0	8867.0	8608.4	8416.5	8034.6	7261.9	6282.3	5281.9
20°	9671.6	9730.2	9498.6	9546.3	9236.0	9061.0	8866.0	8488.1	7805.9	6724.8	5577.2
22.5°	9917.2	9940.1	9682.5	9746.2	9407.0	9232.0	9093.7	8739.7	8066.5	6958.6	5669.6
25°	10112.2	10169.8	9875.4	9880.5	9543.3	9368.3	9215.1	8892.9	8177.9	7020.2	5599.1
27.5°	10392.6	10439.4	10006.8	9969.0	9642.8	9449.8	9283.8	8966.5	8172.8	6883.0	5332.6
30°	10781.4	10520.9	10078.4	9980.8	9613.9	9418.0	9240.0	8828.2	7989.9	6513.1	4848.3
32.5°	10670.0	10459.2	10022.6	9867.5	9503.5	9293.6	9089.7	8588.6	7565.2	5940.2	4187.8
35°	10350.8	10283.2	9824.7	9776.0	9335.4	9115.7	8910.8	8225.5	6913.8	5191.4	3455.9
37.5°	10081.3	9965.9	9670.6	9594.0	9131.5	8888.9	8562.7	7683.5	6052.6	4236.7	2759.8
40°	9751.1	9673.6	9388.1	9306.7	8771.6	8401.6	8002.8	6701.0	5012.4	3297.8	2131.2
42.5°	9400.1	9330.5	9061.0	8889.9	8176.8	7687.5	7068.0	5511.5	3858.7	2485.2	1597.2
45°	8944.6	8846.2	8509.0	8190.8	7168.4	6468.2	5771.2	4205.8	2824.4	1769.3	977.6
47.5°	8161.9	8005.8	7597.0	6957.6	5701.6	5029.3	4303.2	2852.3	1744.4	910.9	492.3
50°	6510.0	6237.6	5693.6	4932.8	3651.8	3007.4	2438.5	1450.0	748.8	469.4	289.4
52.5°	4011.9	3762.2	3298.7	2564.8	1683.7	1296.8	1021.4	675.2	412.7	265.5	107.4
55°	1732.4	1576.3	1354.5	1033.3	733.9	603.6	485.3	337.1	212.8	81.6	36.9
57.5°	654.3	607.6	550.9	452.5	338.1	282.4	237.7	149.2	51.8	30.9	20.9
60°	308.3	279.5	246.6	195.9	129.3	93.4	58.7	37.8	24.9	16.9	12.0
62.5°	84.5	63.6	52.7	42.7	32.9	28.9	24.9	18.9	14.0	8.9	6.9
65°	24.9	21.8	20.9	18.0	14.9	12.9	10.9	8.9	6.9	4.9	4.9
67.5°	8.9	8.9	8.0	6.9	6.0	4.9	4.9	4.0	4.0	4.0	4.0
70°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.9	2.9	4.0	4.0
72.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	2.9	4.0	4.0
75°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	2.9	4.0	4.0
77.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
80°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
87.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192384

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7
2.5°	1571.4	1513.6	1432.1	1390.3	1353.5	1343.6	1268.0	1219.3	1161.6	1101.9	1039.2
5°	2058.6	1911.4	1755.3	1624.1	1557.4	1518.6	1371.4	1261.0	1154.6	1041.2	944.7
7.5°	2541.9	2278.4	2050.7	1838.9	1722.4	1635.0	1424.2	1258.1	1097.0	949.8	819.5
10°	3009.4	2629.5	2266.5	1980.1	1820.0	1689.7	1417.1	1201.4	999.5	830.4	694.1
12.5°	3482.8	2928.8	2446.5	2055.7	1864.7	1697.7	1369.5	1106.9	893.1	714.1	572.9
15°	3905.4	3161.5	2558.8	2073.5	1842.9	1645.9	1275.9	986.5	773.7	595.7	472.4
17.5°	4198.9	3286.9	2565.9	2007.9	1751.3	1539.4	1145.7	860.2	653.4	496.2	387.9
20°	4332.1	3282.9	2471.4	1871.6	1603.2	1382.4	991.6	731.0	545.0	416.7	324.2
22.5°	4292.3	3157.5	2304.2	1678.8	1422.2	1201.4	848.4	616.6	468.4	358.0	284.4
25°	4093.3	2938.8	2108.4	1485.8	1227.2	1021.4	719.0	527.1	406.8	323.2	258.6
27.5°	3768.2	2640.4	1844.9	1260.0	1023.4	863.3	605.6	455.5	358.0	285.4	269.5
30°	3292.9	2278.4	1535.6	1016.4	826.4	683.2	491.3	367.0	286.4	253.6	254.6
32.5°	2768.7	1879.6	1207.3	776.8	622.5	527.1	363.0	256.6	209.9	207.9	208.8
35°	2246.6	1463.9	898.0	567.8	456.5	379.9	233.7	161.2	156.1	155.2	157.2
37.5°	1783.1	1089.0	647.4	396.8	302.3	231.7	126.3	109.4	105.4	107.4	108.5
40°	1331.7	763.7	437.6	234.7	147.2	106.5	76.5	70.7	68.7	69.6	69.6
42.5°	916.0	477.4	260.6	97.4	70.7	58.7	48.7	45.8	43.8	42.7	43.8
45°	493.3	297.3	101.4	49.8	41.8	37.8	30.9	28.9	27.8	26.9	26.9
47.5°	315.3	110.4	45.8	30.9	26.9	24.9	20.9	18.9	18.0	16.9	16.9
50°	118.3	42.7	27.8	19.8	16.9	16.0	12.9	12.0	10.9	10.9	10.9
52.5°	40.7	25.8	18.0	12.9	10.9	10.0	8.9	8.0	8.0	8.0	8.0
55°	22.9	16.0	10.9	8.0	8.0	6.9	6.9	6.9	6.9	6.9	6.9
57.5°	14.0	8.9	6.9	6.0	6.0	6.0	6.0	6.9	6.9	6.9	6.9
60°	8.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.9	6.9	6.9
62.5°	4.9	4.9	4.9	4.9	4.9	6.0	6.0	6.9	6.9	6.9	6.9
65°	4.9	4.9	4.9	4.9	4.9	6.0	6.0	6.9	6.9	6.9	6.9
67.5°	4.0	4.9	4.9	6.0	6.0	6.0	6.0	6.9	6.9	8.0	6.9
70°	4.9	4.9	4.9	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.0
72.5°	4.9	4.9	4.9	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.0
75°	4.9	4.9	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.0	8.0
77.5°	4.9	4.9	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.9	8.0
80°	4.9	4.9	6.0	6.9	6.9	6.9	6.9	8.0	8.0	8.9	8.9
82.5°	4.9	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.9	8.9	8.9
85°	4.9	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.9	8.9	8.9
87.5°	4.9	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192384

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7
2.5°	1005.4	947.8	901.1	902.0	863.3	833.3	795.7	774.8	757.9	729.9	704.1
5°	874.2	785.7	719.0	706.1	661.4	615.6	568.9	534.0	509.2	482.3	457.5
7.5°	731.9	630.5	554.0	536.0	498.2	455.5	412.7	377.9	348.1	319.3	289.4
10°	593.7	501.2	431.6	413.7	375.9	331.2	290.4	259.5	236.7	213.9	191.0
12.5°	480.4	398.8	333.2	310.3	279.5	244.6	211.9	182.0	157.2	147.2	144.3
15°	388.9	311.3	259.5	240.6	214.8	179.0	160.1	155.2	154.1	154.1	154.1
17.5°	314.3	253.6	206.8	187.0	174.1	172.1	172.1	172.1	173.0	175.0	179.0
20°	263.5	209.9	191.9	193.9	193.9	195.9	199.9	202.9	206.8	211.9	217.8
22.5°	233.7	222.8	220.8	226.8	227.7	233.7	241.7	247.7	254.6	262.6	267.5
25°	255.6	259.5	262.6	271.5	274.5	284.4	296.4	305.3	313.3	322.2	328.2
27.5°	278.4	285.4	291.4	300.4	302.3	315.3	325.2	331.2	337.1	341.1	345.1
30°	262.6	269.5	275.5	283.5	283.5	297.3	302.3	307.3	312.3	314.3	318.2
32.5°	215.8	222.8	228.8	234.7	235.7	245.7	251.6	253.6	257.6	258.6	261.5
35°	162.1	165.1	171.0	176.1	177.0	184.0	189.0	191.0	193.9	193.9	195.9
37.5°	111.4	113.4	118.3	121.4	123.4	128.3	131.2	133.2	135.2	136.3	137.2
40°	72.7	73.6	76.5	79.6	81.6	84.5	86.5	88.5	89.6	91.6	91.6
42.5°	44.7	45.8	47.8	49.8	49.8	52.7	53.8	55.6	56.7	57.6	57.6
45°	27.8	28.9	28.9	29.8	30.9	31.8	33.8	33.8	34.9	34.9	34.9
47.5°	16.9	18.0	16.9	18.0	18.0	18.9	19.8	19.8	19.8	19.8	19.8
50°	10.9	10.9	10.9	10.9	10.9	10.9	12.0	12.0	12.0	12.0	10.9
52.5°	8.0	8.0	6.9	8.0	6.9	6.9	6.9	6.9	6.9	6.9	6.0
55°	6.9	6.9	6.9	6.9	6.0	6.0	6.0	4.9	4.9	4.0	4.0
57.5°	6.9	6.9	6.0	6.0	6.0	4.9	4.9	4.9	4.0	4.0	2.9
60°	6.9	6.9	6.0	6.0	6.0	4.9	4.9	4.0	4.0	2.9	2.9
62.5°	6.9	6.9	6.0	6.0	6.0	6.0	4.9	4.9	4.0	4.0	2.9
65°	6.9	6.9	6.9	6.0	6.0	6.0	4.9	4.9	4.0	4.0	2.9
67.5°	6.9	6.9	6.9	6.9	6.0	6.0	6.0	4.9	4.0	4.0	2.9
70°	6.9	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.9	4.0	2.9
72.5°	8.0	8.0	6.9	6.9	6.9	6.0	6.0	4.9	4.9	4.0	4.0
75°	8.0	8.0	6.9	6.9	6.9	6.0	6.0	4.9	4.9	4.0	4.0
77.5°	8.0	8.0	8.0	8.0	6.9	6.9	6.0	6.0	4.9	4.9	4.0
80°	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.0	4.9	4.9	4.0
82.5°	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.0	4.9	4.9	4.0
85°	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.0	4.9	4.9	4.0
87.5°	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.0	4.9	4.9	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192384

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7	1133.7
2.5°	680.3	667.3	666.3	655.4	633.5	644.5	630.5	620.5
5°	435.6	421.7	407.7	409.7	393.8	396.8	385.9	379.9
7.5°	276.5	261.5	257.6	257.6	239.7	239.7	232.7	228.8
10°	174.1	162.1	158.1	151.2	143.2	142.3	139.2	138.3
12.5°	141.2	141.2	138.3	139.2	139.2	139.2	138.3	138.3
15°	154.1	155.2	152.1	153.2	155.2	154.1	155.2	155.2
17.5°	178.1	183.0	179.0	181.0	185.0	184.0	185.0	185.9
20°	217.8	225.7	220.8	224.8	229.7	228.8	231.7	232.7
22.5°	271.5	281.5	276.5	280.4	288.4	286.4	290.4	292.4
25°	331.2	341.1	335.1	340.1	345.1	347.1	347.1	348.1
27.5°	345.1	351.1	347.1	352.0	354.0	356.0	354.0	355.0
30°	316.2	321.2	317.3	322.2	322.2	324.2	322.2	320.2
32.5°	260.6	264.6	259.5	265.5	264.6	265.5	266.6	267.5
35°	197.0	198.9	195.9	197.0	197.9	198.9	201.9	201.9
37.5°	137.2	140.3	137.2	138.3	138.3	140.3	142.3	142.3
40°	91.6	94.5	91.6	93.4	92.5	93.4	95.4	95.4
42.5°	57.6	59.6	57.6	58.7	58.7	58.7	59.6	60.7
45°	34.9	35.8	34.9	35.8	35.8	35.8	36.9	36.9
47.5°	19.8	20.9	19.8	19.8	20.9	19.8	20.9	20.9
50°	10.9	10.9	10.9	10.9	10.9	10.0	10.0	10.9
52.5°	6.0	6.0	4.9	4.9	4.9	4.9	4.9	4.9
55°	2.9	2.9	2.0	2.0	2.0	0.9	2.0	0.9
57.5°	2.0	2.0	0.9	0.9	0.9	0.9	0.0	0.0
60°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
62.5°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
65°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
67.5°	2.9	2.0	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.9	2.0	2.0	0.9	0.9	0.0	0.0	0.0
72.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
75°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
77.5°	2.9	2.9	2.0	2.0	0.9	0.9	0.9	0.0
80°	2.9	2.9	2.0	2.0	2.0	0.9	0.9	0.9
82.5°	2.9	2.9	2.0	2.0	2.0	0.9	0.9	0.9
85°	2.9	2.9	2.0	2.0	2.0	0.9	0.9	0.9
87.5°	2.9	2.9	2.0	2.0	2.0	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)