

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192390

Luminaire Tested: **LDA6A50940D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26670)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50940D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4595.8 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.6 / 1.28
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192390

CATALOG NUMBER: LDA6A50940D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192390

CATALOG NUMBER: LDA6A50940D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	75		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80635	80635	80635
5°	155178	77251	28929
10°	256664	67795	10410
15°	378930	54694	16589
20°	550213	34834	28078
25°	790400	30431	34048
30°	895233	26352	24776
35°	895310	13686	12715
40°	723133	5095	5324
45°	541483	1768	1923
50°	354479	699	623
55°	41662	593	105
60°	1250	680	0
65°	272	804	0
70°	176	994	0
75°	0	1546	0
80°	0	2305	347
85°	0	4592	692

TEST NUMBER: P1192390

CATALOG NUMBER: LDA6A50940D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.8	3.3
10°-20°	614.9	13.4
20°-30°	1349.1	29.4
30°-40°	1497.6	32.6
40°-50°	867.0	18.9
50°-60°	103.0	2.2
60°-70°	4.0	0.1
70°-80°	4.3	0.1
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2115.7	46.0
0°-40°	3613.4	78.6
0°-60°	4583.4	99.7
0°-90°	4595.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4595.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1471	1471	1471	1471	1471	
5°	2820	2280	1404	804	526	324
15°	6677	3862	964	261	292	2005
25°	13067	4485	503	560	563	5902
35°	13378	3271	204	201	190	8065
45°	6984	770	23	27	25	5458
55°	436	6	6	4	1	959
65°	2	4	6	4	0	4
75°	0	4	7	4	0	0
85°	0	4	7	4	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192390

CATALOG NUMBER: LDA6A50940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9
2.5°	2139.1	2096.8	2054.5	2051.3	2016.2	1969.7	2001.8	1933.6	1954.2	1902.6	1870.6
5°	2819.9	2773.4	2711.4	2693.8	2633.9	2564.7	2590.5	2470.7	2458.4	2359.2	2279.6
7.5°	3654.4	3600.7	3503.7	3457.1	3358.0	3254.7	3267.0	3074.9	3017.2	2853.9	2708.2
10°	4610.8	4572.7	4433.3	4337.1	4181.1	4030.4	4004.6	3720.6	3594.5	3338.3	3109.1
12.5°	5684.1	5627.3	5434.1	5288.4	5075.7	4884.5	4827.7	4420.8	4194.6	3823.9	3498.5
15°	6676.7	6638.4	6472.1	6253.2	5983.6	5736.8	5639.6	5164.5	4807.1	4314.5	3862.0
17.5°	7949.2	7843.8	7544.3	7114.6	6729.4	6483.5	6365.8	5770.8	5332.9	4731.7	4154.4
20°	9431.4	9288.9	8830.2	8235.4	7596.0	7164.3	6905.0	6264.6	5722.2	5024.0	4344.4
22.5°	11576.7	11286.6	10415.8	9349.8	8460.5	7884.1	7513.3	6582.7	6006.4	5206.9	4449.8
25°	13067.2	12812.1	12016.8	10615.1	9189.7	8526.6	8005.0	6846.1	6192.3	5315.3	4484.9
27.5°	14011.4	13876.1	12960.9	11560.3	9753.7	8891.3	8301.5	7012.4	6262.5	5312.3	4413.7
30°	14142.5	14150.8	13301.8	11813.4	9798.1	8900.5	8237.4	6941.1	6116.8	5111.9	4179.1
32.5°	14085.7	13973.1	12925.8	11334.0	9306.4	8518.4	7888.3	6640.5	5765.7	4709.0	3772.2
35°	13378.2	13127.2	12019.9	10263.9	8590.7	7840.8	7253.0	6159.2	5206.9	4175.0	3271.2
37.5°	12080.9	11683.2	10446.8	8951.1	7712.7	7051.6	6607.5	5543.6	4628.4	3619.3	2773.4
40°	10104.9	9677.3	8805.5	7761.2	6785.2	6331.7	5905.1	4868.1	3976.7	3051.2	2292.0
42.5°	8360.3	8125.9	7475.2	6675.6	6026.0	5559.1	5152.2	4164.7	3352.8	2498.6	1623.7
45°	6984.4	6825.4	6415.3	5828.7	5184.2	4758.6	4387.8	3380.7	2450.0	1586.5	770.5
47.5°	6014.6	5838.0	5373.2	4755.4	3998.4	3535.6	3118.3	2108.1	1337.6	613.5	179.7
50°	4156.4	3947.8	3453.0	2858.0	2210.5	1862.3	1571.0	852.1	351.2	106.3	20.7
52.5°	1880.9	1736.3	1426.4	1093.8	723.0	537.1	350.1	147.7	37.2	15.5	11.4
55°	435.9	382.2	290.3	178.6	88.9	58.9	39.2	15.5	11.4	8.2	6.2
57.5°	27.9	24.8	21.7	17.6	14.4	12.4	11.4	8.2	6.2	5.2	4.1
60°	11.4	11.4	10.3	8.2	7.3	6.2	6.2	4.1	4.1	4.1	4.1
62.5°	5.2	5.2	5.2	4.1	3.1	3.1	3.1	3.1	3.1	3.1	4.1
65°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1	3.1	4.1
67.5°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	2.1	3.1	3.1	4.1
70°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	2.1	3.1	4.1	4.1
72.5°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	2.1	3.1	4.1	4.1
75°	0.0	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1
77.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	2.1	3.1	4.1	4.1
80°	0.0	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1
82.5°	0.0	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1
85°	0.0	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1
87.5°	0.0	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192390

CATALOG NUMBER: LDA6A50940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9
2.5°	1823.0	1778.7	1732.2	1684.6	1662.9	1627.8	1572.1	1532.9	1497.7	1451.2	1392.4
5°	2183.6	2084.4	1980.1	1883.0	1835.5	1773.5	1665.0	1577.2	1495.7	1403.8	1312.8
7.5°	2543.0	2371.5	2206.2	2048.3	1971.8	1883.0	1715.6	1580.3	1452.2	1325.2	1201.3
10°	2862.2	2614.2	2377.7	2157.8	2054.5	1935.7	1716.7	1535.9	1374.8	1217.9	1068.0
12.5°	3159.7	2824.0	2515.2	2230.1	2094.7	1952.2	1686.8	1471.8	1278.8	1095.9	921.4
15°	3422.0	2998.5	2612.2	2264.1	2106.1	1935.7	1631.9	1386.2	1170.3	963.7	739.6
17.5°	3609.0	3098.7	2647.3	2244.5	2066.8	1877.8	1543.2	1279.8	1046.4	792.3	524.8
20°	3708.1	3129.7	2624.6	2182.5	1991.4	1786.9	1438.9	1167.1	899.7	597.1	428.6
22.5°	3743.2	3111.1	2561.6	2094.7	1893.3	1685.7	1332.4	1049.4	731.3	506.1	439.0
25°	3726.7	3055.3	2480.0	1991.4	1790.0	1581.4	1229.1	898.6	591.9	503.1	468.0
27.5°	3616.2	2930.3	2327.1	1836.5	1634.1	1427.5	1049.4	663.2	523.7	472.1	481.3
30°	3372.4	2676.2	2065.9	1583.5	1392.4	1174.4	713.7	487.6	411.2	416.3	416.3
32.5°	2980.0	2296.1	1701.2	1258.1	1011.2	732.3	406.9	305.8	310.9	309.9	305.8
35°	2498.6	1875.7	1305.6	772.7	495.8	336.7	205.5	199.3	205.5	204.5	201.4
37.5°	2056.5	1437.8	808.8	309.9	199.3	145.7	121.8	121.8	123.9	123.9	122.9
40°	1551.4	845.0	283.0	102.2	71.2	68.2	69.2	69.2	70.2	71.2	72.3
42.5°	868.7	278.9	74.4	40.3	40.3	38.3	38.3	38.3	40.3	40.3	41.3
45°	234.5	59.9	24.8	23.7	22.8	21.7	21.7	21.7	22.8	22.8	23.7
47.5°	35.1	17.6	14.4	13.4	13.4	12.4	12.4	12.4	13.4	13.4	13.4
50°	13.4	10.3	9.3	8.2	8.2	8.2	7.3	7.3	8.2	8.2	8.2
52.5°	8.2	7.3	6.2	5.2	6.2	5.2	5.2	5.2	6.2	6.2	6.2
55°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.2	6.2
57.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.2	6.2
60°	4.1	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.2	6.2	6.2
62.5°	4.1	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.2	6.2	6.2
65°	4.1	5.2	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
67.5°	4.1	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
70°	5.2	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
72.5°	5.2	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3
75°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3
77.5°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3
80°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3
82.5°	5.2	5.2	6.2	6.2	6.2	7.3	6.2	7.3	7.3	7.3	7.3
85°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3
87.5°	5.2	5.2	6.2	6.2	6.2	7.3	6.2	6.2	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192390

CATALOG NUMBER: LDA6A50940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9
2.5°	1351.1	1327.2	1283.9	1254.0	1241.6	1216.8	1170.3	1165.2	1109.3	1080.4	1050.5
5°	1235.3	1176.5	1103.2	1056.7	1029.8	977.1	904.8	871.7	803.6	759.2	694.1
7.5°	1093.8	1002.9	902.7	843.9	800.5	711.6	583.6	507.2	406.0	347.1	304.7
10°	931.7	810.8	659.0	561.9	490.6	386.3	306.8	281.9	255.2	233.5	212.8
12.5°	741.7	538.2	391.4	334.6	307.7	276.8	243.8	214.8	209.6	211.7	219.0
15°	505.1	359.4	309.9	287.1	268.5	238.6	245.8	254.1	261.3	266.4	275.8
17.5°	380.1	332.6	284.0	285.1	292.3	299.5	310.9	323.2	333.6	340.8	353.3
20°	374.9	345.0	351.2	363.6	371.8	382.2	401.8	413.1	426.6	435.9	449.3
22.5°	408.0	434.9	443.1	452.5	464.8	476.2	496.8	512.3	522.7	531.9	541.2
25°	484.4	505.1	512.3	519.6	527.8	536.0	549.5	562.9	559.9	562.9	564.0
27.5°	489.6	505.1	508.2	512.3	512.3	519.6	519.6	527.8	514.4	512.3	508.2
30°	421.5	426.6	429.7	429.7	425.6	430.8	425.6	431.8	416.3	411.2	406.0
32.5°	310.9	318.1	315.0	314.0	310.9	316.1	309.9	316.1	302.6	299.5	294.4
35°	199.3	210.7	205.5	208.7	206.6	211.7	207.6	211.7	201.4	200.4	197.3
37.5°	125.0	129.1	127.0	128.1	128.1	131.2	129.1	131.2	127.0	127.0	123.9
40°	73.4	75.4	75.4	76.4	77.5	78.5	77.5	79.6	77.5	78.5	75.4
42.5°	42.4	43.4	43.4	44.4	45.4	45.4	45.4	47.5	45.4	46.5	44.4
45°	23.7	25.8	24.8	25.8	25.8	26.9	26.9	26.9	26.9	26.9	25.8
47.5°	14.4	15.5	15.5	15.5	15.5	15.5	16.5	16.5	15.5	15.5	15.5
50°	9.3	9.3	9.3	9.3	10.3	10.3	10.3	9.3	9.3	9.3	8.2
52.5°	6.2	6.2	6.2	6.2	7.3	6.2	6.2	6.2	5.2	5.2	5.2
55°	6.2	6.2	6.2	6.2	6.2	5.2	5.2	5.2	4.1	3.1	3.1
57.5°	6.2	6.2	6.2	6.2	6.2	5.2	5.2	4.1	4.1	3.1	3.1
60°	6.2	6.2	6.2	6.2	6.2	5.2	5.2	4.1	4.1	3.1	3.1
62.5°	6.2	6.2	6.2	6.2	6.2	5.2	5.2	4.1	4.1	3.1	3.1
65°	6.2	6.2	6.2	6.2	6.2	5.2	5.2	5.2	4.1	3.1	3.1
67.5°	6.2	7.3	6.2	6.2	6.2	6.2	5.2	5.2	4.1	3.1	3.1
70°	6.2	7.3	6.2	6.2	6.2	6.2	5.2	5.2	4.1	3.1	3.1
72.5°	7.3	7.3	7.3	6.2	6.2	6.2	6.2	5.2	4.1	3.1	3.1
75°	7.3	7.3	7.3	6.2	6.2	6.2	6.2	5.2	4.1	3.1	3.1
77.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1	3.1
80°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1	3.1
82.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1	3.1
85°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1	3.1
87.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.1	4.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192390

CATALOG NUMBER: LDA6A50940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9
2.5°	1057.6	1047.3	1040.1	1023.6	1014.3	1004.0	988.5	981.2
5°	671.4	640.4	620.8	591.9	547.4	557.8	534.0	525.7
7.5°	289.2	275.8	271.6	265.5	255.2	250.0	248.9	246.8
10°	198.4	187.0	185.9	187.0	188.0	187.0	187.0	187.0
12.5°	223.1	224.2	226.2	229.3	230.3	230.3	229.3	229.3
15°	281.0	283.0	286.2	290.3	292.3	292.3	292.3	292.3
17.5°	360.4	363.6	368.8	372.9	377.0	377.0	377.0	378.1
20°	463.7	463.7	470.0	475.1	478.3	479.2	480.3	481.3
22.5°	555.8	556.7	560.9	565.0	568.1	567.0	565.0	565.0
25°	573.2	570.2	571.2	571.2	570.2	565.0	565.0	562.9
27.5°	511.3	507.2	507.2	504.1	503.1	500.9	496.8	494.7
30°	406.0	403.9	402.8	399.8	404.9	397.7	393.5	391.4
32.5°	292.3	293.3	292.3	289.2	294.4	287.1	285.1	281.9
35°	196.2	197.3	196.2	194.1	194.1	194.1	192.1	190.0
37.5°	123.9	122.9	123.9	123.9	126.1	122.9	122.9	120.9
40°	75.4	75.4	76.4	76.4	77.5	75.4	74.4	74.4
42.5°	44.4	44.4	45.4	45.4	46.5	44.4	44.4	44.4
45°	25.8	25.8	25.8	25.8	26.9	25.8	24.8	24.8
47.5°	14.4	14.4	14.4	14.4	14.4	14.4	14.4	13.4
50°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3
52.5°	5.2	4.1	4.1	4.1	4.1	3.1	3.1	3.1
55°	2.1	2.1	2.1	2.1	2.1	1.1	1.1	1.1
57.5°	2.1	2.1	2.1	1.1	1.1	1.1	0.0	0.0
60°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
62.5°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
65°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
67.5°	2.1	2.1	2.1	1.1	1.1	0.0	0.0	0.0
70°	2.1	2.1	2.1	1.1	1.1	1.1	0.0	0.0
72.5°	2.1	2.1	2.1	1.1	1.1	1.1	0.0	0.0
75°	3.1	2.1	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	3.1	2.1	2.1	2.1	1.1	1.1	1.1	0.0
80°	3.1	2.1	2.1	2.1	1.1	1.1	1.1	1.1
82.5°	3.1	2.1	2.1	2.1	1.1	1.1	1.1	1.1
85°	3.1	2.1	2.1	2.1	1.1	1.1	1.1	1.1
87.5°	3.1	2.1	2.1	2.1	1.1	1.1	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)