

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192397

Luminaire Tested: **LDA6A50940D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192397
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26674)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50940D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4674.2 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 2.68 / 0.47 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192397

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192397

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91		
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	59	54	77	66	59	54	65	58	53	63	57	53	61	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	40375	40375	40375
5°	106405	36837	11875
10°	212460	28234	4715
15°	386796	19819	5153
20°	594760	14223	32541
25°	697516	21243	26929
30°	759452	13337	7843
35°	799316	5528	3252
40°	819614	2433	1846
45°	760839	1605	1364
50°	533663	1228	623
55°	195185	889	392
60°	41214	899	230
65°	3489	1064	272
70°	1170	1314	497
75°	233	1737	868
80°	347	2589	1294
85°	0	5158	1321

TEST NUMBER: P1192397

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.7	2.0
10°-20°	509.5	10.9
20°-30°	1231.5	26.3
30°-40°	1447.7	31.0
40°-50°	1093.6	23.4
50°-60°	274.4	5.9
60°-70°	13.3	0.3
70°-80°	6.3	0.1
80°-90°	5.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1833.7	39.2
0°-40°	3281.4	70.2
0°-60°	4649.4	99.5
0°-90°	4674.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4674.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	736	736	736	736	736	
5°	1934	1404	669	284	216	241
15°	6815	2956	349	94	91	2063
25°	11532	3678	351	488	445	5305
35°	11944	2710	83	59	49	7437
45°	9814	1065	21	22	18	7231
55°	2042	30	9	8	4	2259
65°	27	7	8	7	2	73
75°	1	5	8	7	4	3
85°	0	5	8	6	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1192397

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5
2.5°	1285.0	1264.3	1249.9	1225.0	1212.7	1217.9	1192.0	1156.9	1146.6	1115.6	1061.9
5°	1933.6	1912.0	1877.8	1825.1	1785.9	1779.7	1729.1	1644.4	1590.7	1511.2	1403.8
7.5°	2730.1	2711.4	2654.6	2576.1	2510.0	2485.2	2410.8	2262.1	2143.3	1984.3	1799.3
10°	3816.7	3744.4	3637.9	3478.9	3327.0	3256.8	3125.6	2879.8	2686.6	2468.7	2217.7
12.5°	5179.2	5051.0	4878.6	4639.9	4378.6	4247.5	4038.8	3662.7	3325.0	2951.1	2585.5
15°	6815.3	6686.1	6436.2	6066.4	5645.9	5435.3	5127.5	4534.5	4031.5	3483.0	2956.2
17.5°	8745.8	8535.0	8202.5	7666.4	7015.7	6685.2	6249.2	5428.0	4678.1	3962.4	3280.5
20°	10195.0	10041.0	9726.0	9165.2	8389.4	7963.9	7378.2	6247.1	5279.3	4345.6	3526.4
22.5°	11084.4	10946.0	10656.7	10187.8	9475.1	9003.0	8342.9	6966.0	5746.2	4611.0	3649.3
25°	11531.6	11432.5	11231.1	10822.0	10199.1	9725.0	9057.7	7498.1	6062.3	4754.6	3678.2
27.5°	11925.1	11758.9	11431.4	11152.6	10600.9	10118.5	9486.5	7762.5	6172.8	4738.1	3605.0
30°	11997.5	11902.4	11644.2	11245.5	10732.1	10244.6	9578.4	7724.2	6047.8	4545.9	3405.5
32.5°	11935.4	11852.8	11657.6	11222.7	10648.4	10110.3	9379.0	7410.3	5681.2	4189.6	3068.8
35°	11943.8	11812.5	11470.6	11098.8	10382.0	9749.8	8891.4	6836.0	5167.8	3726.8	2710.4
37.5°	11785.7	11569.8	11287.9	10808.5	9840.7	9056.8	8075.4	6095.4	4550.0	3254.7	2292.0
40°	11453.1	11288.8	10913.9	10177.4	8918.3	7932.9	7026.0	5245.2	3875.5	2739.3	1868.6
42.5°	10909.8	10713.6	10189.9	9079.4	7582.7	6723.3	5907.3	4375.5	3212.4	2240.4	1466.8
45°	9813.8	9514.3	8829.4	7505.2	6228.6	5499.3	4834.1	3567.8	2604.0	1752.8	1064.9
47.5°	8063.1	7807.9	7083.9	5978.6	4973.5	4409.5	3842.5	2813.6	1937.8	1126.9	547.4
50°	6257.4	6056.0	5503.5	4533.5	3694.7	3147.3	2701.1	1796.3	1032.9	518.5	245.9
52.5°	4117.3	3990.2	3516.1	2830.2	2121.6	1731.2	1405.8	779.8	481.3	230.4	84.7
55°	2042.2	1878.9	1652.7	1225.0	886.3	716.9	608.3	384.3	199.3	66.1	29.9
57.5°	832.5	796.4	716.9	553.6	425.6	359.5	287.2	119.8	44.4	26.9	18.5
60°	375.9	359.5	312.0	219.0	118.8	73.4	51.6	33.1	22.8	16.5	12.4
62.5°	66.1	60.9	53.8	41.3	33.1	28.9	24.8	18.5	14.4	11.4	9.3
65°	26.9	26.9	24.8	21.7	17.6	16.5	14.4	11.4	9.3	8.2	7.3
67.5°	14.4	13.4	13.4	11.4	10.3	9.3	8.2	7.3	7.3	6.2	6.2
70°	7.3	7.3	7.3	6.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
72.5°	4.1	4.1	4.1	4.1	4.1	4.1	3.1	3.1	3.1	4.1	4.1
75°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
77.5°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
80°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	5.2
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	3.1	4.1	5.2
85°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	3.1	4.1	5.2
87.5°	0.0	0.0	1.1	1.1	1.1	2.1	2.1	3.1	3.1	4.1	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192397

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5
2.5°	1059.8	1006.1	964.8	925.5	916.2	884.2	854.2	802.6	756.1	712.7	663.2
5°	1362.5	1257.1	1169.3	1083.6	1055.6	1001.9	929.6	836.6	749.9	669.4	584.6
7.5°	1691.9	1513.3	1357.3	1212.7	1162.1	1085.6	968.9	836.6	711.7	596.0	492.7
10°	2015.3	1748.7	1513.3	1304.6	1228.2	1129.0	968.9	800.5	641.4	507.2	404.9
12.5°	2327.1	1961.5	1643.4	1367.6	1267.4	1143.4	943.1	737.6	552.6	420.4	334.6
15°	2570.9	2141.2	1735.3	1392.4	1267.4	1123.8	883.1	649.7	462.8	349.2	272.7
17.5°	2753.8	2247.7	1766.3	1368.7	1224.1	1062.9	792.3	546.4	381.1	289.2	215.8
20°	2860.2	2274.5	1734.3	1299.4	1141.4	970.9	679.7	450.4	323.4	243.8	174.5
22.5°	2885.0	2237.3	1659.9	1210.6	1047.4	874.9	580.5	402.8	312.0	248.9	218.0
25°	2857.1	2161.9	1561.8	1120.8	958.6	788.2	544.4	433.8	373.9	351.2	375.9
27.5°	2746.5	2021.5	1441.0	1020.5	857.3	698.2	516.4	437.0	375.9	365.6	354.3
30°	2549.3	1809.6	1255.1	834.6	662.1	529.9	366.7	260.3	207.6	210.7	208.7
32.5°	2240.4	1501.9	982.3	583.6	455.5	358.5	242.7	153.9	144.6	144.6	142.5
35°	1900.6	1219.8	738.5	410.1	317.1	252.0	144.6	112.6	95.1	82.6	74.4
37.5°	1554.6	949.3	509.3	276.9	201.4	129.1	69.2	56.8	50.6	47.5	46.5
40°	1203.4	668.3	325.4	151.9	88.9	56.8	44.4	38.3	35.1	34.0	34.0
42.5°	890.4	430.8	175.6	59.9	47.5	39.2	32.0	27.9	26.9	26.9	25.8
45°	536.0	215.8	66.1	37.2	31.0	27.9	23.7	21.7	20.7	20.7	21.7
47.5°	247.9	80.5	36.2	24.8	22.8	20.7	18.5	17.6	17.6	17.6	18.5
50°	89.9	35.1	22.8	17.6	16.5	15.5	14.4	13.4	13.4	14.4	14.4
52.5°	34.0	21.7	16.5	13.4	12.4	12.4	11.4	11.4	11.4	11.4	11.4
55°	20.7	15.5	12.4	10.3	10.3	9.3	9.3	9.3	9.3	9.3	9.3
57.5°	13.4	11.4	9.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
60°	10.3	8.2	7.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2	8.2
62.5°	8.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2
65°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2	9.3
67.5°	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2
70°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2
72.5°	5.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2
75°	5.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3	8.2	8.2	8.2
77.5°	5.2	6.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2	9.3
80°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	8.2	8.2	8.2	9.3
82.5°	5.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2	9.3	9.3
85°	5.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	8.2	8.2	9.3
87.5°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	8.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192397

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5
2.5°	636.3	593.9	564.0	537.1	526.8	503.1	477.2	447.3	422.4	420.4	399.8
5°	527.8	468.9	426.6	399.8	386.3	361.5	331.6	312.0	284.0	275.8	255.2
7.5°	426.6	371.8	332.6	307.9	292.4	262.3	228.3	206.6	183.8	166.3	143.5
10°	347.1	294.4	252.0	227.2	211.7	179.7	144.6	119.8	99.2	95.1	93.0
12.5°	278.9	225.2	182.9	156.0	139.4	109.5	100.2	96.0	93.0	89.9	89.9
15°	216.9	162.2	116.7	106.3	103.3	100.2	98.1	96.0	94.0	93.0	94.0
17.5°	158.0	114.7	109.5	108.5	106.3	106.3	108.5	109.5	111.5	113.6	116.7
20°	139.4	140.5	151.9	160.1	157.0	172.5	194.1	211.7	254.1	279.9	315.0
22.5°	250.0	287.2	339.8	371.8	389.4	441.1	497.9	583.6	627.0	689.0	744.7
25°	427.6	471.0	516.4	528.9	538.2	543.3	536.0	496.8	487.6	470.0	464.8
27.5°	320.2	299.5	306.8	309.9	306.8	302.7	290.3	268.5	263.4	255.2	257.2
30°	189.0	182.9	191.1	190.0	190.0	190.0	185.9	168.3	160.1	150.8	144.6
32.5°	139.4	128.1	118.8	110.6	107.4	102.2	99.2	91.9	88.9	84.7	84.7
35°	69.2	66.1	66.1	64.1	63.0	64.1	64.1	60.9	58.9	57.9	57.9
37.5°	45.4	45.4	46.5	45.4	45.4	45.4	45.4	44.4	43.4	42.4	42.4
40°	34.0	34.0	35.1	35.1	34.0	34.0	34.0	33.1	33.1	33.1	33.1
42.5°	26.9	26.9	26.9	26.9	25.8	26.9	26.9	26.9	25.8	25.8	24.8
45°	22.8	21.7	21.7	21.7	21.7	21.7	22.8	21.7	21.7	20.7	20.7
47.5°	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	18.5	17.6	17.6
50°	14.4	14.4	14.4	14.4	14.4	13.4	13.4	12.4	12.4	11.4	11.4
52.5°	11.4	11.4	10.3	10.3	10.3	10.3	10.3	10.3	9.3	9.3	9.3
55°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	8.2	7.3	7.3
57.5°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.2
60°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.3	6.2	6.2	6.2
62.5°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.3	6.2	6.2	5.2
65°	9.3	9.3	9.3	9.3	8.2	8.2	8.2	7.3	7.3	6.2	6.2
67.5°	9.3	9.3	9.3	9.3	9.3	8.2	8.2	8.2	7.3	7.3	6.2
70°	9.3	9.3	9.3	9.3	9.3	8.2	8.2	8.2	7.3	7.3	6.2
72.5°	9.3	9.3	9.3	9.3	9.3	8.2	8.2	8.2	7.3	7.3	6.2
75°	9.3	9.3	9.3	9.3	9.3	8.2	8.2	8.2	7.3	7.3	6.2
77.5°	9.3	9.3	9.3	9.3	9.3	8.2	8.2	8.2	7.3	7.3	6.2
80°	9.3	9.3	9.3	9.3	9.3	8.2	8.2	8.2	7.3	7.3	6.2
82.5°	9.3	9.3	9.3	9.3	9.3	8.2	8.2	8.2	7.3	7.3	6.2
85°	9.3	9.3	8.2	8.2	8.2	8.2	8.2	7.3	6.2	6.2	5.2
87.5°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.2	5.2	5.2	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192397

CATALOG NUMBER: LDA6A50940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	736.5	736.5	736.5	736.5	736.5	736.5	736.5	736.5
2.5°	395.7	381.1	378.1	382.2	365.6	365.6	365.6	372.9
5°	246.8	232.4	228.3	229.3	215.8	206.6	211.7	215.8
7.5°	134.3	118.8	113.6	113.6	100.2	95.1	96.0	98.1
10°	89.9	87.8	87.8	86.7	84.7	83.7	84.7	84.7
12.5°	86.7	85.7	85.7	84.7	84.7	83.7	83.7	84.7
15°	90.8	90.8	90.8	89.9	89.9	88.9	90.8	90.8
17.5°	115.7	117.7	121.8	123.9	128.1	123.9	131.2	130.2
20°	339.8	373.9	437.0	460.7	528.9	495.8	567.0	557.8
22.5°	769.5	794.4	804.7	809.9	810.8	843.9	849.1	860.5
25°	454.5	448.2	443.1	443.1	424.5	446.2	442.1	445.2
27.5°	242.7	240.7	235.6	237.6	228.3	235.6	237.6	237.6
30°	137.3	133.2	129.1	129.1	120.9	125.0	123.9	123.9
32.5°	79.6	77.5	75.4	74.4	72.3	72.3	71.2	71.2
35°	54.7	53.8	52.7	51.6	49.5	48.6	48.6	48.6
37.5°	40.3	39.2	38.3	38.3	37.2	35.1	35.1	35.1
40°	31.0	29.9	28.9	28.9	27.9	25.8	25.8	25.8
42.5°	23.7	22.8	21.7	20.7	20.7	19.6	18.5	18.5
45°	19.6	19.6	18.5	18.5	17.6	17.6	17.6	17.6
47.5°	16.5	16.5	15.5	15.5	15.5	14.4	14.4	13.4
50°	10.3	9.3	9.3	8.2	8.2	7.3	7.3	7.3
52.5°	8.2	7.3	7.3	6.2	6.2	5.2	5.2	5.2
55°	6.2	6.2	5.2	5.2	5.2	4.1	4.1	4.1
57.5°	5.2	5.2	4.1	4.1	4.1	3.1	3.1	3.1
60°	5.2	4.1	4.1	3.1	3.1	3.1	2.1	2.1
62.5°	5.2	4.1	4.1	3.1	3.1	2.1	2.1	2.1
65°	5.2	4.1	4.1	3.1	3.1	3.1	3.1	2.1
67.5°	5.2	5.2	4.1	4.1	4.1	3.1	3.1	3.1
70°	6.2	5.2	5.2	4.1	4.1	4.1	4.1	3.1
72.5°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
75°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
77.5°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
80°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
82.5°	5.2	5.2	5.2	4.1	4.1	4.1	4.1	4.1
85°	4.1	4.1	4.1	3.1	3.1	3.1	3.1	2.1
87.5°	3.1	3.1	2.1	2.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)