

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192403

Luminaire Tested: **LDA6A50940D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26675)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50940D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4894.2 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 2.52 / 0.5 / 1.32
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192403

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192403

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48		
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	49	42	37	60	49	42	37	48	42	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61892	61892	61892
5°	158535	57071	20922
10°	334296	45540	5917
15°	482114	32299	4921
20°	544146	21451	6931
25°	590810	21618	49926
30°	657126	14255	17458
35°	663897	8091	6706
40°	668309	3328	3034
45°	662828	2085	1768
50°	520281	1407	1228
55°	156582	984	593
60°	33068	899	450
65°	3749	1064	402
70°	994	1314	657
75°	233	1737	868
80°	0	2936	1294
85°	0	5158	2579

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192403

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.9	2.9
10°-20°	682.3	13.9
20°-30°	1286.5	26.3
30°-40°	1427.0	29.2
40°-50°	1087.4	22.2
50°-60°	242.6	5.0
60°-70°	13.2	0.3
70°-80°	6.1	0.1
80°-90°	5.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2112.7	43.2
0°-40°	3539.7	72.3
0°-60°	4869.8	99.5
0°-90°	4894.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4894.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1129	1129	1129	1129	1129	
5°	2881	2134	1037	498	380	373
15°	8495	4650	569	101	87	2369
25°	9768	5437	357	597	825	4546
35°	9920	3383	121	106	100	6214
45°	8550	996	27	28	23	6367
55°	1638	43	10	9	6	2022
65°	29	7	8	7	3	68
75°	1	4	8	7	4	2
85°	0	4	8	6	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192403

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0
2.5°	1937.8	1903.7	1899.5	1888.2	1799.4	1798.4	1797.3	1750.8	1708.5	1686.8	1594.8
5°	2880.9	2856.0	2825.0	2785.8	2639.1	2618.4	2601.0	2531.7	2383.0	2296.3	2134.1
7.5°	4255.7	4242.3	4086.3	4065.6	3796.0	3730.0	3664.8	3487.2	3200.0	3014.1	2726.9
10°	6005.4	5941.5	5822.7	5661.6	5310.3	5185.4	5064.5	4700.9	4211.3	3821.9	3333.2
12.5°	7586.9	7505.3	7360.7	7172.7	6730.6	6560.1	6369.1	5922.8	5324.8	4691.6	4000.5
15°	8494.8	8481.4	8314.0	8237.6	7881.3	7707.8	7549.7	7036.3	6289.5	5544.8	4650.3
17.5°	9032.0	9033.1	8910.1	8864.6	8533.1	8367.8	8234.6	7860.6	7078.7	6174.9	5143.0
20°	9327.4	9357.4	9242.7	9171.4	8940.1	8793.4	8669.4	8284.1	7603.5	6600.4	5421.9
22.5°	9547.4	9561.8	9422.4	9363.6	9104.3	8962.8	8884.2	8515.6	7850.3	6827.6	5506.6
25°	9767.5	9760.2	9603.1	9485.4	9230.2	9092.9	8996.9	8677.7	7953.6	6880.3	5437.4
27.5°	9999.8	10032.8	9741.6	9553.6	9325.3	9164.2	9056.8	8727.3	7946.3	6743.0	5186.3
30°	10381.0	10113.5	9822.1	9562.9	9300.5	9130.1	9007.2	8587.9	7747.0	6378.3	4709.2
32.5°	10220.9	10031.9	9745.7	9479.2	9198.3	9010.3	8860.5	8362.6	7328.7	5778.2	4068.7
35°	9920.3	9869.7	9586.7	9369.8	9050.5	8848.1	8673.5	8015.6	6680.0	5056.3	3382.9
37.5°	9649.6	9597.0	9428.6	9204.4	8841.9	8630.1	8309.9	7464.0	5836.1	4152.4	2660.8
40°	9338.8	9326.4	9138.3	8930.7	8494.8	8104.4	7772.8	6490.9	4831.0	3265.1	2070.0
42.5°	8994.8	8987.5	8834.7	8527.9	7887.5	7403.0	6848.3	5393.0	3714.5	2478.0	1538.0
45°	8549.6	8507.2	8243.8	7796.5	6877.3	6176.9	5520.0	4120.3	2723.8	1770.4	995.8
47.5°	7778.0	7703.6	7319.4	6553.9	5451.8	4736.0	4131.7	2833.4	1699.2	1000.9	493.8
50°	6100.5	5903.2	5355.8	4551.1	3421.0	2799.2	2324.1	1405.9	754.0	496.8	316.1
52.5°	3768.1	3555.3	3037.8	2430.5	1560.8	1209.5	997.8	677.6	417.3	286.2	121.8
55°	1638.3	1538.0	1269.5	1010.2	722.1	574.3	495.8	343.0	216.9	104.3	43.4
57.5°	639.4	619.7	540.3	455.5	341.9	278.9	246.8	154.9	59.9	37.2	24.8
60°	301.6	282.0	242.7	201.4	126.1	90.8	70.2	43.4	29.9	22.8	16.5
62.5°	82.6	71.2	57.9	49.5	38.3	34.0	29.9	23.7	18.5	14.4	11.4
65°	28.9	28.9	25.8	23.7	19.6	17.6	16.5	13.4	11.4	9.3	7.3
67.5°	13.4	13.4	12.4	11.4	9.3	9.3	8.2	7.3	6.2	5.2	5.2
70°	6.2	5.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1	4.1	4.1
72.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1	4.1	4.1	4.1
75°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	4.1
77.5°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	4.1
80°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	4.1
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	3.1	4.1	4.1
85°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	4.1	4.1	4.1
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.1	3.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192403

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0
2.5°	1555.6	1516.3	1464.7	1379.0	1340.7	1332.5	1262.2	1198.2	1141.4	1100.1	1035.0
5°	2028.7	1915.0	1776.7	1610.3	1547.3	1502.9	1368.7	1240.5	1131.1	1037.1	937.9
7.5°	2497.7	2272.4	2064.8	1822.1	1704.4	1615.5	1416.2	1234.4	1069.1	941.0	809.9
10°	2949.0	2628.8	2277.6	1958.5	1800.4	1666.1	1404.8	1174.4	967.8	818.1	679.7
12.5°	3377.7	2918.0	2451.2	2026.7	1837.6	1669.3	1349.0	1078.4	856.3	695.2	550.6
15°	3803.3	3127.7	2552.4	2041.1	1812.8	1610.3	1247.8	950.2	731.3	569.1	442.1
17.5°	4068.7	3244.4	2553.4	1977.0	1719.9	1498.8	1109.4	817.0	604.2	458.6	347.1
20°	4199.9	3230.0	2456.4	1829.4	1561.8	1338.6	946.1	680.8	488.6	367.7	273.7
22.5°	4161.7	3101.9	2285.9	1634.1	1386.2	1174.4	805.6	571.2	421.5	319.1	247.9
25°	3982.0	2894.3	2084.4	1450.2	1212.7	1012.3	707.5	525.7	415.3	357.4	307.9
27.5°	3671.0	2621.6	1837.6	1257.1	1043.3	883.1	641.4	510.2	429.7	385.3	389.4
30°	3212.5	2260.1	1518.4	998.8	817.0	686.9	481.3	355.3	262.3	225.2	225.2
32.5°	2699.1	1847.9	1173.4	738.5	590.9	498.9	338.9	242.7	194.1	176.6	168.3
35°	2217.7	1446.1	870.8	535.1	426.6	355.3	222.1	136.4	125.0	120.9	118.8
37.5°	1744.6	1085.6	631.1	388.4	296.5	235.6	113.6	87.8	76.4	71.2	67.1
40°	1307.6	762.3	437.0	237.6	164.2	108.5	66.1	53.8	47.5	46.5	44.4
42.5°	915.1	511.3	270.7	104.3	76.4	60.9	45.4	38.3	35.1	34.0	33.1
45°	536.0	319.1	110.6	57.9	47.5	42.4	33.1	28.9	26.9	26.9	25.8
47.5°	336.7	129.1	58.9	37.2	32.0	29.9	24.8	21.7	20.7	20.7	20.7
50°	138.4	56.8	35.1	25.8	22.8	21.7	18.5	16.5	16.5	16.5	16.5
52.5°	50.6	32.0	23.7	18.5	16.5	15.5	13.4	12.4	12.4	13.4	12.4
55°	28.9	21.7	16.5	13.4	11.4	11.4	10.3	10.3	10.3	10.3	10.3
57.5°	18.5	14.4	11.4	9.3	8.2	8.2	8.2	8.2	8.2	9.3	8.2
60°	12.4	10.3	8.2	7.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2
62.5°	9.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2
65°	7.3	6.2	7.3	7.3	7.3	7.3	7.3	8.2	8.2	8.2	9.3
67.5°	5.2	5.2	6.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	9.3
70°	5.2	5.2	6.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	9.3
72.5°	5.2	5.2	6.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	9.3
75°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	7.3	8.2	8.2	9.3
77.5°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	8.2	9.3
80°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	9.3	9.3
82.5°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	9.3	9.3
85°	5.2	6.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	8.2	9.3
87.5°	5.2	5.2	6.2	6.2	6.2	7.3	7.3	8.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192403

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0
2.5°	990.6	945.1	908.0	888.3	866.7	829.5	794.4	762.3	748.8	705.5	713.7
5°	860.5	783.0	721.0	693.1	661.0	609.4	564.0	520.5	497.9	460.7	447.3
7.5°	715.9	624.9	550.6	518.5	490.6	442.1	399.8	359.5	330.5	292.4	276.9
10°	573.2	486.5	418.3	390.5	359.5	310.9	268.5	233.5	209.7	180.8	166.3
12.5°	453.4	375.9	306.8	278.9	253.1	212.8	179.7	147.7	121.8	106.3	102.2
15°	353.3	278.9	222.1	199.4	177.7	138.4	113.6	105.4	101.2	97.1	96.0
17.5°	265.5	205.5	154.9	132.2	119.8	109.5	105.4	101.2	99.2	96.0	97.1
20°	204.6	146.7	126.1	122.9	120.9	115.7	114.7	113.6	112.6	113.6	115.7
22.5°	194.1	182.9	189.0	193.2	202.5	203.5	220.1	233.5	245.9	279.9	296.5
25°	327.5	347.1	378.1	397.7	424.5	452.5	504.1	549.5	597.1	640.4	678.6
27.5°	410.1	419.4	419.4	429.7	418.3	416.3	410.1	404.9	426.6	419.4	442.1
30°	227.2	237.6	255.2	264.4	275.8	284.0	281.0	270.7	276.9	268.5	276.9
32.5°	162.2	162.2	166.3	167.4	169.4	170.4	171.5	172.5	173.5	168.3	171.5
35°	115.7	111.5	109.5	109.5	108.5	106.3	105.4	105.4	106.3	101.2	103.3
37.5°	65.0	63.0	63.0	63.0	63.0	63.0	64.1	65.0	65.0	65.0	67.1
40°	43.4	43.4	43.4	44.4	44.4	44.4	45.4	45.4	46.5	46.5	47.5
42.5°	33.1	32.0	33.1	33.1	33.1	34.0	34.0	35.1	35.1	35.1	36.2
45°	25.8	25.8	25.8	25.8	26.9	26.9	26.9	26.9	27.9	26.9	27.9
47.5°	20.7	20.7	20.7	21.7	21.7	20.7	21.7	21.7	21.7	21.7	21.7
50°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	17.6	16.5	17.6
52.5°	13.4	12.4	12.4	12.4	12.4	11.4	11.4	12.4	12.4	11.4	11.4
55°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
57.5°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.3
60°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	7.3	7.3	6.2
62.5°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	7.3	6.2	6.2
65°	9.3	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.2	6.2
67.5°	9.3	9.3	8.2	8.2	8.2	8.2	8.2	7.3	7.3	6.2	6.2
70°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.2
72.5°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	7.3
75°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	7.3
77.5°	8.2	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	7.3	6.2
80°	9.3	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	7.3	6.2
82.5°	8.2	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.2	6.2
85°	8.2	8.2	8.2	8.2	8.2	7.3	7.3	7.3	6.2	6.2	6.2
87.5°	8.2	8.2	8.2	7.3	7.3	7.3	7.3	6.2	6.2	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192403

CATALOG NUMBER: LDA6A50940D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0	1129.0
2.5°	670.4	655.9	668.3	652.8	647.7	636.3	631.1	636.3
5°	422.4	406.9	410.1	399.8	383.2	383.2	378.1	380.2
7.5°	255.2	239.7	240.7	231.3	219.0	216.9	211.7	213.9
10°	147.7	131.2	131.2	120.9	110.6	109.5	106.3	106.3
12.5°	98.1	96.0	94.0	93.0	90.8	90.8	90.8	88.9
15°	91.9	90.8	89.9	89.9	87.8	87.8	88.9	86.7
17.5°	94.0	93.0	91.9	91.9	91.9	91.9	93.0	90.8
20°	112.6	113.6	113.6	116.7	118.8	119.8	122.9	118.8
22.5°	295.4	304.7	312.0	350.1	383.2	370.8	393.5	355.3
25°	706.6	732.4	754.0	758.2	778.9	807.8	826.3	825.4
27.5°	442.1	443.1	455.5	455.5	451.4	468.0	479.2	477.2
30°	272.7	271.7	275.8	265.5	264.4	271.7	275.8	275.8
32.5°	168.3	167.4	170.4	168.3	163.1	171.5	169.4	169.4
35°	101.2	102.2	100.2	100.2	96.0	100.2	99.2	100.2
37.5°	66.1	65.0	64.1	64.1	62.0	63.0	62.0	59.9
40°	46.5	46.5	45.4	45.4	44.4	43.4	43.4	42.4
42.5°	35.1	35.1	34.0	34.0	33.1	32.0	32.0	31.0
45°	26.9	25.8	24.8	24.8	24.8	23.7	23.7	22.8
47.5°	20.7	20.7	20.7	19.6	19.6	18.5	18.5	17.6
50°	16.5	16.5	16.5	16.5	15.5	15.5	15.5	14.4
52.5°	11.4	11.4	10.3	10.3	9.3	9.3	9.3	8.2
55°	8.2	8.2	8.2	7.3	7.3	7.3	6.2	6.2
57.5°	7.3	7.3	6.2	6.2	6.2	5.2	5.2	5.2
60°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
62.5°	5.2	5.2	5.2	4.1	4.1	4.1	4.1	3.1
65°	5.2	5.2	4.1	4.1	4.1	3.1	3.1	3.1
67.5°	5.2	5.2	5.2	4.1	4.1	4.1	4.1	3.1
70°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
72.5°	6.2	5.2	5.2	5.2	5.2	4.1	4.1	4.1
75°	6.2	6.2	5.2	5.2	5.2	5.2	5.2	4.1
77.5°	6.2	5.2	5.2	5.2	5.2	5.2	4.1	4.1
80°	6.2	5.2	5.2	5.2	5.2	4.1	4.1	4.1
82.5°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
85°	5.2	5.2	4.1	4.1	4.1	4.1	4.1	4.1
87.5°	4.1	4.1	3.1	3.1	3.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)