

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175513

Luminaire Tested: **LDA6A10835D010TE LAR35FL 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26295)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A10835D010TE LAR35FL 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 934.3 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.84
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175513

CATALOG NUMBER: LDA6A10835D010TE LAR35FL 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175513

CATALOG NUMBER: LDA6A10835D010TE LAR35FL 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	99	96	105	101	98	95	98	96	93		96	94	92		94
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91
5	100	94	90	87	99	93	89	86	92	88	85		90	87	85		89
6	97	90	86	83	96	90	86	83	88	85	82		87	84	82		86
7	94	87	83	80	93	87	82	79	85	82	79		84	81	79		83
8	91	84	80	77	90	84	79	77	83	79	76		82	78	76		81
9	88	81	77	74	87	81	77	74	80	76	74		79	76	73		79
10	86	79	74	72	85	78	74	71	78	74	71		77	74	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150536
5°	143655
10°	122727
15°	100483
20°	64312
25°	24776
30°	5083
35°	1352
40°	422
45°	132
50°	60
55°	29
60°	33
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175513

CATALOG NUMBER: LDA6A10835D010TE LAR35FL 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.1	25.2
10°-20°	472.6	50.6
20°-30°	207.1	22.2
30°-40°	17.3	1.9
40°-50°	1.7	0.2
50°-60°	0.3	0.0
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.9	97.9
0°-40°	932.2	99.8
0°-60°	934.2	100.0
0°-90°	934.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	934.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2746	
5°	2610	235
15°	1770	473
25°	410	207
35°	20	17
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175513

CATALOG NUMBER: LDA6A10835D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2746.0
1°	2732.8
2°	2711.3
3°	2686.6
4°	2655.3
5°	2610.5
6°	2546.6
7°	2463.9
8°	2373.2
9°	2287.1
10°	2204.7
11°	2122.0
12°	2041.4
13°	1957.7
14°	1868.8
15°	1770.5
17.5°	1468.2
20°	1102.4
22.5°	719.9
25°	409.6
27.5°	190.7
30°	80.3
32.5°	41.7
35°	20.2
37.5°	10.8
40°	5.9
42.5°	3.1
45°	1.7
47.5°	1.0
50°	0.7
52.5°	0.3
55°	0.3
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175513

CATALOG NUMBER: LDA6A10835D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)