

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192409

Luminaire Tested: **LDA6A50950D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26673)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50950D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4420.7 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.56 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192409

CATALOG NUMBER: LDA6A50950D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192409

CATALOG NUMBER: LDA6A50950D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	55	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	68602	68602	68602
5°	137381	65260	17499
10°	230395	55788	4782
15°	351829	41822	6947
20°	504096	30587	81849
25°	749438	50749	41978
30°	875964	22434	6533
35°	880788	4671	3447
40°	729302	2612	2004
45°	545902	1667	1582
50°	382580	1185	913
55°	61494	927	726
60°	3772	932	592
65°	1103	1258	558
70°	689	1362	866
75°	466	1610	1144
80°	347	2399	1705
85°	692	4780	2013



TEST NUMBER: P1192409

CATALOG NUMBER: LDA6A50950D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.7	2.9
10°-20°	547.5	12.4
20°-30°	1317.4	29.8
30°-40°	1403.6	31.8
40°-50°	875.3	19.8
50°-60°	127.9	2.9
60°-70°	8.1	0.2
70°-80°	6.4	0.1
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1994.6	45.1
0°-40°	3398.2	76.9
0°-60°	4401.4	99.6
0°-90°	4420.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4420.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1251	1251	1251	1251	1251	
5°	2496	2002	1186	591	318	289
15°	6199	3445	737	114	122	1839
25°	12390	4097	839	869	694	5583
35°	13161	3040	70	64	52	7940
45°	7041	890	22	25	20	5543
55°	643	15	10	11	8	1138
65°	8	6	10	8	4	13
75°	2	4	8	8	5	2
85°	1	4	8	6	3	1
90°	0	0	0	0	0	

TEST NUMBER: P1192409

CATALOG NUMBER: LDA6A50950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4
2.5°	1861.6	1798.3	1819.8	1772.4	1755.3	1759.6	1725.2	1697.2	1682.2	1645.7	1608.2
5°	2496.5	2423.4	2444.8	2374.1	2330.0	2320.2	2266.6	2206.5	2152.8	2071.1	2002.4
7.5°	3266.6	3176.5	3191.4	3085.2	2996.0	2965.9	2884.3	2767.1	2658.8	2520.0	2387.9
10°	4138.9	4054.1	4049.8	3887.6	3735.0	3675.9	3556.8	3363.5	3178.7	2970.2	2753.2
12.5°	5166.9	5039.1	5017.7	4809.3	4581.5	4484.9	4318.4	4022.9	3730.7	3426.8	3114.2
15°	6199.2	6061.8	6027.4	5765.3	5447.3	5317.3	5095.0	4701.8	4299.0	3869.3	3445.0
17.5°	7299.3	7079.0	6893.2	6590.3	6222.9	6089.6	5801.8	5298.1	4791.0	4260.4	3693.1
20°	8640.9	8395.0	8133.9	7616.2	6942.6	6680.5	6364.7	5796.4	5163.8	4550.4	3876.8
22.5°	10480.1	10076.1	9521.8	8689.3	7763.3	7389.5	6901.8	6166.0	5450.5	4762.0	3999.3
25°	12390.0	11832.4	11223.5	9944.1	8514.3	8057.6	7416.4	6448.5	5678.3	4917.7	4097.1
27.5°	13489.9	13042.1	12351.4	11010.7	9123.3	8523.9	7784.8	6661.2	5823.3	4992.9	4125.0
30°	13838.1	13475.0	12847.6	11472.6	9327.3	8613.1	7819.2	6663.4	5753.5	4861.9	3963.9
32.5°	13693.0	13348.3	12654.3	11183.6	8953.6	8296.2	7525.9	6392.7	5409.8	4459.1	3550.4
35°	13161.2	12705.8	11862.6	10224.4	8317.6	7664.6	6944.7	5908.1	4881.2	3912.3	3040.0
37.5°	11967.8	11495.1	10535.9	8994.3	7498.1	6929.7	6350.8	5365.7	4349.5	3414.9	2595.2
40°	10191.1	9691.7	8903.0	7821.3	6614.0	6226.2	5737.4	4765.3	3786.6	2927.3	2183.9
42.5°	8398.2	8078.1	7610.8	6753.6	5912.4	5530.1	5055.2	4111.0	3245.1	2424.4	1658.6
45°	7041.4	6788.0	6477.4	5936.1	5142.3	4782.4	4341.0	3452.5	2529.8	1619.9	889.5
47.5°	6135.9	5826.5	5555.9	4952.2	4100.2	3663.1	3194.8	2275.2	1458.8	702.5	246.0
50°	4485.9	4113.2	3860.7	3184.0	2410.6	2046.3	1703.7	1056.0	472.7	156.8	40.8
52.5°	2274.1	1992.6	1844.4	1393.3	920.6	688.6	506.0	218.0	93.5	31.1	23.7
55°	643.4	517.8	464.0	306.2	166.5	117.1	76.3	38.7	28.0	21.5	15.0
57.5°	66.7	56.9	53.7	44.1	35.4	33.3	30.1	23.7	18.3	15.0	9.7
60°	34.4	31.1	30.1	26.8	22.6	20.4	19.2	16.1	11.9	8.5	7.6
62.5°	18.3	17.2	15.0	13.9	11.9	11.9	10.7	8.5	7.6	7.6	6.4
65°	8.5	8.5	8.5	8.5	7.6	7.6	6.4	6.4	6.4	6.4	6.4
67.5°	6.4	6.4	6.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
70°	4.3	4.3	4.3	4.3	3.2	3.2	3.2	3.2	3.2	4.3	4.3
72.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	3.2	3.2	4.3	4.3
75°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	3.2	3.2	4.3	4.3
77.5°	1.1	1.1	2.2	2.2	2.2	2.2	2.2	3.2	3.2	4.3	4.3
80°	1.1	1.1	1.1	1.1	2.2	2.2	2.2	3.2	3.2	4.3	4.3
82.5°	1.1	1.1	1.1	1.1	2.2	2.2	2.2	3.2	3.2	4.3	4.3
85°	1.1	1.1	1.1	1.1	2.2	2.2	2.2	2.2	3.2	4.3	4.3
87.5°	0.0	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.2	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192409

CATALOG NUMBER: LDA6A50950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4
2.5°	1562.9	1536.1	1493.1	1450.2	1437.4	1401.8	1359.9	1310.5	1264.3	1227.8	1192.4
5°	1891.7	1819.8	1739.2	1630.7	1592.0	1531.8	1441.6	1344.9	1261.1	1185.9	1116.0
7.5°	2219.3	2084.0	1936.8	1780.0	1713.3	1624.3	1482.4	1346.1	1221.4	1110.7	1006.5
10°	2509.3	2301.0	2093.7	1877.7	1784.2	1669.4	1480.3	1306.2	1147.3	1002.2	871.2
12.5°	2776.9	2488.9	2214.0	1936.8	1819.8	1681.1	1448.1	1237.5	1048.4	878.8	725.1
15°	3011.0	2640.5	2299.9	1964.8	1816.5	1657.6	1384.6	1143.0	932.5	736.9	570.4
17.5°	3174.4	2726.4	2324.6	1935.8	1772.4	1589.8	1287.9	1030.1	799.1	594.0	403.9
20°	3272.0	2748.9	2301.0	1872.4	1691.9	1502.9	1197.8	936.7	712.3	524.3	365.2
22.5°	3325.8	2759.6	2283.7	1849.8	1666.1	1485.6	1202.0	952.8	760.6	633.8	621.0
25°	3379.6	2794.0	2313.9	1875.5	1703.7	1536.1	1265.5	1010.9	879.7	839.0	852.9
27.5°	3376.3	2772.5	2285.9	1852.0	1686.5	1512.6	1210.7	943.2	852.9	789.6	736.9
30°	3185.1	2568.4	2071.1	1610.3	1421.3	1189.1	806.7	554.3	424.3	354.4	319.1
32.5°	2742.5	2094.7	1582.4	1119.4	934.5	675.7	346.9	182.6	156.8	139.7	124.6
35°	2279.5	1668.3	1191.2	705.7	469.5	256.7	119.3	77.4	72.0	69.8	68.7
37.5°	1879.8	1319.1	783.0	282.5	168.7	95.6	54.8	49.4	48.4	49.4	48.4
40°	1483.5	870.1	310.4	94.4	51.5	41.9	38.7	35.4	35.4	36.5	35.4
42.5°	888.4	324.5	94.4	35.4	33.3	30.1	29.0	28.0	26.8	28.0	28.0
45°	293.2	82.8	31.1	24.6	23.7	22.6	21.5	21.5	21.5	21.5	22.6
47.5°	66.7	29.0	21.5	18.3	18.3	17.2	17.2	16.1	17.2	17.2	18.3
50°	25.8	18.3	15.0	13.9	13.9	12.9	12.9	12.9	12.9	13.9	13.9
52.5°	16.1	12.9	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	11.9
55°	10.7	9.7	8.5	8.5	8.5	8.5	8.5	9.7	9.7	9.7	9.7
57.5°	7.6	7.6	7.6	7.6	8.5	7.6	8.5	7.6	7.6	8.5	9.7
60°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	8.5	8.5	9.7
62.5°	6.4	7.6	7.6	7.6	7.6	7.6	7.6	8.5	8.5	8.5	9.7
65°	6.4	6.4	7.6	7.6	7.6	7.6	8.5	8.5	8.5	9.7	9.7
67.5°	5.4	6.4	6.4	7.6	7.6	7.6	7.6	8.5	8.5	8.5	9.7
70°	5.4	5.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	8.5	8.5
72.5°	5.4	5.4	6.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	8.5
75°	5.4	5.4	6.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	8.5
77.5°	5.4	5.4	6.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	8.5
80°	5.4	5.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	7.6	8.5
82.5°	5.4	5.4	6.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6	7.6
85°	5.4	5.4	6.4	6.4	6.4	6.4	6.4	6.4	7.6	7.6	7.6
87.5°	5.4	5.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192409

CATALOG NUMBER: LDA6A50950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4
2.5°	1145.1	1101.0	1079.5	1047.4	1049.6	995.8	975.4	936.7	915.3	892.6	866.9
5°	1031.3	954.0	899.2	856.1	832.5	762.6	715.4	654.2	590.8	529.7	479.1
7.5°	888.4	786.3	702.5	647.8	614.5	473.7	383.6	311.5	283.6	262.1	240.6
10°	729.4	602.7	454.4	379.2	333.0	266.3	239.5	198.7	169.6	142.8	126.7
12.5°	569.3	376.0	271.8	249.3	233.2	173.0	136.4	126.7	103.2	97.8	95.6
15°	357.7	247.1	192.3	165.4	143.9	120.3	110.6	109.6	113.9	115.0	113.9
17.5°	253.6	197.6	145.0	141.9	141.9	154.6	156.8	166.5	175.0	182.6	183.7
20°	325.4	292.2	340.6	362.0	399.7	445.7	513.6	608.0	690.8	774.5	839.0
22.5°	623.1	696.2	803.6	841.2	904.5	1003.3	1096.8	1183.8	1271.8	1337.3	1351.4
25°	916.3	966.8	1030.1	1016.2	1035.5	1030.1	977.5	906.6	869.0	800.3	776.7
27.5°	701.5	648.8	604.9	554.3	529.7	482.2	414.6	371.7	333.0	294.3	278.2
30°	285.8	250.2	224.4	206.3	195.5	169.6	156.8	142.8	136.4	126.7	121.4
32.5°	111.7	105.2	102.0	98.9	97.8	94.4	91.3	87.0	85.9	85.9	81.6
35°	66.7	66.7	66.7	65.5	66.7	65.5	64.5	63.3	64.5	64.5	61.3
37.5°	47.2	48.4	48.4	48.4	48.4	48.4	48.4	48.4	47.2	47.2	44.1
40°	35.4	36.5	37.6	36.5	37.6	37.6	36.5	35.4	35.4	35.4	33.3
42.5°	29.0	29.0	29.0	29.0	30.1	29.0	29.0	29.0	29.0	29.0	28.0
45°	23.7	23.7	23.7	23.7	24.6	24.6	23.7	23.7	24.6	24.6	23.7
47.5°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	17.2	17.2	17.2	16.1
50°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	15.0	13.9	13.9
52.5°	11.9	11.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9	12.9	11.9
55°	10.7	10.7	11.9	11.9	11.9	11.9	11.9	10.7	10.7	10.7	9.7
57.5°	9.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	9.7	9.7	8.5
60°	9.7	9.7	10.7	10.7	10.7	10.7	9.7	9.7	8.5	8.5	7.6
62.5°	9.7	9.7	10.7	10.7	10.7	9.7	9.7	8.5	8.5	7.6	7.6
65°	9.7	10.7	10.7	10.7	10.7	9.7	9.7	8.5	8.5	7.6	7.6
67.5°	9.7	10.7	10.7	10.7	10.7	9.7	9.7	8.5	8.5	7.6	7.6
70°	9.7	9.7	9.7	9.7	9.7	9.7	9.7	8.5	8.5	7.6	7.6
72.5°	8.5	9.7	9.7	9.7	9.7	9.7	8.5	8.5	8.5	7.6	7.6
75°	8.5	8.5	8.5	8.5	9.7	8.5	8.5	8.5	7.6	7.6	6.4
77.5°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	7.6	7.6	7.6	6.4
80°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	7.6	7.6	6.4	6.4
82.5°	8.5	8.5	8.5	8.5	8.5	8.5	7.6	7.6	6.4	6.4	6.4
85°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	6.4	6.4	5.4	5.4
87.5°	7.6	7.6	7.6	7.6	7.6	6.4	6.4	5.4	4.3	4.3	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192409

CATALOG NUMBER: LDA6A50950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4
2.5°	839.0	820.7	816.4	816.4	806.7	787.5	784.2	777.7
5°	424.3	379.2	370.6	361.0	344.9	325.4	320.0	318.0
7.5°	219.1	199.8	196.6	190.2	180.4	170.8	168.7	167.6
10°	128.9	117.1	111.7	102.0	92.5	87.0	87.0	85.9
12.5°	95.6	95.6	95.6	95.6	95.6	95.6	95.6	95.6
15°	116.0	119.3	119.3	120.3	121.4	122.4	124.6	122.4
17.5°	195.5	211.6	210.6	212.7	220.2	229.8	225.6	231.0
20°	949.5	1073.1	1108.6	1144.0	1251.4	1352.4	1332.0	1403.0
22.5°	1364.2	1401.8	1386.8	1377.2	1399.7	1387.9	1438.4	1405.1
25°	731.5	723.9	723.9	691.7	698.3	682.1	703.6	694.0
27.5°	269.7	246.0	243.9	228.8	238.5	215.9	222.5	218.0
30°	116.0	117.1	112.8	109.6	106.3	104.2	104.2	103.2
32.5°	79.5	79.5	77.4	75.2	73.0	70.9	69.8	68.7
35°	59.1	59.1	56.9	56.0	54.8	52.6	51.5	51.5
37.5°	43.0	43.0	41.9	40.8	38.7	37.6	36.5	36.5
40°	33.3	32.2	31.1	31.1	29.0	29.0	28.0	28.0
42.5°	26.8	26.8	26.8	25.8	24.6	23.7	23.7	23.7
45°	23.7	23.7	22.6	21.5	21.5	21.5	20.4	20.4
47.5°	16.1	16.1	15.0	15.0	13.9	13.9	12.9	12.9
50°	12.9	12.9	12.9	12.9	11.9	10.7	10.7	10.7
52.5°	11.9	10.7	10.7	10.7	9.7	9.7	8.5	8.5
55°	9.7	9.7	8.5	8.5	7.6	7.6	7.6	7.6
57.5°	8.5	7.6	7.6	7.6	6.4	6.4	6.4	6.4
60°	7.6	6.4	6.4	6.4	5.4	5.4	5.4	5.4
62.5°	6.4	6.4	6.4	6.4	5.4	5.4	5.4	5.4
65°	6.4	6.4	6.4	5.4	5.4	5.4	5.4	4.3
67.5°	6.4	6.4	6.4	6.4	5.4	5.4	5.4	5.4
70°	6.4	6.4	6.4	6.4	5.4	5.4	5.4	5.4
72.5°	6.4	6.4	6.4	6.4	5.4	5.4	5.4	5.4
75°	6.4	6.4	6.4	6.4	5.4	5.4	5.4	5.4
77.5°	6.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
80°	6.4	5.4	5.4	5.4	5.4	4.3	4.3	5.4
82.5°	5.4	5.4	5.4	5.4	4.3	4.3	4.3	4.3
85°	4.3	4.3	4.3	4.3	3.2	3.2	3.2	3.2
87.5°	3.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)