

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192423

Luminaire Tested: **LDA6A50950D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192423
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26669)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50950D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4112.4 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 2.14 / 1.07 / 1.49
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192423

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192423

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62		
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55		
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49		
7	72	59	52	46	70	59	51	46	57	51	46	56	50	45	55	49	45	43		
8	67	54	47	41	65	54	46	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	37	33	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	72204	72204	72204
5°	115579	71296	46230
10°	168885	68475	31156
15°	230898	64932	23530
20°	288863	61483	23761
25°	333685	61280	36843
30°	365531	58003	34277
35°	377453	49182	26461
40°	369406	38365	20832
45°	336740	28313	15994
50°	270652	20895	10720
55°	164802	14776	6050
60°	85519	9769	2357
65°	41678	5163	1103
70°	19122	2228	1026
75°	7964	1610	1144
80°	4072	1705	1357
85°	2705	3397	2013

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192423

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.1	3.3
10°-20°	478.6	11.6
20°-30°	906.2	22.0
30°-40°	1097.5	26.7
40°-50°	918.6	22.3
50°-60°	445.1	10.8
60°-70°	109.1	2.7
70°-80°	17.7	0.4
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1519.9	37.0
0°-40°	2617.5	63.6
0°-60°	3981.2	96.8
0°-90°	4112.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4112.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1317	1317	1317	1317	1317	
5°	2100	1809	1296	948	840	229
15°	4068	2829	1144	523	415	1174
25°	5517	3333	1013	596	609	2541
35°	5640	2945	735	424	395	3495
45°	4344	1986	365	222	206	3296
55°	1724	814	155	84	63	1616
65°	321	178	40	13	8	362
75°	38	19	8	6	5	51
85°	4	3	5	4	3	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192423

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1
2.5°	1671.6	1633.0	1641.5	1648.0	1619.0	1637.3	1606.2	1595.5	1569.6	1576.0	1556.7
5°	2100.3	2046.6	2030.5	2030.5	1982.1	1998.3	1970.3	1920.9	1870.4	1855.3	1809.2
7.5°	2561.2	2502.1	2476.2	2465.5	2394.6	2384.9	2361.4	2285.1	2202.3	2158.3	2076.6
10°	3033.9	2980.1	2943.6	2918.9	2821.1	2803.9	2762.0	2654.6	2550.5	2455.9	2321.6
12.5°	3554.9	3483.0	3434.6	3393.7	3268.1	3241.3	3178.9	3034.9	2870.5	2756.6	2579.4
15°	4068.4	3995.4	3932.0	3873.0	3720.4	3681.7	3597.9	3415.2	3223.0	3053.2	2828.7
17.5°	4557.3	4464.8	4387.4	4308.0	4128.6	4080.2	3970.7	3767.6	3499.1	3306.8	3036.1
20°	4951.5	4861.3	4772.0	4671.2	4466.0	4407.9	4274.6	4034.1	3728.9	3497.9	3182.2
22.5°	5273.7	5171.7	5083.6	4951.5	4720.6	4652.9	4499.2	4226.4	3896.5	3626.9	3280.0
25°	5516.6	5408.0	5317.8	5169.6	4913.9	4835.5	4656.1	4360.6	4000.8	3704.3	3332.6
27.5°	5707.8	5583.2	5481.1	5316.7	5035.3	4947.3	4750.6	4431.5	4042.6	3719.2	3330.4
30°	5774.5	5653.0	5538.0	5360.8	5057.8	4960.1	4755.9	4410.0	4005.0	3657.0	3256.2
32.5°	5745.5	5619.7	5495.0	5307.1	4986.9	4881.7	4675.4	4305.9	3890.1	3523.7	3119.8
35°	5640.1	5512.3	5379.1	5184.7	4849.5	4735.5	4529.3	4146.9	3715.0	3348.7	2944.8
37.5°	5449.0	5321.1	5195.4	4986.0	4643.2	4525.0	4322.0	3925.6	3504.4	3134.8	2741.6
40°	5162.0	5035.3	4919.3	4707.7	4362.8	4243.5	4051.3	3658.0	3252.0	2886.6	2508.5
42.5°	4792.4	4671.2	4566.8	4359.6	4022.2	3908.3	3727.9	3347.6	2968.3	2614.9	2259.3
45°	4343.5	4232.8	4137.2	3941.7	3630.1	3520.5	3360.4	3000.5	2647.1	2316.2	1986.4
47.5°	3825.5	3724.7	3640.9	3460.4	3171.4	3071.4	2934.0	2599.8	2283.9	1982.1	1688.8
50°	3173.5	3085.5	3027.3	2871.6	2613.8	2529.9	2423.6	2142.2	1883.2	1623.2	1380.5
52.5°	2421.5	2352.7	2325.9	2208.8	2009.0	1951.0	1882.2	1666.2	1477.1	1271.9	1082.8
55°	1724.3	1679.2	1661.9	1585.7	1454.6	1417.1	1357.8	1224.7	1099.0	954.0	814.3
57.5°	1174.3	1150.6	1137.7	1090.4	1009.8	984.2	950.8	864.9	784.3	689.7	589.8
60°	780.0	770.2	759.5	730.6	683.2	663.9	647.8	590.9	541.5	482.5	412.6
62.5°	506.0	501.7	494.1	475.9	457.6	444.8	427.6	390.0	361.0	330.9	278.2
65°	321.3	316.9	313.7	301.9	290.1	277.3	270.7	249.3	231.0	211.6	178.4
67.5°	198.7	195.5	194.5	186.9	178.4	170.8	166.5	152.6	141.9	130.0	108.5
70°	119.3	118.1	116.1	111.7	106.3	101.0	98.9	89.1	82.8	75.2	61.3
72.5°	68.7	67.6	66.7	63.3	60.2	58.0	56.0	52.6	45.1	40.8	34.4
75°	37.6	37.6	36.5	34.4	33.3	31.1	30.1	28.0	24.6	22.6	19.2
77.5°	21.5	20.4	20.4	19.2	18.3	18.3	17.2	16.1	13.9	13.9	11.9
80°	12.9	12.9	12.9	11.9	11.9	11.9	10.7	10.7	9.7	8.5	8.5
82.5°	8.5	7.6	7.6	7.6	7.6	7.6	6.4	6.4	6.4	6.4	5.4
85°	4.3	4.3	4.3	4.3	3.2	4.3	3.2	3.2	3.2	3.2	3.2
87.5°	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.2	2.2	2.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192423

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1
2.5°	1506.2	1495.4	1474.0	1443.9	1433.2	1426.7	1391.2	1359.0	1336.4	1307.5	1279.5
5°	1725.3	1685.6	1633.9	1571.8	1547.0	1525.5	1460.1	1399.8	1350.4	1295.6	1244.2
7.5°	1952.0	1877.8	1790.9	1692.1	1651.2	1613.6	1514.8	1425.6	1349.3	1271.0	1196.7
10°	2164.8	2051.9	1926.2	1794.1	1732.8	1678.0	1547.0	1432.1	1331.0	1230.1	1138.8
12.5°	2373.1	2219.6	2053.1	1883.2	1803.8	1732.8	1570.6	1429.9	1305.3	1187.1	1081.9
15°	2574.0	2375.3	2170.1	1961.8	1866.1	1779.0	1586.7	1422.4	1278.4	1144.1	1027.1
17.5°	2736.2	2502.1	2254.0	2009.0	1901.5	1800.7	1584.6	1401.0	1241.9	1095.7	971.2
20°	2850.1	2580.4	2304.3	2030.5	1913.4	1801.6	1568.4	1371.9	1204.3	1053.9	928.2
22.5°	2914.6	2617.0	2321.6	2030.5	1904.8	1787.7	1546.0	1345.0	1176.3	1029.2	909.0
25°	2941.4	2623.5	2314.0	2013.2	1883.2	1762.9	1520.1	1319.3	1153.8	1013.1	901.4
27.5°	2920.0	2585.9	2272.2	1966.0	1832.8	1712.5	1470.8	1274.1	1114.2	979.8	873.4
30°	2834.0	2491.4	2178.7	1874.7	1740.4	1623.2	1389.1	1198.9	1045.3	916.3	815.4
32.5°	2694.3	2353.8	2046.6	1750.1	1616.9	1503.9	1280.6	1100.1	953.0	830.4	737.0
35°	2524.6	2190.4	1893.9	1605.0	1477.1	1369.7	1159.2	983.0	847.6	734.9	648.9
37.5°	2333.4	2010.1	1716.7	1451.4	1328.9	1226.9	1030.2	864.9	740.2	636.0	559.7
40°	2118.6	1813.4	1537.3	1286.0	1169.9	1075.4	889.5	743.4	629.5	536.1	471.6
42.5°	1891.9	1607.1	1350.4	1115.1	1005.6	919.7	751.0	621.0	520.9	444.8	393.2
45°	1649.1	1385.8	1150.6	940.1	848.7	762.8	619.8	501.7	423.3	365.2	326.7
47.5°	1390.2	1157.1	949.7	766.0	686.5	611.3	491.0	400.7	343.7	299.6	270.7
50°	1130.2	933.6	757.4	600.6	532.8	472.7	380.3	319.1	277.3	245.0	221.3
52.5°	883.1	724.2	580.2	452.3	401.9	358.9	295.4	252.4	221.3	196.7	179.4
55°	662.8	537.3	424.3	328.7	298.7	271.9	229.8	195.5	174.1	154.6	141.9
57.5°	480.2	383.6	301.9	241.7	222.5	204.0	174.1	150.4	134.3	119.3	109.6
60°	337.4	266.4	213.7	177.2	162.2	151.5	127.8	112.8	99.8	89.1	79.5
62.5°	226.7	180.5	149.2	125.7	116.1	108.5	93.5	80.6	70.9	62.3	53.7
65°	145.0	121.5	101.0	84.9	78.4	73.0	63.3	52.6	46.2	39.8	33.3
67.5°	89.1	76.3	63.3	52.6	48.4	45.1	38.7	32.2	28.0	23.7	20.4
70°	51.5	44.1	36.5	31.1	29.0	26.8	22.6	19.2	17.2	13.9	11.9
72.5°	29.0	25.8	21.5	18.3	17.2	16.1	13.9	11.9	10.7	9.7	8.5
75°	17.2	15.0	12.9	11.9	10.7	10.7	9.7	8.5	7.6	7.6	6.4
77.5°	10.7	9.7	8.5	8.5	7.6	7.6	7.6	6.4	6.4	6.4	6.4
80°	7.6	7.6	6.4	6.4	6.4	6.4	5.4	5.4	5.4	5.4	5.4
82.5°	5.4	5.4	5.4	4.3	4.3	4.3	4.3	4.3	5.4	5.4	5.4
85°	3.2	3.2	4.3	4.3	4.3	4.3	4.3	4.3	5.4	5.4	5.4
87.5°	3.2	3.2	3.2	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192423

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1
2.5°	1249.5	1236.6	1212.8	1191.3	1188.2	1158.1	1126.9	1120.5	1109.7	1092.6	1072.1
5°	1192.5	1158.1	1117.3	1087.2	1074.3	1031.4	988.4	969.1	947.6	914.3	894.9
7.5°	1125.8	1075.4	1018.4	984.2	965.7	912.1	862.7	834.7	805.8	770.2	746.7
10°	1052.8	989.5	922.8	884.1	862.7	804.6	752.0	719.8	688.6	653.2	628.5
12.5°	984.2	912.1	839.1	798.2	774.6	714.5	660.7	626.3	595.2	566.2	537.3
15°	922.8	842.3	766.0	725.2	700.4	639.3	587.6	553.3	523.2	495.2	469.5
17.5°	863.7	780.0	704.7	665.0	640.2	583.3	533.9	502.8	473.7	448.0	425.4
20°	823.0	743.4	672.5	634.9	613.4	563.0	520.9	496.3	475.9	453.3	434.1
22.5°	812.2	741.3	680.1	648.9	632.8	593.0	563.0	548.0	541.5	527.5	516.7
25°	812.2	749.8	698.4	672.5	659.7	629.5	605.9	600.6	596.3	587.6	582.3
27.5°	791.8	733.7	687.6	665.0	654.3	627.4	607.0	600.6	595.2	588.7	582.3
30°	738.0	684.3	641.4	621.0	610.2	584.5	563.0	555.4	550.1	540.4	535.0
32.5°	666.1	614.5	579.1	555.4	545.8	520.9	500.6	492.0	487.8	479.1	469.5
35°	585.5	540.4	506.0	486.7	477.0	455.5	437.2	428.7	424.3	414.6	402.8
37.5°	503.9	463.0	435.0	416.8	409.2	392.1	376.0	369.6	365.2	357.8	348.1
40°	423.3	394.3	369.6	355.6	349.1	335.2	321.3	314.8	311.5	305.0	297.6
42.5°	356.7	333.0	313.7	301.9	296.5	285.8	273.9	267.5	264.3	257.8	252.4
45°	298.7	280.4	265.4	254.6	250.3	240.6	231.0	225.6	222.5	217.0	211.6
47.5°	250.3	234.2	221.3	213.7	209.5	202.1	193.3	188.0	186.0	181.5	176.2
50°	205.2	193.3	182.6	176.2	173.0	165.4	158.0	153.7	151.5	147.3	141.9
52.5°	165.4	156.8	147.3	140.7	137.6	132.2	124.6	120.3	117.1	112.8	106.3
55°	130.0	122.4	115.0	108.5	106.3	99.8	93.5	87.0	83.7	79.5	74.0
57.5°	101.0	92.5	84.9	79.5	77.4	70.9	64.5	58.0	54.8	49.4	46.2
60°	72.0	64.5	56.9	53.7	51.5	45.1	39.8	34.4	32.2	29.0	26.8
62.5°	47.2	41.9	35.4	32.2	31.1	26.8	22.6	21.5	19.2	18.3	17.2
65°	29.0	25.8	21.5	19.2	18.3	17.2	15.0	13.9	12.9	11.9	11.9
67.5°	17.2	16.1	13.9	12.9	11.9	10.7	10.7	9.7	9.7	8.5	8.5
70°	11.9	10.7	9.7	8.5	8.5	8.5	8.5	8.5	8.5	7.6	7.6
72.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
75°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
77.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	5.4	5.4
80°	5.4	6.4	6.4	6.4	6.4	5.4	5.4	5.4	5.4	5.4	5.4
82.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
85°	5.4	5.4	5.4	5.4	5.4	4.3	4.3	4.3	4.3	4.3	3.2
87.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2	3.2	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192423

CATALOG NUMBER: LDA6A50950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1	1317.1
2.5°	1070.1	1060.4	1050.6	1065.8	1064.6	1049.7	1060.4	1043.2
5°	884.1	870.2	859.5	869.1	863.7	848.7	855.2	840.1
7.5°	732.7	716.6	703.7	711.2	702.6	688.6	686.5	680.1
10°	612.5	595.2	583.3	588.7	580.2	567.2	564.1	559.7
12.5°	520.9	504.9	494.1	498.5	489.8	478.0	475.9	479.1
15°	450.2	438.4	429.6	433.0	421.1	414.6	412.6	414.6
17.5°	409.2	396.4	390.0	393.2	384.6	378.1	377.1	376.0
20°	426.5	416.8	414.6	420.1	413.6	408.2	411.5	407.3
22.5°	520.0	518.9	520.0	532.8	529.7	527.5	529.7	529.7
25°	585.5	589.8	590.9	604.9	605.9	603.7	609.1	609.1
27.5°	583.3	584.5	583.3	597.3	599.5	595.2	600.6	601.6
30°	531.9	531.9	528.5	540.4	540.4	538.2	540.4	541.5
32.5°	464.0	463.0	461.9	467.3	467.3	464.0	466.3	466.3
35°	400.7	396.4	396.4	399.7	398.5	395.4	396.4	395.4
37.5°	345.9	340.6	340.6	342.8	339.5	336.3	337.4	337.4
40°	295.4	291.1	291.1	294.3	292.2	288.9	291.1	291.1
42.5°	248.1	247.1	247.1	249.3	249.3	247.1	250.3	251.4
45°	209.5	206.3	206.3	208.4	208.4	206.3	207.4	206.3
47.5°	174.1	170.8	170.8	170.8	168.7	165.4	165.4	164.4
50°	138.5	133.2	132.2	132.2	130.0	126.8	126.8	125.7
52.5°	103.2	97.8	97.8	96.7	94.4	93.5	92.5	92.5
55°	70.9	66.7	67.6	65.5	65.5	63.3	64.5	63.3
57.5°	44.1	41.9	41.9	40.8	38.7	37.6	37.6	36.5
60°	25.8	23.7	23.7	23.7	22.6	21.5	21.5	21.5
62.5°	17.2	16.1	16.1	16.1	13.9	13.9	12.9	12.9
65°	10.7	9.7	9.7	9.7	8.5	8.5	8.5	8.5
67.5°	8.5	8.5	7.6	7.6	7.6	7.6	7.6	7.6
70°	7.6	7.6	7.6	7.6	7.6	6.4	6.4	6.4
72.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
75°	6.4	6.4	5.4	6.4	5.4	5.4	5.4	5.4
77.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
80°	5.4	5.4	5.4	5.4	5.4	4.3	4.3	4.3
82.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
85°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	3.2	2.2	2.2	2.2	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)